

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

74099-0011

Status:


Active

Overview:

SL™ Modular Connectors

Description:

SL™ Wire-to-Board Header, Surface Mount, Single Row, Vertical, 3.05mm Pocket, Shrouded, 11 Circuits, Tin (Sn) Plating



Documents:

3D Model

Drawing (PDF)

Product Specification PS-70400 (PDF)

Product Specification PS-70541 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification		
CSA	LR19980	
UL	E29179	
General		
Product Family	PCB Headers	
Series	74099	
Application	Signal, Wire-to-Board	
Overview	SL™ Modular Connectors	
Product Name	SL™	
UPC	756054640357	
Physical		
Breakaway	No	
Circuits (Loaded)	11	
Circuits (maximum)	11	
Color - Resin	Black	
Durability (mating cycles max)	25	
Flammability	94V-0	
Glow-Wire Compliant	No	
Material - Metal	Brass, Phosphor Bronze	
Material - Plating Mating	Tin	
Material - Plating Termination	Tin	
Material - Resin	High Temperature Thermoplastic	
Net Weight	2.153/g	
Number of Rows	1	
Orientation	Vertical	
PCB Thickness - Recommended	1.60mm	
Packaging Type	Tube	
Pitch - Mating Interface	2.54mm	
Plating min - Mating	3.810µm	
Plating min - Termination	3.810µm	
Polarized to Mating Part	Yes	
Shrouded	Fully	
Surface Mount Compatible (SMC)	Yes	
Temperature Range - Operating	-40°C to +105°C	
Termination Interface: Style	Surface Mount	
Electrical		
Current - Maximum per Contact	3A	
Voltage - Maximum	250V	

Solder Process Data

Duration at Max. Process Temperature (seconds)

40

Lead-free Process Capability

Reflow Capable (SMT only)

Max. Cycles at Max. Process Temperature

3

EU RoHS

ELV and RoHS Compliant

REACH SVHC

Contains SVHC: No

Low-Halogen Status

Not Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com

For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

74099Series

Mates With

SL™ Crimp Housing 70066 Option N, 70066 Option G, 70430 Option G, 70400 Option G

Process Temperature max. C245

Material Info

Reference - Drawing Numbers

Product SpecificationPS-70400, PS-70541

Sales DrawingSD-74099-001

This document was generated on 07/09/2014

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[74099-0011](#)