

Tweezers

Precision tweezers: Pointed tips straight

120 mm/4.724 Inch



Model	■	Description
00SASL	20 g	Same as 00SA, but economy model.
00CSA	18 g	Model same as 00SA, but with shorter tips.
00BSA	20 g	Model same as 00SA, but with serrated finger grips for secure handling.
00DSA	20 g	Model same as 00SA, but with serrated finger grips and inside-serrated tips for secure handling.
64SA	17 g	Precision tweezers with pointed tips and serrated finger grips for secure handling.
11N	17 g	Precision tweezers with medium-pointed tips for use on soft components. Nickel-silver , non-magnetic.
AAZ	16 g	Precision tweezers with medium-pointed tips, nickel-plated . Suitable for electronic assembly tasks.

125 mm/4.921 Inch



Model	■	Description
AAS	16 g	Precision tweezers with fine but robust tips.
AASA	16 g	Precision tweezers with fine but robust tips for standard applications.
AASASL	16 g	Same as AASA, but economy model.