


REV.	DATE	DESCRIPTION
NC	10/01/97	INITIAL RELEASE
NC	04/19/07	REVISE PLATING TO NEXCOTE / UPDATE DRAWING FORMAT



				UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY.	APPROVALS	DATE	Amphenol Connex							
8				UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 - 8mm ± 0.20mm 8 - 30mm ± 0.40mm 30 - 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 - .315 = ± 0.007" .315 - 1.180 = ± 0.015" 1.180 - 4.724 = ± 0.020"	DRAWN	G.R.S.	04/19/07	PART DESCRIPTION N PANEL RECEPTACLE JACK / EXTENDED BODY						
7			CHECKED											
6					ISSUED			PART NO. 172190						
5					SHEET	1 OF 1								
4					CAD FILE C:/172/172190.DWG			DWG. NO.	172190.DWG	REV.	A	SIZE	A	SCALE
3	CONTACT PIN	PHOS. BRONZE	GOLD	1	DO NOT SCALE DRAWING									
2	INSULATOR	TEFLON	NATURAL	1										
1	BODY	BRASS	NEXCOTE	1										
DESCRIPTION				MATERIAL	FINISH	QTY								

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[172190](#)