

HAHN - Elektrobau GmbH & Co. KG

Bellersheimerstraße 45
35410 Hungen
Germany

phone: +49 (0) 6402/808 -0
fax: +49 (0) 6402/808 -60
email: info@hahn-trafo.de

Data sheet: BV EI 303 2034

Size 3 a: height 24.0 mm	1,9 VA	ta 70/F	BV EI 303 ...
--------------------------	--------	---------	---------------

Several hundreds of typen provide high electrical safety and long service -life for printed circuit boards, household appliances, leisure electronics, heating and control technology as well as in assembly techniques. Transformers for special requirements with lower open circuit (no -load) loss capacity are also available in the range.

absolutely short -circuit-proof

minimal size

test certifications to ENEC 10 -, VDE, UL - and CSA-regulations

vaccum encapsulated, bobbin with dual chamber windings

temperature class ta 40°C/F and ta 70°C/F

hight electrical safety and long service -life properties




individually tested with certificate

excellent temperature fluctuation resistance properties

self-extinguishing cast housing and sealing material



Article no. BV	Output ta 40°C/F	prim.V	Connecting pins	Operating point sec. $\pm 5\%$	Connecting pins	No-load voltage V $\pm 5\%$
BV EI 303 2034	1,9	230	1-5	18 V 105 mA	7-9	25,8



Maße ohne Toleranzangabe $\pm 0,3$ mm
Ausführungsänderungen vorbehalten

Dimensions with no indication of tolerances $\pm 0,3$ mm.