



product details

HQL-E 400W/N/SI COATED E40 FLH1

Product description: HQL-E 400W/N/SI COATED E40 FLH1
EAN/ Product: 4050300427676
Quantity: Sleeves (FLH) contains 1 Piece (PCE)

You can find this product in the eCatalog:
http://catalog.myosram.com?~language=EN&~country=COM&it_p=4050300427676

Applications				
Burning position	any			
General Description				
ILCOS	ME-400/37/2B-H 133/-E40-117.5/292			
SEG no.	8333348			
Sstl-Number	4834715			
Base (standard designation)	E40			
Technical - Electrical Data				
PFC capacitor at 50 Hz	45 µF ¹⁾			
Construction wattage	400 W			
Nominal wattage (packaging)	400 W			
Technical - Geometries				
Length	297 mm			
Diameter	117 mm			
Technical - Life				
Lifespan	9000 h ²⁾			
Technical - Light Technical Data				
Colour temperature	3700 K			
Colour rendering group	2B			
Colour rendering index Ra	60 ... 69			
Luminous efficacy	78 lm/W			
Luminous flux	31000 lm			
Packaging units				
EAN	Packaging type and content	Dimensions in h x w x l	Gross weight	Volume
4050300427676	Sleeves contains 1 Piece	118,000 mm x 118,000 mm x 300,000 mm	289,000 g (0,000 g)	4,177 Cubic dec.
4050300427683	Shipping carton box contains 6 Piece	345,000 mm x 289,000 mm x 400,000 mm	2.269,000 g (0,000 g)	38,640 Cubic dec.

¹⁾ at rated voltage and $\cos \varphi \geq 0.9$

²⁾ Average lifespan