


Post Headers (Board Applied) (Continued)

Vertical Mount Type (2.5mm)




#2 hole is not punched

PC Board Layout

(Applicable board thickness: 1.6mm)

Horizontal Mount Type




#2 hole is not punched


PC Board Layout

(Applicable board thickness: 1.6mm)

3~11 Positions



3~9 Positions



Material: (Vertical and Horizontal Type)

Header— Recognized by UL flame retardant grade. UL 94V-0 rated, 6/6 nylon, natural color

Post— Brass, Tin over copper plated

No. of Pos.	Dimensions		Part No. of Polarized Post Header	
	A	B	Vertical Mount Type	Horizontal Mount Type
3	7.5	10.0	171886-4	171887-4
4	10.0	12.5	171886-5	171887-5
5	12.5	15.0	171886-6	171887-6
6	15.0	17.5	171886-7	171887-7
7	17.5	20.0	171886-8	171887-8
8	20.0	22.5	171886-9	171887-9
9	22.5	25.0	1-171886-0	1-171887-0
11	27.5	30.0	1-171886-2	—