

Search Results

- Evaluate
 - FAQ's
- How to Buy
 - Bill of Material
 - Favorite Products List
 - Locate Distributor

Home > Product On-Line Catalog > Search Results >

Current refinements (click  to remove) Search Tips 

Text Search: 'FXPE10J-NM9'

Your search criteria matched only one product, shown below

FXPE10J-NM9



- Patch cords are tested to support network transmission speeds up to 10 Gb/s for link lengths up to 300 meters with an 850nm source per IEEE 802.3ae 10 GbE standard
- Pass all TIA/EIA-568-B.3 performance requirements
- Insertion loss per connection: 0.10dB typical; 0.30dB maximum
- Include color-specific keys with positive and negative keying features to visually and mechanically distinguish connections to prevent unauthorized mating with unlike keyed or non-keyed adapters
- Part of a complete keyed LC system that includes Opti-Core® Patch Cords and Pigtails, OptiCam® Pre-Polished Cam Connectors, Opticom® Fiber Adapter Panels (FAPs), and Mini-Com® Adapter Modules
- Backward compatible for use with all 50/125µm system requirements
- Factory terminated and 100% tested for insertion loss
- Insertion loss data recorded for every multimode patch cord
- Lifetime traceability of test data to a Q.C. number on each patch cord
- Highest quality flame retardant fiber optic cable with tight-buffered coating on each optical fiber

Additional lengths and availability: Keyed LC patch cords and pigtails are available in 1m – 10m lengths in 1m increments, and 15m, 20m, and 30m lengths. For other lengths, contact Customer Service for actual lead times.

Additional keyed colors include the following: G – Violet, H – Aqua, J – Rose, K – Slate, L – Brown, P – White, Q – Charcoal, R – Lavender, S – Peach, T – Steel Blue, V – Maroon and W – Mint.

▪ Part Number	FXPE10J-NM9
▪ RoHS Compliancy Status	Compliant
▪ Note	Intended for use in fixed installations which are outside the scope of RoHS.
▪ Part Description	LC (keyed J – rose) to pigtail, multimode duplex patch cord (one duplex keyed LC connector on one end and pigtail on the other end) – 10Gig™ 50/125µm.
▪ Product Type	Keyed LC Patch Cords
▪ Length (m)	9
▪ Fiber Compatibility	10Gig 50/125µm
▪ Fiber Type	Jacketed
▪ Connector 1 Type	Keyed LC (J-Rose)
▪ Connector 2 Type	Pigtail
▪ Key Type and Color	Keyed J - Rose
▪ Pricing Description	Keyed LC (J-Rose) to Pigtail, 10Gig, OM3, Duplex, Plenum rated, 9m
▪ Min. Order UOM	PC
▪ Min. Order Qty.	1
▪ BOM Qty. (# of Pkgs.)	0
▪ Add to Favorite Product List	<input type="checkbox"/>

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.