


**Rewireable Connector for cable,
straight entry
Type 4795**

Pin temperature 70 °C
 Protection class I




Order no	Colour	Max. cable diameter	Max. wire size
4795.0000	black	10 mm	3 x 2 mm² / 14 AWG

Cord retaining clamp see page 169

**Rewireable Plug
for cable
straight entry
Type 4796**

Pin temperature 70 °C
 Protection class I



Order no	Colour	Max. cable diameter	Max. wire size
4796.0000	black	10 mm	3 x 2 mm² / 14 AWG

Cord retaining clamp see page 169

Details Types 4795, 4796

Technical data

- Rated current/voltage: 16 A/250 VAC
- Insulation resistance: > 10 MΩ (500 VDC, 1 Min.)
- Dielectric strength: 2 kV (50 Hz, 1 Min.), to accessible surfaces
- Materials:
 - Body and cable guard: Thermoplastic UL 94V-0

Standards

Type 4795: IEC/EN 60320-1/C19
 4796: IEC/EN 60320-2-2/I

Approvals

 VDE (16 A / 250 VAC)
 UL/CSA (21 A / 250 VAC)