

MSTBC-MT 1,5-2,5 BA

Order No.: 3190658

Supplied in tape form - please note the drawing.

<http://eshop.phoenixcontact.de/phoenix/treeViewClick.do?UID=3190658>

Module female contact, is inserted into the MSTBC connector shell after the conductor has been crimped, for conductors from 1.5 - 2.5 mm², ribbon contact

Commercial data

GTIN (EAN)	
sales group	E192
Pack	3500 pcs.
Customs tariff	85366990
Catalog page information	Page 497 (CC-2009)

Product notes

WEEE/RoHS-compliant since:
01/01/2003



<http://www.download.phoenixcontact.com>
Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation. The General Terms and Conditions of Use apply to Internet downloads.

Technical data

Technical data

Nominal current	12 A
Conductor cross section stranded min.	1.5 mm ²
Max. conductor cross section, stranded	2.5 mm ²

Connection data


Core diameter including insulation	2.11 mm ... 3.1 mm
Stripping length of individual wires	4 mm

Material data

Contact material	CuFe
Contact surface material	Tin-plated

Diagrams/Drawings

Dimensioned drawing



Address

PHOENIX CONTACT Deutschland GmbH
Flachsmarktstr. 8
32825 Blomberg, Germany
Phone +49 5235 3 12000
Fax +49 5235 3 41200
<http://www.phoenixcontact.de>



© 2010 Phoenix Contact
Technical modifications reserved;