

Office

CHERRY MX-Board 3.0



Models may vary from the image shown

Extremely Robust Professional Keyboard for Fast and Precise Input.

The CHERRY MX-Board 3.0 captivates with its world-exclusive use of Gold Crosspoint contacts in the MX modules, ensuring perfect and extremely fast keystrokes. This professional, maximum-precision keyboard is even sturdier and more robust than its predecessor, making it the perfect partner for every type of exacting input imaginable.

Key benefits

- Original CHERRY MX module: Quality "Made in Germany" proven effective billions of times
- MX module with Gold Crosspoint contacts for reliable contact capability and exemplary responsiveness
- N-key rollover: Simultaneous operations of up to 14 keys without any key ghosting effects
- Available in four different key confirmation types
- Professional quality with a perfect key stroke: 50 million operations for each key
- The integrated metal plate and extensive anti-slip protection ensure it remains robust
- Detachable cable
- Win-Key lock: Windows buttons can be disabled to prevent inadvertent operation

Technical Data:

Housing Color: Black

Key color: Black

Weight (product):

Approx. 830 g / 1.83 Lbs.

Total Weight (with packaging):

1215g / 2.67 Lbs

Cable Length:

Approx. 1.80 m / Approx. 5.91 ft.

Current Consumption:

Max. 16mA

Operating Temperature:

0° C to 50° C / 32° F to 122° F

Storage Temperature:

-20°C to 60°C / -4° F to 140° F



Interface:

USB

Product Approvals:

cURus

C-Tick

VCCI

CE

FCC

BSMI

KC



System Requirements:

USB connection

Delivery Volume:

- CHERRY MX-Board 3.0
- Operating instructions in hard copy
- Detachable cable (USB A plug / USB mini B plug)
- 2 non-slip surfaces
- 2 rubber caps for adjustable feet

Dimensions (product):

Approx. . 446 x 158 x 28 mm

Approx. 17.56" x 6.22" x 1.10" inches

Reliability:

MTBF (90) > 80,000 hours

Keyboard:

- Key technology: MX
- Service Life, standard key: > 50 million key operations
- Operation characteristics: Product dependent, see table "Models"
- Inscription Technology: Laser
- Inscription layout: Standard
- Number of Keys: 104 Number

Packaging Unit:

Number of products in the master package: 8

Number of master packages per pallet: 20

Warranty:





2 years



Model:

Product Name	Order Number	EAN Code	Operation Characteristics
CHERRY MX-Board 3.0	G80-3850LYBEU-2	4025112080135	RED SWITCH Linear (45 cN)
CHERRY MX-Board 3.0	G80-3850LSBEU-2	4025112080494	BLUE SWITCH Click Pressure point
CHERRY MX-Board 3.0	G80-3850LUBEU-2	4025112080487	BLACK SWITCH Linear (60 cN)
CHERRY MX-Board 3.0	G80-3850LXBEU-2	4025112080500	BROWN SWITCH Pressure point

(Possible country/layout versions, others available on request)



ZF Electronic Systems Pleasant Prairie, LLC
11200 88th Avenue
Pleasant Prairie, WI 53158
USA
Phone: 262.942.6500
Internet: www.cherrycorp.com

E-Mail: cep_sales@zf.com
Fax: 262.942.6566

The manufacturer accepts no liability for errors or non-availability, and reserves the right to change specifications without prior notice. Technical data relates to product specifications only. Features may differ from those described. Only drawings combined with product specifications shall be deemed binding.

© 2008 ZF Electronics Corporation, Last update: November 18, 2013_V01