




MARKETING SALES DRAWING

DIMENSIONS IN INCHES - DO NOT SCALE THIS DRAWING
DIMENSIONS IN METRIC - []

Electrical Testing
per Tusonix standard
test plans and Mil-Std-202
Test Methods.



NOTES:

- SUPPLIED WITH SILVER PLATED HEX NUT AND LOCKWASHER.
- 4202-501 SUPPLIED WITH TURRET HEAD OPTION, 4202-503 SUPPLIED WITHOUT TURRET HEAD.

MIN. CAP. (pF)	WORKING VOLTAGE (VVdc)		CURRENT (Idc)	DWV (VDC)	I.R. MIN. @ 100 VDC	MINIMUM NO LOAD INSERTION LOSS (dB) AT 25°C PER MIL-STD -220			
	85°C	125 °C				10 MHz	100 MHz	1 GHz	10 GHz
1500		200/140 AC	10 AC	500	10 G Ω	-----	45	70	70

X-2015 Rev-0	REVISION RECORD	Original Release C.O. 20020607-1-01	0		--TOLERANCES-- Unless Otherwise Specified		Title MIL-15733/61-0002 BUSHING STYLE EMI FILTER		
					DECIMAL ±		Drawn L.E. 06-07-02		Scale 3 X
					ANGLES ±		Approved T.C. 06-07-02		
					TUSONIX TUCSON, ARIZONA		A	4202-501	