



Professionally approved products.

Product Datasheet


Double Universal Joint with Needle Roller Bearing

EN



UJDN Properties

Maximum working angle	90 degrees
Maximum speed	4000 rpm
Maximum power	40 kW
Maximum torque	200 Nm



Dimensions in mm

RS Stock No	Mfr part No.	Bore d	Dia	Overall length	Pivot to face centre	Pivot to pivot centre	Hub Length	Weight
		H7	D	L3	L1	L4	C	KG
7906807	UJDN22X10	10	22	74	24	26	12	0.15
7906801	UJDN25X12	12	25	86	28	30	13	0.25
7906810	UJDN28X14	14	28	96	30	36	14	0.40
7906813	UJDN32X16	16	32	104	34	36	16	0.45
7906817	UJDN36X18	18	36	114	37	40	17	0.70
7906826	UJDN42X20	20	42	128	41	46	18	1.00
7906829	UJDN45X22	22	45	145	47.5	50	22	1.55
7906823	UJDN50X25	25	50	163	54	55	26	2.00

NB: Protective gaiters are unnecessary for most applications.