

3M™ Tin-Plated Copper Foil with Conductive Adhesive Tape 1183

Data Sheet

January 2014

Description

3M™ Tin-Plated Copper Foil Tape 1183 consists of a 1-ounce dead soft tin-plated copper foil backing and an electrically conductive, pressure-sensitive acrylic adhesive. This tape is supplied on a removable liner for easy handling and die-cutting. It has excellent solderability.

Agency Approvals & Self Certifications

Meets flame retardant requirements of UL510, Product Category OANZ2, and 3M File No. 17385

RoHS
2011/65/EC

"RoHS 2011/65/EU" means that the product or part does not contain any of the substances in excess of the maximum concentration values ("MCVs") in EU RoHS Directive 2011/65/EU. The MCVs are by weight in homogeneous materials. This information represents 3M's knowledge and belief, which may be based in whole or in part on information provided by third party suppliers to 3M.

Applications

Tin-Plated Copper Foil Tape 1183 is typically used for applications requiring excellent electrical conductivity from the application substrate through the adhesive to the foil backing. Common uses include grounding and EMI shielding in equipment, components, shielded rooms, etc. The tin plating facilitates soldering to the backing and resists oxidation and corrosion.

Shielding Effectiveness

Many factors determine the true shielding effectiveness of a shielding tape, including type and thickness of foil, adhesive type, intimacy of contact, smoothness of application surface, strength and frequency of the EMI signal, etc. However, using standard tests and fixtures, it is possible to determine a value for the attenuation. For 3M 1183 tape, typical shielding effectiveness (far field) is in the range of 70dB to 85dB (30 MHz to 1 GHz).

Specifications

Tin-Plated Copper Foil Tape 1183 is a tin-plated copper foil tape with acrylic conductive pressure-sensitive adhesive.

The tape shall be coated on one side with pressure-sensitive adhesive, which shall not require heat, moisture or other preparation prior to or subsequent to application. The adhesive coating shall be smooth and uniform and be free of lumps and bare spots. There shall be no separator between adjacent layers of the roll. The tape shall perform at a temperature of -40F° (-40°C) to 266°F (130°C) without substantial loss of tensile or electrical properties.

3M™ Tin-Plated Copper Foil with Conductive Adhesive Tape 1183

Typical Properties

Not for specifications. Values are typical, not to be considered minimum or maximum. Properties measured at room temperature 73°F (~23°C) unless otherwise stated.

Property (Test Method)	Typical Value US units (metric)
Color	Tin (foil may have a slight color variation)
Adhesive	Acrylic Conductive
Type of Backing	Tin-Plated Copper
Backing Thickness	1.4 mil (0.04mm)
Total Thickness (ASTM D1000)	2.6 mils (0.066mm)
Electrical Resistance ¹	0.005 Ω
Flame Retardancy ²	Pass
Breaking Strength (ASTM D3759)	25 lbs/in (44N/10mm)
Adhesion Strength (ASTM D3330)	35 oz/in (3.8N/10mm)
Temperature Range	-40°C to +130°C
Shielding Effectiveness (ASTM 4935)	70dB to 85 dB, 30 MHz to 1 GHz

1. Mil-STD-202 Method 303 maintained at 5 psi (3.4N/cm²) measured over 1 in² surface area. Conductive particles in the adhesive provide the electrical path between the application substrate and the foil backing.
2. UL Recognized for flame retardancy per UL 510, Product Category OANZ2, File E17385

Shelf Life & Storage

This product has a 5-year shelf life from date of manufacture when stored in a humidity controlled storage (10°C/50°F to 27°C/80°F and <75% relative humidity).

Availability

This 1183 Tape is available in 1/4" to 23" widths, standard length is 18 yards, longer lengths are available. Check with Customer Service

Please contact your local distributor; available from 3M.com/electrical [Where to Buy] or call 1-866-357-2737 or call 1-800-245-3573.

Important Notice

All statements, technical information, and recommendations related to 3M's products are based on information believed to be reliable, but the accuracy or completeness is not guaranteed. Before using this product, you must evaluate it and determine if it is suitable for your intended application. You assume all risks and liability associated with such use. Any statements related to the product, which are not contained in 3M's current publications, or any contrary statements contained on your purchase order, shall have no force or effect unless expressly agreed upon, in writing, by an authorized officer of 3M.

Warranty; Limited Remedy; Limited Liability

This product will be free from defects in material and manufacture at the time of purchase. **3M MAKES NO OTHER WARRANTIES INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE.** If this product is defective within the warranty period stated above, your exclusive remedy shall be, at 3M's option, to replace or repair the 3M product or refund the purchase price of the 3M product. **Except where prohibited by law, 3M will not be liable for any indirect, special, incidental or consequential loss or damage arising from this 3M product, regardless of the legal theory asserted.**

3M is a trademark of 3M Company.



Electrical Markets Division

6801 River Place Blvd.
Austin, TX 78726-9000
800 676 8381
FAX: 800 828 9329
www.3M.com/oem

Please recycle
© 3M 2014 All rights reserved
78-8124-4704-9 Rev C