

SAC-4P-100,0-PVC/0,34

Order No.: 1501838

<http://eshop.phoenixcontact.de/phoenix/treeViewClick.do?UID=1501838>

Cable ring, PVC, black, 4-pos., conductor colors: Brown / white / blue / black, cable length: 100 m

Commercial data

GTIN (EAN)	4017918813963
Note	Made-to-order
sales group	D111
Pack	1 pcs.
Customs tariff	85444995
Weight/Piece	3.8239 KG
Catalog page information	Page 134 (PC-2009)

Product notes

WEEE/RoHS-compliant since:
01/01/2003



<http://www.download.phoenixcontact.com>
Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation. The General Terms and Conditions of Use apply to Internet downloads.

Technical data**General data**

Number of positions	4
Length of cable	100 m
Ambient temperature (operation)	-25 °C ... 80 °C (cable, fixed installation)

Conductor data

Cable type	PVC black
Cable abbreviation	LiYY
Conductor cross section	0.34 mm ²
AWG signal line	22
Conductor structure signal line	42x 0.10 mm
Core diameter including insulation	1.52 mm ±0.02 mm
Thickness, insulation	≥ 0.23 mm (Core insulation)
	≥ 0.76 mm (Outer cable sheath)
External cable diameter	5.20 mm
Wire colors	Brown, white, blue, black
External sheath, color	Black RAL 9005
Insulation resistance	≥ 100 MΩ*km
Conductor resistance	max. 57.3 Ω/km
Nominal voltage, conductor	300 V
Test voltage, conductor	2500 V
Overall twist	4 wires, twisted
Outer sheath, material	PVC
Material conductor insulation	PVC
Conductor material	Bare Cu litz wires
Cable weight	43 kg/km
Ambient temperature (operation)	-5 °C ... 80 °C (cable, flexible installation)

Address

PHOENIX CONTACT Inc., USA
586 Fulling Mill Road
Middletown, PA 17057, USA
Phone (800) 888-7388
Fax (717) 944-1625
<http://www.phoenixcon.com>



© 2010 Phoenix Contact
Technical modifications reserved;