


3M™ Dissipative Vinyl Three-Layer Mats and Rolls 8200 Series

Premium Performance

3M™ Dissipative Vinyl Three-Layer Mats and Rolls 8200 Series are soft table and floor mats with a three-layer construction. The top layer is durable static dissipative vinyl, which has sufficiently low resistance to discharge static-laden conductors, yet will help prevent the shorting of pins on the backs of printed circuit boards laid on the mat. The middle layer is a highly-conductive scrim that provides the main discharge path to ground, and the bottom layer is static-dissipative foam, providing a durable nonskid cushion. Non-standard sizes are available on a custom order basis. Compatible with 3M constant monitors.



Product Bulletin

Properties	Typical Value
Material	Top layer - Static Dissipative Vinyl Middle layer - Highly-conductive Scrim Bottom layer - Static Dissipative Foam
Thickness	0.140 in (3.5 mm)
Hardness (top)	75 Shore A
*Resistance	
Surface to Ground (RTG)	2×10^9 ohms
Surface to Surface	3×10^9 ohms
Tolerances	Width +/- .250" Length +/- .250"

*Tested per ESD Association Standard S4.1 at 72°F, 50% RH using 3M Test Kit 701 for Static Control Surfaces (Megohmmeter).

*Color and appearance of mats may vary by lot.

Product Kits

Product No.	Description	Size, ft.	(m)
Includes one 15 ft. (4.6 m) 3M™ Ground Cord 3040 and two 3M™ Snap Fasteners 3050, installed			
8201	Floor Mat, Brown	4 x 6	(1.2 x 1.8)
8203	Floor Mat, Gray	4 x 6	(1.2 x 1.8)
8204	Floor Mat, Blue	4 x 6	(1.2 x 1.8)
Includes two 15 ft. (4.6 m) 3M Ground Cords 3040 and two 3M Snap Fasteners 3050, not installed			
8251	Floor Roll, Brown	4 x 24	(1.2 x 7.3)
8253	Floor Roll, Gray	4 x 24	(1.2 x 7.3)
8254	Floor Roll, Blue	4 x 24	(1.2 x 7.3)



3M™ Dissipative Vinyl Three-Layer Mats and Rolls 8200 Series

Product Kits (continued)

Product No.	Description	Size, ft.	(m)
Includes one 3M™ Wrist Strap Grounding System 3048 and two 3M Snap Fasteners 3050, installed			
8211	Table Mat, Brown	2 x 4	(0.6 x 1.2)
8213	Table Mat, Gray	2 x 4	(0.6 x 1.2)
8214	Table Mat, Blue	2 x 4	(0.6 x 1.2)
8221	Table Mat, Brown	2 x 3	(0.6 x 0.9)
8223	Table Mat, Gray	2 x 3	(0.6 x 0.9)
8224	Table Mat, Blue	2 x 3	(0.6 x 0.9)
Includes two 15 ft. (4.6 m) 3M Ground Cords 3040 and two 3M Snap Fasteners 3050, not installed			
8261	Table Roll, Brown	2 x 24	(0.6 x 7.3)
8263	Table Roll, Gray	2 x 24	(0.6 x 7.3)
8264	Table Roll, Blue	2 x 24	(0.6 x 7.3)
These mats do not come with additional hardware			
8231	Table Roll, Brown	2 x 50	(0.6 x 15.2)
8233	Table Roll, Gray	2 x 50	(0.6 x 15.2)
8234	Table Roll, Blue	2 x 50	(0.6 x 15.2)
8241	Table Roll, Brown	2.5 x 50	(0.8 x 15.2)
8243	Table Roll, Gray	2.5 x 50	(0.8 x 15.2)
8244	Table Roll, Blue	2.5 x 50	(0.8 x 15.2)
8271	Table Roll, Brown	3 x 50	(0.9 x 15.2)
8273	Table Roll, Gray	3 x 50	(0.9 x 15.2)
8274	Table Roll, Blue	3 x 50	(0.9 x 15.2)
82A1	Floor Roll, Brown	4 x 50	(1.2 x 15.2)
82A3	Floor Roll, Gray	4 x 50	(1.2 x 15.2)
82A4	Floor Roll, Blue	4 x 50	(1.2 x 15.2)
8281	Table Roll, Brown	2 x 40	(0.6 x 12.2)
8283	Table Roll, Gray	2 x 40	(0.6 x 12.2)
8284	Table Roll, Blue	2 x 40	(0.6 x 12.2)
8291	Floor Roll, Brown	4 x 40	(1.2 x 12.2)
8293	Floor Roll, Gray	4 x 40	(1.2 x 12.2)
8294	Floor Roll, Blue	4 x 40	(1.2 x 12.2)

****Material Might have slight color and texture variance between lots**

*****Mat Rolls rolls need to be unrolled before being cut. When rolled some shrinkage may occur. Please allow time for mat to relax at room temperature 24-48 hours prior to cutting.**

Roll Width Tolerance: +/- .25 inches

Cut Mats Have a Tolerance of +/- .25 inches on width and length.

3M is a trademark of 3M Company.

Important Notice

All statements, technical information, and recommendations related to 3M's products are based on information believed to be reliable, but the accuracy or completeness is not guaranteed. Before using this product, you must evaluate it and determine if it is suitable for your intended application. You assume all risks and liability associated with such use. Any statements related to the product which are not contained in 3M's current publications, or any contrary statements contained on your purchase order shall have no force or effect unless expressly agreed upon, in writing, by an authorized officer of 3M.

Warranty; Limited Remedy; Limited Liability.

This product will be free from defects in material and manufacture for a period of one year from the time of purchase. **3M MAKES NO OTHER WARRANTIES INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE.** If this product is defective within the warranty period stated above, your exclusive remedy shall be, at 3M's option, to replace or repair the 3M product or refund the purchase price of the 3M product. **Except where prohibited by law, 3M will not be liable for any indirect, special, incidental or consequential loss or damage arising from this 3M product, regardless of the legal theory asserted.**



Electronic Solutions Division Static Control Products

926 JR Industrial Drive
Sanford, NC 27332-9733
Toll-Free: 866-722-3736
International: 919-718-0000
Email: 3mstaticinfo@mmm.com
www.3Mstatic.com

Please recycle. Printed in U.S.A.
© 3M 2012. All rights reserved.
98-0799-1079-4