





RECOMMENDED PCB LAYOUT

NOTE:
MATERIAL:
HOUSING:PBT+30%G.F UL 94V-0
CONTACT:BRASS
SHELL:SPCC
PLATING:
CONTACT: GOLD AND TIN OVER NICKEL PLATING
SHELL: NICKEL OVER ALL PLATING
SPECIFICATION:
CURRENT-MAX[AMPS]1.5A
VOLTAGE-MAX[VOLTS]:30V
WITHSTANDING VOLTAGE:500V AC
CONTACT RESISTANCE[OHMS]:30MΩ MIN
INSULATION RESISTANCE[OHMS]:1000MΩ MIN
ENVIRONMENTAL:
TEMPERATURE RANGE:-40°C TO+105°C
PART NO.:

08/09/26	SYSTEM		變更尺寸		△1	A1
08/05/27	SYSTEM		NEW DWG			A0
DATE	DR.BY	ECN.NO.	DESCRIPTION		MARK	VER.
-TOLERANCES- UNLESS OTHERWISE SPECIFIED 公差參考表			CnC Tech,LLC			
X.X	±0.30	X.X°	±3.00°	APPD:	TITLE: USB 4P A/M SMT H=6.00mm 成品針長2.25mm	
X.XX	±0.15	X.XX°	±1.00°	CHECK:	DATE	SCALE
X.XXX	±0.100	X.XXX°	±0.500°	DRAW:	UNIT	TYPE
				2008.09.26	1:1	mm
				CD	1 / 1	