

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [111025-1207](#)
Status: **Active**
Overview: [CXP Interconnect System](#)
Description: iPass+™ High-Speed Channel (HSC) CXP Cable Assembly, 12X Quad Data Rate (QDR), 84 Circuits, 7.00m Length

Documents:
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification
UL E72548


General
Product Family Cable Assemblies
Series [111025](#)
Assembly Configuration Dual Ended Connectors
Comments Hot Pluggable, Pull to Release Style Latch
Connector to Connector InfiniBand* 12x Both Ends, iPass-to-iPass
Overview [CXP Interconnect System](#)
Product Name InfiniBand*, iPass+™
UPC 883906021450

Physical
Cable Length 7.0m
Circuits (Loaded) 84
Gender Male
Lock to Mating Part Yes
Material - Metal Zinc Alloy
Material - Plating Mating Gold
Packaging Type Bag
Single Ended No
Wire/Cable Type Twin-ax

Electrical
Current - Maximum per Contact 0.5A
Impedance 100#
Voltage - Maximum 30V AC

Material Info

Reference - Drawing Numbers
Sales Drawing SD-111025-120



EU RoHS
ELV and RoHS
Compliant
REACH SVHC
Not Reviewed
Low-Halogen Status
Not Reviewed



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
[111025Series](#)

Mates With
[76105-0584](#) iPass™+ 84 Circuit Connector

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION