

Olympic Wire and Cable

7 Madison Road • Fairfield, NJ 07004

973.227.7996 800.526.2269 • Fax: 973.227.1606

email: sales@olympicwire.com

Olympic P/N 355, UL1007, UL1569 Wire



UL1007, UL1569 Wire

STYLE 1007/STYLE 1569, 105°C, 300 Volts, VW-1, AWM, 80°C
CSA STYLE TR-64& MIL-W-76B, 1000 Volts

Stranded Tinned Copper, color coded, medium wall PVC insulation

Characteristics:

Temperature Rating — -40°C to +105°C Resistant to acids, alkalis, oil, flame, moisture and fungus

SPECIFICATIONS

Conductor Size	18 AWG
Stranding	16/30 Tinned Copper
Insulation	PVC
Nom. Wall Thickness	0.016 in
Nom. O.D.	0.080 in
UL Style	1007 1569
UL Rating	-20°C to 80°C / -20°C to 105°C, 300 V
UL Flame Test	VW-1
CSA Type	TR-64
CSA Flame Test	FT-1
Military Spec.	MIL-W-76B
Military Rating	1000 V, 80°C
RoHS Compliant	 RoHS Compliant

Color Code	Hook Up Wire Color Code Chart
------------	-------------------------------
