

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0679404410](#)
Status: **Obsolete**
Description: 1.27mm (.050") Pitch PLCC Socket, Surface Mount, 44 Circuits, Lead Free

Documents:
[Drawing \(PDF\)](#)

General

Product Family	Other Sockets
Series	67940
Component Type	Socket
Product Name	PLCC

Physical

Circuits (Loaded)	44
Durability (mating cycles max)	20
Entry Angle	Vertical (Top Entry)
Keying to Mating Part	Yes
PC Tail Length	1.40mm (.055")
PCB Locator	No
PCB Retention	Yes
Packaging Type	Tube
Pitch - Mating Interface	1.27mm (.050")
Temperature Range - Operating	-65°C to +125°C

Electrical

Current - Maximum per Contact	1A
Voltage - Maximum	500V

Solder Process Data

Lead-free Process Capability	Reflow Capable (SMT only)
Process Temperature max. C	230

Material Info

EU RoHS
ELV and RoHS
Compliant
REACH SVHC
Not Reviewed
Low-Halogen Status
Not Reviewed

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
[67940Series](#)

Mates With
IC