

	13	12	11	10	9	8	7	6	5	4	3	2	1														
J	ENG. NO.	PIN NO.	DIM. L	DIM. X	DIM. Z	DIM. Y	DIM. W	DIM. T							J												
	A-2220-NA I02	2 I6 I-5(I02)	(34.93) I.375	(15.88) .625	(16.13) .635	_____		_____																			
	A-2220-NA50 I	2 I6 I-5(50 I)	(34.93) I.375	(15.88) .625	(16.13) .635	_____		_____																			
I	A-2220-NAA50 I	2 I6 I- I6(50 I)	(25.40) I.000	(16.89) .665	(5.59) .220	_____		_____							I												
	A-2220-NAB50 I	2 I6 I- I3(50 I)	(42.42) I.670	(16.89) .665	(22.6 I) .890	_____		_____																			
	A-2220-NB I02	2 I6 I- I I(I02)	(44.45) I.750	(18.24) .7 I8	(23.29) .9 I7	_____		_____																			
H	A-2220-NB50 I	2 I6 I- I I(50 I)	(44.45) I.750	(18.24) .7 I8	(23.29) .9 I7	_____		_____							H												
	A-2220-NC I02	2 I6 I-7(I02)	(39.67) I.562	(15.88) .625	(20.88) .822	_____		_____																			
	A-2220-NK I02	2 I6 I-24(I02)	(20.32) .800	(10.16) .400	(7.24) .285	_____		_____																			
	A-2220-NL I02	2 I6 I- I6(I02)	(25.40) I.000	(11.43) .450	(11.05) .435	_____		_____																			
G	A-2220-NAY I02	2 I6 I-5(I02)	(34.93) I.375	(13.72) .540	(18.29) .720	_____		_____							G												
	A-2220-NA I02A	2 I6 I-5(I02)	(34.93) I.375	(15.88) .625	(16.13) .635	_____		_____																			
F														F													
E														E													
D														D													
C														C													
B														B													
A														A													
SEE SHEET 1 EC NO: UCP2011-1878 2011/03/21 DRWN:KKIPPER 2011/03/21 CHKD:SSOUSEK 2012/01/06 APPR:FSMITH REV R2 QUALITY SYMBOLS ▽=0 ▽=0 ▽=0 GENERAL TOLERANCES (UNLESS SPECIFIED) mm INCH 4 PLACES ± --- ± --- 3 PLACES ± --- ± --- 2 PLACES ± --- ± --- 1 PLACE ± --- ± --- ANGULAR ±1/2° DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS DIMENSION STYLE MM/IN DRAWN BY KSS DATE 1984/10/30 CHECKED BY DMS DATE 1984/10/30 APPROVED BY FSMITH DATE 2012/01/06 SCALE --- DESIGN UNITS INCH THIRD ANGLE PROJECTION TITLE WAFER ASSEMBLY CHASSIS MOUNT, KK 2220 SERIES DWG. MATERIAL NO. SEE CHART DOCUMENT NO. SDA-2220 SHEET NO. 2 OF 3 THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION <tr><td>1b_frame_C_P_AM_T Rev. F 2009/06/18</td><td>12</td><td>11</td><td>10</td><td>9</td><td>8</td><td>7</td><td>6</td><td>5</td><td>4</td><td>3</td><td>2</td><td>1</td><td></td></tr>														1b_frame_C_P_AM_T Rev. F 2009/06/18	12	11	10	9	8	7	6	5	4	3	2	1	
1b_frame_C_P_AM_T Rev. F 2009/06/18	12	11	10	9	8	7	6	5	4	3	2	1															

	13	12	11	10	9	8	7	6	5	4	3	2	1	
J	A-2220-NA I02		A-2220-NA50 I		A-2220-NAA50 I		A-2220-NAB50 I		A-2220-NB I02		A-2220-NB50 I			
	PART NO.	ENG. NO.	PART NO.	ENG. NO.	PART NO.	ENG. NO.	PART NO.	ENG. NO.	PART NO.	ENG. NO.	PART NO.	ENG. NO.		
	09-57- I025	A-2220-2A I02	09-78- I02 I	A-2220-2A50 I		A-2220-2AA50 I		A-2220-2AB50 I	09-57- I026	A-2220-2B I02	09-78- I022	A-2220-2B50 I		
	09-57- I035	A-2220-3A I02	09-78- I03 I	A-2220-3A50 I		A-2220-3AA50 I		A-2220-3AB50 I	09-57- I036	A-2220-3B I02	09-78- I032	A-2220-3B50 I		
I	09-57- I045	A-2220-4A I02	09-78- I04 I	A-2220-4A50 I		A-2220-4AA50 I		A-2220-4AB50 I	09-57- I046	A-2220-4B I02	09-78- I042	A-2220-4B50 I		
	09-57- I055	A-2220-5A I02	09-78- I05 I	A-2220-5A50 I		A-2220-5AA50 I		A-2220-5AB50 I	09-57- I056	A-2220-5B I02	09-78- I052	A-2220-5B50 I		
	09-57- I065	A-2220-6A I02	09-78- I06 I	A-2220-6A50 I	09-78- I069	A-2220-6AA50 I	09-78- I067	A-2220-6AB50 I	09-57- I066	A-2220-6B I02	09-78- I062	A-2220-6B50 I		
	09-57- I075	A-2220-7A I02	09-78- I07 I	A-2220-7A50 I		A-2220-7AA50 I		A-2220-7AB50 I	09-57- I076	A-2220-7B I02	09-78- I072	A-2220-7B50 I		
H	09-57- I085	A-2220-8A I02	09-78- I08 I	A-2220-8A50 I		A-2220-8AA50 I	09-78- I087	A-2220-8AB50 I	09-57- I086	A-2220-8B I02	09-78- I082	A-2220-8B50 I		
	09-57- I095	A-2220-9A I02	09-78- I09 I	A-2220-9A50 I		A-2220-9AA50 I		A-2220-9AB50 I	09-57- I096	A-2220-9B I02	09-78- I092	A-2220-9B50 I		
	09-57- I105	A-2220- I0A I02	09-78- I I0 I	A-2220- I0A50 I		A-2220- I0AA50 I	09-78- I I07	A-2220- I0AB50 I	09-57- I I06	A-2220- I0B I02	09-78- I I02	A-2220- I0B50 I		
	09-57- I115	A-2220- I I A I02	09-78- I I I I	A-2220- I I A50 I		A-2220- I I AA50 I		A-2220- I I AB50 I	09-57- I I I6	A-2220- I I B I02	09-78- I I I2	A-2220- I I B50 I		
G	09-57- I125	A-2220- I2A I02	09-78- I I2 I	A-2220- I2A50 I		A-2220- I2AA50 I	09-78- I I27	A-2220- I2AB50 I	09-57- I I26	A-2220- I2B I02	09-78- I I22	A-2220- I2B50 I		
	09-57- I135	A-2220- I3A I02	09-78- I I3 I	A-2220- I3A50 I		A-2220- I3AA50 I		A-2220- I3AB50 I	09-57- I I36	A-2220- I3B I02	09-78- I I32	A-2220- I3B50 I		
	09-57- I145	A-2220- I4A I02	09-78- I I4 I	A-2220- I4A50 I		A-2220- I4AA50 I		A-2220- I4AB50 I	09-57- I I46	A-2220- I4B I02	09-78- I I42	A-2220- I4B50 I		
	09-57- I155	A-2220- I5A I02	09-78- I I5 I	A-2220- I5A50 I		A-2220- I5AA50 I	09-78- I I57	A-2220- I5AB50 I	09-57- I I56	A-2220- I5B I02	09-78- I I52	A-2220- I5B50 I		
F	09-57- I165	A-2220- I6A I02	09-78- I I6 I	A-2220- I6A50 I		A-2220- I6AA50 I		A-2220- I6AB50 I	09-57- I I66	A-2220- I6B I02	09-78- I I62	A-2220- I6B50 I		
	09-57- I175	A-2220- I7A I02	09-78- I I7 I	A-2220- I7A50 I		A-2220- I7AA50 I		A-2220- I7AB50 I	09-57- I I76	A-2220- I7B I02	09-78- I I72	A-2220- I7B50 I		
	09-57- I185	A-2220- I8A I02	09-78- I I8 I	A-2220- I8A50 I		A-2220- I8AA50 I		A-2220- I8AB50 I	09-57- I I86	A-2220- I8B I02	09-78- I I82	A-2220- I8B50 I		
E	A-2220-NC I02		A-2220-NK I02		A-2220-NL I02		A-2220-NAY I02		A-2220-NA I02A					
	PART NO.	ENG. NO.	PART NO.	ENG. NO.	PART NO.	ENG. NO.	PART NO.	ENG. NO.	PART NO.	ENG. NO.				
	09-57- I027	A-2220-2C I02	09-57- I020	A-2220-2K I02	09-57-3026	A-2220-2L I02	09-57-3027	A-2220-2AY I02						
	09-57- I037	A-2220-3C I02	09-57- I030	A-2220-3K I02		A-2220-3L I02	09-57-3037	A-2220-3AY I02						
D	09-57- I047	A-2220-4C I02	09-57- I040	A-2220-4K I02	09-57-3046	A-2220-4L I02	09-57-3047	A-2220-4AY I02						
	09-57- I057	A-2220-5C I02	09-57- I050	A-2220-5K I02	09-57-3056	A-2220-5L I02	09-57-3057	A-2220-5AY I02						
	09-57- I067	A-2220-6C I02	09-57- I060	A-2220-6K I02	09-57-3066	A-2220-6L I02	09-57-3067	A-2220-6AY I02						
	09-57- I077	A-2220-7C I02	09-57- I070	A-2220-7K I02		A-2220-7L I02	09-57-3077	A-2220-7AY I02						
C	09-57- I087	A-2220-8C I02	09-57- I080	A-2220-8K I02		A-2220-8L I02	09-57-3087	A-2220-8AY I02	50-29-1770	A-2220-8A I02A				
	09-57- I097	A-2220-9C I02	09-57- I090	A-2220-9K I02	09-57-3096	A-2220-9L I02	09-57-3097	A-2220-9AY I02						
	09-57- I107	A-2220- I0C I02	09-57- I I00	A-2220- I0K I02		A-2220- I0L I02	09-57-3 I07	A-2220- I0AY I02						
	09-57- I117	A-2220- I I C I02	09-57- I I I0	A-2220- I I K I02		A-2220- I I L I02	09-57-3 I I7	A-2220- I I AY I02						
B	09-57- I127	A-2220- I2C I02	09-57- I I20	A-2220- I2K I02	09-57-3 I26	A-2220- I2L I02	09-57-3 I27	A-2220- I2AY I02						
	09-57- I137	A-2220- I3C I02	09-57- I I30	A-2220- I3K I02		A-2220- I3L I02	09-57-3 I37	A-2220- I3AY I02						
	09-57- I147	A-2220- I4C I02	09-57- I I40	A-2220- I4K I02		A-2220- I4L I02	09-57-3 I47	A-2220- I4AY I02						
	09-57- I157	A-2220- I5C I02	09-57- I I50	A-2220- I5K I02	09-57-3 I56	A-2220- I5L I02	09-57-3 I57	A-2220- I5AY I02						
A	09-57- I167	A-2220- I6C I02	09-57- I I60	A-2220- I6K I02		A-2220- I6L I02	09-57-3 I67	A-2220- I6AY I02						
	09-57- I177	A-2220- I7C I02	09-57- I I70	A-2220- I7K I02		A-2220- I7L I02	09-57-3 I77	A-2220- I7AY I02						
	09-57- I187	A-2220- I8C I02	09-57- I I80	A-2220- I8K I02		A-2220- I8L I02	09-57-3 I87	A-2220- I8AY I02						
	09-57- I197	A-2220- I9C I02												
SEE SHEET 1 EC NO: UCP2011-1878 DRWN:KK/PPR CHKD:SSOUSEK APPR:FSM ITH 2011/03/21 2011/03/21 2012/01/06 REV DESCRIPTION QUALITY SYMBOLS ▽=0 ▽=0 ▽=0 GENERAL TOLERANCES (UNLESS SPECIFIED) mm INCH 4 PLACES ± --- ± --- 3 PLACES ± --- ± --- 2 PLACES ± --- ± --- 1 PLACE ± --- ± --- ANGULAR ±1/2° DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS DIMENSION STYLE MM/IN DRAWN BY DATE KSS 1984/10/30 CHECKED BY DATE DMS 1984/10/30 APPROVED BY DATE FSM ITH 2012/01/06 SCALE --- DESIGN UNITS INCH THIRD ANGLE PROJECTION TITLE WAFER ASSEMBLY CHASSIS MOUNT, KK 2220 SERIES DWG. MATERIAL NO. SEE CHART DOCUMENT NO. SDA-2220 SHEET NO. 3 OF 3 SIZE C THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION														
1b_frame_C_P_AM_T Rev. F 2009/06/18	12	11	10	9	8	7	6	5	4	3	2	1		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[09-57-1050](#)