

AULT SPECIFICATIONS

12-20VA Wall Plug Series

INPUT

Voltage	230 VAC
Line Frequency	50 Hz
Configuration	Euro Wall Plug, No Ground

OUTPUT

<i>Model Number</i>	<i>Rated Output Volts AC</i>	<i>Output Current Amps</i>	<i>Max VA</i>	<i>Agency Approvals</i>
A48-062667-A000G	6	2.67	16.0	EN60950
A48-072286-A000G	7	2.29	16.0	EN60950
A48-082000-A000G	8	2.00	16.0	EN60950
A48-091778-A000G	9	1.78	16.0	EN60950
A48-101600-A000G	10	1.60	16.0	EN60950
A48-111455-A000G	11	1.46	16.0	EN60950
A48-141143-A000G	14	1.14	16.0	EN60950
A48-151333-A000G	15	1.33	20.0	EN60950
A48-161000-A000G	16	1.00	16.0	EN60950
A48-180889-A000G	18	0.89	16.0	EN60950
A48-200750-A000G	20	0.75	15.0	EN60742
A48-220727-A000G	22	0.73	16.0	EN60950
A48-240833-A000G	24	0.83	20.0	EN60742

*To be assigned at time of order placement.

ELECTRICAL

Topology	Step Down AC/AC Transformer
Dielectric Withstand	3000 VAC primary-secondary
Protection	Current, Thermal or Energy Limiting
EMI	Complies with EMC Directives
CE	CE Compliant

ENVIRONMENTAL

Operating Temperature	0° to 40° C with no derating
Storage Temperature	-30° to +85° C
Relative Humidity	5% to 95% non-condensing
Altitude	0 - 10,000 feet
Cooling	Convectional-non vented case

MECHANICAL

Case and Dimensions	A48 - Euro Wall Plug 81 L X 55 W X 48 H (mm) 3.2 L X 2.2 W X 1.9 H (in)
Case Material	Black 94V1 Polycarbonate
Weight	18 ounces, 520 grams, (excluding cord)
Cord and Connectors	6 ft., 2 Conductor, 22-24 AWG, Ault #3 Connector Other connectors are also available.

WARRANTY

1 Year