



### FEATURES:

- Slim retractable probe fully insulated to within 1/8" (3,18) of tip
- Needle point tip adjusts to desired length from 0-3" (0-76mm)
- Stainless Steel needle point easily pierces varnish and thin insulation
- Tip can be re-pointed if necessary
- Multi-stacking Banana plug molded directly on the wire
- Banana plug spring is nickel plated Beryllium Copper for long insertion life
- 4 foot test lead wire is silicone insulated for high temperature resistance. Also remains flexible at low temperature.

### MATERIALS:

Probe Body – Polypropylene and PVC, color: one black, one red.

Tip: Stainless Steel

Wire: 20 AWG, Silicone insulation

### RATINGS:

Operating Voltage: 30VAC/60VDC

Current: 3 Amperes

**ORDERING INFORMATION:** Model 5952A – (Includes a set of one black and one red test lead).

All dimensions are in inches. Tolerances (except noted): .xx =  $\pm .02$ " (.51 mm), .xxx =  $\pm .005$ " (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pomona:

5952A