


**Part Number: 87794-0001****2.50mm / 3.00mm Pitch Wire-to-Board Receptacle Housing with Fuse, with Bottom Flange, 16 Circuits***Series image - Reference only*

Status: **OBSOLETE**
Replacement: Contact Molex
Series: [87794](#)
Category: Crimp Housings

Mates With Part(s):
[53526](#) Wire-to-Board Header

Use With:
[503509001](#) Crimp Terminals, [505359001](#) Crimp Terminals

Product Environmental Compliance

EU RoHS: ELV and RoHS Compliant

China RoHS:

REACH SVHC: Contains SVHC: No

Low-Halogen Status: Low-Halogen

Part Detail**General**

Status	Obsolete
Category	Crimp Housings
Series	87794
Application	Power
Product Name	N/A

Physical

Circuits (maximum)	16
Color - Resin	Black
Gender	Female
Glow-Wire Compliant	No
Lock to Mating Part	Yes
Material - Resin	Polyphenylene Ether Alloy
Number of Rows	2
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	2.50mm, 3.00mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40°C to +105°C

Electrical

(Please review the Product Specification for specific details.)

Current - Maximum per Contact	10A
-------------------------------	-----

Material Info

UPC	822348104260
-----	--------------

Reference - Drawing Numbers

Product Specification	PS-87527-001
Sales Drawing	SD-87794-001

Application Tooling

Tooling specifications and manuals are found by selecting the products below.

Crimp Height Specifications are then contained in the Application Tooling Specification document.

Previously Available Application Tooling

[Check our list of old tooling that used to be available for this part](#)