





DESCRIPTION: M12 FEMALE - PANEL MOUNT (REAR) - 5 POS.



PANEL CUTOUT



NUT



NOTE:

MATERIAL

HOUSING: PBT UL94V-0, BLACK
CONTACT: BRASS
NUT: BRASS
SHELL: BRASS
O-RING: EPDM, BLACK

FINISH

CONTACT: GOLD PLATED
OVER 50µ" NICKEL
NICKEL PLATED
NICKEL PLATED

ELECTRICAL


RATED CURRENT: 5A
RATED VOLTAGE: 125V
INSULATION RESISTANCE: 100 mOhms MIN.
CONTACT RESISTANCE: 10 MOhms MAX.
WATER PROOF: IP67

ENVIRONMENT

OPERATION TEMPERATURE: -40°C TO +85°C

860-005-213R00Y

1 = GOLD FLASH
4 = 10µ" GOLD



PLC LAYOUT

RoHS COMPLIANT

DO NOT SCALE FROM DRAWING



THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN: M. SIGMON

DATE: 03-07-16

CHECKED:

DATE:

NorComp

SCALE: N.T.S.

SHEET 1 OF 1

REV 1

DWG NO.

860-005-213R00Y