


- Plug-in unit
- Fixed output voltages
- Thermal fuse in transformer
- Exchangeable DC plugs
- Plugg-inn enhet
- Faste utgangsspenninger
- Termosikring i transformator
- Utskiftbare DC plugger



### Technical specifications


Input voltage:  
Output voltage:  
Max output power:  
Insulation class:  
Electrical safety standard:  
EMC standards  
• Emission:  
• Immunity:  
Output terminals  
Cord with/without plug:  
Dimensions excl. plug:  
Weight:

### Tekniske data

Inngangsspenning:  
Utgangsspenning:  
Maks. utgangseffekt:  
Isolasjonsklasse:  
Elektrisk sikkerhetsstandard:  
EMC standarder  
• Emisjon:  
• Immunitet:  
Utgangsterminaler  
Sek. ledning med/uten plugg:  
Mål uten plugg:  
Vekt:

230 VAC +6/-10%, 50/60Hz  
3-35 VAC  
8,5 VA  
II  
EN 60742, EN 60950  
EN 61000-6-3  
EN 61000-6-1  
Accessories /Tilbehør  
95 x 51 x 57 mm  
390 g

### VAC



| Voltage version (VAC)<br>Spenningsversjoner (VAC) | Nominal load (mA)<br>Merkelast (mA) |
|---------------------------------------------------|-------------------------------------|
| 3                                                 | 1500                                |
| 4,5                                               | 1000                                |
| 6                                                 | 1300                                |
| 7,5                                               | 810                                 |
| 9                                                 | 780                                 |
| 12                                                | 710                                 |
| 15                                                | 510                                 |
| 18                                                | 470                                 |
| 21                                                | 340                                 |
| 24                                                | 310                                 |
| 35                                                | 140                                 |

Max. load (A): See diagram  
Maks. last (A): Se kurve