

ULTRA MINIATURE CERAMIC SMD CRYSTAL

ABM12



RoHS/RoHS II Compliant



1.6 x 1.2 x 0.45mm

Moisture Sensitivity Level (MSL) – This product is Hermetically Sealed and not Moisture Sensitive - MSL = N/A: Not Applicable

FEATURES:

- Suitable for RoHS reflow profile
- Available tight tolerance and stability
- Electron beam sealed ceramic package assures high precision and reliability
- Smallest package size in industry 1.6 x 1.2 x 0.46mm


APPLICATIONS:

- Blue-tooth, Wireless applications
- Computers, Modems, Microprocessors
- Communication, Test equipment
- High density applications
- PCMCIA
- Portable radios and MP3 players

STANDARD SPECIFICATIONS:

Parameters	Minimum	Typical	Maximum	Units	Notes
Frequency Range	24.000		80.000	MHz	
Standard Frequencies	26.000, 32.000 and 36.000MHz				(Contact Abracon for other frequencies)
Operation Mode	Fundamental				
Operating Temperature	-10		+50	°C	See options
Storage Temperature	-40		+85	°C	
Frequency Tolerance @+25°C	-50		+50	ppm	See options
Frequency Stability over the Operating Temperature (ref. to +25°C)	-50		+50	ppm	See options
Equivalent series resistance (R1) (Effective 8/14/2012)			200	Ω	24.000~39.999MHz
			100		40.000~80.000 MHz
Shunt capacitance (C0)			5	pF	
Load capacitance (CL)	8				Standard (See options if other than STD)
Drive Level		10	100	μW	
Aging	-5		+5	ppm	@25°C±3°C First year
Insulation Resistance	500			MΩ	@ 100Vdc ± 15V

OPTIONS & PART IDENTIFICATION: (Left blank if standard)



ULTRA MINIATURE CERAMIC SMD CRYSTAL

ABM12




RoHS/RoHS II Compliant




1.6 x 1.2 x 0.45mm

OUTLINE DRAWING:



Recommended land pattern




Pin 2 and pin 4 are connected to the metal lid (*1). (Please connect to GND)

Note 1: Due to material availability, the outline and finish color of the component lid may vary. This variation in no way affects the electrical performance of the product.

Note 2: Due to materials availability, this part may be manufactured with the chamfer on pin 1 or 2. This variation in no way affects the electrical performance of the product.

Dimensions: mm

REFLOW PROFILE:



ULTRA MINIATURE CERAMIC SMD CRYSTAL

ABM12



RoHS/RoHS II Compliant




1.6 x 1.2 x 0.45mm

TAPE & REEL:

Option "-T": Tape and reel (1,000pcs/reel)

Option "-T3": Tape and reel (3,000pcs/reel)



Dimensions: mm



Need a test socket for the ABM12 Series? To view compatible **PRECISION TEST & BURN-IN SOCKETS** for these parts, [click here](#). P/N AXS-1612-04-01C

ATTENTION Abracon Corporation's products are COTS – Commercial-Off-The-Shelf products; suitable for Commercial, Industrial and, where designated, Automotive Applications. Abracon's products are not specifically designed for Military, Aviation, Aerospace, Life-dependant Medical applications or any application requiring high reliability where component failure could result in loss of life and/or property. For applications requiring high reliability and/or presenting an extreme operating environment, written consent and authorization from Abracon Corporation is required. Please contact Abracon Corporation for more information.

ABRACON IS
ISO9001:2008
CERTIFIED



ABRACON
CORPORATION

Visit www.abracon.com for Terms & Conditions of Sale
30332 Esperanza, Rancho Santa Margarita, California 92688
tel 949-546-8000 | fax 949-546-8001 | www.abracon.com

Revised: 12.09.13

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

ABRACON:

[ABM12-26.000MHZ-B2X-T](#) [ABM12-27.000MHZ-B2X-T](#) [ABM12-28.63636MHZ-B2X-T](#) [ABM12-30.000MHZ-B2X-T](#)
[ABM12-32.000MHZ-B2X-T](#) [ABM12-36.000MHZ-B2X-T](#) [ABM12-40.000MHZ-B2X-T](#) [ABM12-44.000MHZ-B2X-T](#)
[ABM12-48.000MHZ-B2X-T](#) [ABM12-26.000MHZ-B2X-T3](#) [ABM12-27.000MHZ-B2X-T3](#) [ABM12-28.63636MHZ-B2X-T3](#)
[ABM12-30.000MHZ-B2X-T3](#) [ABM12-32.000MHZ-B2X-T3](#) [ABM12-36.000MHZ-B2X-T3](#) [ABM12-40.000MHZ-B2X-T3](#)
[ABM12-44.000MHZ-B2X-T3](#) [ABM12-48.000MHZ-B2X-T3](#)