

37.5-75 WATT 4:1 INPUT RANGE DC-DC CONVERTERS



- 37.5-75W Isolated Output
- Half Brick Package
- 4 : 1 Input Range
- Regulated Outputs
- Efficiency to 85%
- 300KHz Switching Frequency
- Five-Sided Shield Metal Case
- Continuous Short Circuit Protection

NOTE: 1. Nominal Input Voltage 24 or 48 VDC

All Specifications Typical At Nominal Line, Full Load and 25°C Unless Otherwise Noted.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Cincon:

<u>CHB75W-48S33</u>	<u>CHB75W-48S05</u>	<u>CHB75W-48S15</u>	<u>CHB75W-48S12</u>	<u>CHB75W-48S24</u>	<u>CHB75W-24S12N</u>
<u>CHB75W-48S33N</u>	<u>CHB75W-48S05N</u>	<u>CHB75W-24S24</u>	<u>CHB75W-48S12N</u>	<u>CHB75W-24S12</u>	<u>CHB75W-24S24N</u>
<u>CHB75W-24S05N</u>	<u>CHB75W-48S24N</u>	<u>CHB75W-24S15N</u>	<u>CHB75W-24S05</u>	<u>CHB75W-24S33</u>	<u>CHB75W-24S15</u>
<u>CHB75W-48S15N</u>	<u>CHB75W-24S33N</u>				