




D

C

B

A

VACCUM PICK UP AREA



A-A (SCALE 2:1)
(SOCKET ASSY IS NOT SECTIONEND)

1. MATERIAL
- ① HOUSING : HIGH TEMP, THERMO-PLASTIC, UL94V-0, BLACK
 - ② CONTACT : COPPER ALLOY
FINISH : Au PL. AT CONTACT AREA ON OVERALL OVER Ni UNDER PL. 0.00127 MIN.
 - ③ SOLDER BALL : Sn/Ag/Cu FOR LEAD FREE PRODUCT
 - ④ CAP : HIGH TEMP. THERMO-PLASTIC, UL94V-0, BLACK
- △ INDICATED DATE CODE ON THE HSG

0.76 um MIN	1554116-3
0.38 um MIN	1554116-2
Au AT CONTACT AREA	PART NUMBER

1554116-2, -3 : AS SHOWN

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ±
1 PLC ±
2 PLC ±0.5
3 PLC ±3
4 PLC ±
ANGLES ±
FINISH -

DWN
T.TOKUNAGA
17MAY2010

CHK
H.TAGUCHI
17MAY2010

APVD
T.NAKASHIMA
17MAY2010

PRODUCT SPEC
108-78496

APPLICATION SPEC
114-5432

WEIGHT
13.4 g

CUSTOMER DRAWING

TE Connectivity

NAME
SOCKET ASSY
LGA1356-2

SIZE
A2

CAGE CODE
00779

DRAWING NO
C=1554116

RESTRICTED TO
-

SCALE
1:1


SHEET
1 OF 4

REV
C




1554116

B

A



LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
—	—		—	SEE SHEET 1	—	—	—



THESE VIEWS DON'T SHOW CAP

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN		 TE Connectivity	
DIMENSIONS: mm		CHK			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD		NAME	
		PRODUCT SPEC		SOCKET ASSY	
0 PLC ± 0.3 1 PLC ± 0.3 2 PLC ± 0.3 3 PLC ± 0.3 4 PLC ± 0.3 ANGLES ± 3°		APPLICATION SPEC		LGA1356-2	
MATERIAL		WEIGHT		SIZE	RESTRICTED TO
		—		A2	—
		CUSTOMER DRAWING		CAGE CODE	
				DRAWING NO	
				00779	
				©	
				1554116	
				SCALE	
				NTS	
				SHEET	
				3 of 4	
				REV	
				C	

CUSTOMER DRAWING	SCALE NTS	SHEET 4 OF 4	REV C
------------------	--------------	-----------------	----------

