

Part Number . . . **BFG.1B.100.PCSG**

Size/Series 1B / B

[Request a quote](#)


MECHANICAL DETAILS

Shell Style/Model BFG*: Cap for plug (G key)
Keying 1 key (alpha=0, plug: male contacts, receptacle: female contacts)
Housing Material POM (Polyoxymethylene) shell without treatment, silicone gasket
Cable Fixing J : 0 - 0 mm
Variant :

PERFORMANCE DETAILS

OTHER CHARACTERISTICS

Humidity (max): <=95% [at 60 deg C /140 F]
Vibration: 15 g [10 Hz - 2000 Hz]
Shock Resistance: 100 g [6 ms]
Salt Spray Corrosion: >144 hr
Climatical Category: 50/175/21
Shielding (min): 75 dB (10 MHz)
Shielding (min): 40 dB (1 GHz)
IP Rating 50
Catalog

[Copyright](#) [Privacy policy](#) [Product safety](#)

