



UNIT:mm




CABLE WHITE PRINT
HI-SPEED USB Revision 2.0 SHIELDED 28AWG/1P+28AWG/2C
E189529 AWM STYLE 2725 80°C 30V VW-1 VEGA TECH

PIN ASSIGNMENT:



Electrical test:
1. 100% short, open, miswire test
2. Conduct resistance: 2 Ohm(max)
3. Insulation resistance: 10Mohm(min)
4. dielectric test: DC 300V



⑦	PE BAG	1/10	CLEAR SIZE: 280*330*0.05mm PRINT BLACK"MADE IN CHINA"+10PCS"及印生产周期,有透气孔.
⑥	PE BAG	1	CLEAR SIZE: 130*230*0.05mm PRINT BLACK"MADE IN CHINA"+1PC"及印生产周期,有透气孔.
⑤	TIE	1	BLACK L=80mm
④	OUT JACKET	12g	BLACK PVC-50P (MOULD NO:WM-40 & WM-88)
③	CABLE	1	BLACK USB2.0 UL2725 28#/1P+28#/2C+AEB OD:3.8mm L=3000±15
②	CONN	1set	USB2.0 刺破式 ATYPE MALE SHELL:NICKEL PIN:G/F 4PCS TYPE INSULATOR COLOR:WHITE
①	CONN	1set	USB2.0 刺破式 MINI 5P MALE SHELL:NICKEL PIN:G/F 3PCS INSULATOR COLOR:BLACK
NO.	NAME	Q'TY	SPECIFICATION

Cnc Tech, LLC				
Industrial Cable and Connector Technology				
DRAWN	ZHONGHS	DRAWING NO		
CHECKED		CUSTOMER		
APPROVAL		ITEM NO.	102-1031-BL-00300	
DECIDED		DATE	2012-02-16	
VERSIONS/EDITION	A/0	PROJECTION		

