

Posi-Tite™

WATERTITE CONNECTOR



The World's First No Crimp, Reusable, Watertite Connector.

The Test Results Are In!

Posi-Tite is still exceeding our tests at over 12 months of submersion. They have been abused & re-used over 100 times.

There's More...

Did we mention this is all done without crimping or tools? A Perfect connection anywhere by anyone, guaranteed!

Don't just take our word...

We'll send you a sample in a test tube of colored water as per SAE/USCAR-2 5.6.5 Submersion Test.

QUICK & EASY

1

Strip wire 3/8" & pass through cap.

2

Push wire while twisting seal. Bare wire end should protrude through clear wire guide & insulation into seal.

3

Handtighten to threaded female. Repeat for other side.

4


DONE!



NO CRIMPING



NO TOOLS NEEDED



WT1800 seals 20 - 18 ga. wire

Min. O.D. : .060" 1.54mm

Max. O.D. : .096" 2.46mm

WT1416 seals 14-16 ga. wire

Min. O.D. : .085" 2.18mm

Max. O.D. : .115" 2.95mm

POSI-TITE CONNECTORS MEET & EXCEED SAE/USCAR-2 5.6.5 SUBMERSION TEST