

LOC	DIST	P	F	ZONE	LTR	REVISIONS		
						DESCRIPTION	DATE	APPD
AR	35				A	REV, REDWN PER ECN 0899	-	-
					B	REV PER ECN 1456	11-3-87	J.P.
					C	REVSD/ECN CF-1706	07/88	DN
					D	REV PER ECN CF1807	JPG	5-5-88
					E	REV PER ECN BD4386		12-6-90
					F	REV PER EC 0020-1041-93		12/10/93
					G	OBSOLETE -11 PER EC 0410-197-96	21 AUG 97	JGH


- 1

UL RATED 94V-0 THERMOPLASTIC, COLOR: BLACK.
- 2




PHOSPHOR BRONZE PER QQ-B-750.
- 3

PLATED WITH .000030 GOLD ON LOCALIZED GOLD PLATE AREA, .000100 - .000200 BRIGHT TIN LEAD ON TERMINATION END, ALL OVER .000050 NICKEL ON ENTIRE CONTACT.
- 4

POLARIZING FEATURE DOES NOT EXIST ON END OPPOSITE THE POSN #1 INDICATOR ON 10 POSN PRODUCT.



TERMINATED VIEW



DETAIL Z
SCALE 10:1
TYPICAL

OBSOLETE	2.100	2.380	2.150	43	44	1- 746292 -3
	3.100	3.380	3.150	63	64	1- -2
	2.900	3.180	2.950	59	60	1- -1
	2.400	2.680	2.450	49	50	1- -0
	1.900	2.180	1.950	39	40	-9
	1.600	1.880	1.650	33	34	-8
	1.400	1.680	1.450	29	30	-7
	1.200	1.480	1.250	25	26	-6
	1.100	1.380	1.150	23	24	-5
	.900	1.180	.950	19	20	-4
	.700	.980	.750	15	16	-3
	.600	.880	.650	13	14	-2
	.400	.680	.450	9	10	746292 -1
	D	C	B	A	NO OF POSN	PART NUMBER

		D	C	B	A	NO OF POSN	PART NUMBER
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ON : 2 PL DEC ± - 3 PL DEC ± .005 ANGLES ± _____	DR	J. PEACHEY	2-19-86		AMP AMP INCORPORATED Harrisburg, Pa. 17105		
	CHK	JAY SAUDER	3-18-86				
	APPD	JAY SAUDER	3-18-86				
	APPD	D. HOFFMAN	3-18-86				
MATERIAL	PRODUCT SPEC	108-40000		NAME RECEPTACLE KIT, AMP-LATCH NOVO, DUAL BAR PLZN, 30 GOLD DUPLEX CONTACTS, W/O STRAIN RLF			
MOLDED PARTS: 	CONTACTS: 						
FINISH	APPLICATION SPEC	114-40005		SIZE	FSCM NO	DRAWING NO	
CONTACTS: 	WEIGHT	-			00779		746292
				SCALE 4:1		SHEET 1 of 1	