



# EPIC® Rectangular Connectors

HBE 16 Housings: Single Lever on Base



## HOODS

### TOP ENTRY



### SIDE ENTRY



All dimensions are in mm.

**Specifications:** DIN 43652  
**Temperature Range:** -40°C to +125°C



**Protection class:** NEMA 4, NEMA 12, IP65  
**Material:** Aluminum alloy, powder coated

| Position of Cable Entry | Size of Entry |      |        | Part Numbers |          |          | Complete your installation with a SKINTOP®, Pg 352 |           |               |               |
|-------------------------|---------------|------|--------|--------------|----------|----------|----------------------------------------------------|-----------|---------------|---------------|
|                         | PG            | NPT  | Metric | PG           | NPT      | Metric   | PG- Nylon                                          | PG- Metal | Metric- Nylon | Metric- Metal |
| Top Entry               | 21            | 3/4" | 25     | 10080900     | 100809NP | 19080900 | 53015150                                           | 52015750  | 53111030      | 53112030      |
| Side Entry              | 21            | 3/4" | 25     | 10082900     | 100829NP | 19082900 | 53015150                                           | 52015750  | 53111030      | 53112030      |
|                         | 29            | 1"   | 32     | 10092900     | 100929NP | 19092900 | 53015160                                           | 52015760  | 53111040      | 53112040      |

Top Entry Metric hoods do not come with a neck.

## HIGH PROFILE HOODS

### TOP ENTRY



### SIDE ENTRY



All dimensions are in mm.

**Specifications:** DIN 43652  
**Temperature Range:** -40°C to +125°C

**Protection class:** NEMA 4, NEMA 12, IP65  
**Material:** Aluminum alloy, powder coated

| Position of Cable Entry | Size of Entry |      |        | Part Numbers |          |          | Complete your installation with a SKINTOP®, Pg 352 |           |               |                |
|-------------------------|---------------|------|--------|--------------|----------|----------|----------------------------------------------------|-----------|---------------|----------------|
|                         | PG            | NPT  | Metric | PG           | NPT      | Metric   | PG- Nylon                                          | PG- Metal | Metric- Nylon | Metric- Metric |
| Top Entry               | 21            | 3/4" | 25     | 70094200     | 700942NP | 79094200 | 53015150                                           | 52015750  | 53111030      | 53112030       |
|                         | 29            | 1"   | 32     | 70094400     | 700944NP | 79099400 | 53015160                                           | 52015760  | 53111040      | 53112040       |
|                         | -             | -    | 40     | -            | -        | 79094600 | -                                                  | -         | 53111050      | 53112050       |
| Side Entry              | 21            | 3/4" | 25     | 70104200     | 701042NP | 79104200 | 53015150                                           | 52015750  | 53111030      | 53112030       |
|                         | 29            | 1"   | 32     | 70104400     | 701044NP | 79104400 | 53015160                                           | 52015760  | 53111040      | 53112040       |
|                         | -             | -    | 40     | -            | -        | 79104800 | -                                                  | -         | 53111050      | 53112050       |



High Profile Metric hoods do not come with a neck.

# EPIC® Rectangular Connectors




HBE 16 Housings: Single Lever on Base

## PANEL MOUNT BASES






**Specifications:** DIN 43652  
**Temperature Range:** -40°C to +125°C  
**Protection class:** NEMA 4, NEMA 12, IP65  
**Material:** Aluminum alloy, powder coated



| Description                    | Part Numbers |
|--------------------------------|--------------|
| Panel Mount without Dust Cover | 10072900     |
| Panel Mount with Dust Cover    | 10073900     |

All dimensions are in mm.

## SURFACE MOUNT BASES



All dimensions are in mm.

**Specifications:** DIN 43652  
**Temperature Range:** -40°C to +125°C

**Protection class:** NEMA 4, NEMA 12, IP65  
**Material:** Aluminum alloy, powder coated

| # of Entries            | Size of Entry |      |        | Part Numbers |          |          | Complete your installation with a SKINTOP®, Pg 352 |           |               |               |
|-------------------------|---------------|------|--------|--------------|----------|----------|----------------------------------------------------|-----------|---------------|---------------|
|                         | PG            | NPT  | Metric | PG           | NPT      | Metric   | PG- Nylon                                          | PG- Metal | Metric- Nylon | Metric- Metal |
| 2 Entries               | 21            | 3/4" | 25     | 10075900     | 100759NP | 19075900 | 53015150                                           | 52015750  | 53111030      | 53112030      |
| 1 Entry                 | 21            | 3/4" | 25     | 10074900     | 100749NP | 19074900 | 53015150                                           | 52015750  | 53111030      | 53112030      |
| 2 Entries w/ dust cover | 21            | 3/4" | 25     | 10078900     | 100789NP | 19078900 | 53015150                                           | 52015750  | 53111030      | 53112030      |
| 1 Entry with dust cover | 21            | 3/4" | 25     | 10076900     | 100769NP | 19076900 | 53015150                                           | 52015750  | 53111030      | 53112030      |

## DUST COVERS WITH ATTACHMENT STRING



**Material:** Thermoplastic Resin

**Temperature:** -40°C to 125°C


| Dust cover with single lever for HBE 16 Hoods                                                       | Part #   |
|-----------------------------------------------------------------------------------------------------|----------|
| Dust cover with single lever bolts for HBE 16 Panel Mount or Surface Mount Base/ Cable Coupler Hood | 10088700 |

# EPIC® Rectangular Connectors



HBE 16 Housings: Single Lever on Base

## HIGH PROFILE SURFACE MOUNT BASES



All dimensions are in mm.


**Specifications:** DIN 43652  
**Temperature Range:** -40°C to +125°C

**Protection class:** NEMA 4, NEMA 12, IP65  
**Material:** Aluminum alloy, powder coated


| # of Entries                     | Size of Entry |      |        | Part Numbers |          |          | Complete your installation with a SKINTOP® |           |               |               |
|----------------------------------|---------------|------|--------|--------------|----------|----------|--------------------------------------------|-----------|---------------|---------------|
|                                  | PG            | NPT  | Metric | PG           | NPT      | Metric   | PG- Nylon                                  | PG- Metal | Metric- Nylon | Metric- Metal |
| <b>2 Entries</b>                 | 21            | 3/4" | 25     | 70111200     | 701112NP | 79111200 | 53015150                                   | 52015750  | 53111030      | 53112030      |
|                                  | 29            | 1"   | 32     | 70111400     | 701114NP | 79111400 | 53015160                                   | 52015760  | 53111040      | 53112040      |
| <b>1 Entry</b>                   | 21            | 3/4" | 25     | 70110200     | 701102NP | 79110200 | 53015150                                   | 52015750  | 53111030      | 53112030      |
|                                  | 29            | 1"   | 32     | 70110400     | 701104NP | 79110400 | 53015160                                   | 52015760  | 53111040      | 53112040      |
| <b>2 Entries with dust cover</b> | 21            | 3/4" | 25     | 70115200     | 701152NP | 79115200 | 53015150                                   | 52015750  | 53111030      | 53112030      |
|                                  | 29            | 1"   | 32     | 70115400     | 701154NP | 79115400 | 53015160                                   | 52015760  | 53111040      | 53112040      |
| <b>1 Entry with dust cover</b>   | 21            | 3/4" | 25     | 70114200     | 701142NP | 79114200 | 53015150                                   | 52015750  | 53111030      | 53112030      |
|                                  | 29            | 1"   | 32     | 70114400     | 701144NP | 79114400 | 53015160                                   | 52015760  | 53111040      | 53112040      |

## CABLE COUPLER HOODS

### STANDARD PROFILE



### HIGH PROFILE



**Specifications:** DIN 43652  
**Temperature Range:** -40°C to +125°C

**Protection class:** NEMA 4, NEMA 12, IP65  
**Material:** Aluminum alloy, powder coated

| Position of Cable Entry | Size of Entry |      |        | Part Numbers |          |          | Complete your installation with a SKINTOP® |           |               |               |
|-------------------------|---------------|------|--------|--------------|----------|----------|--------------------------------------------|-----------|---------------|---------------|
|                         | PG            | NPT  | Metric | PG           | NPT      | Metric   | PG- Nylon                                  | PG- Metal | Metric- Nylon | Metric- Metal |
| <b>Standard Profile</b> | 21            | 3/4" | 25     | 10086900     | 100869NP | 19086900 | 53015150                                   | 52015750  | 53111030      | 53112030      |
| <b>High Profile</b>     | 21            | 3/4" | 25     | 70092200     | 700922NP | 79092200 | 53015150                                   | 52015750  | 53111030      | 53112030      |
|                         | 29            | 1"   | 32     | 70092400     | 700924NP | 79092400 | 53015160                                   | 52015760  | 53111040      | 53112040      |

Cable coupler metric hoods do not come with a neck.



# EPIC® Rectangular Connectors



HBE 16 Housings: Double Levers on Base

## HOODS

### TOP ENTRY



### SIDE ENTRY



All dimensions are in mm.

**Specifications:** DIN 43652  
**Temperature Range:** -40°C to +125°C



**Protection class:** NEMA 4, NEMA 12, IP65  
**Material:** Aluminum alloy, powder coated

| Position of Cable Entry | Size of Entry |      |        | Part Numbers |          |          | Complete your installation with a SKINTOP®, Pg 352 |           |               |               |
|-------------------------|---------------|------|--------|--------------|----------|----------|----------------------------------------------------|-----------|---------------|---------------|
|                         | PG            | NPT  | Metric | PG           | NPT      | Metric   | PG- Nylon                                          | PG- Metal | Metric- Nylon | Metric- Metal |
| Top Entry               | 21            | 3/4" | 25     | 100800C0     | 100800NP | 19080000 | 53015150                                           | 52015750  | 53111030      | 53112030      |
|                         | 29            | 1"   | 32     | 100900C0     | 100900NP | 19090000 | 53015160                                           | 52015760  | 53111040      | 53112040      |
| Side Entry              | 21            | 3/4" | 25     | 100820C0     | 100820NP | 19082000 | 53015150                                           | 52015750  | 53111030      | 53112030      |
|                         | 29            | 1"   | 32     | 100920C0     | 100920NP | 19092000 | 53015160                                           | 52015760  | 53111040      | 53112040      |

Top Entry metric hoods do not come with a neck.

## HIGH PROFILE HOODS

### TOP ENTRY



### SIDE ENTRY



All dimensions are in mm.


**Specifications:** DIN 43652  
**Temperature Range:** -40°C to +125°C

**Protection class:** NEMA 4, NEMA 12, IP65  
**Material:** Aluminum alloy, powder coated

| Position of Cable Entry | Size of Entry |      |        | Part Numbers |          |          | Complete your installation with a SKINTOP®, Pg 352 |           |               |               |
|-------------------------|---------------|------|--------|--------------|----------|----------|----------------------------------------------------|-----------|---------------|---------------|
|                         | PG            | NPT  | Metric | PG           | NPT      | Metric   | PG- Nylon                                          | PG- Metal | Metric- Nylon | Metric- Metal |
| Top Entry               | 21            | 3/4" | 25     | 701002C0     | 701002NP | 79100200 | 53015150                                           | 52015750  | 53111030      | 53112030      |
|                         | 29            | 1"   | 32     | 701004C0     | 701004NP | 79100400 | 53015160                                           | 52015760  | 53111040      | 53111040      |
|                         | -             | -    | 40     | -            | -        | 79100800 | -                                                  | -         | 53111050      | 53112050      |
| Side Entry              | 21            | 3/4" | 25     | 701022C0     | 701022NP | 79102200 | 53015150                                           | 52015750  | 53111030      | 53112030      |
|                         | 29            | 1"   | 32     | 701024C0     | 701024NP | 79102400 | 53015160                                           | 52015760  | 53111040      | 53111040      |
|                         | -             | -    | 40     | -            | -        | 79102800 | -                                                  | -         | 53111050      | 53112050      |


High Profile Metric hoods do not come with a neck.

### PANEL MOUNT BASES



**Specifications:**  
**Temperature Range:**  
**Protection class:**  
**Material:**


DIN 43652  
 -40°C to +125°C  
 NEMA 4, NEMA 12, IP65  
 Aluminum alloy, powder coated



All dimensions are in mm.

| Description                    | Part Numbers |
|--------------------------------|--------------|
| Panel Mount without Dust Cover | 100720C0     |


### SURFACE MOUNT BASES



**Specifications:**  
**Temperature Range:**

DIN 43652  
 -40°C to +125°C


**Protection class:** NEMA 4, NEMA 12, IP65  
**Material:** Aluminum alloy, powder coated



All dimensions are in mm.

| # of Entries | Size of Entry |      |        | Part Numbers |          |          | Complete your installation with a SKINTOP®, Pg 352 |           |               |               |
|--------------|---------------|------|--------|--------------|----------|----------|----------------------------------------------------|-----------|---------------|---------------|
|              | PG            | NPT  | Metric | PG           | NPT      | Metric   | PG- Nylon                                          | PG- Metal | Metric- Nylon | Metric- Metal |
| 2 Entries    | 21            | 3/4" | 25     | 100750C0     | 100750NP | 19075000 | 53015150                                           | 52015750  | 53111030      | 53112030      |
| 1 Entry      | 21            | 3/4" | 25     | 100740C0     | 100740NP | 19074000 | 53015150                                           | 52015750  | 53111040      | 53112030      |

### DUST COVERS WITH ATTACHMENT STRING



**Material:** Thermoplastic Resin

**Temperature:** -40°C to +125°C



|                                                                                                        | Part #   |
|--------------------------------------------------------------------------------------------------------|----------|
| Dust cover with double levers and gasket for HBE 16 Hoods                                              | 10088500 |
| Dust cover with double lever bolts for HBE 16 Panel Mount or Surface Mount Base/<br>Cable Coupler Hood | 10087000 |

# EPIC® Rectangular Connectors

HBE 16 Housings: Double Levers on Base



## HIGH PROFILE SURFACE MOUNT BASES



All dimensions are in mm.


**Specifications:** DIN 43652  
**Temperature Range:** -40°C to +125°C

**Protection class:** NEMA 4, NEMA 12, IP65  
**Material:** Aluminum alloy, powder coated


| # of Entries               | Size of Entry |      |        | Part Numbers |          |          | Complete your installation with a SKINTOP®, Pg 352 |           |               |               |
|----------------------------|---------------|------|--------|--------------|----------|----------|----------------------------------------------------|-----------|---------------|---------------|
|                            | PG            | NPT  | Metric | PG           | NPT      | Metric   | PG- Nylon                                          | PG- Metal | Metric- Nylon | Metric- Metal |
| 2 Entries without cover    | 21            | 3/4" | 25     | 700862C0     | 700862NP | 79086200 | 53015150                                           | 52015750  | 53111030      | 53112030      |
|                            | 29            | 1"   | 32     | 700864C0     | 700864NP | 79086400 | 53015160                                           | 52015760  | 53111040      | 53112040      |
| 1 Entry without dust cover | 21            | 3/4" | 25     | 70085200     | 700852NP | 79085200 | 53015150                                           | 52015750  | 53111030      | 53112030      |
|                            | 29            | 1"   | 32     | 700854C0     | 700854NP | 79085400 | 53015160                                           | 52015760  | 53111040      | 53112040      |

## CABLE COUPLER HOODS

### STANDARD PROFILE



### HIGH PROFILE



All dimensions are in mm.

**Specifications:** DIN 43652  
**Temperature Range:** -40°C to +125°C

**Protection class:** NEMA 4, NEMA 12, IP65  
**Material:** Aluminum alloy, powder coated

| Profile          | Size of Entry |      |        | Part Numbers |          |          | Complete your installation with a SKINTOP®, Pg 352 |           |               |               |
|------------------|---------------|------|--------|--------------|----------|----------|----------------------------------------------------|-----------|---------------|---------------|
|                  | PG            | NPT  | Metric | PG           | NPT      | Metric   | PG- Nylon                                          | PG- Metal | Metric- Nylon | Metric- Metal |
| Standard Profile | 21            | 3/4" | 25     | 100860C0     | 100860NP | 19086000 | 53015150                                           | 52015750  | 53111030      | 53112030      |
| High Profile     | 21            | 3/4" | 25     | 700902C0     | 700902NP | 79090200 | 53015150                                           | 52015750  | 53111030      | 53112030      |
|                  | 29            | 1"   | 32     | 700904C0     | 700904NP | 79090400 | 53015160                                           | 52015760  | 53111040      | 53112040      |

Cable Coupler Metric hoods do not come with a neck.