


MATERIAL	FLAMMABILITY RATING	CONTINUOUS OPERATING TEMP.
ABS	UL94-HB	-40°C ~ +60°C / -40°F ~ 140°F
CLEAR PC	UL94-V0 UV STABILIZED	-40°C ~ +130°C / -40°F ~ 266°F
ABS / PC BLEND	UL94-5VA	-40°C ~ +85°C / -40°F ~ 185°F
PBT / PC BLEND	UL94-5VA + UV (f1)	-40°C ~ +75°C / -40°F ~ 167°F

FINISH:
BODY _____ LIGHT GRAY


COVER _____ LIGHT GRAY OR CLEAR

LATCHES & HINGES _____ PLASTIC



WALL MOUNTING BRACKETS__ STAINLESS STEEL & HARDWARE



BODY




Ø.165in [4.20mm]
FOR M5 x 10mm LG. SELF-TAPPING SCREWS (ABS VERSIONS ONLY)
M5 THREADED INSERTS ON ALL OTHER VERSIONS
USE M5 x 8mm LG. MACHINE SCREWS.





Ø.165in [4.20mm]
FOR M5 x 10mm LG. SELF-TAPPING SCREWS

COVER



ASSEMBLY



NOTES:

1) UNIT COMES COMPLETE WITH
(4) WALL MOUNTING BRACKETS &
(4) M4 x 10mm LG. SELF-TAPPING SCREWS.
(NOT SHOWN)

2) BOXES DESIGNED TO MEET THESE STANDARDS:
NEMA 1,2,4,4X, AND IEC529-IP65 REQUIREMENTS.

TOLERANCE:

ALL DIMENSIONS HAVE ±0.039in [±1mm]
TOLERANCE UNLESS OTHERWISE SPECIFIED.

PART NO.	MATERIAL		USE
	BODY	COVER	
NBF-32040	ABS	ABS	INDOOR
NBF-32140	ABS / PC	ABS / PC	INDOOR
NBF-32240	ABS / PC	CLEAR PC	INDOOR
NBF-32340	PBT / PC	PBT / PC	OUTDOOR
NBF-32440	PBT / PC	CLEAR PC	OUTDOOR