





LOC	DIST	REVISIONS					
AD	00	P	LTR	DESCRIPTION	DATE	OWN	APVD
			L2	REVISED PER ECO-09-017580	30JUL09	HMR	JO
			L3	REVISED PER ECO-10-000445	20JAN10	KK	HMR



- | | | |
|---|--|---|
| 1 | MATERIAL: HSG FLAME RETARDANT THERMOPLASTIC,
COLOR: BLACK. POSTS: PHOS BRONZE | |
| 2 | .000030 GOLD ON CONTACT AREA,
.000100—.000200 BRIGHT TIN-LEAD ON SOLDER
LEADS, ALL OVER .000050 NICKEL | |
| 3 | RECESSED DATE CODE AND CSA LOGO | |
| 4 | .000030 GOLD ON CONTACT AREA,
.000100—.000200 MATTE TIN ON SOLDER LEADS,
ALL OVER .000050 NICKEL | |
| 5 | ROHS 2002/95/EC COMPLIANT | 7 |
| 6 | PRELIMINARY PART | 7 |
| 7 | OBSOLETE PARTS: OBSOLETE CIS STREAMLINING
PER D.RENAUD/D.SINISI | 7 |



SECTION M-M



ADS,	4		1.000	.600	6	14	6	7-102802-6	
		OBSOLETE	.800	.400	4	10	5	7-102802-5	
		7	8.300	7.900	79	160	5	7-102802-4	
		OBSOLETE	2.500	2.100	21	44	5	7-102802-3	
		OBSOLETE	7.700	7.300	73	148	5	7-102802-2	
		7	OBSOLETE	6.800	6.400	64	130	5	6-102802-9
		OBSOLETE	4.600	4.200	42	86	5	6-102802-8	
		7	OBSOLETE	3.900	3.500	35	72	5	6-102802-7
		NG	OBSOLETE	1.800	1.400	14	30	5	6-102802-6
			OBSOLETE	1.300	.900	9	20	5	6-102802-5
OBSOLETE	1.100		.700	7	16	5	6-102802-4		
7	OBSOLETE		1.500	1.100	11	24	5	6-102802-3	
OBSOLETE	.900		.500	5	12	5	6-102802-2		
OBSOLETE	—		—	—	—	—	—		
7	OBSOLETE		4.800	4.400	44	90	5	6-102802-0	
2	OBSOLETE		3.300	2.900	29	60	5	5-102802-9	
	OBSOLETE		2.300	1.900	19	40	5	5-102802-8	
	OBSOLETE		3.800	3.400	34	70	5	5-102802-7	
	7	OBSOLETE	5.300	4.900	49	100	5	5-102802-6	
	OBSOLETE	4.300	3.900	39	80	5	5-102802-5		
	OBSOLETE	2.800	2.400	24	50	5	5-102802-4		
	7	OBSOLETE	2.100	1.700	17	36	5	5-102802-3	
	OBSOLETE	6.300	5.900	59	120	5	5-102802-2		
	4	OBSOLETE	—	—	—	—	—	—	
		7	OBSOLETE	.800	.400	4	10	2-102802-5	
OBSOLETE		8.300	7.900	79	160	2-102802-4			
OBSOLETE		2.500	2.100	21	44	2-102802-3			
OBSOLETE		7.700	7.300	73	148	2-102802-2			
7		OBSOLETE	6.800	6.400	64	130	1-102802-9		
OBSOLETE		4.600	4.200	42	86	1-102802-8			
OBSOLETE		3.900	3.500	35	72	1-102802-7			
BY 6-102802-5		1.800	1.400	14	30	1-102802-6			
BY 6-102802-4		1.300	.900	9	20	1-102802-5			
7	OBSOLETE	1.100	.700	7	16	1-102802-4			
	OBSOLETE	1.500	1.100	11	24	1-102802-3			
	OBSOLETE	.900	.500	5	12	1-102802-2			
	OBSOLETE	—	—	—	—	—			
	7	OBSOLETE	4.800	4.400	44	90	1-102802-0		
	OBSOLETE	3.300	2.900	29	60	102802-9			
	OBSOLETE	2.300	1.900	19	40	102802-8			
	OBSOLETE	3.800	3.400	34	70	102802-7			
	7	OBSOLETE	5.300	4.900	49	100	102802-6		
	OBSOLETE	4.300	3.900	39	80	102802-5			
7	OBSOLETE	2.800	2.400	24	50	102802-4			
	OBSOLETE	2.100	1.700	17	36	102802-3			
	OBSOLETE	6.300	5.900	59	120	102802-2			
	OBSOLETE	—	—	—	—	—			
	FINISH	”C”	”B”	”A”	NO OF POSN	PART NUMBER			

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN B. HAYMAKER		30MAR00		 Tyco Electronics Corporation Harrisburg, PA 17105-3608	
		CHK J. GESFORD		30MAR00			
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD J. GESFORD		NAME	
mm		0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± 0.13[.005] 4 PLC ± ± - ANGLES		PRODUCT SPEC - APPLICATION SPEC -		ASSY, HEADER, MOD II, .025 SQ POSTS .100X.100CL, DOUBLE ROW, RIGHT ANGLE WITH GUIDE PINS	
MATERIAL		FINISH		WEIGHT		SIZE	CAGE CODE
		SEE TABLE		-		A2	00779
				CUSTOMER DRAWING		DRAWING NO	RESTRICTED TO
						C-102802	-
						SCALE	SHEET
						4:1	1 of 1
						REV	13