

Product Description

Enables the use of cable glands with larger connection threads than the existing threaded holes; With guide notch for O-ring; Assembling with wrench



Application range

- Equipment group II / Category 2G+1D
- Devices, machines and apparatus
- Mobile offshore and marine applications
- Chemical and petrochemical industry

Benefits

- Enables the use of cable glands with larger connection threads than the existing threaded holes
- With guide notch for O-ring
- Assembling with wrench

Design

- Metric connection thread acc. to EN 50262

Technical Data

Colour delivered

RAL 7035 light grey

Range of temperature

-30°C up to +90°C

Material

Body: Nickel plated brass O-Ring: NBR

Article List

Part number	Thread/ male M1	Thread/ female M2	Overall height mm	SW mm	Thread length/ outside mm	Outer Ø mm	PU
SKINDICHT® ME-M ATEX							
52104580	12 x 1,5	16 x 1,5	17	18	5	20	50
52104581	16 x 1,5	20 x 1,5	20	22	6	24	50
52104582	20 x 1,5	25 x 1,5	22.5	27	6.5	30	50
52104583	25 x 1,5	32 x 1,5	21.5	34	6.5	37,7	25
52104584	32 x 1,5	40 x 1,5	23	42	7	46	25
52104585	40 x 1,5	50 x 1,5	26	54	8	59	25
52104586	50 x 1,5	63 x 1,5	32	67	9	73	10

Footnote:

Photographs are not to scale and do not represent detailed images of the respective products.