





P	LTR	DESCRIPTION	DATE	DWN	APVD
	NC	NEW RELEASE PER E.O. PI5936	26FEB1999	-	RDR
	A	REVISED AND REDRAWN PER E.O. 166	-	-	RDR
	C	REVISED PER PCN-24-226269	06JAN2025	AJT	MB



3D VIEW



4. MATERIAL:
- CONNECTOR: PA66 GF15, GRAY
CAP:PA66 GF15, BLACK
WEDGE LOCK (INCLUDED): PBT GF30 (GREEN)
PINS:COPPER ALLOY, NICKEL PLATED

3. THE 12 PIN BUSBAR HAS A MAXIMUM CURRENT RATING OF 78 AMPS, 13 AMPS PER PIN.
2. FOR WIRE, CONTACT PERFORMANCE, AND APPLICATION CHARACTERISTICS, SEE ENVELOPE DRAWING 0425-015-0000 AND 0425-017-0000.
1. MATES WITH DT06-12SA-XXXX (XXXX = ALL MODIFICATIONS). CONSULT FACTORY FOR MODIFICATIONS.

NOTES:

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN P. BURKE	08MAY2000	 TE Connectivity		
		CHK -	15MAY2000			
DIMENSIONS: INCHES[mm]		APVD R. REED	16MAY2000	NAME DT 12 WAY RECEPTACLE KEY ARRANGEMENT 12 PIN BUSBAR-NICKEL PLATED COLOR:GREY		
		PRODUCT SPEC 108-151009				
		APPLICATION SPEC 114-151009		SIZE A3	CAGE CODE 00779	DRAWING NO G-DT04-12PA-P021
MATERIAL 4		WEIGHT 18 g		RESTRICTED TO -		
		CUSTOMER DRAWING	SCALE 2:1	SHEET 1	OF 1	REV C