



[United States](#) > [Government Solutions](#) > [Online Product Catalog](#)

Government Solutions

Market

- Defense
- Energy
- Green Solutions
- Health Safety
- Homeland Security

Contracts

- General Services Administration
- Veterans Affairs

Product Information

- Government Catalogs
- Online Product Catalog
- FEDSPEC Locator
- NSN Locator

News


- Industry Links

Contact Information

- Contact Us

[Product Catalog for Government Solutions](#) > [Defense Solutions](#) > [Aircraft Maintenance Products](#) > [3M™ Tapes](#) > [3M™ Foam Tapes](#) > [3M™ Foam Tapes - Single Coated](#) > [3M™ Vinyl Foam Tape 4516](#) >

3M™ Vinyl Foam Tape 4516 Black, 1/4 in x 36 yd, 36 per case



[Click to Enlarge](#)

3M™ Vinyl Foam Tape 4516 is a vinyl, conformable, single-coated, closed-cell foam tape. 1/16 in thick.

Where To Buy

[Where to Buy](#)

Quick Links

- [Contact Us](#)
- [Material Safety Data Sheets \(MSDS\)](#)
- [OH&ES Distributor Login](#)
- [Industrial Distributor Login](#)

Additional Information

Documents

Packaging

Bonds and seals to a variety of surfaces.

3M ID: 70-0024-5901-7

GTIN(UPC/EAN): 0 00 21200 03305 6

Characteristics:

Name	Value
Adhesive Type	Acrylic
Backing Material	Foam
Carrier Material	Vinyl
Density	25 Pound Per Cubic Foot
Diameter	10.9 Inch
Double Sided Adhesive	No
Length	36 Linear Yard
Length (metric)	32.91 Linear Metre
Liner Color	White
Liner Thickness	3 Milli-inch (mil)
Liner Type	Paper
Product Form	Roll
Shelf Life	18 Month
Tape Type	Single Coated
Temperature Resistance - Initial	250 Degree Fahrenheit
Temperature Resistance - Long Term	150 Degree Fahrenheit
Thickness	62 Milli-inch (mil)
Thickness (metric)	1.5 Millimetre
Trademark Name 1	3M
Units per Case	36
Width	0.25 Inch
Width (metric)	6.35 Millimetre