

SCT Splice Cover (Dual Wall) Heat-Shrinkable Tubing




Table 1: Dimensions (mm/inches)

Size	As Supplied	As Recovered		
	Minimum Expanded I.D. (D)	Maximum Recovered I.D. (d)	Recovered Total Wall (W)	Minimum Recovered Adhesive Wall (W1)
No.1	7.62 (0.300)	1.65 (0.065)	1.52 (0.060) ± 0.30 (0.012)	0.76 (0.030)
No.2	9.02 (0.355)	2.29 (0.090)	1.52 (0.060) ± 0.30 (0.012)	0.76 (0.030)
No.3	11.56 (0.455)	2.54 (0.100)	2.29 (0.090) ± 0.30 (0.012)	1.40 (0.055)
No.4	17.78 (0.700)	4.45 (0.175)	2.54 (0.100) ± 0.30 (0.012)	1.52 (0.060)
No.5	27.94 (1.100)	8.38 (0.330)	2.54 (0.100) ± 0.30 (0.012)	1.52 (0.060)

Color: Jacket shall be black; adhesive liner shall be amber. Marking is SCT-1, SCT-2, SCT-3, SCT-4, SCT-5

© 2000,2011 Tyco Electronics Corporation, a TE Connectivity Ltd. Company. All Rights Reserved.

Customer Drawing

		TE Connectivity 305 Constitution Drive Menlo Park, CA 94025 USA		Raychem Tubing		Title: SCT Splice Cover Dual Wall Heat-Shrinkable Tubing	
TE Connectivity reserves the right to amend this drawing at any time. Users should evaluate the suitability of the product for their application				Document No : SCT			
Cage Code: 06090	Scale: None	Size: A		Rev. Date: 15-Apr-11	Rev.: J1	Sheet: 1 of 3	

Print Date: 18-Apr-11 If this document is printed it becomes uncontrolled. Check for the latest revision.



Table 2: Properties

Property	Unit	Requirements	Test Method
Dimensions	Inches	Table 1	ASTM D 2671
Tensile Strength	PSI	1500 minimum	ASTM D 2671
Ultimate Elongation	Percent	300 minimum	ASTM D 2671 Speed 2 in./min. Note 1
Secant Modulus (Expanded Tubing)	PSI	35000 minimum	ASTM D 2671 Speed 2 in./min.
Longitudinal Change	Percent	+0 to -10	ASTM D 2671 Note 1
Concentricity (Expanded Form)	Percent	60 minimum	ASTM D 2671
Dielectric Strength* (Jacket Only)	Volts/mil	500 minimum	ASTM D 149
Volume Resistivity	Ohm-cm	10 ¹³ minimum	ASTM D 257
Immersion Leak Resistance	Micro-amps	0.25 maximum	Note 2
Thermal Cycling 25 cycles -40°C to 135°C, followed by: Immersion Leak Resistance, Note 2.	Micro-amps	0.25 maximum	Note 3
Heat Shock 4 hrs @ 250°C	--	No dripping, flowing or cracking of jacket	ASTM D 2671
Thermal Aging 1000 hrs @ 150°C, followed by: Immersion Leak Resistance, Note 2.	Micro-amps	0.25 maximum	Note 4
Fluid Resistance 24 hrs. @ 25 ± 3°C ASTM Reference Fuel C VV-F-800 Diesel Fuel 24 hrs @ 100 ± 3°C ASTM #3 Oil Followed by: Immersion Leak Resistance, Note 2.	Micro-amps	0.25 maximum	Note 5

Qualification Sizes: SCT-2 qualifies SCT-1, SCT-2 and SCT-3
SCT-4 qualifies SCT-4 and SCT-5

Note 1: Tensile Strength & Secant Modulus
Calculate Tensile Strength and Secant Modulus based on wall thickness of jacket only

Customer Drawing

Rev. Date: 15-Apr-11	Rev.: J1	Document No. SCT	Sheet: 2 of 3
-------------------------	-------------	----------------------------	------------------

Print Date: 18-Apr-11 If this document is printed it becomes uncontrolled. Check for the latest revision.



Note 2: Immersion Leak Resistance

A) Size SCT-2

Prepare 3 test assemblies insulated with SCT-2 as follows:

Construct a 2-wire to 2-wire inline splice in any suitable manner (crimped, soldered, twisted or welded). Splice an AWG 18 and an AWG 14 to an AWG 20 and AWG 14. Each wire shall be approximately 12 inches long. The wire insulation shall be cross-linked polyolefin and the conductor shall be bare copper. Shrink a 2-inch length of SCT-2 over the splice area with an appropriate heat gun. Apply heat until the SCT-2 is completely recovered on the splice and the adhesive liner flows at both ends. Allow the test assemblies to cool to room temperature and immerse them, except for the ends, in a 5% salt solution for 24 hours at room temperature. Apply 50 volts DC to the immersed specimens and measure the current leakage.

B) Size SCT-4

Prepare 3 test assemblies with SCT-4 as follows:

Construct a 3-wire to 3-wire to 3-wire inline splice in any suitable manner (crimped, soldered, twisted or welded). Splice three AWG 12 wires to three AWG 12 wires. Each wire shall be approximately 12 inches long. The wire insulation shall be cross-linked polyolefin and the conductor shall be bare copper. Shrink a 3-inch length of SCT-4 over the splice area with an appropriate heat gun. Apply heat until the SCT-4 is completely recovered on the splice and the adhesive liner flows at both ends. While the assembly is still hot from the recovery process, press the ends of the SCT-4 together where the wires emerge. Using parallel jaw pliers, align the wires and assure that they are completely coated with adhesive. Allow the test assemblies to cool to room temperature and immerse them, except for the ends in a 5% salt solution for 24 hours at room temperature. Apply 50 volts DC to the immersed specimens and measure the current leakage.

Note 3: Thermal Cycling

Prepare 3 splice assemblies in accordance with Note 2 and subject them to 25 thermal cycles. One cycle consists of 30 minutes at -40°C and 30 minutes at 135°C with a maximum of 5 minutes between temperatures. Specimens shall be allowed to cool to room temperature for one hour minimum and shall be measured for current leakage in accordance with Note 2.

Note 4: Thermal Aging

Prepare 3 splice assemblies in accordance with Note 2 and heat for 1000 hrs at 150°C. Specimens shall be allowed to cool to room temperature for one hour minimum and shall be measured for current leakage in accordance with Note 2.

Note 5: Fluid Resistance

Prepare 9 splice assemblies in accordance with Note 2 and immerse 3 assemblies in each of the fluids specified for 24 hours at the specified temperature. Measure current leakage in accordance with Note 2.

Acceptance tests shall consist of:

- Dimensions
- Tensile Strength
- Ultimate Elongation
- Heat Shock

Qualification tests shall consist of all the tests in this Customer Drawing

Customer Drawing

Rev. Date: 15-Apr-11	Rev.: J1	Document No. SCT	Sheet: 3 of 3
-------------------------	-------------	----------------------------	------------------

Print Date: 18-Apr-11 If this document is printed it becomes uncontrolled. Check for the latest revision.