

2014



Professional Quality Bits



Complete Bits Program



Terminator Impact Insert & Power Bit Sets

DESCRIPTION **Page**



Terminator Impact Bits 4-5

Standard Bits

DESCRIPTION **Page**



Torx® Insert/Power Bits 6-8



Phillips Insert/Power Bits 14-16



Hex Metric & Inch Insert/Power Bits 17-21



Square Insert/Power Bits 22



Slotted Insert/Power Bits 22-23



Pozidriv® Insert/Power Bits 24



Nut Setters 42-43

Specialty Bits

DESCRIPTION **Page**



Xeno Phillips Terminal Block 16



Torx® Align Bits 9



Ball End Torx® 13



Security Torx® 10-11



TorxPlus® 12-13



Security Hex 18,21



XZN Insert 26



Triple Square Insert Bits 25



Tri-Wing 25



Torq Set 25



Spanner 26

Cutting Tools

DESCRIPTION **Page**



Counter Sink 26



Drill Bit 26

High Performance Bits

DESCRIPTION **Page**



Slotted Dura Insert Bits 27



Phillips Dura Bits 27



Insert/Power Bits - Tungsten Carbide Coated



Pozidriv® Dura Bits 27



Insert/Power Bits - Tungsten Carbide Coated



Torx® Dura Insert Bits 27



Slotted Diamond Bits 27



Phillips Diamond Bits 27



Insert/Power Bits



Pozidriv® Diamond Bits 27



Torx® Diamond Bits 27



Phillips TiN Coated 28



Insert/Power Bits - Titanium



Torx® TiN Coated - Titanium 28

Insert & Power Bit Sets

DESCRIPTION **Page**



Security Bits Collector 29



BitFlip Sets 30



Insert Bit Selectors 31



XSelector/XLSelector Sets 31



6-in-1 Multi-Bit Sets 32



Stubby Bit Holder Sets 32



Topra Ratchet Bit Sets 33



Power Bit Belt Packs 33



PokitPak Sets 33

Stainless Steel Insert & Power Bits

DESCRIPTION	Page
 Insert Bits 7, 16, 17, 23, 24 Slotted/Phillips/ Torx®/Hex/Pozidriv®	
 Power Bits 7, 16, 24 Phillips/Torx®/Pozidriv®	

TorqueControl Insert & Micro Bit Sets

DESCRIPTION	Page
 TorqueControl Bit Sets	34


ESD Safe Micro Bit Handles/Bits & Sets

DESCRIPTION	Page
 Micro Bits	35-37
 ESD Safe Micro Bit Sets	38

ESD 1/4" Quick Release Bit Holder Blade Set

DESCRIPTION	Page
 1/4" Quick Release	39



Bit Holders

DESCRIPTION	Page
 ESD Safe Bit Holders	39
 SoftFinish® Cushion Grip	40
 MicroFinish Non-Slip Grip	40
 3K Ergo Bit Holder	40
 T-handle	40
 SoftGrip Stubby Bit Holder	40
 Flexible Shaft Bit Holder	40
 Drive-Loc VI Bit Holder	40
 Protturn Precision	40
 Multi-Bit Holders	41

Bit Holders

DESCRIPTION	Page
 Micro Bit Power Tool Adapter	36
 ClicFix Quick Release Insert Bits	41
 CentroFix Quick Release All 1/4" Drive Tools	41
 Protturn Quick Release 1/4" Drive	41
 Stainless Steel Bit Holder	42
 Magnetic Bit Holders & Retaining Ring Bit Holder	42
 Auto Lock Insert Bit Holder	42

Bit Sockets

DESCRIPTION	Page
 Torx® 1/4" Drive	44
 Torx® 3/8" Drive	44
 Torx® 3/8" - 5/16" Bits	44
 Security Torx® 3/8"	44
 Slotted Bit Sockets 1/2" Drive	44
 Phillips Bit Socket 1/2" Drive	44
 Hex Bit Sockets 1/4" Drive	45
 Hex Bit Sockets 3/8" Drive	45
 Ball End Hex Sockets	45
 Socket Adapters	46
 Impact Bit Holding Sockets	46
 6" Bit Sockets 1/4" & 3/8" Drive	46
 Socket Sets	47-48

Wiha Terminator Hex Inch & Metric Impact Bits - Insert & Power

**Up To 30X
Performance Over
Standard
Screwdriver Bits**



Impact rated bits for long life in impact applications

Provide up to 30 times impact performance over standard bits

Standard 1/4" drive - No special adaptor required

Wiha enhanced bi-material torsion zone

Precision machined exact fit tips

Wiha exclusive CVM tool steel

Guaranteed to out perform impact imposters


**765 Phillips Terminator Impact Bits,
1/4" Insert - 10 Bit Pack**

Item	+				SHOP
No.	Size	mm	pkg.		
76501	1	29	10		
76502	2	29	10		
76503	3	29	10		

**768 Phillips Terminator Impact Bits,
1/4" Insert - 2 Bit Pack**

Item	+				SHOP
No.	Size	mm	pkg.		
76801	1	29	2		
76802	2	29	2		
76803	3	29	2		


**765 Pozidriv® Terminator Impact Bits,
1/4" Insert - 10 Bit Pack**

Item	+				SHOP
No.	Size	mm	pkg.		
76506	1	29	10		
76507	2	29	10		
76508	3	29	10		

**768 Pozidriv® Terminator Impact Bits,
1/4" Insert - 2 Bit Pack**

Item	+				SHOP
No.	Size	mm	pkg.		
76806	1	29	2		
76807	2	29	2		
76808	3	29	2		


**765 TORX® Terminator Impact Bits,
1/4" Insert - 10 Bit Pack**

Item	T				SHOP
No.	Size	mm	pkg.		
76510	T10	29	10		
76511	T15	29	10		
76512	T20	29	10		
76513	T25	29	10		
76514	T27	29	10		
76516	T30	29	10		
76517	T40	29	10		

**768 TORX® Terminator Impact Bits,
1/4" Insert - 2 Bit Pack**

Item	T				SHOP
No.	Size	mm	pkg.		
76810	T10	29	2		
76811	T15	29	2		
76812	T20	29	2		
76813	T25	29	2		
76814	T27	29	2		
76816	T30	29	2		
76817	T40	29	2		


**765 Square Terminator Impact Bits,
1/4" Insert - 10 Bit Pack**

Item	□				SHOP
No.	Size	mm	pkg.		
76538	1	29	10		
76539	2	29	10		
76540	3	29	10		

**768 Square Terminator Impact Bits,
1/4" Insert - 2 Bit Pack**

Item	□				SHOP
No.	Size	mm	pkg.		
76838	1	29	2		
76839	2	29	2		
76840	3	29	2		


**765 Hex Inch Terminator Impact Bits,
1/4" Insert - 10 Bit Pack**

Item	Hex				SHOP
No.	Inch	mm	pkg.		
76530	1/8	29	10		
76531	9/64	29	10		
76532	5/32	29	10		
76533	3/16	29	10		
76534	7/32	29	10		
76535	1/4	29	10		

**768 Hex Inch Terminator Impact Bits,
1/4" Insert - 2 Bit Pack**


Item	Hex				SHOP
No.	Inch	mm	pkg.		
76830	1/8	29	2		
76831	9/64	29	2		
76832	5/32	29	2		
76833	3/16	29	2		
76834	7/32	29	2		
76835	1/4	29	2		


**765 Hex Metric Terminator Impact Bits,
1/4" Insert - 10 Bit Pack**

Item	Hex				SHOP
No.	mm	mm	pkg.		
76523	3.0	29	10		
76524	4.0	29	10		
76525	5.0	29	10		
76526	6.0	29	10		

**768 Hex Metric Terminator Impact Bits,
1/4" Insert - 2 Bit Pack**

Item	Hex				SHOP
No.	mm	mm	pkg.		
76823	3.0	29	2		
76824	4.0	29	2		
76825	5.0	29	2		
76826	6.0	29	2		

1/4" Drive Insert & Power Bits


**Up To 30X Performance
Over Standard Screwdriver Bits**



Wiha Terminator Hex Inch & Metric Impact Bits



765 Phillips Terminator Impact Bits, 1/4" Power - 10 Bit Pack

Item No.	Size	mm	pkg.	SHOP
76543	1	49	10	
76544	2	49	10	
76545	3	49	10	

768 Phillips Terminator Impact Bits, 1/4" Power - 2 Bit Pack

Item No.	Size	mm	pkg.	SHOP
76843	1	49	2	
76844	2	49	2	
76845	3	49	2	



765 Pozidriv® Terminator Impact Bits, 1/4" Power - 10 Bit Pack

Item No.	Size	mm	pkg.	SHOP
76548	1	49	10	
76549	2	49	10	
76550	3	49	10	

768 Pozidriv® Terminator Impact Bits, 1/4" Power - 2 Bit Pack

Item No.	Size	mm	pkg.	SHOP
76848	1	49	2	
76849	2	49	2	
76850	3	49	2	



765 TORX® Terminator Impact Bits, 1/4" Power - 10 Bit Pack

Item No.	Size	mm	pkg.	SHOP
76553	T10	49	10	
76554	T15	49	10	
76555	T20	49	10	
76556	T25	49	10	
76557	T27	49	10	
76558	T30	49	10	
76559	T40	49	10	

768 TORX® Terminator Impact Bits, 1/4" Power - 2 Bit Pack

Item No.	Size	mm	pkg.	SHOP
76853	T10	49	2	
76854	T15	49	2	
76855	T20	49	2	
76856	T25	49	2	
76857	T27	49	2	
76858	T30	49	2	
76859	T40	49	2	



765 Square Terminator Impact Bits, 1/4" Power - 10 Bit Pack

Item No.	Size	mm	pkg.	SHOP
76578	1	49	10	
76579	2	49	10	
76580	3	49	10	

768 Square Terminator Impact Bits, 1/4" Power - 2 Bit Pack

Item No.	Size	mm	pkg.	SHOP
76878	1	49	2	
76879	2	49	2	
76880	3	49	2	



765 Hex Inch Terminator Impact Bits, 1/4" Power - 10 Bit Pack

Item No.	Inch	mm	pkg.	SHOP
76570	1/8	49	10	
76571	9/64	49	10	
76572	5/32	49	10	
76573	3/16	49	10	
76574	7/32	49	10	
76575	1/4	49	10	

768 Hex Inch Terminator Impact Bits, 1/4" Power - 2 Bit Pack

Item No.	Inch	mm	pkg.	SHOP
76870	1/8	49	2	
76871	9/64	49	2	
76872	5/32	49	2	
76873	3/16	49	2	
76874	7/32	49	2	
76875	1/4	49	2	



765 Hex Metric Terminator Impact Bits, 1/4" Power - 10 Bit Pack

Item No.	mm	mm	pkg.	SHOP
76563	3.0	49	10	
76564	4.0	49	10	
76565	5.0	49	10	
76566	6.0	49	10	

768 Hex Metric Terminator Impact Bits, 1/4" Power - 2 Bit Pack

Item No.	mm	mm	pkg.	SHOP
76863	3.0	49	2	
76864	4.0	49	2	
76865	5.0	49	2	
76866	6.0	49	2	



Includes magnetic bit holder



76891 8 Pc. Bit Buddy Set With Terminator Impact Insert Bits - 29mm

76891 Set includes the following bits:

- ⊕ Phillips: 2, 3
 - ⊖ Square: 2, 3
 - ⊗ Torx®: T20, T25, T30
- Includes magnetic bit holder

76893 8 Pc. Bit Buddy Set With Terminator Impact Insert Bits - 29mm

76893 Set includes the following bits:

- ⬡ Hex Inch: 5/32, 3/16, 7/32, 1/4"
 - ⬡ Hex Metric: 4, 5, 6mm
- Includes magnetic bit holder

76895 8 Pc. Bit Buddy Set With Terminator Impact Insert Bits - 29mm

76895 Set includes the following bits:

- ⊗ Torx®: T10, T15, T20, T25, T27, T30, T40
- Includes magnetic bit holder

Power Bit Buddy Sets



76892 7 Pc. Bit Buddy Set With Terminator Impact Power Bits - 49mm

76892 Set includes the following bits:

- ⊕ Phillips: 2, 3
- ⊖ Square: 2, 3
- ⊗ Torx®: T20, T25, T30

76894 7 Pc. Bit Buddy Set With Terminator Impact Power Bits - 49mm

76894 Set includes the following bits:

- ⬡ Hex Inch: 5/32, 3/16, 7/32, 1/4"
- ⬡ Hex Metric: 4, 5, 6mm

76896 7 Pc. Bit Buddy Set With Terminator Impact Power Bits - 49mm

76896 Set includes the following bits:

- ⊗ Torx®: T10, T15, T20, T25, T27, T30, T40



91247 Empty Bit Buddy Case Holds Terminator Impact Insert Bits

91247 Holds 7 Impact Bits

91313 Empty Bit Buddy Case Holds Terminator Impact Power Bits

91313 Holds 7 Impact Bits

TORX® Bits

Impact resistant modified CVM,
tool steel, hardened

*The ideal multi-purpose bits for all
around quality and performance*

Made in Germany - Production Quality

Suitable for all applications
for both manual and machine
Hardness HRC 59-61

Highly resistant to wear and
tear for a long tool life



Wiha TORX® Insert Bit



[SHOP](#)

715 TORX® Bits, 1/4"

Item No.	Size	mm	pkg.	lbs.
71523	T3	25	10	.12
71524	T4	25	10	.12
71505	T5	25	10	.12
71506	T6	25	10	.12
71507	T7	25	10	.12
71508	T8	25	10	.12
71509	T9	25	10	.12
71510	T10	25	10	.12
71515	T15	25	10	.12
71520	T20	25	10	.12
71525	T25	25	10	.12
71527	T27	25	10	.13
71530	T30	25	10	.14
71540	T40	25	10	.15

30 Piece Contractor Grade Bits

725 TORX® Insert Bit Packs, 30 Pcs., 1/4"

Item No.	Size	mm	lbs.
72572	T7	25	.36
72573	T8	25	.36
72574	T9	25	.36
72575	T10	25	.36
72576	T15	25	.36
72577	T20	25	.36
72578	T25	25	.36
72579	T27	25	.36
72580	T30	25	.36
72581	T40	25	.36

[SHOP](#)

Wiha TORX® Bit Packs



2 bit
pack

[SHOP](#)

715 TORX® Insert Bit Packs, 1" CVM S2 modified tool steel.

Item No.	Size	mm	lbs.
71548	T3	25	.03
71549	T4	25	.03
71550	T5	25	.03
71551	T6	25	.03
71552	T7	25	.03
71553	T8	25	.03
71554	T9	25	.03
71555	T10	25	.03
71556	T15	25	.03
71557	T20	25	.03
71558	T25	25	.03
71559	T27	25	.04
71560	T30	25	.04
71561	T40	25	.04

Wiha TORX® Bit Packs



[SHOP](#)

71571 Torx® Insert Bit Packs, 1" CVM S2 modified tool steel. Extra hard with natural finish. Exact fit machined tips. 6 pc. bit pack.

71571 Set includes the following bits:



T15, T20, T25, T27,
wt. .08 T30, T40 x 1" (25mm)

[SHOP](#)

71570 Torx® Insert Bit Packs, 1" CVM S2 modified tool steel. Extra hard with natural finish. Exact fit machined tips. 6 pc bit pack.

71570 Set includes the following bits:



T5, T6, T7, T8, T9,
wt. .07 T10 x 1" (25mm)

Wiha TORX® 5/16" Bits



5/16"

[SHOP](#)

725 TORX® Bits, 5/16"

Item No.	Size	mm	pkg.	lbs.
72525	T25	35	10	.27
72527	T27	35	10	.27
72530	T30	35	10	.27
72540	T40	35	10	.28
72545	T45	35	10	.31
72550	T50	35	10	.32
72555	T55	35	10	.52

2 bit
pack



5/16"
Insert Bits

[SHOP](#)

725 TORX® Insert Bit Packs, 5/16"

CVM S2 modified tool steel

Item No.	Size	mm	lbs.
72531	T30	35	.28
72541	T40	35	.28
72546	T45	35	.31
72551	T50	35	.32
72556	T55	35	.52

Wiha TORX® Power Bits


[SHOP](#)

745 TORX® Power Bits 1/4" Hex Drive, Length 2.0"/50mm

Item	No.	Size	mm	pkg.	lbs.
	74511	T6	50	10	.18
	74512	T7	50	10	.18
	74513	T8	50	10	.18
	74517	T9	50	10	.18
	74519	T10	50	10	.18
	74521	T15	50	10	.18
	74523	T20	50	10	.18
	74529	T25	50	10	.18
	74531	T27	50	10	.18
	74533	T30	50	10	.18
	74535	T40	50	10	.18


[SHOP](#)

745 TORX® Power Bits 1/4" Hex Drive, Length 3.5"/90mm

Item	No.	Size	mm	pkg.	lbs.
	74563	T6	90	1	.03
	74565	T7	90	1	.03
	74567	T8	90	1	.03
	74569	T9	90	1	.03
	74571	T10	90	1	.03
	74573	T15	90	1	.03
	74575	T20	90	1	.04
	74577	T25	90	1	.04
	74579	T27	90	1	.04
	74581	T30	90	1	.04
	74583	T40	90	1	.04


[SHOP](#)

745 TORX® Power Bits 1/4" Hex Drive, Length 6.0"/150mm

Item	No.	Size	mm	pkg.	lbs.
	74586	T10	150	1	.04
	74587	T15	150	1	.04
	74588	T20	150	1	.04
	74589	T25	150	1	.04
	74590	T27	150	1	.04
	74591	T30	150	1	.04


[SHOP](#)

745 TORX® Power Bit Packs, 2" CVM S2 modified tool steel.

Item	No.	Size	mm	lbs.
	74501	T6	50	.05
	74502	T7	50	.05
	74503	T8	50	.05
	74504	T9	50	.05
	74506	T10	50	.05
	74508	T15	50	.05
	74510	T20	50	.05
	74514	T25	50	.06
	74515	T27	50	.06
	74516	T30	50	.06
	74518	T40	50	.06

Wiha TORX® Double End Bits


[SHOP](#)

744 TORX® Double End Bits 1/4" Hex Drive, Length 2.56"/65mm

Item	No.	Size	Size	mm	pkg.	lbs.
	74411	T6	T6	65	10	.32
	74413	T7	T7	65	10	.32
	74415	T8	T8	65	10	.32
	74417	T9	T9	65	10	.32
	74419	T10	T10	65	10	.32
	74421	T15	T15	65	10	.32
	74423	T20	T20	65	10	.32
	74429	T25	T25	65	10	.33
	74431	T27	T27	65	10	.34
	74433	T30	T30	65	10	.35
	74435	T40	T40	65	10	.38


[SHOP](#)

744 TORX® Double End Bit Pack 1/4" Hex Drive, Length 2.56"/65mm

Item	No.	Size	Size	mm	pkg.	lbs.
	74460	T6	T6	65	10	.32
	74461	T7	T7	65	10	.32
	74462	T8	T8	65	10	.32
	74463	T9	T9	65	10	.32
	74464	T10	T10	65	10	.32
	74465	T15	T15	65	10	.32
	74466	T20	T20	65	10	.32
	74467	T25	T25	65	10	.33
	74468	T27	T27	65	10	.34
	74469	T30	T30	65	10	.35
	74470	T40	T40	65	10	.38



745 TORX® Power Bits. 1/4" Hex Drive, Length 2.75"/70mm

Item	No.	Size	mm	pkg.	lbs.
	74536	T6	70	1	.02
	74538	T7	70	1	.02
	74542	T8	70	1	.02
	74544	T9	70	1	.02
	74546	T10	70	1	.02
	74548	T15	70	1	.02
	74551	T20	70	1	.03
	74553	T25	70	1	.03
	74556	T27	70	1	.04
	74558	T30	70	1	.04
	74561	T40	70	1	.04



715 Stainless Steel TORX® Bits, 1/4"

Item	No.	Size	mm	pkg.
	71500	T8	25	1
	71501	T9	25	1
	71502	T10	25	1
	71503	T15	25	1
	71504	T20	25	1
	71511	T25	25	1
	71512	T30	25	1
	71513	T40	25	1



745 Stainless Steel TORX® Power Bits 1/4" Hex Drive, Length 2.0"/50mm

Item	No.	Size	mm	pkg.
	70411	T15	50	1
	70413	T20	50	1
	70414	T25	50	1
	70416	T30	50	1
	70417	T40	50	1

Wiha TORX® Bit Sets

BitFlip Standard



38028 TORX® BitFlip Standard

with Wiha cushion grip handle and insulated shaft.

Set includes the following 1/4" bits:

TORX®: T8, T10, T15, T20,	lbs.
T25, T27, T30, T40	.44

[SHOP](#)


79242 Bit-Selector With TORX® Bits

Set Includes Universal Magnetic 1/4" Bit Holder
& The Following 10 Insert Bits:

TORX®: T5, T6, T7, T8, T9,	lbs.
T10, T15, T20, T25, T30	.32

79245 Bit-Selector With TORX® Bits

Set Includes Auto Lock Magnetic 1/4" Bit Holder
& The Following 10 Insert Bits:

TORX®: T7, T8, T9, T10,	lbs.
T15, T20, T25, T27, T30, T40	.34

[SHOP](#)


79445 XSelector Bit Set With TORX® Bits

Set Includes Quick Release Holder
and the following 10 bits:

TORX®: T7, T8, T9, T10, T15, T20,	lbs.
T25, T27, T30, T40	.29

[SHOP](#)


71195 PokitPak - TORX® Insert Bits In Molded Case -

Set includes 6 - 1/4" Insert Bits & Magnetic Bit Holder

TORX®:	lbs.
T8, T10, T15, T20, T25, T30	.15

[SHOP](#)


38003 TORX® Multi-Bit Screwdriver with Wiha Powerhandle

Set includes the following 1/4" bits:

TORX®:	lbs.
T5, T6, T7, T8, T9, T10	.40

[SHOP](#)

38004 TORX® Multi-Bit Screwdriver with Wiha Powerhandle

Set includes the following 1/4" bits:

TORX®:	lbs.
T8, T9, T10, T15, T20, T25	.40

38008 TORX® Multi-Bit Screwdriver with Wiha Powerhandle

Set includes the following 1/4" bits:

TORX®:	lbs.
T10, T15, T20, T25, T30, T40	.36




38045 TORX® SoftFinish® CushionGrip Stubby Bit Holder

with Wiha cushion grip handle and CVM tool steel shaft.

Set includes the following 1/4" bits:

TORX®: T8, T10, T15, T20, T25, T30	lbs. .20
------------------------------------	----------

[SHOP](#)


28295 TORX® Topra Ratchet Bit Set, 12 Pcs.

Set Includes Topra Handle, Magnetic Bit
Holder & The Following Bits:

TORX®: T7, T8, T9, T10, T15,	lbs.
T20, T25, T27, T30, T40	.65

[SHOP](#)

[SHOP](#)


74985 Power Bit Belt Pack With TORX® Bits

Set includes the following 10 bits:

TORX®: T6, T7, T8, T9,	lbs.
T10, T15, T20, T25, T27, T30	.28

Wiha TORX® Align Insert Bits and Power Bits

Torx® Align Tapered For Snug Fit In Screw

Highly resistant
to wear and
tear for a
long tool life



Impact resistant modified
chrome-vanadium-
molybdenum, tool steel,
hardened

**Made in Germany -
Production Quality**

Suitable for all applications
for both manual and machine
Hardness HRC 59-61



SHOP

715 TORX® Align Bits, 1/4"

Item No.	Size	mm	pkg.	lbs.
71536	T6	25	10	.12
71537	T7	25	10	.12
71538	T8	25	10	.12
71539	T9	25	10	.12
71541	T10	25	10	.12
71542	T15	25	10	.12
71543	T20	25	10	.12
71544	T25	25	10	.13
71545	T27	25	10	.13
71546	T30	25	10	.14
71547	T40	25	10	.15

(Also Known As Torx Wedge Fit)



747 TORX® Align Bits 1/4" Hex Drive, Length 2.0"/50mm

Item No.	Size	mm	pkg.	lbs.
74711	T6	50	10	.18
74714	T7	50	10	.18
74717	T8	50	10	.18
74721	T9	50	10	.18
74724	T10	50	10	.18
74728	T15	50	10	.20
74732	T20	50	10	.22
74736	T25	50	10	.22
74739	T27	50	10	.22
74742	T30	50	10	.22

(Also Known As Torx Wedge Fit)



2 bit
pack

733 TORX® Align Insert Bit Packs, 1"

CVM S2 modified tool steel

Item No.	Size	mm	lbs.
73310	T6	25	.03
73311	T7	25	.03
73312	T8	25	.03
73313	T9	25	.03
73314	T10	25	.03
73315	T15	25	.03
73316	T20	25	.03
73317	T25	25	.03
73318	T27	25	.03
73319	T30	25	.03
73320	T40	25	.04

SHOP



2 bit
pack



747 TORX® Align Power Bit Packs, 2"

Item No.	Size	mm	lbs.
74760	T6	50	.05
74761	T7	50	.05
74762	T8	50	.05
74763	T9	50	.05
74764	T10	50	.05
74765	T15	50	.05
74766	T20	50	.06
74767	T25	50	.06
74768	T27	50	.06
74769	T30	50	.06

SHOP

Wiha TORX® Align Coated Insert Bits PokitPak



79283 PokitPak - TORX® Align Coated Insert Bits In Molded Case -

Set Includes 6 - 1/4" Insert Bits

TORX® Align:

T10, T15, T20, T25, T30, T40

lbs. .12

SHOP



74981 Power Bit Belt Pack With TORX® Align Bits

Set includes the following 10 bits:

TORX® Align: T6, T7, T8, T9,
T10, T15, T20, T25, T27, T30

lbs. .28

SHOP

Wiha Security TORX® Insert Bits and Power Bits

Tamper Resistant Torx®

Made in
Germany -
Production
Quality



Impact resistant modified
CVM tool steel, hardened

Highly resistant
to wear and
tear for a
long tool life

Suitable for all applications
for both manual and machine
Hardness HRC 59-61



SHOP

701 Security TORX® Bits, 1/4"

Item	No.	Size	mm	pkg.	lbs.
	70127	T7s	25	10	.12
	70128	T8s	25	10	.12
	70129	T9s	25	10	.12
	70135	T10s	25	10	.12
	70139	T15s	25	10	.12
	70142	T20s	25	10	.12
	70148	T25s	25	10	.12
	70160	T27s	25	10	.13
	70163	T30s	25	10	.13
	70168	T40s	25	10	.14



5/16"

SHOP

725 Security TORX® Bits, 5/16"

Item	No.	Size	mm	pkg.	lbs.
	72542	T40s	35	10	.28
	72547	T45s	35	10	.32
	72552	T50s	35	10	.34
	72557	T55s	35	10	.52

2 bit
pack



SHOP

725 Security TORX® Bits, 5/16" 2 Bit Pk.

Item	No.	Size	mm	lbs.
	72562	T40s	35	.28
	72563	T45s	35	.29
	72564	T50s	35	.30
	72567	T55s	35	.32



SHOP

701 Security TORX® Insert Bit Packs, 1"

CVM S2 modified tool steel.

Item	No.	Size	mm	lbs.
	70150	T7s	25	.03
	70151	T8s	25	.03
	70152	T9s	25	.03
	70153	T10s	25	.03
	70154	T15s	25	.03
	70155	T20s	25	.03
	70156	T25s	25	.03
	70157	T27s	25	.03
	70158	T30s	25	.03
	70159	T40s	25	.03



SHOP

705 Security TORX® Power Bits, 1/4" Hex Drive, Length 2.0"/50mm

Item	No.	Size	mm	pkg.	lbs.
	70507	T7s	50	10	.18
	70508	T8s	50	10	.18
	70509	T9s	50	10	.18
	70510	T10s	50	10	.19
	70515	T15s	50	10	.19
	70520	T20s	50	10	.21
	70525	T25s	50	10	.23
	70527	T27s	50	10	.23
	70530	T30s	50	10	.23
	70540	T40s	50	10	.23
	70545	T45s	50	10	.33
	70550	T50s	50	10	.37
	70555	T55s	50	10	.37

2 bit
pack



SHOP

705 Security TORX® Power Bit Packs, 2"

Item	No.	Size	mm	lbs.
	70556	T7s	50	.07
	70557	T8s	50	.07
	70558	T9s	50	.07
	70559	T10s	50	.07
	70560	T15s	50	.07
	70561	T20s	50	.07
	70562	T25s	50	.07
	70563	T27s	50	.07
	70564	T30s	50	.07
	70565	T40s	50	.07
	70566	T45s	50	.07
	70567	T50s	50	.07
	70568	T55s	50	.07

Wiha Security TORX® Insert Bits/Power Bit Sets


[SHOP](#)

79247	Bit-Selector With Security TORX® Bits Set Includes Magnetic 1/4" Bit Holder & The Following 10 Bits:	
	Security TORX®: T7s, T8s, T9s, T10s, T15s, T20s, T25s, T27s, T30s, T40s	lbs. .32

70190	Bit-Selector With Security TORX® Bits Set includes the following 7 bits:	
	Security TORX®: T7s, T8s, T9s, T10s, T15s, T20s, T25s	lbs. .21


[SHOP](#)

	28297	Security TORX® Topra Ratchet Bit Set, 12 Pcs. Set Includes Topra Handle, Magnetic Bit Holder & The Following Bits:	
	Security TORX®: T7s, T8s, T9s, T10s, T15s, T20s, T25s, T27s, T30s, T40s	lbs. .65	


[SHOP](#)

	38009	Security TORX® Screwdriver with Wiha Powerhandle Set includes the following 1/4" bits:	
	Security TORX®: T7s, T8s, T9s, T10s, T15s, T20s	lbs. .36	

	38010	Security TORX® Screwdriver with Wiha Powerhandle Set includes the following 1/4" bits:	
	Security TORX®: T10s, T15s, T20s, T25s, T30s, T40s	lbs. .41	


[SHOP](#)

	79447	XSelector Bit Set With Security TORX® Bits Set Includes Quick Release Holder and the following 10 bits:	
	Security TORX®: T7s, T8s, T9s, T10s, T15s, T20s, T25s, T27s, T30s, T40s	lbs. .27	


[SHOP](#)

	38047	Security TORX® SoftFinish® CushionGrip Stubby Bit Holder with Wiha cushion grip handle and CVM tool steel shaft.	
	Security TORX®: T8s, T10s, T15s, T20s, T25s, T30s	lbs. .20	


[SHOP](#)

	74987	Power Bit Belt Pack With Security TORX® Bits Set includes the following 10 bits:	
	Security TORX®: T7s, T8s, T9s, T10s, T15s, T20s, T25s, T27s, T30s, T40s	lbs. .29	



Wiha TORXPlus® Insert Bits and Power Bits

TORXPlus®

Made in Germany -
Production Quality

Highly resistant
to wear and
tear for a
long tool life

Impact resistant modified
chrome-vanadium-molybdenum,
tool steel, hardened

Suitable for all applications
for both manual and
machine Hardness
HRC 59-61



TORXPlus®



Security TORXPlus®



SHOP

716 TORXPlus® Insert Bits, 1/4" Hex, 1" OAL

Item No.	Size	mm	pkg.	lbs.
71603	IP3	25	10	.12
71604	IP4	25	10	.12
71605	IP5	25	10	.12
71606	IP6	25	10	.12
71607	IP7	25	10	.12
71608	IP8	25	10	.12
71609	IP9	25	10	.12
71610	IP10	25	10	.12
71615	IP15	25	10	.12
71620	IP20	25	10	.12
71625	IP25	25	10	.12
71627	IP27	25	10	.13
71630	IP30	25	10	.13
71640	IP40	25	10	.15



2 bit
pack



SHOP

716 TORXPlus® Insert Bit Packs, 1"

CVM S2 modified tool steel

Item No.	Size	mm	lbs.
71631	IP3	25	.03
71632	IP4	25	.03
71633	IP5	25	.03
71634	IP6	25	.03
71635	IP7	25	.03
71636	IP8	25	.03
71637	IP9	25	.03
71638	IP10	25	.03
71639	IP15	25	.03
71641	IP20	25	.03
71642	IP25	25	.03
71643	IP27	25	.03
71644	IP30	25	.03
71645	IP40	25	.04



SHOP

746 TORXPlus® Power Bits, 1/4" Hex, 2" OAL

Item No.	Size	mm	pkg.	lbs.
74601	IP5	50	10	.18
74602	IP6	50	10	.18
74603	IP7	50	10	.18
74604	IP8	50	10	.18
74608	IP9	50	10	.18
74612	IP10	50	10	.20
74616	IP15	50	10	.20
74620	IP20	50	10	.20
74624	IP25	50	10	.20
74628	IP27	50	10	.25
74632	IP30	50	10	.25
74636	IP40	50	10	.25



2 bit
pack



746 TORXPlus® Power Bit Packs, 2"

Item No.	Size	mm	lbs.
74659	IP5	50	.05
74660	IP6	50	.05
74661	IP7	50	.05
74662	IP8	50	.05
74663	IP9	50	.05
74664	IP10	50	.05
74665	IP15	50	.05
74666	IP20	50	.05
74667	IP25	50	.05
74668	IP27	50	.05
74669	IP30	50	.05
74670	IP40	50	.05

Wiha Security TORXPlus® Insert Bit



SHOP

716 Security TORXPlus® Insert Bits, 1/4" Hex, 1" OAL

Item No.	Size	mm	pkg.	lbs.
71648	IPR8	25	1	.11
71650	IPR10	25	1	.11
71652	IPR15	25	1	.11
71654	IPR20	25	1	.12
71656	IPR25	25	1	.13
71657	IPR27	25	1	.13
71658	IPR30	25	1	.14
71660	IPR40	35	1	.14

Torx® Profiles



Torx®



TorxPlus®



**Security
Torx®**



**Security
TorxPlus®**



**Ball End
Torx®**

Wiha TORXPlus® Insert Bit Selectors



71690	Bit-Selector With TORXPlus® Bits Set Includes Magnetic 1/4" Bit Holder & The Following 10 Bits:	lbs.
	TORXPlus®: IP7, IP8, IP9, IP10, IP15, IP20, IP25 IP27, IP30, IP40	.31
71692	Bit-Selector With TORXPlus® Bits Set Includes Magnetic 1/4" Bit Holder & The Following 10 Bits:	lbs.
	TORXPlus®: IP3, IP4, IP5, IP6, IP7, IP8, IP9, IP10, IP15, IP20	.31




74982	Power Bit Belt Pack With TORXPlus® Bits Set includes the following 10 bits:	lbs.
	TORXPlus®: IP6, IP7, IP8, IP9, IP10, IP15, IP20, IP25, IP27, IP30	.28

Wiha Ball End TORX® Bits



745	Ball End TORX® Bits.			
1/4" Hex Drive, Length 2.0"/50mm				
Item				
No.	Size	mm	pkg.	lbs.
74524	T9	50	10	.18
74526	T10	50	10	.18
74528	T15	50	10	.18
74532	T20	50	10	.18
74534	T25	50	10	.18
74537	T27	50	10	.18
74539	T30	50	10	.18
74541	T40	50	10	.18

 2 bit
 pack


745	Ball End TORX® Power Bit Packs, 1"			
Item				
No.	Size	mm	lbs.	
74505	T9	50	.05	
74520	T10	50	.05	
74522	T15	50	.05	
74543	T20	50	.05	
74545	T25	50	.06	
74547	T27	50	.06	
74549	T30	50	.08	
74550	T40	50	.08	

Wiha Insert Security TORXPlus® XSelector




79450	XSelector Bit Set With Security TORXPlus® Bits Set Includes Quick Release Holder and the following 7 bits:	lbs.
	TORXPlus®: IPR8, IPR10, IPR15, IPR20, IPR25, IPR27, IPR30	.18

Wiha TORX® MagicSpring Screw Holding Power Bits

 Screw Holding
 TORX Bits

2 bit pack



745	TORX® MagicSpring Screw Holding Power Bits, 1/4" Hex Drive, Length 2.0"/50mm			
Item				
No.	Size	mm	pkg.	lbs.
74552	T10	50	2	.05
74554	T15	50	2	.05
74555	T20	50	2	.05
74557	T25	50	2	.05
74562	T30	50	2	.05
74564	T40	50	2	.05

Wiha Phillips Insert Bits



SHOP

711 Phillips Insert Bits, 1/4"

Item	+	—	—	—
No.	Size	mm	pkg.	lbs.
71100	0	25	10	.10
71101	1	25	10	.11
71102	2	25	10	.11
71103	3	25	10	.11

711 Phillips Insert Bit Bulk Packs, 1/4"

				
No.	Size	mm	pkg.	lbs.
71125	2	25	25 pc	.29
71150	2	25	50 pc	.60
71199	2	25	100 pc	1.16

725 Phillips Insert Contractor Grade, 1/4"


				
No.	Size	mm	pkg.	lbs.
72519	0	25	30 pc	.85
72521	1	25	30 pc	.85
72522	2	25	30 pc	.85
72523	3	25	30 pc	.85

Phillips Bits

The ideal multi-purpose bits for all around quality & performance

Made in Germany - Production Quality

Suitable for all applications for both manual and machine
Hardness HRC 59-61



Impact resistant modified CVM, tool steel, hardened

Highly resistant to wear and tear for a long tool life



Phillips

High grade CVM steel, hardened torsion zone to prevent uneven torque distribution DIN 3126 ISO 1173 with anti-camout ribs

Wiha Phillips Insert Bit Packs



2 bit pack



SHOP

711 Phillips Insert Bit Packs, 1"

CVM S2 modified tool steel

+	—	—	—
Item	+	—	—
No.	Size	mm	lbs.
71149	0	25	.03
71151	1	25	.03
71152	2	25	.03
71153	3	25	.04



SHOP

71155 Phillips Insert Bit Packs, 1" CVM

S2 modified tool steel. Extra hard with natural finish. Exact fit machined tips. 6 pc. bit pack.

71155 Set includes the following bits:

⌘ Phillips:
wt. .08 6 pieces 2 x 1" (25mm)



SHOP

71154 Phillips Insert Bit Packs, 1" CVM

S2 modified tool steel. Extra hard with natural finish. Exact fit machined tips. 3 pc. bit pack.

71154 Set includes the following bits:

⌘ Phillips:
wt. .04 1, 2, 3 x 1" (25mm)



SHOP

71056 Slotted/Phillips Insert Bit Packs, 1"

CVM S2 modified tool steel. Extra hard with natural finish, exact fit machined tips. 6 pc. bit pk.

71056 Set includes the following bits:

⌘ Slotted:
4.5, 5.5, 6.5 x 1" (25mm)

⌘ Phillips:
1, 2, 3 x 1" (25mm) .08

Wiha Insert Bit Sets



SHOP



71198 PokitPak - Slotted & Phillips Insert Bits In Molded Case -

⌘ Set Includes 6 - 1/4" Insert Bits & lbs. Magnetic Bit Holder

.15 ⌘ Slotted: 4.5, 6.5mm
⌘ Phillips: 0, 1, 2, 3

Wiha Phillips 5/16" Insert Bits


2 bit
pack

[SHOP](#)

721 Phillips Insert Bit Packs, 1"

CVM S2 modified tool steel. 5/16" Hex Drive.

Item	+	—	—	—
No.	Size	mm	lbs.	
72102	2	32	.05	
72103	3	32	.06	
72104	4	32	.07	

Wiha Phillips ACR Insert Bits


[SHOP](#)

711 Phillips ACR Insert Bits, 1/4"

Item	+	—	—	—
No.	Size	mm	pkg.	lbs.
71126	1	25	10	.11
71127	2	25	10	.11
71128	3	25	10	.11

Wiha Phillips Long Insert Bits


[SHOP](#)

711 Phillips Long Insert Bits. 1/4" Hex Drive, Length 2.0"/50mm

Item	+	—	—	—
No.	Size	mm	pkg.	lbs.
71105	1	50	10	.25
71106	2	50	10	.25
71107	3	50	10	.27


2 bit
pack


[SHOP](#)

711 Phillips Long Insert Bit Packs, 2"

CVM S2 modified tool steel

Item	+	—	—	—
No.	Size	mm	lbs.	
71165	1	50	.06	
71166	2	50	.06	
71167	3	50	.06	

Wiha Phillips Power Bits



741 Phillips Power Bits

1/4" Hex Drive, Length 2.0"/50mm

Item	+	—	—	—
No.	Size	mm	pkg.	lbs.
74103	1	50	10	.24
74112	2	50	10	.25
74124	3	50	10	.26

[SHOP](#)

2 bit
pack


741 Phillips Power Bit Packs, 2"

CVM S2 modified tool steel.

Item	+	—	—	—
No.	Size	mm	lbs.	
74164	1	50	.06	
74165	2	50	.06	
74166	3	50	.06	

[SHOP](#)


74150 Phillips Power Bit Packs, 2" CVM

S2 modified tool steel. Extra hard with natural finish. Exact fit machined tips. 3 pc. bit pack.

74150 Set includes the following bits:

+	—	—	—
wt.	.09	1, 2, 3 x 2" (50mm)	

[SHOP](#)


741 Phillips Power Bits. 1/4" Hex Drive, Length 2.75"/70mm

Item	+	—	—	—
No.	Size	mm	pkg.	lbs.
74167	00	70	1	.29
74168	0	70	1	.29
74106	1	70	1	.29
74115	2	70	1	.37
74127	3	70	1	.41

[SHOP](#)


741 Phillips Power Bits

1/4" Hex Drive, Length 3.5"/90mm

Item	+	—	—	—
No.	Size	mm	pkg.	lbs.
74109	1	90	1	.34
74118	2	90	1	.47
74130	3	90	1	.53

[SHOP](#)


741 Phillips Power Bits

1/4" Hex Drive, Length 4.33"/110mm

Item	+	—	—	—
No.	Size	mm	pkg.	lbs.
74111	1	110	1	.40
74121	2	110	1	.56
74131	3	110	1	.65

[SHOP](#)


741 Phillips Power Bits

1/4" Hex Drive, Length 127mm/5"

Item	+	—	—	—
No.	Size	mm	pkg.	lbs.
74113	1	127	1	.04
74123	2	127	1	.06
74133	3	127	1	.07

[SHOP](#)


741 Phillips Power Bits

1/4" Hex Drive, Length 150mm/5.9"

Item	+	—	—	—
No.	Size	mm	pkg.	lbs.
74116	1	150	1	.05
74126	2	150	1	.07
74136	3	150	1	.09

[SHOP](#)

Wiha Phillips Power Bit Packs



714 Phillips Double End Bits 1/4" Hex Drive, Length 2.36"/60mm

Item No.	Size	Size	mm	pkg.	lbs.	SHOP
71404	1 x 1	60	10	.31		
71414	2 x 2	60	10	.31		
71424	3 x 3	60	10	.32		



2 bit
pack



714 Phillips Double End Power Bit Packs, 60mm OAL

Item No.	Size	Size	mm	lbs.	SHOP
71464	1 + 1	60	.07		
71465	2 + 2	60	.07		
71466	3 + 3	60	.07		



743 Slotted & Phillips Double End Bits. 1/4" Hex Drive, Length 2.36"/60mm

Item No.	mm	Size	mm	pkg.	lbs.	SHOP
74303	4.5 x 1	60	10	.22		
74306	5.5 x 2	60	10	.30		
74309	7.0 x 3	60	10	.30		



2 bit
pack



743 Slotted/Phillips Double End Power Bit Packs, 60mm OAL

Item No.	mm	Size	mm	lbs.	SHOP
74304	4.5 + 1	60	.07		
74308	5.5 + 2	60	.07		
74310	7.0 + 3	60	.07		

Terminal Block Xeno Bits



714 Xeno Combination Terminal Block Power Bits. 1/4" Hex Drive, OAL 2.0"/50mm

Item No.	Size	mm	pkg.	lbs.
71452	1	50	10	.24
71453	2	50	10	.25



2 bit
pack



714 Xeno Combination Terminal Block Power Bit Packs, 2" CVM S2 modified tool steel

Item No.	Size	mm	lbs.
71455	1	50	.06
71456	2	50	.06

Wiha Stainless Steel Phillips Insert Bits & Power Bits



711 Stainless Steel Phillips Insert Bits, 1/4"

Item No.	Size	mm	pkg.	SHOP
71133	1	25	1	
71134	2	25	1	
71135	3	25	1	



704 Stainless Steel Phillips Power Bits, 1/4"

Item No.	Size	mm	pkg.	SHOP
70401	1	50	1	
70402	2	50	1	
70405	3	50	1	

Hex Bits


The ideal multi-purpose bits for all around quality & performance

Made in Germany - Production Quality

Impact resistant modified CVM, tool steel, hardened

Suitable for all applications for both manual and machine
Hardness HRC 59-61

Highly resistant to wear and tear for a long tool life



71396 Hex Inch Insert Bit Packs, 1" CVM

S2 modified tool steel. Extra hard with natural finish. Exact fit machined tips. 6 pc. bit pack.

71396 Set includes the following bits:

Hex Inch:

1/16, 3/32, 1/8, 5/32
wt. .13 3/16, 1/4" x 1" (25mm)

SHOP

Wiha Hex Inch & Metric Insert Bits



713 Hex Inch Insert Bits, 1/4"

Item No.	Inch	mm	pkg.	lbs.
71329	.050	25	10	.12
71326	1/16	25	10	.12
71328	5/64	25	10	.12
71330	3/32	25	10	.12
71333	7/64	25	10	.12
71336	1/8	25	10	.12
71339	9/64	25	10	.12
71342	5/32	25	10	.12
71345	3/16	25	10	.13
71348	7/32	25	10	.13
71351	1/4	25	10	.13
71353	5/16	25	10	.20
71356	3/8	25	10	.25



713 Hex Inch Insert Bit Packs, 1"

CVM S2 modified tool steel.

Item No.	Inch	mm	lbs.
71359	.050	25	.03
71360	1/16	25	.03
71361	5/64	25	.03
71362	3/32	25	.03
71363	7/64	25	.03
71364	1/8	25	.03
71365	9/64	25	.03
71366	5/32	25	.04
71367	3/16	25	.04
71368	7/32	25	.04
71369	1/4	25	.04
71373	5/16	25	.05
71387	3/8	25	.06



713 Hex Metric Insert Bits, 1/4"

Item No.	mm	mm	pkg.	lbs.
71303	1.5	25	10	.12
71306	2.0	25	10	.12
71308	2.5	25	10	.12
71309	3.0	25	10	.12
71312	4.0	25	10	.12
71315	5.0	25	10	.14
71318	6.0	25	10	.14
71321	8.0	25	10	.20
71324	10.0	25	10	.27

725 Hex Metric Insert Contractor Grade, 1/4"

Item No.	Size	mm	pkg.	lbs.
72582	2.0	25	30 pc	.85
72583	2.5	25	30 pc	.85
72584	3.0	25	30 pc	.85
72585	4.0	25	30 pc	.85
72586	5.0	25	30 pc	.85
72587	6.0	25	30 pc	.85

733 Hex Metric Insert Bit Packs, 1"

CVM S2 modified tool steel.

Item No.	mm	mm	lbs.
73301	1.5	25	.03
73302	2.0	25	.03
73303	2.5	25	.03
73304	3.0	25	.03
73305	4.0	25	.03
73306	5.0	25	.03
73307	6.0	25	.04
73308	8.0	25	.05
73309	10.0	25	.06

Hex Metric Long Insert Bit On 5/16"



72388 Hex Metric Bit On 5/16" Stock

Item No.	mm	mm	pkg.	lbs.
72388	12.0	75	10	.14

Wiha Stainless Steel Hex Metric Insert Bits



701 Stainless Steel Hex MM Insert Bits, 1/4"

Item No.	mm	mm	pkg.
70170	1.5	25	1
70171	2.0	25	1
70172	2.5	25	1
70173	3.0	25	1
70174	4.0	25	1
70175	5.0	25	1
70176	6.0	25	1

Wiha Hex Inch & Metric Power Bits



743 Hex Inch Power Bits. 1/4" Hex Drive, Length 2.0"/50mm

Item No.	Inch	mm	pkg.	lbs.	SHOP
74311	3/32	50	10	.30	
74312	7/64	50	10	.30	
74313	1/8	50	10	.30	
74314	9/64	50	10	.30	
74315	5/32	50	10	.30	
74316	3/16	50	10	.30	
74317	7/32	50	10	.30	
74318	1/4	50	10	.30	



2 bit pack



743 Hex Inch Power Bit Packs, 2"

Item No.	Inch	mm	lbs.	SHOP
74381	3/32	50	.07	
74382	7/64	50	.07	
74383	1/8	50	.07	
74384	9/64	50	.07	
74385	5/32	50	.07	
74386	3/16	50	.07	
74387	7/32	50	.07	
74388	1/4	50	.07	



743 Hex Inch Power Bits 1/4" Hex Drive, Length 2.75"/70mm

Item No.	Inch	mm	pkg.	lbs.	SHOP
74341	5/64	70	1	.36	
74342	3/32	70	1	.36	
74343	7/64	70	1	.36	
74344	1/8	70	1	.36	
74345	9/64	70	1	.36	
74346	5/32	70	1	.36	
74347	3/16	70	1	.36	
74348	7/32	70	1	.36	
74349	1/4	70	1	.36	



743 Hex Metric Power Bits. 1/4" Hex Drive, Length 2.0"/50mm

Item No.	mm	mm	pkg.	lbs.	SHOP
74325	2.5	50	10	.25	
74330	3.0	50	10	.25	
74340	4.0	50	10	.25	
74350	5.0	50	10	.25	
74360	6.0	50	10	.25	
74380	8.0	50	10	.38	



2 bit pack



743 Hex Metric Power Bit Packs, 2"

Item No.	mm	mm	lbs.	SHOP
74361	2.5	50	.07	
74362	3.0	50	.07	
74363	4.0	50	.07	
74364	5.0	50	.07	
74365	6.0	50	.07	
74366	8.0	50	.09	

743 Hex Metric Power Bits

1/4" Hex Drive, Length 2.75"/70mm

Item No.	mm	mm	pkg.	lbs.	SHOP
74351	2.0	70	1	.36	
74352	2.5	70	1	.36	
74353	3.0	70	1	.36	
74354	4.0	70	1	.36	
74355	5.0	70	1	.36	
74356	6.0	70	1	.36	
74357	8.0	70	1	.36	

Wiha Security Hex Insert Bits



719 Security Hex In Insert Bits, 1/4"

Item No.	Inch	mm	pkg.	lbs.	SHOP
71930	5/64	25	10	.12	
71932	3/32	25	10	.12	
71934	7/64	25	10	.12	
71936	1/8	25	10	.12	
71938	9/64	25	10	.12	
71940	5/32	25	10	.12	
71955	3/16	25	10	.13	
71956	7/32	25	10	.14	
71960	1/4	25	10	.15	

719 Security Hex Metric Insert Bits, 1/4"

Item No.	mm	mm	pkg.	lbs.	SHOP
71939	2.0	25	10	.12	
71941	2.5	25	10	.12	
71942	3.0	25	10	.12	
71943	4.0	25	10	.12	
71944	5.0	25	10	.15	
71945	6.0	25	10	.15	
71946	8.0	25	10	.20	



2 bit pack



719 Security Hex Inch Insert Bit Packs, 1"

CVM S2 modified tool steel.

Item No.	Inch	mm	lbs.	SHOP
71970	5/64	25	.03	
71971	3/32	25	.03	
71972	7/64	25	.03	
71973	1/8	25	.03	
71974	9/64	25	.03	
71975	5/32	25	.03	
71976	3/16	25	.04	
71977	7/32	25	.04	
71978	1/4	25	.04	



2 bit pack



719 Security Hex Metric Insert Bit Packs, 1" CVM S2 modified tool steel.

Item No.	mm	mm	lbs.	SHOP
71979	2.0	25	.03	
71980	2.5	25	.03	
71981	3.0	25	.03	
71982	4.0	25	.03	
71983	5.0	25	.04	
71984	6.0	25	.04	
71985	8.0	25	.05	

Wiha Ball End Hex Inch Insert Bits


[SHOP](#)

717 Ball End Hex Inch Insert Bits, 1/4"

Item	No.	Inch	mm	pkg.	lbs.
	71701	3/32	25	10	.12
	71702	7/64	25	10	.12
	71703	1/8	25	10	.12
	71704	9/64	25	10	.12
	71705	5/32	25	10	.12
	71706	3/16	25	10	.13
	71707	7/32	25	10	.13
	71708	1/4	25	10	.13


[SHOP](#)

717 Ball End Hex Inch Insert Bit Packs, 1"

Item	No.	Inch	mm	lbs.
	71711	3/32	25	.03
	71712	7/64	25	.03
	71713	1/8	25	.03
	71714	9/64	25	.03
	71715	5/32	25	.04
	71716	3/16	25	.04
	71717	7/32	25	.04
	71718	1/4	25	.04

Ball End Hex Metric Power Bits


[SHOP](#)

717 Ball End Hex Metric Insert Bits 1/4" Hex Drive, Length 1.5"/38mm

Item	No.	mm	mm	pkg.
	71719	1.5	38	1
	71720	2.0	38	1
	71721	2.5	38	1
	71722	3.0	38	1
	71723	4.0	38	1
	71724	5.0	38	1
	71725	6.0	38	1

Wiha MagicRing Insert Bits

Screw Holding
Hex Bits



Spring
steel
retaining
ring


[SHOP](#)

713 MagicRing Metric Insert Bits, 1/4"

Item	No.	mm	mm	pkg.	lbs.
	71304	3.0	25	1	.01
	71307	4.0	25	1	.01
	71310	5.0	25	1	.01
	71311	6.0	25	1	.01



[SHOP](#)

713 MagicRing Inch Insert Bits, 1/4"

Item	No.	Inch	mm	pkg.	lbs.
	71343	1/8	25	1	.01
	71346	9/64	25	1	.01
	71349	5/32	25	1	.01
	71352	3/16	25	1	.01
	71354	7/32	25	1	.01
	71358	1/4	25	1	.01



Spring steel
retaining ring



743 MagicRing Metric Power Bits, 1/4"

Item	No.	mm	mm	pkg.	lbs.
	74301	3.0	50	1	.02
	74305	4.0	50	1	.02
	74307	5.0	50	1	.03
	74319	6.0	50	1	.03

[SHOP](#)


743 MagicRing Inch Power Bits, 1/4"

Item	No.	mm	mm	pkg.	lbs.
	74369	1/8	50	1	.02
	74371	9/64	50	1	.02
	74373	5/32	50	1	.02
	74375	3/16	50	1	.03
	74377	7/32	50	1	.03
	74379	1/4	50	1	.03

[SHOP](#)

1/4" Ball End MagicRing Bits

Screw Holding
Hex Bits



717 MagicRing Metric Power Ball End Bits

Item	No.	mm	mm	pkg.	lbs.
	71730	3.0	50	1	.02
	71740	4.0	50	1	.02
	71750	5.0	50	1	.03
	71760	6.0	50	1	.03

[SHOP](#)

Screw Holding Hex Bits



717 MagicRing Inch Power Ball End Bits

Item	No.	mm	mm	pkg.	lbs.
	71726	1/8	50	1	.02
	71728	9/64	50	1	.02
	71732	5/32	50	1	.02
	71734	3/16	50	1	.03
	71736	7/32	50	1	.03
	71738	1/4	50	1	.03

[SHOP](#)

Screw Holding Hex Bits



Wiha Hex Inch & Metric Bit Sets



[SHOP](#)

79246	Bit-Selector With Hex Inch Bits Set Includes Magnetic 1/4" Bit Holder & The Following 10 Bits:	
	Hex Inch: 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4"	lbs. .32
79256	Bit-Selector With Hex Metric Bits Set Includes Magnetic 1/4" Bit Holder & The Following 8 Bits:	
	Hex Metric: 1.5, 2.0, 2.5, 3.0, 4.0, 5.0, 6.0, 8.0mm	lbs. .30



[SHOP](#)

79446	XSelector Bit Set With Hex Inch Bits Set Includes Quick Release Holder and the following 10 bits:	
	Hex Inch: 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4"	lbs. .27




[SHOP](#)

38058	Hex Inch SoftFinish® CushionGrip Stubby Bit Holder with Wiha cushion grip handle and CVM tool steel shaft. Set includes the following 1/4" bits:	
	Hex Inch: 3/16, 5/32, 9/64, 1/8, 7/64, 3/32"	lbs. .21




[SHOP](#)

38057	Hex Metric SoftFinish® CushionGrip Stubby Bit Holder with Wiha cushion grip handle and CVM tool steel shaft. Set includes the following 1/4" bits:	
	Hex Metric: 2.0, 2.5, 3.0, 4.0, 5.0, 6.0mm	lbs. .21



[SHOP](#)

28298	Hex Inch Topra Ratchet Bit Set, 12 Pc. Set includes Topra Handle, Magnetic bit holder and the following bits:	
	Hex Inch: 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4"	lbs. .65



[SHOP](#)

28299	Hex Metric Topra Ratchet Bit Set, 10 Pc. Set includes Topra Handle, Magnetic bit holder and the following bits:	
	Hex Metric: 1.5, 2.0, 2.5, 3.0, 4.0, 5.0, 6.0, 8.0mm	lbs. .65



[SHOP](#)

74986	Power Bit Belt Pack With Inch & Metric Hex Bits Set includes the following 10 bits:	
	Inch: 1/8, 9/64, 5/32, 3/16, 7/32, 1/4"	lbs.
	Metric: 3.0, 4.0, 5.0, 6.0mm	.34


Wiha Security Hex Inch & Metric Bit Sets


[SHOP](#)


79266	Bit-Selector With Security Hex Inch Bits Set Includes Magnetic 1/4" ClicFix Bit Holder & The Following 9 Bits:	lbs.
	Security Hex Inch: 5/64, 3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4"	.31


[SHOP](#)

38014	Security Hex Inch Multi-Bit Screwdriver, 6 Pc. Set With Wiha Powerhandle & CVM steel, hardened shaft.	lbs.
	Set includes the following 1/4" bits: Security Hex: 3/32, 1/8, 5/32, 3/16, 7/32"	.39


[SHOP](#)

71998	PokitPak - Security Hex Inch Insert Bits In Molded Case - Set includes 6 - 1/4" Insert Bits	lbs.
	Inch Security Hex: 3/32, 7/64, 1/8, 9/64, 5/32, 3/16"	.12


[SHOP](#)

71995	PokitPak - Security Hex Metric Insert Bits In Molded Case Set Includes 6 - 1/4" Insert Bits	lbs.
	Metric: 2.5, 3.0, 4.0, 5.0, 6.0, 8.0mm	.21

Wiha Ball End Hex Inch & Metric Bit Sets


[SHOP](#)

79276	Bit-Selector With Ball End Hex Inch Bits Set Includes Magnetic 1/4" Bit Holder & The Following 8 Bits:	lbs.
	Ball End Hex Inch: 3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4"	.30



38056	Ball End Hex SoftFinish® CushionGrip Stubby Bit Holder with Wiha cushion grip handle and CVM tool steel shaft.	lbs.
	Set includes the following 1/4" bits: Ball Hex: 1/8, 9/64, 5/32, 3/16, 7/32, 1/4"	.21

Wiha MagicRing Hex Inch & Metric Bit Sets



Screw Holding


[SHOP](#)

71399	Bit-Selector With Metric & Inch MagicRing Insert 1/4" Bits Set Includes Magnetic 1/4" Bit Holder & The Following 10 Bits:	lbs.
	No Ball End	.46
	Hex Metric: 3.0, 4.0, 5.0, 6.0mm	
	Hex Inch: 1/8, 9/64, 5/32, 3/16, 7/32, 1/4"	


[SHOP](#)


74989	Power Bit Belt Pack With Screw Holding Hex MagicRing Bits Set includes the following 10 bits:	lbs.
	Inch: 1/8, 9/64, 5/32, 3/16, 7/32, 1/4"	.34
	Metric: 3.0, 4.0, 5.0, 6.0mm	
74999	Power Bit Belt Pack With Ball End Screw Holding Hex Bits	lbs.
	Inch: 1/8, 9/64, 5/32, 3/16, 7/32, 1/4"	.37
	Metric: 3.0, 4.0, 5.0, 6.0mm	

Square Insert & Power Bits

The ideal multi-purpose tools to meet production requirements for both quality & performance

Highly resistant to wear and tear for a long tool life



Suitable for all applications for both manual and machine
Hardness HRC 59-61

Impact resistant modified CVM, tool steel, hardened

 Square





718 Square Insert Bits, 1/4"

Item No.	Size	mm	pkg.	lbs.
71801	1	25	10	.11
71802	2	25	10	.11
71803	3	25	10	.11



2 bit pack



718 Square Insert Bit Packs, 1"

CVM S2 modified tool steel.

Item No.	Size	mm	lbs.
71851	1	25	.03
71852	2	25	.03
71853	3	25	.03



2 bit pack



71854 Square Insert Bit Packs, 1" CVM

S2 modified tool steel. 3 pc. bit pack

71854 Set includes the following bits:

 Square:
wt. .04 1, 2, 3 x 1" (25mm)

Square Bits



748 Square Power Bits, 1/4" Hex Drive, Length 2.0"/50mm

Item No.	Size	mm	pkg.	lbs.
74813	1	50	10	.20
74816	2	50	10	.20
74819	3	50	10	.20





2 bit pack

748 Square Power Bit Packs, 2"

CVM S2 modified tool steel.

Item No.	Size	mm	lbs.
74860	1	50	.05
74861	2	50	.05
74862	3	50	.05







74890 Square Power Bit Packs, 2" CVM

S2 modified tool steel. Extra hard with natural finish. Exact fit machined tips. 3 pc. bit pack.

74890 Set includes the following bits:

 Square:
wt. .08 1, 2, 3 x 2.0" (50mm)





74895 Square Power Bit Packs, 2.0" CVM

S2 modified tool steel. Extra hard with natural finish. Exact fit machined tips. 6 pc. bit pack.

74895 Set includes the following bits:

 Square: 2 of each sizes
wt. 1.2 1, 2, 3 x 2.0" (50mm)

Slotted Bits

The ideal multi-purpose bits for all around quality & performance

Made in Germany - Production Quality

Highly resistant to wear and tear for a long tool life



Impact resistant modified CVM, tool steel, hardened

Suitable for all applications for both manual and machine
Hardness HRC 59-61

Wiha Slotted Insert Bits & Power Bits

 Slotted





710 Slotted Insert Bits, 1/4" Hex Drive, Length 25mm/.984"

Item No.	mm	Inch	mm	Inch	pkg.
71001	4.5	.177	0.6	.024	10
71004	5.5	.216	0.8	.030	10
71002	6.5	.255	1.2	.039	10
71003	8.0	.315	1.6	.063	10





740 Slotted Power Bits, 1/4" Hex Drive, Length 2.0"/50mm 10pk. weight .20 lbs.

Item No.	mm	Inch	mm	Inch	pkg.
74003	3.0	.118	0.5	.020	10
74006	3.5	.139	0.6	.024	10
74009	4.0	.157	0.5	.020	10
74010	4.0	.157	0.8	.030	10
74012	4.5	.177	0.6	.024	10
74015	5.5	.216	0.8	.032	10
74018	6.5	.255	1.2	.039	10
74021	8.0	.315	1.2	.039	10
74023	8.0	.315	1.6	.063	10

Wiha Slotted Insert & Power Bits


[SHOP](#)

720 Slotted Insert Bits. 5/16" Hex Drive, Length 41mm

Item No.	mm	Inch	mm	pkg.	lbs.
72048	6.5	.255	1.2	10	.27
72049	8.0	.315	1.6	10	.31
72050	10.0	.393	1.6	10	.46
72051	12.0	.472	2.0	10	.56


[SHOP](#)

720 Slotted Insert Bit Packs, 1"

CVM S2 modified tool steel. 5/16" Hex Drive.

Item No.	mm	mm	Inch	mm	lbs.
72025	1.2	6.5	.255	41	.06
72031	1.6	8.0	.315	41	.08
72039	1.6	10.0	.393	41	.10
72047	2.0	12.0	.472	41	.12


[SHOP](#)

710 Slotted Insert Bits. 1/4" Hex Drive, Length 1.54"/39mm 2 pc. Bit pack.

Item No.	mm	Inch	mm	Inch	pkg.
71030	3.0	.118	0.5	.020	2
71031	3.5	.139	0.6	.024	2
71032	4.0	.157	0.8	.031	2
71033	4.5	.177	0.6	.024	2
71034	5.5	.216	1.0	.039	2
71035	6.5	.255	1.2	.047	2
71036	8.0	.315	1.6	.063	2


[SHOP](#)

740 Slotted Power Bits, 1/4" Hex Drive, Length 2.75"/70mm

Item No.	mm	Inch	mm	Inch	pkg.
74033	2.5	.098	0.4	.015	1
74034	3.0	.118	0.5	.020	1
74035	3.5	.139	0.6	.024	1
74036	4.0	.157	0.8	.020	1
74039	5.5	.216	1.0	.032	1
74041	6.5	.255	1.2	.039	1


[SHOP](#)

743 Slotted and Phillips Double End Bits, 1/4" Hex Drive, Length 2.36"/60mm

Item No.	mm	Size	mm	pkg.	lbs.
74303	4.5 x 1	60	10	.22	
74306	5.5 x 2	60	10	.30	
74309	7.0 x 3	60	10	.30	


[SHOP](#)

710 Slotted Insert Bit Packs, 1" CVM S2 modified tool steel.

Item No.	mm	mm	Inch	mm	lbs.
71051	0.6	4.5	.177	25	.03
71052	0.8	5.5	.216	25	.03
71053	1.2	6.5	.255	25	.03
71054	1.6	8.0	.315	25	.03


[SHOP](#)

71055 Slotted Insert Bit Packs, 1" CVM S2 modified tool steel. Extra hard with natural finish. Exact fit machined tips. 3 pc. bit pack.

Set includes the following bits:

Item No.	mm	mm	Inch	mm	lbs.
71055	5.5, 6.5, 8.0	25	.04		


[SHOP](#)

74050 Slotted Power Bit Packs, 2" CVM

S2 modified tool steel. Extra hard with natural finish. Exact fit machined tips. 3 pc. bit pack.

Set includes the following bits:

Item No.	mm	mm	Inch	mm	lbs.
74050	4.5, 5.5, 6.5	50	.08		



2 bit pack

740 Slotted Power Bit Packs, 2"

CVM S2 modified tool steel.

Item No.	mm	mm	lbs.
74061	3.0	50	.05
74062	3.5	50	.05
74063	4.0	50	.05
74064	4.0	50	.05
74065	4.5	50	.05
74066	5.5	50	.05
74067	6.5	50	.06
74068	8.0	50	.08
74069	8.0	50	.08

[SHOP](#)

1/4" Stainless Steel Insert Bits


[SHOP](#)

701 Stainless Steel Slotted Insert Bits, 1/4" Hex Drive, Length 25mm/.984"

Item No.	mm	Inch	mm	Inch	pkg.
70130	4.5	.177	0.6	.024	1
70131	5.5	.216	0.8	.030	1
70132	6.5	.255	1.2	.039	1
70133	8.0	.315	1.6	.063	1

30 Piece Contractor Grade Bits

725 Slotted Insert Contractor Grade, 1/4"

Item No.	Size	mm	pkg.	lbs.
72534	4.5	25	30 pc	.85
72535	5.5	25	30 pc	.85
72536	6.0	25	30 pc	.85

Pozidriv® Bits

The ideal multi-purpose tools to meet production requirements for both quality and performance

Impact resistant
modified CVM, tool
steel, hardened



Pozidriv®



Suitable for all applications
for both manual and machine
Hardness HRC 59-61



742 Pozidriv® Power Bits. 1/4" Hex Drive, Length 2.0"/50mm

Item No.	Size	mm	pkg.	lbs.	SHOP
74203	1	50	10	.24	
74212	2	50	10	.25	
74221	3	50	10	.26	

PoziDriv® Insert & Power Bits



[SHOP](#)

712 Pozidriv® Insert Bits, 1/4"

Item No.	Size	mm	pkg.	lbs.
71200	0	25	10	.10
71201	1	25	10	.10
71202	2	25	10	.10
71203	3	25	10	.10



742 Pozidriv® Power Bits. 1/4" Hex Drive, Length 3.5"/90mm

Item No.	Size	mm	pkg.	lbs.	SHOP
74207	1	90	10	.34	
74216	2	90	10	.46	
74225	3	90	10	.53	



2 bit
pack

[SHOP](#)

742 Pozidriv® Power Bit Packs, 2"

CVM S2 modified tool steel.

Item No.	Size	mm	lbs.
74261	1	50	.06
74262	2	50	.06
74263	3	50	.07



2 bit
pack

[SHOP](#)

712 Pozidriv® Insert Bit Packs, 1"

CVM S2 modified tool steel.

Item No.	Size	mm	lbs.
71250	0	25	.03
71251	1	25	.03
71252	2	25	.03
71253	3	25	.04



742 Pozidriv® Power Bits. 1/4" Hex Drive, Length 2.75"/70mm

Item No.	Size	mm	pkg.	SHOP
74201	0	70	1	
74205	1	70	1	
74214	2	70	1	

Wiha Stainless Steel Pozidriv® Insert & Power Bits



[SHOP](#)

71254 Pozidriv® Insert Bit Packs, 1" CVM

S2 modified tool steel. Extra hard with natural finish. Exact fit machined tips. 3 pc. bit pack.

71254 Set includes the following bits:

 Pozidriv®:
wt. .04 1, 2, 3 x 1" (25mm)



[SHOP](#)

712 Stainless Steel Pozidriv® Insert Bits, 1/4"

Item No.	Size	mm	pkg.
71241	1	25	1
71242	2	25	1
71243	3	25	1



[SHOP](#)

704 Stainless Steel Pozidriv® Power Bits. 1/4" Hex Drive, Length 2.0"/50mm

Item No.	Size	mm	pkg.
70407	1	50	1
70408	2	50	1
70410	3	50	1

Specialty Bits

Highly resistant to wear and tear for a long tool life



Tri-Wing

Torq Set

Suitable for all applications for both manual and machine Hardness HRC 59-61

Tri-Wing Bits



719 Triwing Insert Bits, 1/4"/25mm

Item No.	Size	mm	pkg.	lbs.
71900	0	25	10	.10
71901	1	25	10	.10
71902	2	25	10	.10
71903	3	25	10	.10
71904	4	25	10	.13
71905	5	25	10	.13



749 Tri-Wing Power Bits, 1/4"/50mm

Item No.	Size	mm	pkg.	lbs.
74901	3	50	10	.24
74902	4	50	10	.24
74903	5	50	10	.24
74904	6	50	10	.46



719 Tri-Wing Insert Bit Packs, 1"

Item No.	Size	mm	lbs.
71949	0	25	.03
71950	1	25	.03
71951	2	25	.03
71952	3	25	.03
71953	4	25	.03
71913	5	25	.04



749 Tri-Wing Power Bit Packs, 2"

Item No.	Size	mm	lbs.
74960	3	50	.06
74961	4	50	.06
74962	5	50	.06
74963	6	50	.10



71954 Tri-Wing Insert Bit Packs, 1"

6 pc. bit pack.

71954 Set includes the following bits:

Triwing: 0, 1, 2,
wt. .07 3, 4, 5 x 1" (25mm)

Torq Set Bits



719 Torq Set Insert Bits, 1/4"

Item No.	Size	mm	pkg.	lbs.
71921	0	25	10	.10
71922	1	25	10	.10
71923	2	25	10	.10
71924	3	25	10	.10
71907	4	25	10	.10
71909	5	25	10	.10
71906	6	25	10	.10
71908	8	25	10	.13
71910	10	25	10	.13



749 Torq Set Power Bits, 1/4"/50mm

Item No.	Size	mm	pkg.	lbs.
74911	4	50	10	.03
74912	5	50	10	.03
74913	6	50	10	.03
74914	8	50	10	.04
74915	10	50	10	.04



719 Torq Set Insert Bit Packs, 1"

CVM S2 modified tool steel.

Item No.	Size	mm	lbs.
71911	4	25	.03
71912	5	25	.03
71957	6	25	.03
71958	8	25	.04
71959	10	25	.04



749 Torq Set Power Bit Packs, 2"

CVM S2 modified tool steel.

Item No.	Size	mm	lbs.
74964	4	50	.06
74965	5	50	.06
74966	6	50	.06
74967	8	50	.07
74968	10	50	.07

Specialty Bits

Highly resistant to wear and tear for a long tool life



 Spanner

Suitable for all applications for both manual and machine Hardness HRC 59-61

Spanner Bits



 SHOP

719 Spanner Insert Bits, 1/4"

Item No.	Size	mm	pkg.	lbs.
71914	4	25	10	.11
71916	6	25	10	.12
71918	8	25	10	.12
71920	10	25	10	.12



2 bit pack

719 Spanner Insert Bit Packs, 1"

CVM S2 modified tool steel.

Item No.	Size	mm	lbs.
71963	4	25	.03
71964	6	25	.03
71965	8	25	.04
71966	10	25	.04

 SHOP

XZN Insert Bits

Specialty Bits

Suitable for all applications for both manual and machine Hardness HRC 59-61

Highly resistant to wear and tear for a long tool life



Impact resistant modified CVM, tool steel, hardened

 Triple Square



2 bit pack

701 XZN Insert Bits, 1/4"

Item No.	Size	mm	pkg.	lbs.
70143	M3	25	2	.04
70144	M4	25	2	.04
70145	M5	25	2	.04
70146	M6	25	2	.04
70147	M8	25	2	.04

 SHOP



355 XZN Triple Square L-key

Item No.	Size	mm	pkg.	lbs.
35510	M10	110	1	.01
35512	M12	124	1	.02
35514	M14	138	1	.04
35516	M16	156	1	.07

 SHOP

Countersink & Drill Bits

High quality HSS steel, ground with radial relief. Universal application in metal, plastic and wood. Guarantees outstanding chip removal, chatter free operation & smooth surface finish.

90° Countersink Bit - 1/4" Shank



 SHOP

786 HSS 1/4" Drive Countersinks

High quality HSS steel, ground with radial relief. 1/4" Hex shank according to DIN 3126 C 6.3.

Item No.	Size	Inch	mm	Inch	size	pkg
78615	6.3	.26	35	1.38	M3	1
78617	8.3	.33	35	1.38	M4	1
78619	10.4	.41	35	1.38	M5	1
78621	12.4	.49	35	1.38	M6	1
78622	16.5	.65	35	1.38	M8	1
78624	20.5	.81	35	1.38	M10	1

1/4" Shank High Speed Drill Bits



 SHOP

780 1/4" Shank Stubby High Speed Drill Bits

DIN 3126 C 6.3.

Item No.	Size	Inch	pkg	lbs.
78002	1/16	1.26	1	.02
78005	3/32	1.41	1	.02
78008	1/8	1.57	1	.02
78011	5/32	1.73	1	.03
78015	3/16	1.97	1	.03
78018	1/4	1.97	1	.03

High Precision Tool Holder For Countersinks & Drill Bits



Quick release tool holder for Drills, Countersinks & Power bits

71480 CentroFix Bit Holder

Item No.	Size	Size	mm	Inch	lbs.
71480	1/4"	1/4"	60	2.3	.09

 SHOP


Dura Torsion Insert and Power Bits

Carbide Coated

Positive location in the screw head with decrease of:

- necessary pressure forces
- working time
- costs
- wear & tear of bits & screw heads
- anti-cam-out effect

With the Dura bit Wiha has again proved it's power of innovation. The extra hard, elastic Quattro Torsion bit is equipped with an extremely wear resistant tungsten carbide coating that grips the screw head.



SHOP

710 Dura Bits, Slotted, 1/4"

Item No.	mm	Inch	mm	Inch	mm
71010	0.6	.024	4.5	.177	25
71011	0.8	.030	5.5	.216	25
71012	1.0	.039	5.5	.216	25
71013	1.2	.039	6.5	.255	25
71014	1.2	.039	8.0	.315	25



SHOP

715 Dura Bits, TORX®, 1/4"

Item No.	Size	mm	lbs.
71574	T10	25	.02
71576	T15	25	.02
71578	T20	25	.02
71580	T25	25	.02
71582	T30	25	.02
71584	T40	25	.03



SHOP

711 Dura Bits, Phillips, 1/4"

Item No.	Size	mm	lbs.
71111	1	25	.02
71112	2	25	.02
71113	3	25	.02



SHOP

712 Dura Bits, Pozidriv, 1/4"

Item No.	Size	mm	lbs.
71211	1	25	.02
71212	2	25	.02
71213	3	25	.02



SHOP

741 Dura Phillips Power Bits 1/4" Hex Drive, Length 2.0"/50mm

Item No.	Size	mm	lbs.
74141	1	50	.04
74142	2	50	.04
74143	3	50	.04



SHOP

742 Dura Pozidriv® Power Bits 1/4" Hex Drive, Length 2.0"/50mm

Item No.	Size	mm	lbs.
74241	1	50	.04
74242	2	50	.04
74243	3	50	.04



Bits Tungsten Carbide Coated

SHOP

71094 Bit-Selector With Dura Insert 1/4" Bits. Set Includes Magnetic 1/4" Bit Holder & The Following 10 Bits:

- Slotted: 5.5, 6.5, 8.0mm
- Phillips: 1, 2, 3
- TORX®: T10, T15, T20, T25
- .29 lbs.

Diamond Torsion Insert and Power Bits

Diamond bits supplement Wiha's range of high-quality special bits. When used with machines, the increased tool life of the Wiha Diamond bit reduces cost.

- High wear resistance
- Micro particle coating with sapphire and diamond contents
- Optimized torsion zone

Reduction of:

- pressure forces to be applied
- wear and tear of bit and screw head
- working time & costs
- Cam-out effect



The ideal bit even for the most difficult of applications



SHOP

710 Diamond Bits, Slotted, 1/4"

Item No.	mm	Inch	mm	Inch	mm
71020	4.5	.177	0.6	.024	25
71021	5.5	.216	0.8	.030	25
71022	5.5	.216	1.0	.039	25
71023	6.5	.255	1.2	.039	25
71024	8.0	.315	1.2	.063	25



SHOP

715 Diamond Bits, TORX®, 1/4"

Item No.	Size	mm	lbs.
71516	T10	25	.02
71517	T15	25	.02
71518	T20	25	.02
71519	T25	25	.02
71521	T30	25	.02
71522	T40	25	.03



SHOP

711 Diamond Bits, Phillips, 1/4"

Item No.	Size	mm	lbs.
71181	1	25	.02
71182	2	25	.02
71183	3	25	.02



SHOP

741 Diamond Phillips Power Bits 1/4" Hex Drive, Length 2.0"/50mm

Item No.	Size	mm	lbs.
74161	1	50	.03
74162	2	50	.03
74163	3	50	.04



SHOP

71197 PokitPak - Diamond Coated Insert Bits In Molded Case. 6 - 1/4" Insert Bits

- Slotted: 5.5, 6.5mm
- Phillips: #1, 3 & 2/each #2
- .16 1/4" Magnetic Bit Holder



SHOP

712 Diamond Bits, Pozidriv®, 1/4"

Item No.	Size	mm	lbs.
71221	1	25	.02
71222	2	25	.02
71223	3	25	.02

Wiha TiN Coated Insert/Power Bits

The abbreviation TiN stands for Titanium-Nitride, which has a hardness up to 85 HRC. This coating guarantees a high wear and tear resistance.



- Tough, hard torsion quality with very hard TiN coating
- Optimized torsion zone
- High wear resistance


[SHOP](#)

711 Phillips TiN Coated Insert Bits, 1/4"

Item No.	Size	mm	lbs.
71121	1	25	.02
71122	2	25	.02
71123	3	25	.02

TiN - Titanium Nitride

Wear Characteristics

Wiha TiN Coated Bit

Wiha Diamond Bit

Wiha Dura Bit

Titanium Coated


[SHOP](#)

715 TORX® TiN Coated Insert Bits, 1/4"

Item No.	Size	mm	lbs.
71585	T5	25	.02
71586	T6	25	.02
71587	T7	25	.02
71588	T8	25	.02
71562	T9	25	.02
71563	T10	25	.02
71564	T15	25	.02
71565	T20	25	.02
71566	T25	25	.02
71569	T27	25	.02
71567	T30	25	.02
71568	T40	25	.02

TiN - Titanium Nitride



741 Phillips TiN Coated Power Bits 1/4" Hex Drive, Length 2.0"/50mm

Item No.	Size	mm	lbs.
74101	1	50	.04
74105	2	50	.04
74108	3	50	.04

TiN - Titanium Nitride



711 Phillips TiN Coated Insert Bits 1/4" Hex Drive, Length 2.0"/50mm

Item No.	Size	mm	lbs.
71141	1	50	.04
71142	2	50	.04
71143	3	50	.04

TiN - Titanium Nitride


[SHOP](#)

71196 PokitPak - Phillips TiN Coated Insert Bits In Molded Case -

Set Includes 6 - 1/4" Insert Bits

Phillips: 2 of each - 1, 2, 3

lbs. .31

TiN - Titanium Nitride

[SHOP](#)

71194 PokitPak - Phillips TiN Coated Insert Bits In Molded Case -

Set Includes 6 - 1/4" Insert Bits

Phillips: 1 of each - #1, #3

Phillips: 4 of - #2

lbs. .31

TiN - Titanium Nitride


[SHOP](#)

71596 PokitPak - TORX® Dura Insert Bits In Molded Case -

Set Includes 6 - 1/4" Insert Bits

T10, T15, T20, T25, T30, T40

lbs. .26

TiN - Titanium Nitride

Wiha Security Bits Collector With Extra Fine 72 Tooth Ratchet

72



Low profile 72 tooth



Fast action thumb ring


[SHOP](#)


71988 Bits Collector with Security TORX®, Tri-Wing, Torq Set, Spanner, Security Hex, Slotted, Phillips, Pozidriv® and Square Bits.

38 Piece Set includes: 1/4" Bit Holding Ratchet, 1/4" magnetic bit holder, storage box and 1/4" Insert bits:

- Security TORX®: T8s, T10s, T15s, T20s, T25s, T27s, T30s, T40s
- Security Hex: 5/64, 3/32, 7/64, 1/8, 9/64, 5/32"
- Tri-Wing: 1, 2, 3, 4
- Torq Set: 6, 8, 10
- Spanner: 4, 6, 8, 10
- Slotted: 6.5, 8.0mm
- Phillips: 1, 2
- Pozidriv®: 0, 1, 2, 3
- Square: 1, 2, 3
- lbs. .88

Wiha Security Bits Collector



[SHOP](#)

71990 Bits Collector with Security **TORX**®, Tri-Wing, Torq Set, Spanner, Security Hex, Slotted, Phillips, Pozidriv® and Square bits.

39 Piece Set includes: Handle, 1/4" magnetic bit holder, 1/4" Bit holding socket adapter, storage box and the following 1/4" bits:

- ✱ Security **TORX**®:
T8s, T10s, T15s, T20s, T25s, T27s, T30s, T40s
- ⬢ Security Hex: 5/64, 3/32, 7/64, 1/8, 9/64, 5/32"
- ⚙ Tri-Wing: 1, 2, 3, 4
- ⊕ Torq Set: 6, 8, 10
- ⊖ Spanner: 4, 6, 8, 10
- ⦶ Slotted: 6.5, 8.0mm
- ⊕ Phillips: 1, 2
- ⦶ Pozidriv®: 0, 1, 2, 3
- ⦶ Square: 1, 2, 3
- ⚖ lbs. 1.03



With Quick Release Holder

[SHOP](#)

71991 Bits Collector with Security **TORX**®, Tri-Wing, Torq Set, Spanner, Security Hex, Slotted, Phillips, Pozidriv® and Square bits.

39 Pc. Set includes: Handle, Clicfix quick release bit holder 1/4" Bit holding socket adapter, storage box and the following 1/4" bits:

- ✱ Security **TORX**®:
T8s, T10s, T15s, T20s, T25s, T27s, T30s, T40s
- ⬢ Security Hex: 5/64, 3/32, 7/64, 1/8, 9/64, 5/32"
- ⚙ Tri-Wing: 1, 2, 3, 4
- ⊕ Torq Set: 6, 8, 10
- ⊖ Spanner: 4, 6, 8, 10
- ⦶ Slotted: 6.5, 8.0mm
- ⊕ Phillips: 1, 2
- ⦶ Pozidriv®: 0, 1, 2, 3
- ⦶ Square: 1, 2, 3
- ⚖ lbs. 1.04

71992 Bits Collector with Security 1/4" Insert bits. 29 Piece Set

Set includes: 1/4" Bit Holder, 1/4" Bit holding socket adapter, 1/4" Universal Magnetic Bit Holder, storage box and the following 1/4" bits:

- Security **TORX**®: T9s, T10s, T15s, T20s, T25s, T27s, T30s, T40s
- Security Hex: 1/8, 3/32, 7/64, 9/64, 5/32, 3/16, 7/32, 1/4"
- Tri-Wing: 4, 5 & Torq Set: 5, 8 & Spanner: 6, 8, 10
- Square: 1, 2 & Pozidriv®: 2

⚖ lbs. .99

[SHOP](#)



[SHOP](#)

71994 Bits Collector with **TORX**®, Slotted, Phillips, Pozidriv®, Square and Hex Inch bits. 26 Piece Set

Set includes: Handle, 1/4" bit holder, storage box and the following 1/4" bits:

- ✱ **TORX**®: T8, T10, T15, T20, T25, T27, T30, T40
- ⦶ Slotted: 4.5, 5.5, 6.0mm
- ⊕ Phillips: 1, 2
- ⦶ Pozidriv®: 1, 2, 3
- ⦶ Square: 1, 2
- ⬢ Hex Inch: 1/16, 5/64, 3/32, 1/8, 5/32, 3/16"
- ⚖ lbs. .89

Drive-Loc VI Adjustable



Adjustable locking
(7/8" - 3 1/2" in
1/8" increments)

[SHOP](#)

71997 Drive-Loc VI Bits Collector with Security **TORX**®, Tri-Wing, Torq Set, Spanner, Security Hex, Slotted, Phillips, Pozidriv® and Square bits. 39 Piece Set

Set includes: Drive-Loc VI handle & 4" Bit holder, socket, storage box and the following 1/4" bits:

- ✱ Security **TORX**®:
T8s, T10s, T15s, T20s, T25s, T27s, T30s, T40s
- ⬢ Security Hex: 5/64, 3/32, 7/64, 1/8, 9/64, 5/32"
- ⚙ Tri-Wing: 1, 2, 3, 4
- ⊕ Torq Set: 6, 8, 10
- ⊖ Spanner: 4, 6, 8, 10
- ⦶ Slotted: 6.5, 8.0mm
- ⊕ Phillips: 1, 2
- ⦶ Pozidriv®: 0, 1, 2, 3
- ⦶ Square: 1, 2, 3
- ⚖ lbs. 1.05

[SHOP](#)

71095 Bits Collector with Phillips & Hex Inch bits. 51 Piece Set

Set includes: ClicFix Quick Release Bit Holder storage box and the following 1/4" bits:

- ⊕ 10 Each Phillips: 1, 2 & 5 Phillips: 3
- ⬢ 10 Each Hex Inch: 1/8, 3/16" & 5 Hex Inch: 5/32"
- ⚖ lbs. 1.24

Wiha BitFlip Sets - Insulated & Standard

"8 In 1 Bit Sets"

BitFlip standard SoftFinish® handle, multi-component, cushion grip, easy access & 8 bit storage



Blade CVM tool steel, hardened

BitFlip Insulated

Each insulated tool individually tested to 10,000 volts

BitFlip Insulated



BitFlip Standard



38016 Slotted/Phillips/Square BitFlip Insulated

Wiha cushion grip handle and insulated shaft. Tested to 10,000 volts.

Set includes the following 1/4" bits:

- ↓  **Slotted:** 4.5, 6.5mm
- ↓  **Phillips:** 0, 1, 2, 3
- ↓  **Square:** 1, 2



lbs.

.45



38026 Slotted/Phillips/Square BitFlip Standard

with Wiha cushion grip handle and CVM tool steel shaft.

Set includes the following 1/4" bits:

- ↓  **Slotted:** 4.5, 6.5mm
- ↓  **Phillips:** 0, 1, 2, 3
- ↓  **Square:** 1, 2



lbs.

.44



BitFlip Insulated



BitFlip Standard



38017 Slotted/Phillips/TORX® BitFlip Insulated

Wiha cushion grip handle and insulated shaft. Tested to 10,000 volts.

Set includes the following 1/4" bits:

- ↓  **Slotted:** 4.5, 6.5mm
- ↓  **Phillips:** 1, 2
- ↓  **TORX®:** T10, T15, T20, T25



lbs.

.45



38027 Slotted/Phillips/TORX® BitFlip Standard

with Wiha cushion grip handle and CVM tool steel shaft.

Set includes the following 1/4" bits:

- ↓  **Slotted:** 4.5, 6.5mm
- ↓  **Phillips:** 1, 2
- ↓  **TORX®:** T10, T15, T20, T25



lbs.

.44



BitFlip Insulated



BitFlip Standard



38018 Slotted/Phillips BitFlip Insulated

Wiha cushion grip handle and insulated shaft. Tested to 10,000 volts.

Set includes the following 1/4" bits:

- ↓  **Slotted Sizes:** 4.5, 5.5, 6.5, 8.0mm
- ↓  **Phillips Sizes:** 0, 1, 2, 3



lbs.

.45



38028 TORX® BitFlip Standard

with Wiha cushion grip handle and insulated shaft.

Set includes the following 1/4" bits:

- ↓  **TORX®:** T8, T10, T15, T20, T25, T27, T30, T40




lbs.

.44



Wiha Bit Selectors

Compact size and easy bit selection make the Bit Selector an ideal maintenance tool



Plastic storage box is compact, durable and light weight

Slide out drawer allows quick bit access and secure storage



Molded hex cavity in box end
Magnetic adapter fits into opening so tool case can be used as a handle on quick fastening jobs

1/4" Magnetic Adapter fits all standard 1/4" bits

792 Sets Bit-Selector Sets

These handy sets include 10 hardened bits of chrome-vanadium-molybdenum steel. 1/4" magnetic bit holder can be used in power tools. Plastic storage box is compact, durable and light weight. Molded hex cavity turns box into handle for quick fastening jobs. Quick bit access with slide out drawer. Packaged in clear blister pack.



[SHOP](#)

79243 Bit-Selector With Slotted, Phillips and TORX® Bits Set Includes 1/4" Bit Holder

↓	Slotted: 4.5, 5.5, 6.0mm	.31
+	Phillips: 0, 1, 2, 3	
✳	TORX®: T10, T15, T20	

79248 Bit-Selector With Slotted, Phillips and Square Bits Set Includes 1/4" Bit Holder

↓	Slotted: 4.5, 5.5, 6.0mm	.32
+	Phillips: 0, 1, 2, 3	
□	Square: 1, 2, 3	

71090 Bit-Selector With Slotted, Phillips & Hex 1/4" Bits Set Includes Magnetic 1/4" ClicFix Bit Holder

↓	Slotted: 4.5, 5.5, 6.5	.25
+	Phillips: 1, 2, 3	
⬢	Hex Inch: 1/8, 5/32, 3/16	

Wiha XSelector & XLSelector Bit Sets

Compact size and easy bit selection make the Wiha XSelector an ideal maintenance tool



Easy bit access with hinged cover

XLSelector
Pocket Sized
5.3" x 3.1" x .7"



XSelector Pocket Sized
3 1/8" x 2 1/8" x 1/2"

Sets include
Clicfix quick release holder



These handy sets include 10 hardened bits of CVM steel. 1/4" Quick Release holder can be used in power tools. Quick bit access through integrated bit-clamp.

[SHOP](#)

79443 XSelector Bit Set With Slotted, Phillips, and TORX® Bits Set Includes Quick Release Holder & the following 10 bits:

↓	Slotted: 5.5, 6.5, 8.0mm	
+	Phillips: 0, 1, 2, 3	lbs.
✳	TORX®: T10, T15, T20	.27

Wiha XLSelector 31 Piece Bit Sets



[SHOP](#)

79495 XLSelector Bit Set With Slotted, Phillips, TORX®, Hex Bits

31 Piece Set Includes:	
Universal Bit Holder-magnetic & 30 Insert Bits:	lbs. .29
 Slotted: 4.5, 5.5, 6.0mm	 Phillips: 0, 1, 2, 3
 TORX® : T6, T7, T8, T9, T10, T15, T20, T25	
 Metric Hex : 2.0, 2.5, 3.0, 4.0, 5.0, 6.0mm	
 Inch Hex : 5/64, 3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4"	



[SHOP](#)

79490 XLSelector Security Bit Set

31 Piece Set Includes:	
Universal Bit Holder-magnetic	lbs.
and the following 30 bits:	.28
 Slotted: 6.5mm	 Phillips: 1, 2
 Security TORX®: T8s, T10s, T15s, T20s, T25s	
 Security Hex: 5/64, 3/32, 7/64, 1/8, 9/64, 5/32, 3/16"	
 Spanner: 4, 6, 8, 10	 Torq Set: 6, 8, 10
 Square: 1, 2	 Pozidriv: 1, 2
 Triwing: 2, 3, 4, 5	

Wiha Multi-Bit Screwdrivers

Six Tools in One!

1/4" Magnetic Bit Holder
 directs magnetism through
 the bit for powerful screw holding

Cap rotates
 eliminating palm blisters
Allows one handed
 turning & frees other hand for
 positioning the work piece

Ergonomic Powerhandle
 for maximum comfort and
 exceptional torque

Cap snaps
 on & off, doesn't unscrew
 while you're using the tool

Chambered Bit Storage

- In the handle
- Turn the transparent selector to the bit you need
- No time wasted fumbling or sorting to find the right bit


[SHOP](#)

38006 Slotted/Phillips Multi-Bit Screwdriver with Wiha Powerhandle and insulated shaft. **Set includes the following 1/4" bits:**

↓ ↻	Slotted: 5.5, 6.0mm	↔	lbs.
⊕	Phillips: 0, 1, 2, 3		.39

38007 Slotted/Phillips/Square Multi-Bit Screwdriver with Wiha Powerhandle and insulated shaft. **Set includes the following 1/4" bits:**

↓ ↻	Slotted: 6.5, 8.0mm	↔	lbs.
⊕	Phillips: 1, 2		
□	Square: 1, 2		.41

Wiha ClicFix Quick Release Magnetic Sets


[SHOP](#)

38033 Slotted/Phillips & ClicFix Quick Release Magnetic Bit Holder
 7 Pc. Set with Wiha Powerhandle and CVM steel, hardened shaft.

Set includes the following 1/4" bits:		↔	lbs.
↓ ↻	Slotted: 6.5, 8.0mm		
⊕	Phillips: 0, 1, 2, 3		.43

38059 Slotted/Phillips & ClicFix Quick Release Magnetic Bit Holder
 7 Pc. Set with Wiha Powerhandle and CVM steel, hardened shaft.

Set includes the following 1/4" bits:		↔	lbs.
↓ ↻	Slotted: 4.5, 5.5, 6.5mm		
⊕	Phillips: 1, 2, 3		.43

Wiha Cushion Grip Stubby Bit Sets

Stubby 6 in 1 Multi-Bit Driver Sets

Ergo soft grip
handles

Stainless steel
bit holder

Bits hardened for
extreme durability

Just 2.5" over all length


[SHOP](#)

38043 SoftFinish® CushionGrip Stubby Bit Holder
 with Wiha cushion grip handle and CVM tool steel shaft.

Set includes the following 1/4" bits:

↓ ↻	Slotted: 4.5, 6.5	↔	lbs.
⊕	Phillips: #1, #2		
⊕	Pozidriv®: #1, #2		.20


[SHOP](#)

38048 SoftFinish® CushionGrip Stubby Bit Holder
 with Wiha cushion grip handle and CVM tool steel shaft.

Set includes the following 1/4" bits:

↓ ↻	Slotted: 4.5, 6.5	↔	lbs.
⊕	Phillips: #1, #2		
□	Square: #1, #2		.20

Wiha ClicFix Quick Release Magnetic Holder


[SHOP](#)

38030 ClicFix Quick Release Magnetic Bit Holder

Blade high alloy chrome-vanadium-molybdenum steel, hardened, chrome-plated. Wiha Powerhandle high quality plastic, impact resistant.

Item							
No.	Size	mm	Inch	mm	Inch	lbs	pkg.
38030	1/4"	120	4.7	230	9.0	.27	10

- ⬇️ **Slotted:** 3.0, 4.5, 5.5, 6.5mm
- ⬆️ **Phillips:** 1, 2, 3
- ⬇️ **Square:** 1, 2, 3

Wiha Adjustable TorqueControl Tool Sets In Durable Storage Box



With Certificate
of Calibration



28590 24 Piece TorqueVario-S Micro-Bit Set

Certified to EN ISO 6798, BS EN 26789, ASME B107.14M. Set includes ergonomic multi-component adjustable TorqueVario-S handle, 21 Micro Bits, Micro Bit holder and Torque adjustment tool. Packed in a compact durable storage box.

Item No.		
28590	Slotted: 1.5, 2.0, 3.0, 4.0mm Phillips: #00, #0, #1	lbs.
	TORX®: T6, T7, T8, T9, T10, T15	1.33
	Hex Inch: .050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32	
	28504 - Handle Range 7.5 - 20 Inch lbs.	



With Certificate
of Calibration



28593 24 Piece TorqueVario-S Micro-Bit Set

Certified to EN ISO 6798, BS EN 26789, ASME B107.14M. Set includes ergonomic multi-component adjustable TorqueVario-S handle, 21 Micro Bits, Micro Bit holder and Torque adjustment tool. Packed in a compact durable storage box.

Item No.		
28593	Slotted: 1.5, 2.0, 3.0, 4.0mm Phillips: #00, #0, #1	lbs.
	TORX®: T6, T7, T8, T9, T10, T15	1.33
	Hex Inch: .050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32	
	28501 - Handle Range 15-80 Inch/oz (+/- 10%)	

53 Piece Set



With Certificate
of Calibration




28595 53 Piece TorqueVario-S Bit Set, In Storage Box

Certified to EN ISO 6798, BS EN 26789, ASME B107.14M. Set includes ergonomic multi-component adjustable TorqueVario-S handle, 50 Insert bits, 1/4" Bit holder and Torque adjustment tool.

Item No.		
28595	Slotted: 4.5, 5.5, 6.5, 8.0mm	lbs.
	Phillips: #0, #1, #2, #3	2.85
	TORX®: T6, T7, T8, T9, T10, T15, T20, T25, T27, T30	
	Hex Inch: 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32, 3/16"	
	Hex Metric: 1.5, 2.0, 2.5, 3.0, 4.0, 5.0, 6.0, 8.0mm	
	Pozidriv: #0, #1, #2, #3	
	Torq Set: #4, #5, #6, #8	
	Square: #1, #2, #3	
	Triwing: #0, #1, #2, #3, #4	
	28506 - Handle Range 10 - 50 Inch lbs.	
	28581 - 1/4" Bit Holder	

59 Piece Set



With Certificate
of Calibration



28589 59 Piece TorqueVario-S Bit Set, In Storage Box

Certified to EN ISO 6798, BS EN 26789, ASME B107.14M. Set includes 3 ergonomic multi-component adjustable TorqueVario-S handles, 39 Insert bits, 15 Sockets, 1/4" Bit holder, 1/4" Hex to 1/4" Square adapter and Torque adjustment tool.

Item No.		
28589	Slotted: 4.5, 5.5, 6.5mm	lbs.
	Phillips: #0, #1, #2	2.58
	TORX®: T5, T6, T7, T8, T9, T10, T15, T20, T25, T30	
	Hex Inch: .050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4"	
	Hex Metric: 1.5, 2.0, 2.5, 3.0, 4.0, 5.0, 6.0mm	
	Pozidriv: #1, #2	
	Square: #1, #2, #3	
	Inch Sockets: 5/32, 3/16, 7/32, 1/4, 9/32, 5/16, 3/8"	
	Metric Sockets: 4.0, 4.5, 5.0, 5.5, 6.0, 7.0, 8.0mm	
	3 Handles: 15-80 Inch/oz., 5-10 & 10-50 Inch lbs.	
	1/4" Bit Holder & 1/4" Hex to 1/4" Square adapter	

Wiha SYSTEM 4 Micro Bits

SYSTEM 4 Handles & Micro Bits

Tips Exact
fit, precision
machined

Rotating Cap
for precise
turning and
control

Tapered Handle
allows rapid rotation,
requires less clearance

Bits CVM steel,
hardened

Use bits directly in handle or with 4" bit extension



[SHOP](#)

750 SYSTEM 4 Slotted Bits

High alloy CVM steel, hardened, on 4 mm hex stock.

Item			
No.	mm	mm	Inch lbs.
75008	0.8	28	1.1 .01
75012	1.2	28	1.1 .01
75015	1.5	28	1.1 .01
75018	1.8	28	1.1 .01
75020	2.0	28	1.1 .01
75025	2.5	28	1.1 .01
75030	3.0	28	1.1 .01
75035	3.5	28	1.1 .01
75040	4.0	28	1.1 .01



[SHOP](#)

751 SYSTEM 4 Phillips Bits

High alloy chrome-vanadium-molybdenum steel, hardened, on 4 mm hex stock.

Item			
No.	Size	mm	Inch lbs.
75105	000	28	1.1 .01
75110	00	28	1.1 .01
75115	0	28	1.1 .01
75120	1	28	1.1 .01



[SHOP](#)

753 SYSTEM 4 Hex Metric Bits

High alloy CVM steel, hardened, on 4 mm hex stock.

Item			
No.	mm	mm	Inch lbs.
75307	.7	28	1.1 .01
75309	.9	28	1.1 .01
75313	1.3	28	1.1 .01
75315	1.5	28	1.1 .01
75320	2.0	28	1.1 .01
75325	2.5	28	1.1 .01
75330	3.0	28	1.1 .01
75340	4.0	28	1.1 .01




[SHOP](#)

753 SYSTEM 4 Hex Inch Bits

High alloy chrome-vanadium-molybdenum steel, hardened, on 4 mm hex stock.

Item			
No.	Inch	mm	Inch lbs.
75307	.028	28	1.1 .01
75309	.035	28	1.1 .01
75313	.050	28	1.1 .01
75350	1/16	28	1.1 .01
75352	5/64	28	1.1 .01
75354	3/32	28	1.1 .01
75356	7/64	28	1.1 .01
75358	1/8	28	1.1 .01
75360	9/64	28	1.1 .01
75340	5/32	28	1.1 .01



[SHOP](#)

75800 SYSTEM 4 Standard Precision Micro Bit Handle

Rotating control cap for precise turning and control. Wiha Precision handle, tapered, high quality plastic, impact resistant, ball retainer. Accepts all SYSTEM 4 Series bits. 110mm/4.3" OAL

Item					
No.	mm	Inch	mm	Inch	lbs.
75800	4.0	.1574	14.0	.55	.06



[SHOP](#)

75801 SYSTEM 4 ESD Safe Dissipative Precision Bit Handle

with rotating control cap. Wiha precision handle, tapered, high quality plastic, impact resistant. **Advantages:**

- For working in ESD sensitive applications
Surface resistant 10^6 - 10^9 Ohms
- Ball retainer holds bits securely in place
- Accepts all SYSTEM 4 Series bits
- 110mm/4.3" OAL

Item					
No.	mm	Inch	mm	Inch	lbs.
75801	4.0	.1574	14.0	.55	.06

SYSTEM 4 Micro Bit Extension Blades



[SHOP](#)

75900 Extension blade for SYSTEM 4 Micro Bits

Shaft CVM steel, hardened, corrosion protected. Ball retainer bit extension for 4 mm bits.

Item				
No.	Size	mm	mm	lbs.
75900	4.0	100	4.0	.07



[SHOP](#)

75901 Magnetic Bit extension blade for SYSTEM 4 Micro Bits

Shaft CVM steel, hardened, corrosion protected. Magnetic bit holder.

Item				
No.	Size	mm	mm	lbs.
75901	4.0	100	4.0	.04

Wiha SYSTEM 4 Micro Bits



757 SYSTEM 4 TORX® Bits

High alloy CVM steel, hardened, on 4 mm stock.

Item No.	Size	mm	Inch	lbs.
75703	T3	28	1.1	.01
75704	T4	28	1.1	.01
75705	T5	28	1.1	.01
75706	T6	28	1.1	.01
75707	T7	28	1.1	.01
75708	T8	28	1.1	.01
75709	T9	28	1.1	.01
75710	T10	28	1.1	.01
75715	T15	28	1.1	.01
75720	T20	28	1.1	.01



757 SYSTEM 4 Security TORX® Bits

High alloy CVM steel, hardened, on 4 mm stock.

Item No.	Size	mm	Inch	lbs.
75727	T7s	28	1.1	.01
75728	T8s	28	1.1	.01
75729	T9s	28	1.1	.01
75735	T10s	28	1.1	.01
75739	T15s	28	1.1	.01
75742	T20s	28	1.1	.01



753 SYSTEM 4 Metric & Inch Security Hex Bits

High alloy CVM steel, hardened, on 4 mm hex stock.

Item No.	Metric	mm	Inch	lbs.
75322	2.0	28	1.1	.01
75327	2.5	28	1.1	.01
75332	3.0	28	1.1	.01
75342	4.0	28	1.1	.01
Inch				
75362	5/64	28	1.1	.01
75364	3/32	28	1.1	.01
75366	7/64	28	1.1	.01
75368	1/8	28	1.1	.01
75370	9/64	28	1.1	.01
75372	5/32	28	1.1	.01

Micro Bit 1/4" Drive Power Tool Adapter



75902 Micro Bit 1/4" Drive Power Tool Adapter

Shaft CVM steel, hardened, corrosion protected. For 4mm bits. 2.3" OAL

Item No.	Size	mm	mm	lbs.
75902	4.0	60	4.0	.07

Wiha Pentolobe IPR drivers will fit fasteners used in "Apple" brand products including iPhone, Mac Book & Mac Air



757 SYSTEM 4 Pentolobe IPR Bits

High alloy chrome-vanadium-molybdenum steel, hardened, on 4 mm hex stock.

Item No.	Size	mm	Inch	lbs.
75743	P1	28	1.1	.01
75744	P2	28	1.1	.01
75745	P3	28	1.1	.01
75746	P4	28	1.1	.01
75747	P5	28	1.1	.01
75748	P6	28	1.1	.01



758 SYSTEM 4 Metric & Inch Nut Setters

High alloy CVM steel, hardened, on 4 mm hex stock.

Item No.				
Metric	mm	mm	Inch	lbs.
75820	2.0	30	1.2	.01
75821	2.5	30	1.2	.01
75822	3.0	30	1.2	.01
75823	3.5	30	1.2	.01
75824	4.0	30	1.2	.01
75825	4.5	30	1.2	.01
75826	5.0	30	1.2	.01
75827	5.5	30	1.2	.01
Inch	Inch	mm	Inch	lbs.
75810	5/64	30	1.2	.01
75811	3/32	30	1.2	.01
75812	7/64	30	1.2	.01
75813	1/8	30	1.2	.01
75814	9/64	30	1.2	.01
75815	5/32	30	1.2	.01
75816	3/16	30	1.2	.01
75817	7/32	30	1.2	.01

Micro Bit 1/4" Drive Power Tool Adapter



75802 Micro Bit To 1/4" Drive Insert Bit Adapter

uses magnets to hold 4mm Micro Bits

Item No.	Size	mm	mm	lbs.
75802	4.0	25	4.0	.01

75803 Long Micro Bit To 1/4" Drive Insert Bit Adapter

uses spring clip non-magnetic to hold 4mm Micro Bits

Item No.	Size	mm	mm	lbs.
75803	4.0	38	4.0	.02

Wiha SYS 4 Micro Bits & Compact Bit Sets

SHOP

75999 SYSTEM 4 Slotted, Phillips, Hex Inch & Metric Precision Interchangeable Bit Set, 26 Pcs. In Compact Fold Out Box. Wiha precision handle, bit extension & 24 interchangeable bits.

Item No. Combination Bit Set

75999 Set with Standard Precision Handle

Set includes the following bits:

- ↓  **Slotted:** 1.5, 2.0, 3.0, 4.0mm
- ⊕ **Phillips:** 000, 00, 0, 1
- ⬢ **Hex Metric:** .71, .89, 1.3, 1.5, 2.0, 2.5, 3.0, 4.0mm
- ⬢ **Hex Inch:** .050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32"
- **100mm Bit Extension**
- ↔ **lbs.** .64



26 Pc. Set

SHOP

75792 SYSTEM 4 **TORX®** Precision Interchangeable Bit Set, 11 Pcs. In Compact Fold Out Box.

Sets includes Wiha precision handle, bit extension and 9 Wiha interchangeable bits.

Item SYSTEM 4 TORX® Bit Set

No. Set with ESD Safe Precision Handle

75792 and the following bits:

- ⬤ **TORX®:** T3, T4, T5, T6, T7, T8, T9, T10, T15
- **100mm Bit Extension**
- ↔ **lbs.** .64



11 Pc. Set

SHOP

75395 SYSTEM 4 Hex Inch & Metric Precision Interchangeable Bit Set, 18 Pcs. In Compact Fold Out Box. Wiha precision handle, bit extension and 16 Wiha interchangeable bits.

Item No. Combination Bit Set

75395 Set with Standard Precision Handle

Includes the following bits:

- ⬢ **Hex Metric:** .71, .89, 1.3, 1.5, 2.0, 2.5, 3.0, 4.0mm
- ⬢ **Hex Inch:** .050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32"
- **100mm Bit Extension**
- ↔ **lbs.** .58



18 Pc. Set

SHOP

759 sets SYSTEM 4 Slotted/Phillips/Hex Inch/**TORX®** Precision Interchangeable Bit Set, 27 Pcs. In Compact Fold Out Box. Sets include your choice of Wiha precision handle, bit extension and 25 Wiha interchangeable bits.

Item Handle Options for SYSTEM 4


No. Combination Bit Sets

75991 Set with Standard Precision Handle

75992 Set with ESD Safe Precision Handle

Sets include the following bits:

- ↓  **Slotted:** 1.5, 2.0, 3.0, 4.0mm
- ⊕ **Phillips:** 000, 00, 0, 1
- ⬤ **TORX®:** T3, T4, T5, T6, T7, T8, T9, T10, T15
- ⬢ **Hex Inch:** .050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32"
- **100mm Bit Extension**
- ↔ **lbs.** .64



27 Pc. Set

SHOP

75996 SYSTEM 4 Interchangeable Bit Set, 40 Pcs. In Storage Box. Includes Wiha precision handle, bit extension & 38 interchangeable bits.

Item SYSTEM 4

No. Combination Bit Set

75996 Set with ESD Safe Precision Handle

Set includes the following bits:

- ↓  **Slotted:** 0.8, 1.2, 1.5, 1.8, 2.0, 2.5, 3.0, 3.5, 4.0mm
- ⊕ **Phillips:** 000, 00, 0, 1
- ⬤ **TORX®:** T3, T4, T5, T6, T7, T8, T9, T10, T15
- ⬢ **Hex Metric:** 1.3, 1.5, 2.0, 2.5, 3.0, 4.0mm
- ⬢ **Hex Inch:** .028, .035, .050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32"
- **100mm Bit Extension**
- ↔ **lbs.** 1.04



40 Pc. Set

SHOP

75994 SYSTEM 4 Slotted/Phillips/Hex **Metric/TORX®** Precision Interchangeable Bit Set, 27 Pcs. In Compact Fold Out Box.

Set includes Wiha precision handle, bit extension and 25 Wiha interchangeable bits.

Item SYSTEM 4

No. Combination Bit Set

75994 Set with ESD Safe Precision Handle

Set includes the following bits:

- ↓  **Slotted:** 1.5, 2.0, 3.0, 4.0mm
- ⊕ **Phillips:** 000, 00, 0, 1
- ⬤ **TORX®:** T3, T4, T5, T6, T7, T8, T9, T10, T15
- ⬢ **Hex Metric:** .71, .89, 1.3, 1.5, 2.0, 2.5, 3.0, 4.0mm
- **100mm Bit Extension**
- ↔ **lbs.** .64



27 Pc. Set

Wiha Master Tech Micro Bit Sets

75990 SYSTEM 4 Interchangeable Bit Set, 40 Pcs. In Canvas Pouch. Includes Wiha precision handle, bit extension & 38 interchangeable bits.

Item No. Set with ESD Safe Precision Handle

75990 Set includes the following bits:

↓  **Slot:** 0.8, 1.2, 1.5, 1.8, 2.0, 2.5, 3.0, 3.5, 4.0mm

 **Phillips:** 000, 00, 0, 1

 **TORX®:** T3, T4, T5,

T6, T7, T8, T9, T10, T15

 **Hex Metric:** 1.3, 1.5, 2.0, 2.5, 3.0, 4.0mm

 **Hex Inch:** .028(.7), .035(.9), .050,

1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32"

 **100mm Bit Extension**

 **lbs.** .65



75989 SYSTEM 4 Protturn Precision Power Screwdriver Set With Micro Bits, 40 Pieces In Storage Box. Includes Wiha precision handle, Protturn power screwdriver & 38 interchangeable micro bits.

Item No. Set With Battery Powered Driver & Precision Handle

75989 Set includes the following micro bits:

↓  **Slotted:** 0.8, 1.2, 1.5, 1.8, 2.0, 2.5, 3.0, 3.5, 4.0mm

 **Phillips:** 000, 00, 0, 1

 **TORX®:** T3, T4, T5, T6, T7, T8, T9, T10, T15

 **Hex Metric:** .7, .9, 1.3, 1.5, 2.0, 2.5, 3.0, 4.0mm

 **Hex Inch:** .050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32"

 **lbs.** 1.18



75965 SYSTEM 4 Master Tech ESD & Ratchet With Micro Bits, 65 Pieces In Storage Box. Includes Wiha precision ESD Safe handle, micro bit extension, 72 tooth ratchet & 62 interchangeable micro bits.

Item No. With ESD Precision Handle, 1/4" Ratchet, Micro Bit Extension

75965 Set includes the following micro bits:

↓  **Slotted:** 0.8, 1.2, 1.5, 1.8, 2.0, 2.5, 3.0, 3.5, 4.0mm

 **Phillips:** 000, 00, 0, 1

 **TORX®:** T3, T4, T5, T6, T7, T8, T9, T10, T15, T20

 **Hex Metric:** .7, .9, 1.3, 1.5, 2.0, 2.5, 3.0, 4.0mm

 **Hex Inch:** .050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32"

 **Nut Drivers Metric:** 2.0, 2.5, 3.0, 3.5, 4.0, 4.5, 5.0, 5.5mm

 **Nut Drivers Inch:** 5/64, 3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32"

 **Pentalobe:** 1, 2, 3, 4, 5, 6

Magnetic 1/4" to 4mm Adapter

 **lbs.** 1.16



Micro Bit Handle Storage Sets

Micro precision bits on 4mm hex drive



Storage handle

Bits of exclusive CRM-72 tool steel

Bits hardened for extreme durability



75981 Micro Bit Handle Storage Slotted & Phillips Bit Set, 7 Pcs.

Wiha precision storage handle & 6 interchangeable bits.

Item No. Set with Precision Storage Handle

75981 ↓  **Slotted:** 1.2, 1.5, 2.0mm

 **Phillips:** 000, 00, 0

 **lbs.** .08



75983 Micro Bit Handle Storage Hex Inch Bit Set, 7 Pcs.

Wiha precision storage handle & 6 interchangeable bits.

Item No. Set with Precision Storage Handle

75983  **Hex Inch:** .050, 1/16, 5/64, 3/32, 7/64, 1/8"

 **lbs.** .08



75985 Micro Bit Handle Storage TORX® Bit Set, 7 Pcs.

Wiha precision storage handle & 6 interchangeable bits.

Item No. Set with Precision Storage Handle

75985  **TORX®:** T3, T4, T5, T6, T7, T8

 **lbs.** .08

Technicians MicroBit Sets

- Micro Precision Bits on 4mm Hex Drive
- Bits of Exclusive CRM-72 Tool Steel
- Handle uses non-magnetic ball retainer
- Use bits in extension only
- Standard extension adds 4" to length
- Non-magnetic bit extension


Surface resistance of handles is $10^6 - 10^9$ Ohms

Light weight & compact

Rotation cap

Handle tapered for precise control

Bits hardened for extreme durability



75093 SYSTEM 4 Slotted, Phillips, **TORX** Compact ESD

Precision Interchangeable Bit Set, 16 Pcs. Wiha precision handle, bit extension & 14 interchangeable bits.

Item No. Combination Bit Set

75093 Set with ESD Safe Precision Handle

↓ **Slotted:** 1.5, 2.0, 2.5, 3.0mm

⊕ **Phillips:** 00, 0, 1

⊗ **TORX:** T6, T7, T8, T9, T10, T15, T20

○ **100mm Bit Extension**

↔ **lbs.** .17

[SHOP](#)



75094 SYSTEM 4 Slotted, Phillips, Hex Inch Compact ESD

Precision Interchangeable Bit Set, 16 Pcs. Wiha precision handle, bit extension & 14 interchangeable bits.

Item No. Combination Bit Set

75094 Set with ESD Safe Precision Handle

↓ **Slotted:** 1.5, 2.0, 2.5, 3.0mm

⊕ **Phillips:** 00, 0, 1

⬡ **Hex Inch:** .035, .050, 1/16, 5/64, 3/32, 7/64, 1/8"

○ **100mm Bit Extension**

↔ **lbs.** .17

[SHOP](#)



75095 SYSTEM 4 Slotted, Phillips, Hex **Metric** Compact ESD

Precision Interchangeable Bit Set, 16 Pcs. Wiha precision handle, bit extension & 14 interchangeable bits.

Item No. Combination Bit Set

75095 Set with ESD Safe Precision Handle

↓ **Slotted:** 1.5, 2.0, 2.5, 3.0mm

⊕ **Phillips:** 00, 0, 1

⬡ **Hex Metric:** .9, 1.3, 1.5, 2.0, 2.5, 3.0, 4.0mm

○ **100mm Bit Extension**

↔ **lbs.** .17

[SHOP](#)



75096 SYSTEM 4 Hex Inch & **Metric** Compact ESD Precision

Interchangeable Bit Set, 16 Pcs. Wiha precision handle, bit extension & 14 interchangeable bits.

Item No. Combination Bit Set

75096 Set with ESD Safe Precision Handle

⬡ **Hex Inch:** 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32"

⬡ **Hex Metric:** .9, 1.3, 1.5, 2.0, 2.5, 3.0, 4.0mm

○ **100mm Bit Extension**

↔ **lbs.** .17

[SHOP](#)



Wiha ESD Safe Cushion Grip Bit Holders



ESD Safe

Dissipative material offers protection against electrostatic discharge

Bit holders without magnetics

For working on static sensitive components

Surface resistance of handles is $10^6 - 10^9$ Ohms



[SHOP](#)

28180 ESD Safe Stubby 1/4" Bit Holder With Ring Retainer, Cushion Grip Wiha-SoftFinish® Handle, IEC 61340-5-1, DIN 3126, ISO 1173 Dissipative SoftFinish® cushion grip handle, multi-component, ESD Safe surface resistance $10^6 - 10^9$ Ohm.

Item No.	Inch	mm	Inch	lbs.	pkg.
28180	1/4"	57	2.2	.11	1



[SHOP](#)

38701 ESD Safe Quick Release 1/4" Bit Holder, With Wiha-SoftFinish® Cushion Grip Handle, IEC 61340-5-1, DIN 3126, ISO 1173 Stainless steel with retaining ring bit holder. Dissipative SoftFinish® cushion grip handle, multi-component, ESD Safe surface resistance $10^6 - 10^9$ Ohm.

Item No.	Inch	mm	Inch	mm	Inch	lbs.	pkg.
38701	1/4"	148	5.8	38	1.5	.18	1



In Durable Pouch

Surface resistance of handle is $10^6 - 10^9$ Ohms



[SHOP](#)

38790 ESD Safe 1/4" Quick Release Blade Holder Set With Interchangeable 70mm Blades & Quick Release Blade Holder

20 Pc. set includes ESD Safe Quick Release Holder, cushion grip handle. 70mm blades are CVM tool steel, hardened. Also includes a Quick Release blade extension.

Item nNo. 38790

Slotted: 2.5, 3.0, 3.5, 4.0, 5.5, 6.5mm **Phillips:** 0, 1, 2

TORX: T6, T7, T8, T9, T10, T15 **Pozidriv:** 0, 1, 2

Wiha Bit Holders



[SHOP](#)

38030 ClicFix Quick Release Magnetic Bit Holder Blade high alloy CVM steel, hardened, hard chromed. Wiha Powerhandle impact resistant.

Item							
No.	Size	mm	Inch	mm	Inch	lbs	pkg.
38030	1/4"	120	4.7	230	9.0	.27	1



[SHOP](#)

38800 Bit Holder With Wiha T-handle Magnetic, holds bit and screw. Retainer out of stainless steel. Hex shaft CVM steel, nickel-plated. Wiha-T-handle high quality plastic, impact resistant.

Item							
No.	Size	mm	Inch	mm	Inch	lbs.	pkg.
38800	1/4"	150	6.0	80	3.0	.18	1



[SHOP](#)

38600 Bit Holder 1/4" with Retaining Ring With Flexible Shaft Plastic coated flexible metal. Stainless steel with retaining ring. Wiha-SoftFinish® handle multi-component, cushion grips.

Item							
No.	Inch	mm	Inch	mm	Inch	lbs.	pkg.
38600	1/4"	150	5.9	268	10.6	.30	1



[SHOP](#)

28103 Magnetic 1/4" Bit Holder With Wiha SoftFinish® Stubby Handle For working in confined spaces. Stainless steel with strong magnet. Wiha-SoftFinish® handle multi-component, cushion grips.

Item					
No.	Inch	mm	Inch	lbs.	pkg.
28103	1/4"	57	2.2	.11	1



[SHOP](#)

28489 Drive-Loc VI Bit Holder High alloy CVM steel, through hardened, hard chrome finish. Wiha-SoftFinish® handle multi-component, cushion grips.

Item					
No.	Inch	Extends	lbs.	pkg.	
28489	1/4"	1-3/4" to 4-7/8"	.36	1	



[SHOP](#)

384 1/4" Magnetic Bit Holding Screwdrivers, With Wiha-SoftFinish® Handle Ergonomic cushion grip, magnetic, holds bit and screw. Retainer out of stainless steel. Shaft CVM steel, nickel-plated.

Item							
No.	Size	mm	Inch	mm	Inch	lbs.	pkg.
38450	1/4"	125	5.0	240	9.46	.23	1
38460	1/4"	300	11.8	400	15.69	.37	1



[SHOP](#)

52650 1/4" Bit holding Screwdriver, With Wiha-MicroFinish Handle Non-slip grip, magnetic, holds bit and screw. Retainer out of stainless steel. Shaft CVM steel, nickel-plated. Wiha-MicroFinish handle, cellulose-acetate, impact resistant, non-slip, oil and grease resistant.

Item							
No.	Size	mm	Inch	mm	Inch	lbs.	pkg.
52650	1/4"	125	5.0	225	8.9	.24	1



[SHOP](#)

48401 1/4" Bit holding Screwdriver, With Wiha-Ergo 3K Handle Magnetic, holds bit and screw. Retainer out of stainless steel. Shaft CVM tool steel, nickel plated.

Item							
No.	Size	mm	Inch	mm	Inch	lbs.	pkg.
48401	1/4"	125	5.0	211	8.3	.24	1



[SHOP](#)

48400 1/4" Bit Holding Screwdriver, With Wiha-Protturn Handle Magnetic, holds bit and screw. Retainer out of stainless steel. Shaft CVM steel, nickel-plated. Handle, molded on, impact resistant.

Item							
No.	Size	mm	Inch	mm	Inch	lbs.	pkg.
48400	1/4"	125	5.0	243	9.6	.24	10



[SHOP](#)

66850 1/4" Bit Holding Screwdriver, With Wiha-Protturn Precision handle. Magnetic, holds bit and screw. Retainer out of stainless steel. Shaft chrome-vanadium-molybdenum steel, nickel-plated.

Item							
No.	Size	mm	Inch	mm	Inch	lbs.	pkg.
66850	1/4"	60	2.36	170	6.7	.07	1

Wiha Bit Holders



(bits not included)

38025 Magnetic Bit Holder, 1/4", Wiha-Powerhandle, Insulated, impact resistant. Snap-lock rotatable cap. Chambered bit holder equipped with transparent selector for easy selection of bits. 1/4" bit holder, shielded, magnetic, holds bit and screw. Cavity holds up to 6 bits.

Item No.	Size	mm	Inch	mm	Inch	lbs.	pkg.
38025	1/4"	120	4.7	230	9.0	.26	1

[SHOP](#)



(bits not included)

38015 Magnetic Bit Holder, 1/4", Wiha-Powerhandle impact resistant. Snap-lock rotatable cap. Chambered bit holder equipped with transparent selector for easy selection of bits. 1/4" bit holder, stainless steel, magnetic, holds bit and screw. Shaft CVM steel. Cavity holds up to 6 bits.

Item No.	Size	mm	Inch	mm	Inch	lbs.	pkg.
38015	1/4"	120	4.7	230	9.0	.25	1

[SHOP](#)



38060 Mini Bit Ratchet & ClicFix Set

Extra fine 72 tooth ratchet, rugged drop forged steel. ClicFix quick release holder, precision narrow profile, magnetic. Accepts 1/4" Bits.

Item No. Includes Phillips: #2

38060 lbs. .28



714 Protturn 1/4" Quick Release Bit Holder With magnets

Item No.	Size	mm	Inch	lbs.
71475	2.4"	60	2.4	.06
71476	3.9"	100	3.9	.09
71477	5.9"	150	5.9	.11
71478	7.9"	200	7.8	.14
71479	9.9"	250	9.8	.17

[SHOP](#)

71474 5 Pc. Protturn 1/4" Quick Release Bit Holder Set

Includes: 60mm, 100mm, 150mm, 200mm, 250mm lbs. .58

[SHOP](#)

Wiha Magnetic Bit Holders



- Narrow Profile
- One handed bit changes
- Internal bit lock mechanism



[SHOP](#)

714 ClicFix Bit Holder, Magnetic For Insert Bits

Item No.	Size	Size	mm	Inch	lbs.	pkg.
71490	1/4"	1/4"	60	2.4	.07	1
71491	1/4"	1/4"	75	2.9	.07	1

High Precision Tool Holder



Quick release tool holder for Drills, Countersinks & Power bits

[SHOP](#)

71480 CentroFix Bit Holder

Item No.	Size	Size	mm	Inch	lbs.	pkg.
71480	1/4"	1/4"	60	2.3	.09	1



[SHOP](#)

71494 Stainless Steel Bit Holder, 1/4" For Insert Bits

Internal C-ring for bit holding & magnet.

Item No.	Size	Size	mm	Inch	lbs.
71494	1/4"	1/4"	54	2.1"	.05

Wiha Bit Holders


[SHOP](#)

711 Universal Magnetic Bit Holder, 1/4" For Insert Bits

Item No.	Size	Size	mm	Inch	lbs.
71130	1/4"	1/4"	74	2.9	.06
71131	1/4"	1/4"	59	2.3	.05



Holds 1" (25mm) Bits
All Stainless with Rubber O-Ring

714 Screw Cap Bit Holder with O-Ring


[SHOP](#)

Item No.	Size	Size	mm	Inch	lbs.	
71492	1/4"	1/4"	62	2.4	.08	Non Magnetic
71493	1/4"	1/4"	76	3.0	.08	Magnetic


[SHOP](#)

71470 Auto Lock Magnetic Bit Holder, Spring Loaded Bit Ejection, 1/4" For Insert & Power Bits

Item No.	Size	Size	mm	Inch	lbs.
71470	1/4"	1/4"	60	2.4	.08



Retaining Ring
Bit Holders

Magnetic



714 Bit Holder, Retaining Ring & Magnetic

[SHOP](#)

Item No.	Size	Size	mm	Inch	lbs.
71431	1/4"	1/4"	60	2.4	.05
71433	1/4"	1/4"	67	2.6	.05
71435	1/4"	1/4"	100	3.9	.07
71437	1/4"	1/4"	150	5.9	.11
71439	1/4"	1/4"	200	7.8	.13
71441	1/4"	1/4"	253	10.0	.16

71499 5 Pc. Bit Holder Set In Vinyl Pouch

Includes: 60mm, 100mm, 150mm, 200mm, 253mm

lbs. .60

Wiha Inch & Metric Nut Setters



Magnetic 1/4"

[SHOP](#)


704 Metric Nut Setters Standard With Permanent Industrial Magnet, 1/4" Hex Metric Nut Setters

Item No.	Size	mm	lbs.
70437	5.0	55	.04
70438	5.5	55	.05
70440	6.0	55	.05
70442	7.0	55	.05
70445	8.0	55	.05
70448	10.0	55	.06
70450	13.0	55	.07


[SHOP](#)

704 Nut Setters Standard. 1/4" Hex Inch Permanent industrial magnet.

Item No.	Length	mm	lbs.
70462	2.5"	65	.06
70463	4.0"	102	.10
70464	6.0"	152	.15
70466	12.0"	305	.27


[SHOP](#)

704 Nut Setters Standard. 5/16" Hex Inch Permanent industrial magnet.

Item No.	Length	mm	lbs.
70468	2.5"	65	.07
70469	4.0"	102	.12
70470	6.0"	152	.17
70472	12.0"	305	.28


Wiha Inch & Metric Nut Setters



704 Nut Setters Standard. 3/8" Hex Inch

Permanent industrial magnet.

Item No.	Length	mm	lbs.
70474	2.5"	65	.08
70476	4.0"	102	.14
70477	6.0"	152	.18
70479	12.0"	305	.41



704 Nut Setters Standard. 1/4" Hex Inch

Item No.	Size	mm	lbs.
70424	1/4	55	.05
70427	5/16	55	.05
70430	3/8	55	.06



70494 3 pc. Hex Metric Nut Setter Set

Permanent industrial magnet. 55mm OAL
Hex Metric Nut Setters.

Item No.	Set includes
70494	the following:
	7, 8, 10 x 55mm



70490 3 pc. Hex Inch Nut Setter Set

Permanent industrial magnet. 65mm OAL
Hex Inch Nut Setters.

Item No.	Set includes
70490	the following:
	1/4, 5/16, 3/8 x 2.5"



70491 3 pc. Hex Inch Nut Setter Set

Permanent industrial magnet. 102mm OAL Hex Inch Nut Setters.

Item No.	Set includes
70491	the following:
	1/4, 5/16, 3/8 x 4.0"



70492 3 pc. Hex Inch Nut Setter Set

Permanent industrial magnet. 152mm OAL Hex Inch Nut Setters.


Item No.	Set includes
70492	the following:
	1/4, 5/16, 3/8 x 6.0"



70493 3 pc. Hex Inch Nut Setter Set

Permanent industrial magnet. 305mm OAL
Hex Inch Nut Setters.

Item No.	Set includes
70493	the following:
	1/4, 5/16, 3/8 x 12.0"



74990 19 Piece Quick Change Bit Belt Pack Set

Set includes: 1/4" quick release bit holder
and the following 1/4" bits and Nut Setters:

Slotted - Power: 4.5, 5.5, 6.5mm x 50mm	
Phillips - Power: #1, #2, #3 x 50mm	lbs.
Square - Power: #1, #2, #3 x 50mm	.93
Torx® - Insert: T10, T15, T20, T25, T27, T30 x 25mm	
Nut Setters - Power: 1/4, 5/16, 3/8" Magnetic	

Wiha TORX®, TORXPlus® & Security TORX® Bit Sockets



Set Screw
Replaceable
Bits

761 TORX® Sockets 1/4" Square Drive

Item	No.	Size	mm	lbs.
	76106	T6	38	.04
	76107	T7	38	.04
	76109	T8	38	.04
	76111	T9	38	.04
	76113	T10	38	.04
	76117	T15	38	.04
	76119	T20	38	.04
	76121	T25	38	.04
	76123	T27	38	.04
	76129	T30	38	.05
	76131	T40	38	.05



763 TORX® Sockets 3/8" Square drive, Set screw replaceable bit. 1/4" bits.

Item	No.	Size	mm	lbs.
	76312	T9	42	.09
	76314	T10	42	.09
	76316	T15	42	.09
	76318	T20	42	.09
	76322	T25	42	.09
	76324	T27	42	.09
	76326	T30	42	.09
	76328	T40	42	.09



763 TORX® Sockets 3/8" Square drive, Set screw replaceable bit. 5/16" bits. 2" OAL

Item	No.	Size	mm	lbs.
	76346	T40	51	.11
	76348	T45	51	.11
	76352	T50	51	.11
	76354	T55	51	.13



Set Screw
Replaceable
Bits

763 Security TORX® Sockets

3/8" Square drive, 5/16" bits.

Item	No.	Size	mm
	76339	T40s	51
	76340	T45s	51
	76341	T50s	51
	76342	T55s	51



763 Security TORX® Sockets

1/4" Square drive, 1/4" bits.

Item	No.	Size	mm
	76329	T7s	38
	76330	T8s	38
	76331	T9s	38
	76332	T10s	38
	76333	T15s	38
	76334	T20s	38
	76335	T25s	38
	76336	T27s	38
	76337	T30s	38
	76338	T40s	38



701 Security TORX® Sockets

3/8" Square drive, 1/4" bits. 2" OAL

Item	No.	Size	mm	lbs.
	70107	T7s	42	.09
	70108	T8s	42	.09
	70109	T9s	42	.09
	70110	T10s	42	.09
	70113	T15s	42	.09
	70115	T20s	42	.09
	70117	T25s	42	.09
	70119	T27s	42	.09
	70121	T30s	42	.09
	70123	T40s	42	.09



Set Screw
Replaceable
Bits

716 TORXPlus® Sockets 1/4" Square Drive,

Set Screw Replaceable Bit. 1/4" bits

Item	No.	Size	mm	lbs.
	71661	IP6	38	.04
	71662	IP7	38	.04
	71663	IP8	38	.04
	71664	IP9	38	.04
	71665	IP10	38	.04
	71666	IP15	38	.04
	71667	IP20	38	.04
	71668	IP25	38	.04
	71669	IP27	38	.04
	71670	IP30	38	.04
	71671	IP40	38	.04



716 TORXPlus® Sockets 3/8" Square Drive, Set Screw Replaceable Bit. 1/4" bits

Item	No.	Size	mm	lbs.
	71673	IP9	42	.09
	71674	IP10	42	.09
	71675	IP15	42	.09
	71676	IP20	42	.09
	71677	IP25	42	.09
	71678	IP27	42	.09
	71680	IP30	42	.09
	71681	IP40	42	.09

1/2" Square Drive Sockets



Set Screw
Replaceable
Bits

764 Slotted Bit Sockets 1/2" Square Drive

Item	No.	mm	mm	lbs.	pkg.
	76417	8	59	.12	1
	76418	10	59	.12	1
	76419	12	59	.12	1



Set Screw
Replaceable
Bits

764 TORX® Sockets 1/2" Square Drive

Item	No.	Size	mm	lbs.	pkg.
	76403	T30	59	.10	1
	76404	T40	59	.10	1
	76405	T45	59	.10	1
	76406	T50	59	.10	1
	76407	T55	59	.11	1



Set Screw
Replaceable
Bits

764 Security TORX® Sockets

1/2" Square Drive

Item	No.	Size	mm	lbs.	pkg.
	76411	T40s	59	.11	1
	76412	T45s	59	.11	1
	76413	T50s	59	.11	1
	76414	T55s	59	.12	1



Set Screw
Replaceable
Bits

764 Phillips Bit Sockets 1/2" Square Drive

Item	No.	Size	mm	lbs.	pkg.
	76422	2	59	.15	1
	76423	3	59	.15	1
	76424	4	59	.15	1

Hex Inch/Metric Bit Sockets



SHOP

713 Hex Sockets 1/4" Square drive socket. Replaceable bit. 1/4" bits CVM steel.

Item	No.	Inch	mm	lbs.
	71371	1/16	38	.05
	71370	5/64	38	.05
	71372	3/32	38	.05
	71374	7/64	38	.05
	71376	1/8	38	.05
	71378	9/64	38	.05
	71380	5/32	38	.05
	71382	3/16	38	.05
	71384	7/32	38	.05
	71386	1/4	38	.05



SHOP

713 Hex Sockets 3/8" Square drive socket. Replaceable bit. 1/4" bits CVM tool steel.

Item	No.	Inch	mm	lbs.
	71375	1/8	42	.09
	71377	9/64	42	.09
	71379	5/32	42	.09
	71381	3/16	42	.09
	71383	7/32	42	.09
	71385	1/4	42	.09
	71388	5/16	42	.10
	71390	3/8	42	.10



SHOP

713 Hex Metric Sockets 1/4" Square drive socket. Replaceable bit. 1/4" bits CVM steel.

Item	No.	mm	mm	lbs.
	71301	1.5	38	.04
	71302	2.0	38	.04
	71305	2.5	38	.04
	71313	3.0	38	.04
	71314	4.0	38	.04
	71317	5.0	38	.05
	71319	6.0	38	.05
	71327	8.0	38	.05
	71340	10.0	38	.05



SHOP

713 Hex Metric Sockets 3/8" Square drive socket. Replaceable bit. 1/4" bits CVM steel.

Item	No.	mm	mm	lbs.
	71300	2.0	42	.09
	71316	2.5	42	.09
	71341	3.0	42	.09
	71331	4.0	42	.09
	71323	5.0	42	.09
	71325	6.0	42	.09
	71320	8.0	42	.10
	71322	10.0	42	.11



SHOP

713 Hex Metric Sockets 5/16" Square drive socket. Replaceable bit. 5/16" bits CVM steel.

Item	No.	mm	mm	lbs.
	71332	12.0	75	.22



SHOP

761 Security Hex Inch Sockets 3/8" Square drive socket. Replaceable bit. 1/4" bits CVM steel.

Item	No.	Inch	mm	lbs.
	76164	5/64	42	.09
	76165	3/32	42	.09
	76166	7/64	42	.09
	76167	1/8	42	.09
	76168	9/64	42	.09
	76169	5/32	42	.09
	76170	3/16	42	.09
	76171	7/32	42	.09
	76172	1/4	42	.09



SHOP

761 Security Hex Metric Sockets 3/8" Square drive socket. Replaceable bit. 1/4" bits CVM steel.

Item	No.	mm	mm	lbs.
	76132	2.0	42	.09
	76133	2.5	42	.09
	76134	3.0	42	.09
	76135	4.0	42	.09
	76136	5.0	42	.09
	76137	6.0	42	.09
	76138	8.0	42	.09

Wiha Ball End Hex Inch & Metric Bit Sockets



SHOP

717 Ball End Hex Inch Sockets 1/4" Square drive socket. Replaceable bit. 1/4" bits CVM steel.

Item	No.	Inch	mm	lbs.
	71761	3/32	38	.05
	71762	7/64	38	.05
	71763	1/8	38	.05
	71764	9/64	38	.05
	71765	5/32	38	.05
	71766	3/16	38	.05
	71767	7/32	38	.05
	71768	1/4	38	.05



SHOP

717 Ball End Hex Metric Sockets 1/4" Square drive socket. Replaceable bit. 1/4" bits CVM steel.

Item	No.	mm	mm	lbs.
	71771	1.5	51	.11
	71772	2.0	51	.11
	71773	2.5	51	.11
	71774	3.0	51	.11
	71775	4.0	51	.11
	71776	5.0	51	.12
	71777	6.0	51	.12

Wiha Bit Holding Socket Replacements



SHOP

72014 1/4" Drive Bit Holding Socket With Retaining Ring For 1/4" drive bits.

Item	No.	Bit	mm	Drive	lbs.
	72014	1/4"	25	1/4"	.04



SHOP

72038 3/8" Drive Bit Holding Socket With Retaining Ring For 1/4" drive bits.

Item	No.	Bit	mm	Drive	lbs.
	72038	1/4"	25	3/8"	.08

Socket Adapters


[SHOP](#)

721 Hex To Square 1/4" socket bit adapter.

Item				
No.	Size	mm	Drive	lbs.
72110	1/4"	25	1/4"	.03
72115	1/4"	30	3/8"	.05


[SHOP](#)

724 Tool Shaft

1/4" drive socket power adapter.

Item				
No.	Drive	mm	Drive	lbs.
72401	1/4"	100	1/4"	.09
72405	1/4"	50	1/4"	.03
72410	1/4"	100	3/8"	.17
72415	1/4"	50	3/8"	.06

Impact Bit Holding Sockets


[SHOP](#)

720 Impact Bit Holding Socket With

Retaining Ring For 1/4" drive bits.

Item				
No.	Bit	mm	Drive	lbs.
72001	1/4"	25	1/4"	.05
72002	1/4"	30	3/8"	.10
72003	1/4"	35	1/2"	.21

72090 3 Piece Bit Holding Socket Set

for use with 1/4" Insert bits

Drive:  lbs.

1/4", 3/8", 1/2" .40

[SHOP](#)

[SHOP](#)

720 Impact Bit Holding Socket With

Retaining Ring For 5/16" drive bits.

Item				
No.	Bit	mm	Drive	lbs.
72004	5/16"	25	1/4"	.04
72005	5/16"	30	3/8"	.04
72006	5/16"	35	1/2"	.04

Wiha Long Blade Sockets & Sets


[SHOP](#)

771 Hex Inch Sockets

1/4" Drive 6" Long Bit Socket

Item				
No.	Size	Inch	lbs.	
77128	3/32	6	.12	
77130	7/64	6	.12	
77132	1/8	6	.12	
77134	9/64	6	.12	
77136	5/32	6	.12	
77138	3/16	6	.12	
77139	7/32	6	.12	
77141	1/4	6	.12	

77191 8 Pc. Hex Inch Socket Blade Set

 Inch: 3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4"  wt. .81

[SHOP](#)

771 Hex Inch Sockets

3/8" Drive 6" Long Bit Socket

Item				
No.	Size	Inch	lbs.	
77165	3/32	6	.12	
77167	7/64	6	.12	
77169	1/8	6	.12	
77171	9/64	6	.12	
77173	5/32	6	.12	
77175	3/16	6	.12	
77177	7/32	6	.12	
77179	1/4	6	.12	


[SHOP](#)

771 Hex Metric Sockets

1/4" Drive 6" Long Bit Socket

Item				
No.	Size	Inch	lbs.	
77140	2.5	6	.12	
77142	3.0	6	.12	
77144	4.0	6	.12	
77146	5.0	6	.12	
77148	6.0	6	.12	

77192 5 Pc. Hex Metric Socket Blade Set

Metric: 2.5, 3.0, 4.0, 5.0, 6.0mm

 lbs. .51

[SHOP](#)

771 TORX® Sockets

1/4" Drive 6" Long Bit Socket

Item				
No.	Size	Inch	lbs.	
77151	T8	6	.12	
77153	T9	6	.12	
77152	T10	6	.12	
77154	T15	6	.12	
77156	T20	6	.12	
77158	T25	6	.12	
77160	T27	6	.12	
77162	T30	6	.12	
77164	T40	6	.12	

77193 7 Pc. TORX® Socket Blade Set

TORX®: T10, T15, T20, T25,

 T27, T30, T40  wt. .69


[SHOP](#)

771 TORX® Sockets

3/8" Drive 6" Long Bit Socket

Item				
No.	Size	Inch	lbs.	
77101	T8	6	.12	
77103	T9	6	.12	
77105	T10	6	.12	
77107	T15	6	.12	
77109	T20	6	.12	
77111	T25	6	.12	
77113	T27	6	.12	
77115	T30	6	.12	
77117	T40	6	.12	

77195 9 Pc. TORX® Socket Blade Set

 TORX®: T8, T9, T10, T15, T20, T25, T27, T30, T40  wt. 93


77198 22 Pc. Hex & TORX® Long Blade Socket Set, 1/4" Drive

Inch Hex: 3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4"

Metric Hex: 2.5, 3.0, 4.0, 5.0, 6.0mm

TORX®: T8, T9, T10, T15, T20,

T25, T27, T30, T40

 lbs. 2.82

[SHOP](#)

Wiha Socket Sets On Molded Rails


[SHOP](#)

76191 10 pc. **TORX**® Socket Set

1/4" Square Drive Replaceable Bit Socket.
 Bits CVM tool steel. OAL 1.5"

Item No. 

76191 lbs. Set includes the following:

.48 T7, T8, T9, T10, T15,
 T20, T25, T27, T30, T40

Security Torx®



[SHOP](#)

70195 10 pc. Security **TORX**® Socket Set 1/4" Square drive replaceable bit socket. 1/4" Bits CVM tool steel.

Item No. 

70195 lbs. Set includes the following:

.48 T7s, T8s, T9s, T10s, T15s,
 T20s, T25s, T27s, T30s, T40s


[SHOP](#)


76194 6 pc. **TORX**® Socket Set

1/4" Square Drive Replaceable Bit Socket. Bits CVM tool steel.

Item No. 

76194 lbs. Set includes the following:

.20 T10, T15, T20, T25, T27, T30


[SHOP](#)

76397 9 pc. Security **TORX**® Socket Set 1/4" & 3/8"

Square Drive Replaceable Bit Socket. 1/4" & 5/16" Bits CVM tool steel.

Item No. 

76397 lbs. Set includes the following:

.85 1/4": T10s, T15s, T20s, T25s, T27s, T30s
 3/8": T40s (1/4" bit)
 3/8": T45s, T50s (5/16" bit)



[SHOP](#)

76395 8 pc. **TORX**® Socket Set 3/8" Square Drive Replaceable Bit Socket. Bits CVM tool steel. OAL 1.5"

Item No. 

76395 lbs. Set includes the following:

.60 T9, T10, T15, T20, T25,
 T27, T30, T40



[SHOP](#)

76399 12 pc. Security **TORX**® Socket Set 1/4" & 3/8" Square Drive Replaceable Bit Socket. 1/4" & 5/16" Bits CVM tool steel.

Item No. 

76399 lbs. Set includes the following:

.77 1/4": T7s, T8s, T10s, T15s, T20s, T25s, T27s, T30s, T40s
 5/16": T45s, T50s, T55s


[SHOP](#)

76396 8 pc. **TORX**® Socket Set 3/8" Square Drive Replaceable Bit Socket. 1/4" & 5/16" Bits CVM tool steel. OAL 1.65"

Item No. 

76396 lbs. Set includes the following:

.84 1/4": T20, T25, T27, T30, T40,
 5/16": T45, T50, T55


[SHOP](#)

71698 8 pc. **TORXPlus**® Socket Set On Rail, In Vinyl Pouch


1/4" & 3/8" Square Drive Replaceable Bit Socket. Bits Chrome-
 vanadium-molybdenum tool steel.

Item No. 

71698 lbs. Set includes the following:

.60 1/4": IP9, IP10, IP15, IP20
 3/8": IP25, IP27, IP30, IP40

Wiha Socket Sets On Molded Rails



[SHOP](#)


71391 10 Piece Hex Inch Socket Set 1/4" Square drive replaceable bit socket. Bits CVM tool steel. OAL 1.5"

Item No. 

71391 lbs. Set includes the following:

.48 1/16, 5/64, 3/32, 7/64, 1/8

9/64, 5/32, 3/16, 7/32, 1/4"



[SHOP](#)

71798 8 Piece Ball End Hex Inch Socket Set 1/4" Square Drive Replaceable Bit Socket. 1/4" Bits CVM tool steel. OAL

Item No. 

71798 lbs. Set includes the following:

.72 3/32, 7/64, 1/8, 9/64, 5/32,

3/16, 7/32, 1/4"



[SHOP](#)

71398 7 Piece Ball End Hex Inch Socket Set 1/4" Square Drive Replaceable Bit Socket. 1/4" Bits CVM tool steel. OAL

Item No. 

71398 lbs. Set includes the following:

.48 3/32, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4"



[SHOP](#)

71797 7 Piece Ball End Hex Metric Socket Set 1/4" Square Drive Replaceable Bit Socket. 1/4" Bits CVM tool steel.

Item No. 

71797 lbs. Set includes the following:

.72 Hex Metric: 1.5, 2.0, 2.5, 3.0, 4.0, 5.0, 6.0mm



[SHOP](#)

71392 8 Piece Hex Inch Socket Set 3/8" Square Drive Replaceable Bit Socket. 1/4" Bits CVM tool steel. OAL 1.65"

Item No. 

71392 lbs. Set includes the following:

.78 1/8, 9/64, 5/32, 3/16, 7/32, 1/4, 5/16, 3/8"



[SHOP](#)

71393 5 Piece Hex Inch Socket Set 3/8" Square Drive Replaceable Bit Socket. 1/4" Bits Chrome-vanadium-molybdenum tool steel.

Item No. 

71393 lbs. Set includes the following:

.54 Hex Inch: 1/8, 3/16, 1/4, 5/16, 3/8"



[SHOP](#)

71394 5 Piece Hex Metric Socket Set 3/8" Square Drive Replaceable Bit Socket. 1/4" Bits CVM tool steel.

Item No. 

71394 lbs. Set includes the following:

.56 Hex Metric: 4.0, 5.0, 6.0, 8.0, 10.0mm



[SHOP](#)


71996 9 Piece Hex Metric Socket Set 1/4" & 3/8" Square Drive Replaceable Bit Socket. 1/4" Bits CVM tool steel. OAL 1.65"

Item No. 

71996 lbs. Set includes the following:

.66 1/4": 1.5, 2.0, 2.5, 3.0, 4.0mm

3/8": 5.0, 6.0, 8.0, 10.0mm



[SHOP](#)

71999 9 Piece Security Hex Inch Socket Set 3/8" Square Drive Replaceable Bit Socket. 1/4" Bits CVM tool steel.

Item No. 

71999 lbs. Set includes the following:

.86 Inch: 5/64, 3/32, 7/64, 1/8, 9/64, 5/32,

3/16, 7/32, 1/4"



[SHOP](#)

71989 7 Piece Security Hex Metric Socket Set 3/8" Square Drive Replaceable Bit Socket. 1/4" Bits CVM tool steel.

Item No. 

71989 lbs. Set includes the following:

.72 Metric: 2.0, 2.5, 3.0, 4.0, 5.0, 6.0, 8.0mm

Item No.	Page	Item No.	Page	Item No.	Page	Item No.	Page	Item No.	Page	Item No.	Page
28103	40	70146	26	70558	10	71183	27	71362	17	71512	7
28180	39	70147	26	70559	10	71194	28	71363	17	71513	7
28200	33	70148	10	70560	10	71195	8	71364	17	71515	6
28291	33	70150	10	70561	10	71196	28	71365	17	71516	27
28295	8	70151	10	70562	10	71197	27	71366	17	71517	27
28296	33	70152	10	70563	10	71198	14	71367	17	71518	27
28297	11	70153	10	70564	10	71199	14	71368	17	71519	27
28298	20	70154	10	70565	10	71200	24	71369	17	71520	6
28299	20	70155	10	70566	10	71201	24	71370	45	71521	27
28489	40	70156	10	70567	10	71202	24	71371	45	71522	27
28589	34	70157	10	70568	10	71203	24	71372	45	71523	6
28590	34	70158	10	71001	22	71211	27	71373	17	71524	6
28593	34	70159	10	71002	22	71212	27	71374	45	71525	6
28595	34	70160	10	71003	22	71213	27	71375	45	71527	6
35510	26	70163	10	71004	22	71221	27	71376	45	71530	6
35512	26	70168	10	71010	27	71222	27	71377	45	71536	9
35514	26	70170	17	71011	27	71223	27	71378	45	71537	9
35516	26	70171	17	71012	27	71241	24	71379	45	71538	9
38003	8	70172	17	71013	27	71242	24	71380	45	71539	9
38004	8	70173	17	71014	27	71243	24	71381	45	71540	6
38006	32	70174	17	71020	27	71250	24	71382	45	71541	9
38007	32	70175	17	71021	27	71251	24	71383	45	71542	9
38008	8	70176	17	71022	27	71252	24	71384	45	71543	9
38009	11	70190	11	71023	27	71253	24	71385	45	71544	9
38010	11	70195	47	71024	27	71254	24	71386	45	71545	9
38014	21	70401	16	71030	23	71300	45	71387	17	71546	9
38015	41	70402	16	71031	23	71301	45	71388	45	71547	9
38016	30	70405	16	71032	23	71302	45	71390	45	71548	6
38017	30	70407	24	71033	23	71303	17	71391	48	71549	6
38018	30	70408	24	71034	23	71304	19	71392	48	71550	6
38025	41	70410	24	71035	23	71305	45	71393	48	71551	6
38026	30	70411	7	71036	23	71306	17	71394	48	71552	6
38027	30	70413	7	71051	23	71307	19	71396	17	71553	6
38028	8,30	70414	7	71052	23	71308	17	71397	17	71554	6
38030	32,40	70416	7	71053	23	71309	17	71398	48	71555	6
38033	32	70417	7	71054	23	71310	19	71399	21	71556	6
38043	32	70424	43	71055	23	71311	19	71404	16	71557	6
38045	8	70427	43	71056	14	71312	17	71414	16	71558	6
38047	11	70430	43	71090	31	71313	45	71424	16	71559	6
38048	32	70437	42	71094	27	71314	45	71431	42	71560	6
38056	21	70438	42	71095	29	71315	17	71433	42	71561	6
38057	20	70440	42	71100	14	71316	45	71435	42	71562	28
38058	20	70442	42	71101	14	71317	45	71437	42	71563	28
38059	32	70445	42	71102	14	71318	17	71439	42	71564	28
38060	41	70448	42	71103	14	71319	45	71441	42	71565	28
38450	40	70450	42	71105	15	71320	45	71452	16	71566	28
38460	40	70462	42	71106	15	71321	17	71453	16	71567	28
38600	40	70463	42	71107	15	71322	45	71455	16	71568	28
38701	39	70464	42	71111	27	71323	45	71456	16	71569	28
38790	39	70466	42	71112	27	71324	17	71464	16	71570	6
38800	40	70468	42	71113	27	71325	45	71465	16	71571	6
48400	40	70469	42	71121	28	71326	17	71466	16	71574	27
48401	40	70470	42	71122	28	71327	45	71470	42	71576	27
52650	40	70472	42	71123	28	71328	17	71474	41	71578	27
66850	40	70474	43	71125	14	71329	17	71475	41	71580	27
70107	44	70476	43	71126	15	71330	17	71476	41	71582	27
70108	44	70477	43	71127	15	71331	45	71477	41	71584	27
70109	44	70479	43	71128	15	71332	45	71478	41	71585	28
70110	44	70490	43	71130	42	71333	17	71479	41	71586	28
70113	44	70491	43	71131	42	71336	17	71480	26,41	71587	28
70115	44	70492	43	71133	16	71339	17	71490	41	71588	28
70117	44	70493	43	71134	16	71340	45	71491	41	71596	28
70119	44	70494	43	71135	16	71341	45	71492	42	71603	12
70121	44	70507	10	71141	28	71342	17	71493	42	71604	12
70123	44	70508	10	71142	28	71343	19	71494	41	71605	12
70127	10	70509	10	71143	28	71345	17	71499	42	71606	12
70128	10	70510	10	71149	14	71346	19	71500	7	71607	12
70129	10	70515	10	71150	14	71348	17	71501	7	71608	12
70130	23	70520	10	71151	14	71349	19	71502	7	71609	12
70131	23	70525	10	71152	14	71351	17	71503	7	71610	12
70132	23	70527	10	71153	14	71352	19	71504	7	71615	12
70133	23	70530	10	71154	14	71353	17	71505	6	71620	12
70135	10	70540	10	71155	14	71354	19	71506	6	71625	12
70139	10	70545	10	71165	15	71356	17	71507	6	71627	12
70142	10	70550	10	71166	15	71358	19	71508	6	71630	12
70143	26	70555	10	71167	15	71359	17	71509	6	71631	12
70144	26	70556	10	71181	27	71360	17	71510	6	71632	12
70145	26	70557	10	71182	27	71361	17	71511	7	71633	12

Item No.	Page	Item No.	Page	Item No.	Page	Item No.	Page	Item No.	Page	Item No.	Page
71634	12	71764	45	71976	18	72575	6	74136	15	74379	19
71635	12	71765	45	71977	18	72576	6	74141	27	74380	18
71636	12	71766	45	71978	18	72577	6	74142	27	74381	18
71637	12	71767	45	71979	18	72578	6	74143	27	74382	18
71638	12	71768	45	71980	18	72579	6	74150	15	74383	18
71639	12	71771	45	71981	18	72580	6	74161	27	74384	18
71640	12	71772	45	71982	18	72581	6	74162	27	74385	18
71641	12	71773	45	71983	18	72582	17	74163	27	74386	18
71642	12	71774	45	71984	18	72583	17	74164	15	74387	18
71643	12	71775	45	71985	18	72584	17	74165	15	74388	18
71644	12	71776	45	71988	28	72585	17	74166	15	74411	7
71645	12	71777	45	71989	48	72586	17	74167	15	74413	7
71648	12	71797	48	71990	29	72587	17	74168	15	74415	7
71650	12	71798	48	71991	29	73301	17	74201	24	74417	7
71652	12	71801	22	71992	29	73302	17	74203	24	74419	7
71654	12	71802	22	71994	29	73303	17	74205	24	74421	7
71656	12	71803	22	71995	21	73304	17	74207	24	74423	7
71657	12	71851	22	71996	48	73305	17	74212	24	74429	7
71658	12	71852	22	71997	29	73306	17	74214	24	74431	7
71660	12	71853	22	71998	21	73307	17	74216	24	74433	7
71661	44	71854	22	71999	48	73308	17	74221	24	74435	7
71662	44	71900	25	72001	46	73309	17	74225	24	74460	7
71663	44	71901	25	72002	46	73310	9	74241	27	74461	7
71664	44	71902	25	72003	46	73311	9	74242	27	74462	7
71665	44	71903	25	72004	46	73312	9	74243	27	74463	7
71666	44	71904	25	72005	46	73313	9	74261	24	74464	7
71667	44	71905	25	72006	46	73314	9	74262	24	74465	7
71668	44	71906	25	72014	45	73315	9	74263	24	74466	7
71669	44	71907	25	72025	23	73316	9	74301	19	74467	7
71670	44	71908	25	72031	23	73317	9	74303	16,23	74468	7
71671	44	71909	25	72038	45	73318	9	74304	16	74469	7
71673	44	71910	25	72039	23	73319	9	74305	19	74470	7
71674	44	71911	25	72047	23	73320	9	74306	16,23	74501	7
71675	44	71912	25	72048	23	74003	22	74307	19	74502	7
71676	44	71913	25	72049	23	74006	22	74308	16	74503	7
71677	44	71914	26	72050	23	74009	22	74309	16,23	74504	7
71678	44	71916	26	72051	23	74010	22	74310	16	74505	13
71680	44	71918	26	72090	46	74012	22	74311	18	74506	7
71681	44	71920	26	72102	15	74015	22	74312	18	74508	7
71690	13	71921	25	72103	15	74018	22	74313	18	74510	7
71692	13	71922	25	72104	15	74021	22	74314	18	74511	7
71698	47	71923	25	72110	46	74023	22	74315	18	74512	7
71701	19	71924	25	72115	46	74033	23	74316	18	74513	7
71702	19	71930	18	72388	17	74034	23	74317	18	74514	7
71703	19	71932	18	72401	46	74035	23	74318	18	74515	7
71704	19	71934	18	72405	46	74036	23	74319	19	74516	7
71705	19	71936	18	72410	46	74039	23	74325	18	74517	7
71706	19	71938	18	72415	46	74041	23	74330	18	74518	7
71707	19	71939	18	72519	14	74050	23	74340	18	74519	7
71708	19	71940	18	72521	14	74061	23	74341	18	74520	13
71711	19	71941	18	72522	14	74062	23	74342	18	74521	7
71712	19	71942	18	72523	14	74063	23	74343	18	74522	13
71713	19	71943	18	72525	6	74064	23	74344	18	74523	7
71714	19	71944	18	72527	6	74065	23	74345	18	74524	13
71715	19	71945	18	72530	6	74066	23	74346	18	74526	13
71716	19	71946	18	72531	6	74067	23	74347	18	74528	13
71717	19	71949	25	72534	23	74068	23	74348	18	74529	7
71718	19	71950	25	72535	23	74069	23	74349	18	74531	7
71719	19	71951	25	72536	23	74101	28	74350	18	74532	13
71720	19	71952	25	72540	6	74103	15	74351	18	74533	7
71721	19	71953	25	72541	6	74105	28	74352	18	74534	13
71722	19	71954	25	72542	10	74106	15	74353	18	74535	7
71723	19	71955	18	72545	6	74108	28	74354	18	74536	7
71724	19	71956	18	72546	6	74109	15	74355	18	74537	13
71725	19	71957	25	72547	10	74111	15	74356	18	74538	7
71726	19	71958	25	72550	6	74112	15	74357	18	74539	13
71728	19	71959	25	72551	6	74113	15	74360	18	74541	13
71730	19	71960	18	72552	10	74115	15	74361	18	74542	7
71732	19	71963	26	72555	6	74116	15	74362	18	74543	13
71734	19	71964	26	72556	6	74118	15	74363	18	74544	7
71736	19	71965	26	72557	10	74121	15	74364	18	74545	13
71738	19	71966	26	72562	10	74123	15	74365	18	74546	7
71740	19	71970	18	72563	10	74124	15	74366	18	74547	13
71750	19	71971	18	72564	10	74126	15	74369	19	74548	7
71760	19	71972	18	72567	10	74127	15	74371	19	74549	13
71761	45	71973	18	72572	6	74130	15	74373	19	74550	13
71762	45	71974	18	72573	6	74131	15	74375	19	74551	7
71763	45	71975	18	72574	6	74133	15	74377	19	74552	13

Item No.	Page	Item No.	Page	Item No.	Page	Item No.	Page	Item No.	Page	Item No.	Page
74553	7	74901	25	75709	36	76191	47	76550	5	76896	5
74554	13	74902	25	75710	36	76194	47	76553	5	77101	46
74555	13	74903	25	75715	36	76312	44	76554	5	77103	46
74556	7	74904	25	75720	36	76314	44	76555	5	77105	46
74557	13	74911	25	75727	36	76316	44	76556	5	77107	46
74558	7	74912	25	75728	36	76318	44	76557	5	77109	46
74561	7	74913	25	75729	36	76322	44	76558	5	77111	46
74562	13	74914	25	75735	36	76324	44	76559	5	77113	46
74563	7	74915	25	75739	36	76326	44	76563	5	77115	46
74564	13	74960	25	75742	36	76328	44	76564	5	77117	46
74565	7	74961	25	75743	36	76329	44	76565	5	77128	46
74567	7	74962	25	75744	36	76330	44	76566	5	77130	46
74569	7	74963	25	75745	36	76331	44	76570	5	77132	46
74571	7	74964	25	75746	36	76332	44	76571	5	77134	46
74573	7	74965	25	75747	36	76333	44	76572	5	77136	46
74575	7	74966	25	75748	36	76334	44	76573	5	77138	46
74577	7	74967	25	75792	37	76335	44	76574	5	77139	46
74579	7	74968	25	75800	35	76336	44	76575	5	77140	46
74581	7	74981	9	75801	35	76337	44	76578	5	77141	46
74583	7	74982	13	75802	36	76338	44	76579	5	77142	46
74586	7	74983	33	75803	36	76339	44	76580	5	77144	46
74587	7	74985	8	75810	36	76340	44	76801	4	77146	46
74588	7	74986	20	75811	36	76341	44	76802	4	77148	46
74589	7	74987	11	75812	36	76342	44	76803	4	77151	46
74590	7	74988	33	75813	36	76346	44	76806	4	77152	46
74591	7	74989	21	75814	36	76348	44	76807	4	77153	46
74601	12	74990	43	75815	36	76352	44	76808	4	77154	46
74602	12	74992	33	75816	36	76354	44	76810	4	77156	46
74603	12	74996	33	75817	36	76395	47	76811	4	77158	46
74604	12	74999	21	75820	36	76396	47	76812	4	77160	46
74608	12	75008	35	75821	36	76397	47	76813	4	77162	46
74612	12	75012	35	75822	36	76399	47	76814	4	77164	46
74616	12	75015	35	75823	36	76403	44	76816	4	77165	46
74620	12	75018	35	75824	36	76404	44	76817	4	77167	46
74624	12	75020	35	75825	36	76405	44	76823	4	77169	46
74628	12	75025	35	75826	36	76406	44	76824	4	77171	46
74632	12	75030	35	75827	36	76407	44	76825	4	77173	46
74636	12	75035	35	75900	35	76411	44	76826	4	77175	46
74659	12	75040	35	75901	35	76412	44	76830	4	77177	46
74660	12	75093	39	75902	36	76413	44	76831	4	77179	46
74661	12	75094	39	75965	38	76414	44	76832	4	77191	46
74662	12	75095	39	75981	38	76417	44	76833	4	77192	46
74663	12	75096	39	75983	38	76418	44	76834	4	77193	46
74664	12	75105	35	75985	38	76419	44	76835	4	77195	46
74665	12	75110	35	75989	38	76422	44	76838	4	77198	46
74666	12	75115	35	75990	38	76423	44	76839	4	78002	26
74667	12	75120	35	75991	37	76424	44	76840	4	78005	26
74668	12	75307	35	75992	37	76501	4	76843	5	78008	26
74669	12	75309	35	75994	37	76502	4	76844	5	78011	26
74670	12	75313	35	75996	37	76503	4	76845	5	78015	26
74711	9	75315	35	75999	37	76506	4	76848	5	78018	26
74714	9	75320	35	76106	44	76507	4	76849	5	78615	26
74717	9	75322	36	76107	44	76508	4	76850	5	78617	26
74721	9	75325	35	76109	44	76510	4	76853	5	78619	26
74724	9	75327	36	76111	44	76511	4	76854	5	78621	26
74728	9	75330	35	76113	44	76512	4	76855	5	78622	26
74732	9	75332	36	76117	44	76513	4	76856	5	78624	26
74736	9	75340	35	76119	44	76514	4	76857	5	79242	8
74739	9	75342	36	76121	44	76516	4	76858	5	79243	31
74742	9	75350	35	76123	44	76517	4	76859	5	79245	8
74760	9	75352	35	76129	44	76523	4	76863	5	79246	20
74761	9	75354	35	76131	44	76524	4	76864	5	79247	11
74762	9	75356	35	76132	45	76525	4	76865	5	79248	31
74763	9	75358	35	76133	45	76526	4	76866	5	79256	20
74764	9	75360	35	76134	45	76530	4	76870	5	79266	21
74765	9	75362	36	76135	45	76531	4	76871	5	79276	21
74766	9	75364	36	76136	45	76532	4	76872	5	79283	9
74767	9	75366	36	76137	45	76533	4	76873	5	79443	31
74768	9	75368	36	76138	45	76534	4	76874	5	79445	8
74769	9	75370	36	76164	45	76535	4	76875	5	79446	20
74813	22	75372	36	76165	45	76538	4	76878	5	79447	11
74816	22	75395	37	76166	45	76539	4	76879	5	79450	13
74819	22	75703	36	76167	45	76540	4	76880	5	79490	31
74860	22	75704	36	76168	45	76543	5	76891	5	79495	31
74861	22	75705	36	76169	45	76544	5	76892	5	91247	5
74862	22	75706	36	76170	45	76545	5	76893	5	91313	5
74890	22	75707	36	76171	45	76548	5	76894	5		
74895	22	75708	36	76172	45	76549	5	76895	5		

(800) 494-6104
 fax: (800) 494-7456
 email: cservice@wihatools.com
www.wihatools.com

**SEE OUR GREAT
 WEB SPECIALS!**



Wiha Quality Tools

1348 Dundas Circle
 Monticello, MN 55362
 tel: 763.295.6591
 fax: 763.295.6598

Wiha Tools Canada Ltd.

www.wihatools.ca
 Brampton, ONT L6T 4X4
 tel: 866.494.0096 or 763.295.6591
 fax: 763.295.6598

To:

Catalog Item No. 99951.wo
 version - 5/15/14

**Subject to change
 without notice**

©2014 Willi Hahn Corporation

®Torx is a registered trademark of
 Acument Intellectual Properties LLC.




91330.wo - Tooling Catalog



99004.wo - Shop Tools Catalog



99914.wo - TORX Catalog



99002.wo - Screwdrivers Catalog



99919.wo - Insulated Catalog



99001.wo - TorqueControl Catalog



99934.wo - Hex Tools Catalog



99006.wo - Tech Tools Catalog



99945.wo - ESD Catalog



99977.wo - Pliers/Crimpers Catalog