



- Superior adhesive for long term reliability
- 2-up mount configuration speeds liner removal and installation
- 4-way cable tie entry makes part orientation fast and easy
- Adhesive backing allows routing of wires and cables where mounting holes cannot be drilled
- Used with *PANDUIT*® cable ties for a complete wire routing solution

‡ Cable Tie Cross Section Sizes: M = Miniature, I = Intermediate, S = Standard, HS = Heavy-Standard, LH = Light-Heavy, H = Heavy, HLM = Miniature *Tak-Ty*® Hook & Loop Cable Ties.

Part Number:	ABM2S-A-C0
Product Family:	4-Way Adhesive Backed Cable Tie Mounts
Product Line:	Adhesive Backed

RoHS Compliancy Status: Compliant

Part Description:	4-Way Adhesive Backed Cable Tie Mount
-------------------	---------------------------------------

Product Type:	Cable Tie Mounts - Adhesive Backed
---------------	------------------------------------

Material:	Weather Resistant ABS
-----------	-----------------------

Color:	Black
--------	-------

UL Recognized:	E136577
----------------	---------

Height (In.):	.16
---------------	-----

Height (mm):	4.2
Length (In.):	1.00
Length (mm):	25.4
Width (In.):	1.00
Width (mm):	25.4
Adhesive Type:	Rubber
CE Compliant:	CT-ACC1 / 10.96
Environment:	Indoors
Max. Static Load (g):	227
Max. Static Load (Lbs.):	.50
Metric Screw Size:	M3
Mounting Method:	Adhesive Backed
Screw Size:	#6 (M3)
Std. Pkg. UOM:	PK
Used With Cable Ties:	M, I, S,
UOM:	PC
Std. Pkg. Qty.:	100
Min. Order Qty.:	100