

2014



Professional Insulated Tools

Supporting Arc Flash Protection

10,000 Volt Tested
1000 Volt Rated



#32800

Complete Insulated Program



Arc Flash Protection:

Wiha Insulated tools can be a vital component in your Arc Flash protection strategy. What is Arc Flash?

ARC FLASH

An Arc Flash is an electrical explosion due to a fault condition or short circuit when either a phase to ground or phase to phase conductor is connected. Arc flashes cause electrical equipment to explode, resulting in an arc-plasma fireball. Temperatures may exceed 35,000° F (the surface of the sun is 9000° F). These high temperatures cause rapid heating of surrounding air and extreme pressures, resulting in an arc blast. The arc blast will likely vaporize all solid copper conductors which will expand up to 67,000 times its original volume when it is vaporized. The result of this violent event is usually destruction of the equipment involved, fire, and severe injury or death to any nearby people.

WHY ARC FLASHES HAPPEN

There are a variety of reasons why an Arc Flash can occur, but most of them are preventable. Most arc flashes occur when maintenance workers are manipulating live equipment for testing or repair and accidentally cause a fault. Improper tools, improper electrical equipment, corrosion of equipment, improper work techniques and lack of training are just some of the events that can lead to a devastating arc flash or arc blast.

ARC FLASH COMPLIANCE

There are 4 main regulations that govern electrical safety & arc flash:

1. OSHA Standards 29CFR, Part 1910. Occupational Safety and Health Standards. 1910 sub part S (electrical) Standard number 1910.333 specifically addresses Standards for Work Practices and references NFPA 70E. OSHA 29CFR 1910.335 (a) (1)(i) requires the use of protective equipment when working where a potential electrical hazard exists and 29CFR 1910.132(d)(1) which requires the employer assess the workplace for hazards and the need for personal protective equipment. OSHA compliance is required by any plant building or facility.

2. The National Fire Protection Association (NFPA) Standard 70 - 2002 "The National Electrical Code" (NEC) contains requirements for warning labels.

3. NFPA 70E provides guidance on implementing appropriate work practices that are required to safeguard workers from injury while working on or near exposed electrical conductors or circuit parts that could become energized. Part II 2-1.3.3 regarding Arc Flash Analysis states that a "Flash Hazard Analysis shall be done before a person approaches any exposed electrical conductor or circuit part that has not been placed in an electrical safe work condition". This Arc Flash Hazard Analysis must be done to determine the level of Personal Protection Equipment PPE that a worker must use, and the Arc Flash Boundary in inches along with the incident energy found at each location. Each panel must be marked with an ANSI z535 approved Arc Flash Warning Label.



4. The Institute of Electronics and Electrical Engineers (IEEE) 1584 - 2002 Guide to Performing Arc-Flash Hazard Calculations

copyright © information by: American Trainco, Inc.
<http://www.martinarflash.com>

OSHA

Wiha tools assists with compliance of OSHA 29CFR 1910 (Sub Parts electrical standard)

Wiha Insulated Wrenches

Description	Page
 Insulated Open End Spanners	4-5
 Insulated Gear Wrenches	6
 Ins. Offset Ring Wrenches	7

Wiha Insulated Adjustable Wrenches

Description	Page
 Insulated Adjustable Wrenches	8
8.0, 10.0, 12.0, 15.0"	

Wiha Insulated L-keys

Description	Page
 Insulated L-keys	9


Wiha Insulated 3/8" Hex Drive Bit Sockets

Description	Page
 Ins. 3/8" Hex Dr. Bit Sockets	10

Wiha Insulated Electrician's Knives

Description	Page
 Insulated Knives	8

Wiha Insulated Socket Accessories

Description	Page
 Insulated Sockets 1/4, 3/8, 1/2"	10-14
 Insulated Ratchets	10,13,15
 Insulated T-handle	10,13,15
 Insulated Extension Bars	11,13,15

Wiha Insulated Cable Cutters

Description	Page
 Insulated Cable Cutters	15

Wiha Insulated Hacksaw

Description	Page
 Insulated Hacksaw	15

Wiha Insulated Multi-Bit Holders

Description	Page
 Insulated Multi-Bit Drivers	18

Wiha Insulated SlimLine Tools

Description	Page
 Insulated SlimLine Handle	19
 Insulated SlimLine Blades	19-20
 Insulated SlimLine Blade Sets	20
 Insulated SlimLine Drivers	21
 Insulated SlimLine Driver Sets	22

Wiha Insulated BitFlip Sets

Description	Page
 Insulated BitFlip Sets	27

Wiha Insulated Belt Pack Pouch Sets

Description	Page
 Insulated Belt Pack Pouches	28
Pliers & Cutters	
Pliers/Cutters & Screwdrivers	
Pliers/Cutters & Multi Bit Set	


Wiha Insulated Inomic Pliers

Description	Page
 Insulated Inomic Pliers	37
Inomic Combo Pliers	
Inomic Long Nose Pliers	
Inomic Diagonal Cutters	

Wiha Insulated Industrial Pliers/Cutters

Description	Page
 Insulated Industrial Pliers/Cutters	38-41

Wiha Insulated Tools

Description	Page
 Xeno Terminal Block Combination Screwdrivers	26
 Insulated TorqueControl Handle & Blade Holder	18
 Insulated Voltage Detectors	27
 Insulated Hex Inch/Metric T-handles	17
 Insulated Slotted Drivers	23-24
 Insulated Phillips Drivers	23-24
 Insulated Torx Drivers	26
 Insulated Nut Drivers	25-26
 Insulated Square Tip Drivers	24
 Insulated Tweezers	16

Wiha Insulated 1000Volt Pliers/Cutters

Description	Page
 Insulated Lineman's Pliers	34
 Insulated Combination Pliers	34
 Insulated Heavy Duty Diagonal Cutters	35
 Insulated Serrated Edge Cable Cutter	35
 Insulated Bent Nose Pliers	36
 Insulated Long Nose Pliers	36
 Insulated Round Nose Pliers	36
 Insulated Stripping Pliers	36
 Insulated Pliers Sets	29-33

Wiha Insulated Open-End Wrenches

Insulation Test Standards:

Insulation according to ASTM F-1505-01,
 EN/IEC 60900, VDE 0680, DIN 7446
 and CSA

Each tool individually
 tested to 10,000 volts
 and certified to 1000
 Volt ac or 1500 Volt dc

Insulation

High visibility, grip is
 double coated

Steel

Forged from chrome
 vanadium, meets - DIN 3110

Angled 15°

 **1000V**



 **1000V**

[SHOP](#)

20190 14 Piece Insulated Inch Open End Wrench Set

Item No.	Ø	OAL	Ø	OAL	Weight
	Inch	Inch	Inch	Inch	lbs.
20190	5/16	3.9	3/4	7.0	5.70
	3/8	4.1	13/16	7.5	
	7/16	4.6	7/8	7.6	
	1/2	5.5	15/16	7.9	
	9/16	5.7	1	8.4	
	5/8	6.2	1-1/16	9.2	
	11/16	6.5	1-1/8	9.1	



 **1000V**

[SHOP](#)

20091 15 Piece Insulated Metric Open End Wrench Set

Item No.	Ø _{MM}	OAL	Ø _{MM}	OAL	Weight
	mm	mm	mm	mm	lbs.
20091	6.0	97	14	150	3.0
	7.0	98	15	151	
	8.0	104	16	164	
	9.0	108	17	162	
	10.0	107	19	178	
	11.0	118	22	196	
	12.0	129	24	211	
	13.0	137			



 **1000V**

[SHOP](#)

20192 8 Piece Insulated Inch Open End Wrench Set

Item No.	Ø	OAL	Ø	OAL	Weight
	Inch	Inch	Inch	Inch	lbs.
20192	5/16	3.9	9/16	5.7	1.59
	3/8	4.1	5/8	6.2	
	7/16	4.6	11/16	6.5	
	1/2	5.5	3/4	7.0	



 **1000V**

[SHOP](#)

20093 8 Piece Insulated Metric Open End Wrench Set

Item No.	Ø _{MM}	OAL	Ø _{MM}	OAL	Weight
	mm	mm	mm	mm	lbs.
20093	6.0	97	13.0	137	1.4
	7.0	98	14.0	150	
	8.0	104	17.0	162	
	10.0	107	19.0	178	


 **1000Volt**

201 Inch Open-End Wrenches, With Insulated Handle

Insulation According to VDE Specification 0680 and EN/IEC 60900, DIN 7446 and CSA, up to 1000 Volt. Individually Tested.

Chrome-vanadium steel, hardened. Angled 15°.

Item No.		OAL	OAL		
	Inch	mm	Inch	lbs.	pkg.
20131	1/4	87.5	3.4	.04	1
20133	5/16	100	3.9	.05	1
20135	3/8	105	4.1	.09	1
20136	7/16	117	4.6	.09	1
20137	1/2	140	5.5	.15	1
20138	9/16	146	5.7	.15	1
20140	5/8	158	6.2	.20	1
20141	11/16	165	6.5	.23	1
20142	3/4	178	7.0	.33	1
20144	13/16	191	7.5	.42	1
20145	7/8	192	7.6	.44	1
20146	15/16	201	7.9	.51	1
20147	1	213	8.4	.61	1
20148	1-1/16	233	9.2	.79	1
20149	1-1/8	233	9.2	.77	1
20151	1-1/4"	191	7.5	.90	1
20154	1-1/2"	191	7.5	.92	1

* Lengths are +/- 5% due to coating process


 **1000Volt**

200 Metric Open-End Wrenches, With Insulated Handle

Insulation According to VDE Specification 0680 and EN/IEC 60900, DIN 7446 and CSA, up to 1000 Volt. Individually Tested.

Chrome-vanadium steel, hardened. Angled 15°.

Item No.		OAL	OAL		
	mm	mm	Inch	lbs.	pkg.
20006	6.0	97	3.8	.04	1
20007	7.0	98	3.9	.05	1
20008	8.0	104	4.1	.07	1
20009	9.0	108	4.3	.07	1
20010	10.0	107	4.2	.08	1
20011	11.0	118	4.6	.11	1
20012	12.0	129	5.1	.11	1
20013	13.0	137	5.4	.19	1
20014	14.0	150	5.9	.19	1
20015	15.0	151	5.9	.17	1
20016	16.0	164	6.5	.22	1
20017	17.0	168	6.4	.24	1
20018	18.0	173	6.8	.41	1
20019	19.0	178	7.0	.32	1
20020	20.0	190	6.9	.36	1
20022	22.0	196	7.7	.39	1
20024	24.0	211	8.3	.58	1
20027	27.0	218	8.6	.68	1
20030	30.0	235	9.3	.97	1
20032	32.0	237	9.3	1.01	1

 **1000Volt**


In Tool Box Tray



20194 13 Piece Insulated Inch Open End Wrench Set

In Tool Box Tray

Item No.		OAL		OAL	
	Inch	Inch	Inch	Inch	lbs.
20194	1/4	3.4	11/16	6.5	4.90
	5/16	3.9	3/4	7.0	
	3/8	4.1	13/16	7.5	
	7/16	4.6	7/8	7.6	
	1/2	5.5	15/16	7.9	
	9/16	5.7	1	8.4	
	5/8	6.2			

In Tool Box Tray


 **1000Volt**


20196 13 Pc. Insulated Metric Open End Wrench Set

In Tool Box Tray

Item No.		OAL		OAL	
	mm	mm	mm	mm	lbs.
20196	8.0	104	16.0	164	4.90
	10.0	107	17.0	168	
	11.0	118	18.0	173	
	12.0	129	19.0	178	
	13.0	137	22.0	196	
	14.0	150	24.0	211	
	15.0	151			

Wiha Insulated Ratchet Wrenches

Insulation Test Standards:

Insulation according to ASTM F-1505-01,
 EN/IEC 60900, ISO 3110 and CSA
 Specification



Each tool individually
 tested to 10,000 volts
 and certified to 1000
 Volt ac or 1500 Volt dc

Steel
 Forged from chrome
 vanadium, meets - DIN 3110

1000V



1000Volt

SHOP

213 Inch Insulated Ratchet Wrenches, With Insulated Handle
 Insulation According to EN/IEC 60900, ISO 3110 Specification,
 Up To 1000 Volt. Individually Tested.

Blade chrome-vanadium steel, hardened.

Item No.	 Inch	 mm	 OAL	 OAL	 lbs.	 pkg.
21325	3/8	140	5.5	.14	1	
21327	7/16	143	5.6	.15	1	
21329	1/2	154	6.1	.18	1	
21331	9/16	162	6.4	.22	1	
21333	5/8	177	7.0	.30	1	
21335	3/4	209	8.2	.46	1	

1000Volt

SHOP

212 Metric Insulated Ratchet Wrenches, With Insulated Handle
 Insulation According to EN/IEC 60900, ISO 3110 Specification,
 Up To 1000 Volt. Individually Tested.

Blade chrome-vanadium steel, hardened.

Item No.	 mm	 mm	 OAL	 OAL	 lbs.	 pkg.
21208	8.0	125	4.9	.08	1	
21210	10.0	140	5.5	.12	1	
21212	12.0	150	5.9	.18	1	
21213	13.0	152	6.0	.18	1	
21214	14.0	163	6.4	.22	1	
21217	17.0	193	7.6	.38	1	
21219	19.0	210	8.3	.45	1	



1000Volt

SHOP

21391 6 Piece Inch Insulated Ratchet Wrenches Set

Item No.	 Inch	 OAL	 Inch	 OAL	 lbs.
21391	3/8	5.5	9/16	6.4	1.95
	7/16	5.6	5/8	7.0	
	1/2	6.1	3/4	8.2	



1000Volt

SHOP

21290 7 Piece Metric Insulated Ratchet Wrenches Set

Item No.	 mm	 mm	 mm	 mm	 lbs.
21290	8.0	4.9	14.0	6.4	2.10
	10.0	5.5	17.0	7.6	
	12.0	5.9	19.0	8.3	
	13.0	6.0			

Wiha Insulated Deep Offset Ring Wrenches

Insulation Test Standards:

Insulation according to ASTM F-1505-01, EN/IEC 60900, ISO 3110 and CSA Specification



Steel Forged from chrome vanadium, meets - DIN 3110

Each tool individually tested to 10,000 volts & certified to 1000 Volt ac or 1500 Volt dc

 **1000V**



 **1000V**

SHOP

210 Insulated Metric Offset Ring Wrenches, Insulation

According to EN/IEC 60900, ISO 3110 Specification, Up To 1000 Volt. Individually Tested. Blade Chrome-Vanadium steel, hardened.

Item No.		OAL	OAL		
No.	mm	mm	Inch	lbs.	pkg.
21008	8.0	159	6.3	.16	1
21009	9.0	159	6.3	.18	1
21010	10.0	171	6.8	.20	1
21011	11.0	178	7.0	.22	1
21012	12.0	191	7.5	.30	1
21013	13.0	194	7.6	.30	1
21014	14.0	203	8.0	.34	1
21015	15.0	203	8.0	.34	1
21017	17.0	219	8.6	.44	1
21019	19.0	241	9.5	.52	1
21020	20.0	250	9.8	.58	1
21022	22.0	257	10.1	.64	1
21024	24.0	279	11.0	.90	1
21027	27.0	286	11.3	.96	1
21030	30.0	311	12.3	1.28	1
21032	32.0	318	12.5	1.38	1



 **1000V**

SHOP

21093 15 Piece Metric Insulated Offset Ring Wrenches Set

Item No.	Metric:
21093	8.0, 9.0, 10.0, 11.0, 12.0, 13.0, 14.0, 15.0, 17.0, 19.0, 22.0, 24.0, 27.0, 30.0, 32.0mm



SHOP

21095 8 Piece Metric Insulated Offset Ring Wrenches Set

Item No.	Metric:	
21095	10.0, 11.0, 12.0, 13.0, 14.0, 15.0, 17.0, 19.0mm	lbs. 3.20



 **1000V**

SHOP

210 Insulated Inch Offset Ring Wrenches

Item No.			
No.	Inch	lbs.	pkg.
21040	1/4	.16	1
21042	5/16	.18	1
21044	3/8	.20	1
21046	7/16	.22	1
21048	1/2	.30	1
21050	9/16	.30	1
21052	5/8	.34	1
21054	11/16	.34	1
21056	3/4	.44	1
21057	25/32	.58	1
21058	13/16	.52	1
21060	7/8	.64	1
21062	15/16	.90	1
21064	1.0	.96	1
21066	1-1/16	1.28	1
21068	1-1/4	1.38	1



 **1000V**

SHOP

21094 15 Piece Inch Insulated Offset Ring Wrenches Set

Item No.	Inch:
21094	1/4, 5/16, 3/8, 7/16, 1/2, 9/16, 5/8, 11/16, 3/4, 13/16, 7/8, 15/16, 1, 1-1/16, 1-1/4"

lbs. 8.70



SHOP

21096 8 Piece Inch Insulated Offset Ring Wrenches Set

Item No.	Inch:	
21096	5/16, 3/8, 7/16, 1/2, 9/16, 5/8, 11/16, 3/4"	lbs. 3.20

Wiha Insulated Adjustable Wrenches



△ 1000Volt

76208 Insulated 8" Adjustable Wrench

Insulation According to ASTM, EN/IEC, NFPA, CSA and ISO Specification, up to 1000 Volt. Individually Tested. Etched on scale for pre-setting size. Slip guard handle for added protection.

Item No.	OAL Inch	OAL mm	Capacity Opening	Capacity lbs.	Capacity pkg.
76208	8.0	200	1"	.7	1

SHOP

△ 1000Volt

76210 Insulated 10" Adjustable Wrench

Insulation According to ASTM, EN/IEC, NFPA, CSA and ISO Specification, up to 1000 Volt. Individually Tested. Etched on scale for pre-setting size. Slip guard handle for added protection.

Item No.	OAL Inch	OAL mm	Capacity Opening	Capacity lbs.	Capacity pkg.
76210	10.0	250	1-1/4"	1.4	1

SHOP

△ 1000Volt

76212 Insulated 12" Adjustable Wrench

Insulation According to ASTM, EN/IEC, NFPA, CSA and ISO Specification, up to 1000 Volt. Individually Tested. Etched on scale for pre-setting size. Slip guard handle for added protection.

Item No.	OAL Inch	OAL mm	Capacity Opening	Capacity lbs.	Capacity pkg.
76212	12.0	300	1-1/2"	1.9	1

SHOP

△ 1000Volt

76215 Insulated 15" Adjustable Wrench

Insulation According to ASTM, EN/IEC, NFPA, CSA and ISO Specification, up to 1000 Volt. Individually Tested. Etched on scale for pre-setting size. Slip guard handle for added protection.

Item No.	OAL Inch	OAL mm	Capacity Opening	Capacity lbs.	Capacity pkg.
76215	15.0	380	1-11/16"	2.8	1

SHOP



△ 1000Volt

76290 3 Pc. Insulated Adjustable Wrenches Etched on scale for pre-setting size. Slip guard handle for added protection.

Item No.	Set includes the following:
76290	8.0", 10.0", 12.0" Adjustable Pliers

SHOP

Wiha Insulated Electrician's Knives

Insulation Test Standards:

Insulation according to ASTM, EN/IEC, VDE & CSA Specification Individually tested



Insulation molded on for permanent bonding

△ 1000V

Each tool individually tested to 10,000 volts & rated to 1000 Volt ac or 1500 Volt dc



△ 1000Volt

15000 Insulated Electrician's Cable Stripping Knife, With Insulated Handle, Insulation According To VDE Specification, Up To 1000 Volt. Individually Tested.

Blade tool steel, hardened, molded directly on. Cover included.

Item No.	Blade mm	OAL mm	OAL Inch	Capacity lbs.	Capacity pkg.
15000	50	216	8.5	.30	1

SHOP



△ 1000Volt

15003 Insulated Electrician's Cable Stripping Knife, With Insulated Handle, Insulation According To VDE Specification, Up To 1000 Volt. Individually Tested. Straight, partly insulated, strong blade. Insulation molded directly on. Cover included.

Item No.	Blade mm	OAL mm	OAL Inch	Capacity lbs.	Capacity pkg.
15003	50	230	9.0	.23	1

SHOP



△ 1000Volt

15050 Insulated Stripping Knife, With Insulated Handle Insulation According To VDE Specification, Up To 1000 Volt. Individually Tested. Blade tool steel, hardened. Insulation molded directly on. Hooked cutting edge, half-round ground. Cover included.

Item No.	Blade mm	OAL mm	OAL Inch	Capacity lbs.	Capacity pkg.
15050	35	222	8.75	.22	1

SHOP

Wiha Insulated Hex L-keys

Insulation Test Standards:
Insulation according to ASTM,
F-1505-01, EN/IEC 60900
and CSA



Insulation

Applied directly
onto blade for
permanent
bonding

1000V

Each tool individually
tested to 10,000 volts
and certified to 1000
Volt ac or 1500 Volt dc



#13691

#13690

1000Volt

SHOP

13690 8 Piece Insulated Inch Hex L-key Set

Item No.	Hex	OAL	Hex	OAL	lbs.
13690	1/8	4.1	1/4	5.3	2.17
	5/32	4.1	5/16	5.7	
	3/16	5.3	3/8	9.2	
	7/32	5.3	1/2	9.2	

13691 7 Piece Insulated Metric Hex L-key Set 1000Volt

Item No.	Hex	OAL	Hex	OAL	lbs.
13691	3.0	130	8.0	150	2.07
	4.0	120	10.0	220	
	5.0	140	12.0	260	
	6.0	140			



1000Volt

SHOP

136 Inch Insulated Hex L-keys, With Insulated Handle

Insulation According to IEC 60900 Specification, Up To 1000 Volt.
Individually Tested. Blade chrome-vanadium steel, hardened.

Item No.	Hex	OAL	OAL	lbs.	pkg.
13670	1/16	79	3.1	.05	1
13671	5/64	84	3.3	.05	1
13672	3/32	89	3.5	.05	1
13673	7/64	94	3.7	.06	1
13663	1/8	104	4.1	.06	1
13665	5/32	104	4.1	.06	1
13666	3/16	134	5.3	.10	1
13667	7/32	134	5.3	.12	1
13668	1/4	134	5.3	.16	1
13669	5/16	144	5.7	.24	1
13662	3/8	234	9.2	.51	1
13664	1/2	234	9.2	.77	1



1000Volt

SHOP

13693 10 Piece Insulated Metric Hex L-key Set 1000Volt

Item No.	Hex	OAL	Hex	OAL	lbs.
13693	1.5	100	5.0	140	2.26
	2.0	105	6.0	140	
	2.5	115	8.0	150	
	3.0	130	10.0	220	
	4.0	120	12.0	260	



1000Volt

SHOP

136 Metric Insulated Hex L-keys, With Insulated Handle

Insulation According to IEC 60900 Specification, Up To 1000 Volt.
Individually Tested. Blade chrome-vanadium steel, hardened.

Item No.	Hex	OAL	OAL	lbs.	pkg.
13650	1.5	100	3.9	.09	1
13651	2.0	105	4.1	.09	1
13652	2.5	115	4.5	.09	1
13653	3	130	5.1	.10	1
13654	4	120	4.7	.10	1
13655	5	140	5.5	.10	1
13656	6	140	5.5	.13	1
13658	8	150	5.9	.24	1
13659	10	220	8.7	.51	1
13657	12	260	10.2	.77	1

1000Volt

SHOP

13694 12 Piece Insulated Inch Hex L-key Set 1000Volt

Item No.	Hex	OAL	Hex	OAL	lbs.
13694	1/16	3.1	3/16	5.3	2.40
	5/64	3.3	7/32	5.3	
	3/32	3.5	1/4	5.3	
	7/64	3.7	5/16	5.7	
	1/8	4.1	3/8	9.2	
	5/32	4.1	1/2	9.2	

Wiha Insulated Hex Bit Sockets



 **1000Volt**



318 Insulated 3/8" Drive Sockets - Insulation according to EN/IEC 60900, DIN 7448 Specification, Up To 1000 Volt.

Individually Tested. Chrome-vanadium steel, forged, oil-hardened.

Item No.	Inch	OAL	lbs.	pkg.
31805	3/16	3.1"	.13	1
31807	7/32	3.1"	.14	1
31809	1/4	3.1"	.14	1
31811	5/16	3.1"	.16	1
31813	3/8	3.1"	.18	1
31815	7/16	3.1"	.20	1
31817	1/2	3.1"	.22	1

*Sockets must be used with insulated ratchets & extensions



 **1000Volt**



31890 7 Pc. Insulated 3/8" Drive Socket Set - Inch

CV steel, forged, oil-hardened sockets. Insulated to EN/IEC 60900.

Item No.	Set includes the following:
31890	3/16, 7/32, 1/4, 5/16, 3/8, 7/16, 1/2"

lbs. 1.7

WARNING!

Insulated Tools are intended to provide protection against accidental contact with charged energized circuits. For maximum safety we recommend de-energizing all circuits whenever possible before starting work on electrical apparatus or conductors. Always visually inspect insulation on tools before use, do not use tools if insulation shows signs of wear or damage to the insulated areas of the tool. Wear appropriate eye protection when using hand tools. Use NFPA70E certified insulated protective outer wear when appropriate.

Use & Care Guide For Insulated Tools:

Store tools to minimize risk of damage to insulation, always wear approved eye protection, Inspect insulation prior to each use of any insulated tool. Use insulated tools where the ambient temperature is between -20 to +70° C. Have a qualified safety technician visually inspect insulation on tools annually for safe use.

Wiha Insulated 1/4" Sockets & Sets

Inch -
6 Point



 **1000Volt**



313 Insulated 1/4" Drive Sockets-6 Point, Insulation According To ASTM F-1505-01, DIN 7448 & CSA Specification, Up To 1000 Volt.

Individually Tested. Chrome-vanadium steel, forged, oil-hardened.

Item No.	Inch	lbs.	pkg.
31336	3/16	.03	1
31337	7/32	.03	1
31338	1/4	.03	1
31339	9/32	.04	1
31340	5/16	.04	1
31341	11/32	.05	1
31342	3/8	.05	1
31343	7/16	.06	1
31344	1/2	.07	1
31345	9/16	.07	1

*Sockets must be used with insulated ratchets & extensions

Metric -
6 Point



 **1000Volt**



313 Insulated 1/4" Drive Sockets-6 Point, Insulation According To ASTM F-1505-01, DIN 7448 & CSA Specification, Up To 1000 Volt.

Individually Tested. Chrome-vanadium steel, forged, oil-hardened.

Item No.	mm	lbs.	pkg.
31326	5.0	.03	1
31327	6.0	.03	1
31328	7.0	.03	1
31329	8.0	.04	1
31330	9.0	.04	1
31331	10.0	.05	1
31332	11.0	.05	1
31333	12.0	.06	1
31334	13.0	.06	1
31335	14.0	.07	1

*Sockets must be used with insulated ratchets & extensions



 **1000Volt**



12851 Insulated 1/4" Drive Ratchet, EN/IEC 60900 & CSA
Chrome-Vanadium steel. Reversible.

Item No.	Inch	OAL	lbs.	pkg.
12851	1/4"	140	5.5	.28

Wiha Insulated 1/4" Sockets & Sets



⚡ 1000Volt

[SHOP](#)

31390 13 Piece Insulated 1/4" Drive Socket Set - Inch

CV steel, forged, oil-hardened sockets. Insulated after EN/IEC 60900.

Item No. 31390 Set includes the following:

	3/16, 7/32, 1/4, 9/32, 5/16, 11/32,
lbs.	3/8, 7/16, 1/2, 9/16"
1.39	1/4" x 50mm Extension Bar
	1/4" x 100mm Extension Bar
	1/4" Ratchet - 140mm



⚡ 1000Volt

[SHOP](#)

31391 13 Piece Insulated 1/4" Drive Socket Set - Metric

CV steel, forged, oil-hardened sockets. Insulated after EN/IEC 60900.

Item No. 31391 Set includes the following:

	5, 6, 7, 8, 9, 10, 11, 12, 13, 14mm
lbs.	1/4" x 50mm Extension Bar
1.41	1/4" x 100mm Extension Bar
	1/4" Ratchet - 140mm



⚡ 1000Volt

[SHOP](#)

31394 11 Piece Insulated 1/4" T-handle & Socket Set - Inch

CV steel, forged, oil-hardened sockets. Insulated after EN/IEC 60900.

Item No. 31394 Set includes the following:

	3/16, 7/32, 1/4, 9/32, 5/16, 11/32,
lbs.	3/8, 7/16, 1/2, 9/16"
1.40	Insulated 1/4" T-handle



⚡ 1000Volt

[SHOP](#)

31395 11 Piece Insulated 1/4" T-handle & Socket Set - Metric

CV steel, forged, oil-hardened sockets. Insulated after EN/IEC 60900.

Item No. 31395 Set includes the following:

	5, 6, 7, 8, 9, 10, 11, 12, 13, 14mm
lbs. 1.40	Insulated 1/4" T-handle

Each tool individually tested to 10,000 volts & certified to 1000 Volt ac or 1500 Volt dc

Wiha Insulated 1/4" Socket accessories



⚡ 1000Volt

[SHOP](#)

29006 Insulated 1/4" Drive T-handle, With Insulated Handle

Insulation according to EN/IEC 60900 & CSA specification, up to 1000 Volt. Individually Tested. Blade CV steel, hardened.

Item		OAL	OAL		
No.	Inch	mm	Inch	lbs.	pkg.
29006	1/4	160	6.2"	.57	1



⚡ 1000Volt

[SHOP](#)

128 Insulated 1/4" Extension Bars, ASTM F-1505-01, EN/IEC 60900 & CSA Chrome-Vanadium steel.

Item		OAL	OAL		
No.	Inch	mm	Inch	lbs.	pkg.
12854	1/4"	50	2.0	.08	1
12855	1/4"	100	3.9	.12	1

Wiha Insulated 3/8" Sockets & Sets



 **1000Volt**



314 Insulated 3/8" Drive Sockets - Insulation according to EN/IEC 60900, DIN 7448 & CSA specification, up to 1000 Volt. Individually Tested. CV steel, forged, oil-hardened.

Item			
No.	Inch	lbs.	pkg.
31425	1/4	.07	1
31428	9/32	.07	1
31429	5/16	.07	1
31430	11/32	.07	1
31431	3/8	.08	1
31432	7/16	.08	1
31433	1/2	.10	1
31434	9/16	.10	1
31435	5/8	.10	1
31436	11/16	.13	1
31437	3/4	.14	1
31438	13/16	.17	1
31439	7/8	.18	1

*Sockets must be used with insulated ratchets & extensions



 **1000Volt**



315 Insulated 3/8" Drive Sockets- **Metric** Insulation according to VDE, EN/IEC 60900, DIN 7448 & CSA specification, up to 1000 Volt. Individually Tested. Chrome-vanadium steel, forged, oil-hardened.

Item			
No.	mm	lbs.	pkg.
31506	6.0	.07	1
31507	7.0	.07	1
31508	8.0	.07	1
31509	9.0	.07	1
31510	10.0	.07	1
31511	11.0	.08	1
31512	12.0	.10	1
31513	13.0	.10	1
31514	14.0	.10	1
31515	15.0	.10	1
31516	16.0	.10	1
31517	17.0	.11	1
31518	18.0	.12	1
31519	19.0	.14	1
31520	20.0	.15	1
31521	21.0	.17	1
31522	22.0	.18	1
31524	24.0	.26	1

*Sockets must be used with insulated ratchets & extensions

Wiha Insulated 3/8" Sockets & Sets



 **1000Volt**



31493 10 Piece Insulated 3/8" Drive Socket Set - Inch

CV steel, forged, oil-hardened sockets. Insulated to EN/IEC 60900.

Item No. 31493 Set includes the following:

	5/16, 3/8, 7/16, 1/2,
lbs.	9/16, 5/8, 11/16, 3/4"
2.50	3/8" x 125mm Extension Bar
	3/8" Ratchet - 190mm



 **1000Volt**



31590 10 Piece Insulated 3/8" Drive Socket Set - **Metric**

CV steel, forged, oil-hardened sockets. Insulated to EN/IEC 60900.

Item No. 31590 Set includes the following:

	8, 10, 11, 12, 13, 14, 17, 19mm
lbs.	3/8" x 125mm Extension Bar
2.50	3/8" Ratchet - 190mm



 **1000Volt**



31491 16 Piece Insulated 3/8" Drive Socket Set - Inch/**Metric**

CV steel, forged, oil-hardened sockets. Insulated to EN/IEC 60900.

Item No. 31491 Set includes the following:

	5/16, 3/8, 7/16, 1/2,
lbs.	9/16, 5/8, 11/16, 3/4"
2.01	8, 10, 11, 12, 13, 14, 17, 19mm

Wiha Insulated 3/8" Sockets & Sets



1000Volt

SHOP

31495 24 Piece Insulated 3/8" Drive Socket Set - Inch

CV steel, forged, oil-hardened sockets. Insulated to EN/IEC 60900.

Item No. 31495 Set includes the following:

1/4, 9/32, 5/16, 11/32, 3/8, 7/16

1/2, 9/16, 5/8, 11/16, 3/4" Sockets

lbs. 3/8" x 125mm Extension Bar

9.07 3/8" x 250mm Extension Bar

3/8" Ratchet - 190mm

Insulated Electrician's Knife - 50mm

Slotted: 3.5, 4.5, 6.5mm

Phillips: 1, 2, 3

6.3" Long Nose Pliers

8.0" Combo Pliers

6.3" Diagonal Cutters

*Sockets must be used with insulated ratchets & extensions



1000Volt

SHOP

31592 24 Piece Insulated 3/8" Drive Socket Set - Metric

CV steel, forged, oil-hardened sockets. Insulated to EN/IEC 60900.

Item No. 31592 Set includes the following:

6, 7, 8, 9, 10, 11, 12,

13, 14, 17, 19mm Sockets

lbs. 3/8" x 125mm Extension Bar

9.08 3/8" x 250mm Extension Bar

3/8" Ratchet - 190mm

Insulated Electrician's Knife - 50mm

Slotted: 3.5, 4.5, 6.5mm

Phillips: 1, 2, 3

6.3" Long Nose Pliers

8.0" Combo Pliers

6.3" Diagonal Cutters

*Sockets must be used with insulated ratchets & extensions



1000Volt

SHOP

31496 10 Piece Insulated 3/8" T-handle & Socket Set - Inch

CV steel, forged, oil-hardened sockets. Insulated after EN/IEC 60900.

Item No. 31496 Set includes the following:

5/16, 3/8, 7/16, 1/2, 9/16, 5/8, 11/16, 3/4"

lbs. 3/8" x 125mm Extension Bar

2.47 Insulated 3/8" T-handle

31595 10 Piece Insulated 3/8" T-handle & Socket Set - Metric

CV steel, forged, oil-hardened sockets. Insulated after EN/IEC 60900.

Item No. 31595 Set includes the following:

8, 10, 11, 12, 13, 14, 17, 19mm

lbs. 3/8" x 125mm Extension Bar

2.47 Insulated 3/8" T-handle

Wiha Insulated 3/8" Socket accessories



1000Volt

SHOP

12852 Insulated 3/8" Drive Ratchet, EN/IEC 60900

CV steel. Socket release button. Thumb lever for rapid reverse.

Item No.	Inch	OAL mm	OAL Inch	lbs.	pkg.
12852	3/8"	190	7.5	.93	1



1000Volt

SHOP

128 Insulated 3/8" Extension Bars, EN/IEC 60900

Chrome-Vanadium steel.

Item No.	Inch	OAL mm	OAL Inch	lbs.	pkg.
12856	3/8"	125	4.9	.41	1
12857	3/8"	250	9.8	.57	1

1000Volt



#29009

#12327

SHOP

1000Volt Insulated 3/8" Drive T-handle Or Breaker Bar

Insulation according to EN/IEC 60900 specification, up to 1000 Volt Rated. Individually Tested. Blade chrome-vanadium steel, hardened.

Item No.	Inch	OAL mm	OAL Inch	lbs.	pkg.
29009	3/8"	200	7.9"	.55	1
12327	3/8"	225	9.0"	.68	1

Wiha Insulated 1/2" Sockets & Sets

 **1000Volt**





317 Insulated 1/2" Drive Sockets - Insulation According to ASTM F-1505-01, DIN 7448 & CSA Specification, Up To 1000 Volt. Individually Tested. CV steel, forged, oil-hardened.

Item No.	Inch	lbs.	pkg.
31703	5/16	.16	1
31704	11/32	.16	1
31705	3/8	.16	1
31707	7/16	.16	1
31708	1/2	.16	1
31709	9/16	.17	1
31710	5/8	.19	1
31712	11/16	.19	1
31713	3/4	.21	1
31714	13/16	.23	1
31715	7/8	.27	1
31716	15/16	.35	1
31718	1	.33	1
31720	1-1/8	.44	1
31722	1-1/4	.58	1

*Sockets must be used with insulated ratchets & extensions

 **1000Volt**



Individually Tested





316 Insulated 1/2" Drive Sockets - **Metric** Insulation According to VDE, DIN 7448 & CSA Specification, Up To 1000 Volt.

Item No.	mm	lbs.	pkg.
31608	8.0	.15	1
31609	9.0	.15	1
31610	10.0	.16	1
31611	11.0	.16	1
31612	12.0	.16	1
31613	13.0	.17	1
31614	14.0	.17	1
31615	15.0	.17	1
31616	16.0	.19	1
31617	17.0	.19	1
31618	18.0	.20	1
31619	19.0	.21	1
31620	20.0	.25	1
31621	21.0	.25	1
31622	22.0	.28	1
31623	23.0	.29	1
31624	24.0	.30	1
31626	26.0	.37	1
31627	27.0	.41	1
31628	28.0	.44	1
31630	30.0	.51	1
31632	32.0	.55	1

*Sockets must be used with insulated ratchets & extensions

Wiha Insulated 1/2" Sockets & Sets

Inch



 **1000Volt**



31790 24 Piece Insulated 1/2" Drive Socket Set - Inch


CV steel, forged, oil-hardened sockets. Insulated to EN/IEC 60900.

Item No. Set includes the following:

31790	3/8, 7/16, 1/2, 9/16, 5/8, 11/16, 3/4, 13/16, 7/8, 15/16, 1" Sockets
	1/2" x 125mm Extension Bar
lbs.	1/2" x 250mm Extension Bar
11.41	1/2" Ratchet - 260mm
	Insulated Electrician's Knife - 50mm
	Slotted: 3.5, 4.5, 6.5mm & Phillips: 1, 2, 3
	6.3" Long Nose Pliers
	8.0" Combo Pliers
	6.3" Diagonal Cutters

Each tool individually tested to 10,000 volts & certified to 1000 Volt ac or 1500 Volt dc

Metric



 **1000Volt**



31691 24 Piece Insulated 1/2" Drive Socket Set - Metric

CV steel, forged, oil-hardened sockets. Insulated to EN/IEC 60900.

Item No. Set includes the following:

31691	8, 9, 10, 12, 13, 14, 15, 17, 19, 22, 24mm Sockets
	1/2" x 125mm Extension Bar
lbs.	1/2" x 250mm Extension Bar
11.39	1/2" Ratchet - 260mm
	Insulated Electrician's Knife - 50mm
	Slotted: 3.5, 4.5, 6.5mm & Phillips: 1, 2, 3
	6.3" Long Nose Pliers
	8.0" Combo Pliers
	6.3" Diagonal Cutters



 **1000Volt**



12326 Insulated 1/2" Drive Breaker Bar, IEC/EN 60900 & CSA Chrome-Vanadium steel.

Item No.	Inch	mm	Inch	lbs.	pkg.
12326	1/2"	275	11.0	1.04	1

Wiha Insulated 1/2" Socket accessories

1000Volt

12853 Insulated 1/2" Drive Ratchet, IEC/EN 60900 & CSA

Chrome-Vanadium steel. Reversible.

Item	OAL	OAL			
No.	Inch	mm	Inch	lbs.	pkg.
12853	1/2"	260	10.2	1.55	1

1000Volt

128 Insulated 1/2" Extension Bars, EN/IEC 60900 & CSA

Chrome-vanadium steel.

Item	OAL	OAL			
No.	Inch	mm	Inch	lbs.	pkg.
12858	1/2"	125	4.9	.45	1
12859	1/2"	250	9.8	.91	1

1000Volt

29012 Insulated 1/2" Drive T-handle, With Insulated Handle

Insulation according to EN/IEC 60900 & CSA Specification, Up To 1000 Volt. Individually Tested. Blade VC steel, hardened.

Item	OAL	OAL			
No.	Inch	mm	Inch	lbs.	pkg.
29012	1/2"	200	7.9"	.68	1

Uses standard
12" blade

1000Volt

19767 Hacksaw, With Insulated Handle

Insulation According to EN/IEC 60900, DIN ISO 8976, ASTM F-1505 & CSA Specification, Up To 1000 Volt. Individually Tested.

Item	OAL	OAL			
No.	mm	Inch	lbs.	pkg.	
19767	457mm	18.0"	1.92	1	

1000Volt

29240 Waterpump Pliers, With Insulated Handle

Insulation According to EN/IEC 60900, DIN ISO 8976, ASTM F-1505 & CSA Specification, Up To 1000 Volt. Individually Tested.

Box joint. Chrome-vanadium steel, drop forged, oil hardened.

Item	OAL	OAL	Capacity		
No.	mm	Inch	mm	lbs.	pkg.
29240	240	9.5	7/8"	1.1	1

Wiha Insulated Cable Cutters



For cutting solid
aluminum & copper
conductors

1000Volt

11950 Cable Cutter, With Insulated Handle

Insulation According to EN/IEC 60900, ASTM F-1505 & CSA

Specification, Up To 1000 Volt. Individually Tested.

Blade alloyed tool steel. Induction hardened.

Item	OAL	OAL	Capacity		
No.	mm	Inch	mm	lbs.	pkg.
11950	500	19.6	12	3.0	1

For cutting multi strand aluminum & copper cables

31.5"



1000Volt

40800 Large Capacity Cable Cutter, With Insulated Handle

Insulation According to EN/IEC 60900, ASTM F-1505 & CSA

Specification, Up to 1000 Volt. Individually Tested.

Easy cutting blades, dropped forged, oil hardened. Cuts cable diameters up to 50mm. Not to be used on steel rods.

Item	OAL	OAL	Capacity		
No.	mm	Inch	mm	lbs.	pkg.
40800	800	31.5	50	8.0	1



For cutting
solid aluminum,
copper & medium
hard wires

1000Volt

29250 End Cutters, With Insulated Handle. Insulation According

to EN/IEC 60900, DIN ISO 8976, ASTM F-1505 & CSA Specification.

Individually Tested. Blade alloyed tool steel. Induction hardened.

Item	OAL	OAL	Capacity		
No.	mm	Inch	mm	lbs.	pkg.
29250	250	10	7/8"	1.1	1



1000Volt

116 Waterpump Pliers, With Insulated Handle

Insulation According to EN/IEC 60900, DIN ISO 8976, ASTM F-1505 & CSA Specification, Up To 1000 Volt. Individually Tested.

Chrome-vanadium steel, drop forged, oil hardened.

Item	OAL	OAL			
No.	mm	Inch	lbs.	pkg.	
11625	250	10.0"	1.2	1	
11630	300	12.0"	1.8	1	

Wiha Insulated Ratcheting Cable Cutters

Insulation: VDE, EN/IEC, ASTM, NFPA70E, CSA & OSHA
Tested to 10,000 volts with 1000 volts safety rating



SHOP

1000Volt

119 High Voltage Double-Insulated Ratcheting Cable Cutters

High leverage ratchet cable cutter with shear type blades cuts stranded and flexible copper and aluminum cable. Not for use on steel. Features built in safety release in all cutting positions, and high-visibility comfort grip handles.

Item No.	OAL mm	OAL Inch	up to MCM	Inch Dia.	Capacity	lbs.	pkg.
11960	250	10.0"	500	1.25"	32ml	1.58	1
11975	280	11.0"	750	2.0"	52ml	2.02	1



1000Volt

SHOP

11980 Insulated ACSR Ratcheting Cable Cutter

Replaceable tool steel cutting blades are securely mounted for accurate cutting. Handles lock in closed position for easier storage. High leverage ratchet mechanism for best cutting performance.

Item No.	OAL mm	OAL Inch	up to MCM	Inch Dia.	Capacity	lbs.	pkg.
11980	353	13.9	477	1.25"	32ml	3.42	1

Wiha Insulated Serrated Tweezers



SHOP

1000Volt

75205 Insulated Serrated Straight Fine Tip Tweezers, IEC/EN 60900 & CSA Standards, 10,000 Volt Tested

Item No.	OAL mm	OAL Inch	lbs.	pkg.
75205	130	5.0	.06	1



SHOP

1000Volt

75210 Insulated Serrated Straight Blunt Tip Tweezers, IEC/EN 60900 & CSA Standards, 10,000 Volt Tested

Item No.	OAL mm	OAL Inch	lbs.	pkg.
75210	130	5.0	.08	1

Wiha Insulated Serrated Tweezers

Meets EN/IEC Insulation Standards

Slip guards at tips for user safety

Two layer high contrast insulated coatings



Carbon steel with chrome nickel plated

1000V

10,000 Volt tested 1000Volt rated



SHOP

1000Volt

75215 Insulated Serrated Straight Blunt Tip Tweezers, IEC/EN 60900 & CSA Standards, 10,000 Volt Tested

Item No.	OAL mm	OAL Inch	lbs.	pkg.
75215	145	6.0	.10	1



SHOP

1000Volt

75220 Insulated Serrated Straight Blunt Tip Tweezers, IEC/EN 60900 & CSA Standards, 10,000 Volt Tested

Item No.	OAL mm	OAL Inch	lbs.	pkg.
75220	200	8.0	.18	1



SHOP

1000Volt

75302 Insulated Serrated Angled Fine Tip Tweezers, IEC/EN 60900 & CSA Standards, 10,000 Volt Tested

Item No.	OAL mm	OAL Inch	lbs.	pkg.
75302	145	6.0	.08	1



SHOP

1000Volt

75304 Insulated Serrated Angled Blunt Tip Tweezers, IEC/EN 60900 & CSA Standards, 10,000 Volt Tested

Item No.	OAL mm	OAL Inch	lbs.	pkg.
75304	200	8.0	.16	1


Wiha Insulated T-handle Hex Drivers

Insulation Test Standards:

Insulation according to EN/IEC 60900, ASTM F-1505-01, VDE 0682/part 201, DIN 7437, NFPA70E & CSA specification

Each tool individually tested to 10,000 volts and rated to 1000 Volt ac or 1500 Volt dc

Responds to OSHA's use specification 29 CFR1910



Insulation
Molded directly onto blade for permanent bonding

Blade
CVM tool steel, hardened to average 58/60RC




 **1000Volt**

SHOP

33490 6 Piece Inch T-handle Hex Set

Item			Inch:		lbs.
33490			5/32, 3/16, 7/32, 1/4, 5/16, 3/8"		1.66



 **1000Volt**

SHOP

334 Inch T-handle, With Wiha-Molded Handle. Insulation

According to ASTM F-1505-01, New VDE Specification 0682/part 201 and EN/IEC 60900, NFPA70E & CSA,  up to 1000Volt. Individually Tested. Blade CVM steel, hardened. Insulation molded directly onto blade. Wiha-SoftFinish® handle, multi-component.


Item							
No.	Inch	Inch	Inch	mm	lbs.	pkg.	
33481	5/32	5.9	6.9	176	.09	10	
33482	3/16	5.9	6.9	176	.15	10	
33483	7/32	5.9	6.9	176	.19	10	
33485	1/4	5.9	7.1	176	.20	10	
33486	5/16	5.9	7.1	176	.26	10	
33487	3/8	5.9	7.1	176	.44	10	



SHOP

33478 5 Piece Metric T-handle Hex Set

Item			Metric:		lbs.
33478			4.0, 5.0, 6.0, 8.0, 10.0mm		1.20



 **1000Volt**


SHOP

334 Metric T-handle, With Wiha-Molded Handle. Insulation

According to ASTM F-1505-01, New VDE Specification 0682/part 201 and EN/IEC 60900, NFPA70E & CSA,  up to 1000Volt. Individually Tested. Blade CVM steel, hardened. Insulation molded directly onto blade. Wiha-SoftFinish® handle, multi-component.

Item							
No.	mm	mm	Inch	mm	Inch	lbs.	pkg.
33441	4.0	150	5.9	176	6.9	.09	10
33443	5.0	150	5.9	182	7.1	.15	10
33445	6.0	150	5.9	182	7.1	.18	10
33447	8.0	150	5.9	182	7.1	.26	10
33449	10.0	150	5.9	191	7.5	.46	10

Wiha Insulated T-handle Nut Drivers



 **1000Volt**

SHOP

336 Metric T-handle Nut Drivers, With Wiha-Molded Handle. Insulation

According to ASTM F-1505-01, New VDE Specification 0682/part 201 and EN/IEC 60900, NFPA70E & CSA,  up to 1000Volt. Individually Tested. Blade CVM steel, hardened. Insulation molded directly onto blade. Wiha-SoftFinish® handle, multi-component.

Item							
No.	mm	mm	Inch	mm	Inch	lbs.	pkg.
33632	8.0	200	7.9	232	9.1	.15	5
33634	10.0	230	9.0	262	10.3	.18	5
33637	13.0	230	9.0	262	10.3	.26	5
33641	17.0	230	9.0	268	10.6	.46	5

Wiha Multi-Bit Screwdrivers

Six Tools in One!

Insulated Bit Holder



Tested to 10,000 Volts Insulation meets EN/IEC 60900



380 Sets Multi-Bit Screwdriver Sets with Wiha Powerhandle, cellulose-acetate, impact resistant. Snap-lock rotatable cap. Chambered bit holder equipped with transparent selector and 6 bits. 1/4" Bit holder, stainless steel. Shaft chrome-vanadium-molybdenum steel, hardened, chrome-plated. Packaged in clear blister package. Blade Length = 120mm (4.7") Overall Length = 230mm (9")

38006 Slotted/Phillips Multi-Bit Screwdriver

With Wiha Powerhandle and insulated shaft.

Set includes the following 1/4" bits:

↓  **Slotted Sizes:** 5.5, 6.0mm lbs.

⊕ **Phillips Sizes:** 0, 1, 2, 3 .39

38007 Slotted/Phillips/Square Multi-Bit Screwdriver

With Wiha Powerhandle and insulated shaft.

Set includes the following 1/4" bits:

↓  **Slotted Sizes:** 6.5, 8.0mm lbs.

⊕ **Phillips Sizes:** 1, 2 .41

□ **Square Sizes:** 1, 2

38025 Magnetic Bit Holder, 1/4" Wiha Powerhandle & insulated shaft. Holder only can hold up to 6 bits.

 lbs. .26

Wiha Insulated TorqueControl Tools

Includes Certificate

 1000Volt



Includes *SlimLine* blade holder

287 Insulated TorqueVario-S, With Window Scale Insulation

 up to 1000 Volt. EN/IEC 60900 EN ISO 6798, BS EN 26789, ASME B107.14M & CSA, +/- 6% Accuracy. Ergonomic multi-component handle, light & compact. Handle sizes proportioned to optimize torque range. Audible & perceptible click when torque setting has been attained.

Item No.	Range	Inch	lbs.	mm	lbs.	pkg.
28724	7.5 - 20	.5	Inch lbs	126 - 131	.43	1
28726	10 - 50	2	Inch lbs	133 - 138	.40	1
28727	20 - 70	2	Inch lbs	137 - 142	.69	1

287 Insulated TorqueVario-S Handle - In Newton Meter Scale

Item No.	Range	mm	lbs.	pkg.
28734	0.6 - 2.0	131	.45	1
28736	1.0 - 5.0	138	.45	1
28737	2.0 - 8.0	142	.72	1

Each TorqueVario handle has unique serial number & certificate of calibration

 1000Volt



28350 Insulated *SlimLine* Torque Blade Holder

Chrome-vanadium-molybdenum steel. Through hardened black finish.

ClickFix quick release holder securely locks bits.

Item No.	OAL	OAL	Inch	lbs.	pkg.
28350	6.0	170	6.7	.02	1

Wiha Insulated TorqueControl & *SlimLine* Tool Sets



28791 8 Piece Insulated TorqueControl Set With Slotted & Phillips *SlimLine* Blades Certified to EN ISO 6798, BS EN 26789, ASME B107.14M. Set includes Insulated multi-component adjustable TorqueVario-S handle, 5 *SlimLine* blades, *SlimLine* blade holder & Torque adjustment tool.

Item No.		 lbs.
28791	<i>SlimLine</i> Slotted: 3.0, 4.0, 5.5mm	.87
	<i>SlimLine</i> Phillips: #1, #2	
	28726 - Handle Range 10-50 Inch/lbs.	
	<i>SlimLine</i> Blade Holder	

With Certificate of Calibration



28792 16 Piece Insulated TorqueControl Set With *SlimLine* Blades Certified to EN ISO 6798, BS EN 26789, ASME B107.14M. Set includes Insulated multi-component adjustable TorqueVario-S handle, 13 *SlimLine* blades, *SlimLine* blade holder & Torque adjustment tool.

Item No.		 lbs.
28792	<i>SlimLine</i> Slotted: 4.0, 5.5, 6.5mm	1.27
	<i>SlimLine</i> Phillips: #1, 2	
	<i>SlimLine</i> Terminal Xeno: #1, 2	
	<i>SlimLine</i> TORX®: T8, T10, T15, T20	
	<i>SlimLine</i> Square: #1, 2	
	28727 - Handle Range 20-70 Inch/lbs.	
	<i>SlimLine</i> Blade Holder	

With Certificate of Calibration

Wiha Insulated SlimLine Tools

Insulation Test Standards:

Insulation according to EN/IEC 60900,
ASTM F-1505-01, VDE 0682/part 201,
DIN 7437, NFPA70E & CSA specification



High quality chrome
vanadium steel,
through-hardened

 **1000Volt Rated**
10,000 Volt Tested

Integrated *Slim*
Insulation molded
directly onto blade

Ideal for jobs
where access
is limited

Insulation does
not exceed screw
head diameter

Wiha SlimTECHNOLOGY

Achieves blade
diameters up to 33%
narrower utilizing
integrated insulation



Wiha Insulated SlimLine Handle



 **1000Volt**

SHOP

28301 SlimLine Blade Holder, With Wiha-SoftFinish® Handle
Insulation According to VDE, ASTM F-1505-01 and EN/IEC 60900,
NFPA70E & CSA,  up to 1000 Volt.

Chrome-vanadium steel, through-hardened. Insulation molded
directly onto blade. Quick release holder securely lock blades.
Wiha-SoftFinish® handle, multi-component, cushion grip.

Item							
No.	Size	mm	Inch	mm	Inch	lbs.	pkg.
28301	1/4"	50	2.0	160	6.3	.15	1

Wiha Insulated SlimLine Blades





SHOP

283 Insulated Slotted SlimLine Blades High quality CV steel,
through hardened. *SlimLine* blades have up to 33% narrower insulation
diameter than standard insulated tools.

Item				Slim	Max	Inch/		
No.	mm	Inch	Inch	Dia.	Nm	lbs.	lbs.	Pkg.
28308	3.0	.118	1/8	4.1	0.6	5.3	.02	1
28309	4.0	.157	5/32	4.1	2.5	22.2	.02	1
28312	5.5	.216	7/32	6.1	3.8	33.7	.02	1
28315	6.5	.255	1/4	6.1	5.5	48.8	.02	1





SHOP

283 Insulated Phillips SlimLine Blades
High quality CV steel, through hardened. *SlimLine* blades have up to
33% narrower insulation diameter than standard insulated tools.

Item		Slim	Max	Inch/		
No.	Size	Dia.	Nm	lbs.	lbs.	Pkg.
28317	1	4.1	3.8	33.7	.02	1
28319	2	6.1	5.5	48.8	.02	1

33%
narrower
insulation
diameter



Wiha Insulated SlimLine Blades



283 Insulated Xeno Slotted & Phillips SlimLine Blades

High quality CV steel, through hardened. *SlimLine* blades have up to 33% narrower insulation diameter then standard insulated tools.

Item No.	⊕ Size	Slim Dia.	Max Nm	Inch/ lbs.	⚡ lbs.	Pkg.
28327	1	4.1	3.8	33.7	.02	1
28329	2	6.1	5.5	48.8	.02	1



283 Insulated TORX® SlimLine Blades

High quality CV steel, through hardened. *SlimLine* blades have up to 33% narrower insulation diameter then standard insulated tools.

Item No.	⊕ Size	Slim Dia.	Max Nm	Inch/ lbs.	⚡ lbs.	Pkg.
28339	T8	4.1	1.3	11.5	.02	1
28340	T10	4.1	3.8	33.7	.02	1
28341	T15	6.1	5.5	48.8	.02	1
28342	T20	6.1	5.5	48.8	.02	1



283 Insulated Square SlimLine Blades

High quality CV steel, through hardened. *SlimLine* blades have up to 33% narrower insulation diameter then standard insulated tools.

Item No.	⊕ Size	Slim Dia.	Max Nm	Inch/ lbs.	⚡ lbs.	Pkg.
28346	1	4.1	3.8	33.7	.02	1
28347	2	6.1	5.5	48.8	.02	1



Wiha Insulated SlimLine Blade Sets



⚡ 1000Volt

28391 8 Piece Insulated SlimLine Blade Set

High quality CV steel, through hardened. *SlimLine* blades have up to 33% narrower insulation diameter then standard insulated tools.

Cushion grip handle with quick release holder to securely lock blades. In roll up pouch

Item No.	⚡ lbs.
28391 Slotted: 4.0, 6.5	.45
Phillips: #1, #2	
Xeno: #2	
TORX®: T15, T20	
28301 - SlimLine Cushion Grip Blade Holder	



⚡ 1000Volt

28390 15 Piece Insulated SlimLine Blade Set

High quality CV steel, through hardened. *SlimLine* blades have up to 33% narrower insulation diameter then standard insulated tools.

Cushion grip handle with quick release holder to securely lock blades. In roll up pouch

Item No.	⚡ lbs.
28390 Slotted: 3.0, 4.0, 5.5, 6.5	.56
Phillips: #1, #2	
Xeno: #1, #2	
TORX®: T8, T10, T15, T20	
Square: #1, #2	
28301 - SlimLine Cushion Grip Blade Holder	

Wiha Insulated SlimLine Screwdrivers

Insulation Test Standards:

Insulation according to EN/IEC 60900, ASTM F-1505-01, VDE 0682/part 201, DIN 7437, NFPA70E & CSA specification

Wiha SlimTECHNOLOGY

Achieves blade diameters up to 33% narrower utilizing integrated insulation

slimTECHNOLOGY



Ideal for jobs where access is limited

Integrated Slim Insulation molded directly onto blade

1000Volt Rated
10,000 Volt Tested

←1.4"→



320 Insulated Slotted SlimLine Screwdrivers

Insulation According to ASTM F-1505-01, New VDE Specification 0682/part 201 and EN/IEC 60900, NFPA70E & CSA, **up to 1000 Volt. Individually Tested to 10,000Volts.**

High quality CV steel, through hardened. *SlimLine* blades have up to 33% narrower insulation diameter then standard insulated tools.

Wiha-SoftFinish® handle, multi-component, cushion grip.

Item No.	mm	Inch	Inch	Slim Dia.	mm	mm	lbs.	Pkg.
32046	3.5	.139	9/64	3.5	100	204	.07	1
32049	4.0	.157	5/32	4.0	100	211	.12	1
32052	4.5	.177	3/16	4.5	125	211	.14	1
32055	5.5	.216	7/32	5.5	125	243	.21	1
32058	6.5	.255	1/4	6.5	150	268	.25	1

←1.4"→



307 Insulated Xeno SlimLine Screwdrivers For Terminal Screws

Insulation According to ASTM F-1505-01, New VDE Specification 0682/part 201 and EN/IEC 60900, NFPA70E & CSA, **up to 1000 Volt. Individually Tested to 10,000Volts.**

High quality CV steel, through hardened. *SlimLine* blades have up to 33% narrower insulation diameter then standard insulated tools.

Wiha-SoftFinish® handle, multi-component, cushion grip.

Item No.	Size	Slim Dia.	mm	mm	lbs.	Pkg.
30746	1	4.5	80	191	.12	1
30747	2	6.0	100	218	.21	1

←1.4"→



321 Insulated Phillips SlimLine Screwdrivers

Insulation According to ASTM F-1505-01, New VDE Specification 0682/part 201 and EN/IEC 60900, NFPA70E & CSA, **up to 1000 Volt. Individually Tested to 10,000Volts.**

High quality CV steel, through hardened. *SlimLine* blades have up to 33% narrower insulation diameter then standard insulated tools.

Wiha-SoftFinish® handle, multi-component, cushion grip.

Item No.	Size	Slim Dia.	mm	mm	lbs.	Pkg.
32145	1	4.5	80	204	.12	1
32146	2	6.0	100	211	.21	1

←1.4"→



358 Insulated Square SlimLine Screwdrivers


Insulation According to ASTM F-1505-01, New VDE Specification 0682/part 201 and EN/IEC 60900, NFPA70E & CSA, **up to 1000 Volt. Individually Tested to 10,000Volts.**

High quality CV steel, through hardened. *SlimLine* blades have up to 33% narrower insulation diameter then standard insulated tools.

Wiha-SoftFinish® handle, multi-component, cushion grip.

Item No.	Size	Slim Dia.	mm	mm	lbs.	Pkg.
35844	1	4.0	100	218	.12	1
35845	2	4.5	125	243	.19	1

Wiha Insulated *SlimLine* Screwdriver Sets


 1000Volt




32198 11 Piece Insulated *SlimLine* Slotted, Phillips, Xeno & Square Screwdrivers. Insulation According to ASTM F-1505-01, New VDE Specification 0682/part 201 and EN/IEC 60900, NFPA70E & CSA,  up to 1000 Volt. Individually Tested to 10,000Volts.

High quality CV steel, through hardened. *SlimLine* blades have up to 33% narrower insulation diameter then standard insulated tools.

Wiha-SoftFinish® handle, multi-component, cushion grip.

Item No.	⊕	⊖	↑ ↓	⊖	⊖
	Size	mm		mm	mm
32198	Phillips 1	80	Slotted	3.5	100
	Phillips 2	100	Slotted	4.0	100
	⊖	⊖	Slotted	4.5	125
	Square 1	100	Slotted	5.5	125
	Square 2	125	Slotted	6.5	150
	⊕	⊖			
	Xeno 1	80			
	Xeno 2	100			


 1000Volt



32197 8 Piece Insulated *SlimLine* Slotted, Phillips & Square Screwdrivers. Insulation According to ASTM F-1505-01, New VDE Specification 0682/part 201 and EN/IEC 60900, NFPA70E & CSA,  up to 1000 Volt. Individually Tested to 10,000Volts.

High quality CV steel, through hardened. *SlimLine* blades have up to 33% narrower insulation diameter then standard insulated tools.

Wiha-SoftFinish® handle, multi-component, cushion grip.

Item No.	⊕	⊖	↑ ↓	⊖	⊖
	Size	mm		mm	mm
32197	Phillips 1	80	Slotted	3.5	100
	Phillips 2	100	Slotted	4.0	100
	⊖	⊖	Slotted	4.5	125
	Square 1	100	Slotted	5.5	125
	Square 2	125			


 1000Volt



32196 6 Piece Insulated *SlimLine* Slotted, Phillips & Square Screwdrivers. Insulation According to ASTM F-1505-01, New VDE Specification 0682/part 201 and EN/IEC 60900, NFPA70E & CSA,  up to 1000 Volt. Individually Tested to 10,000Volts.

High quality CV steel, through hardened. *SlimLine* blades have up to 33% narrower insulation diameter then standard insulated tools.


Wiha-SoftFinish® handle, multi-component, cushion grip.

Item No.	⊕	⊖	↑ ↓	⊖	⊖
	Size	mm		mm	mm
32196	Phillips 1	80	Slotted	4.5	125
	Phillips 2	100	Slotted	6.5	150
	⊖	⊖			
	Square 1	100			
	Square 2	125			


 1000Volt

32189 2 Pc. Insulated *SlimLine* Slotted & Phillips Screwdrivers. Insulation According to ASTM F-1505-01, New VDE Specification 0682/part 201 and EN/IEC 60900, NFPA70E & CSA,  up to 1000 Volt. Individually Tested to 10,000Volts. High quality CV steel, through hardened. *SlimLine* blades have up to 33% narrower insulation diameter then standard insulated tools.

Item No.	⊕	⊖	↑ ↓	⊖	⊖
	Size	mm		mm	mm
32189	2	100	4.5	125	.37

Wiha Slim TECHNOLOGY
Achieves blade diameters up to 33% narrower utilizing Wiha integrated insulation

Wiha Insulated Screwdrivers with SoftFinish® Cushion Grip Handle

Insulation Test Standards:

Insulation according to EN/IEC 60900, ASTM F-1505-01, New VDE 0682/part 201, DIN 7437, NFPA70E & CSA

Responds to OSHA's use specification 29 CFR1910

Each tool individually tested to 10,000 volts and rated to 1000 Volt ac or 1500 Volt dc

SoftFinish® handle

solid molded core with soft outer cushion grip. 40% more torque than conventional handles

Insulation
Molded directly onto the blade for permanent bonding

Blade
CVM tool steel, hardened to average 58/60RC

1000V

#32892



page 32



1000Volt

SHOP

320 Slotted Screwdriver, With Wiha-SoftFinish® Handle
Insulation According to ASTM F-1505-01, New VDE Specification 0682/part 201 and EN/IEC 60900, NFPA70E & CSA, **1000 Volt. Individually Tested.**

Item No.	mm	Inch	Inch	mm	Inch	mm	Inch	lbs.	pkg.
32005	2.0	.078	5/64	60	3.0	164	6.5	.05	10
32010	2.5	.098	3/32	75	3.0	179	7.1	.06	10
32012	3.0	.118	1/8	100	4.0	204	8.0	.07	10
32015	3.5	.139	9/64	100	4.0	204	8.0	.07	10
32017	4.0	.157	5/32	100	4.0	211	8.3	.12	10
32023	4.5	.177	3/16	100	4.0	211	8.3	.12	10
32024	4.5	.177	3/16	125	5.0	236	9.3	.12	10
32027	4.5	.177	3/16	150	6.0	261	10.2	.14	10
32025	4.5	.177	3/16	175	7.0	286	11.2	.13	10
32028	4.5	.177	3/16	200	8.0	311	12.3	.15	10
32031	5.5	.216	7/32	125	5.0	243	9.5	.15	10
32026	5.5	.216	7/32	175	7.0	293	11.5	.21	10
32034	6.0	.236	15/64	150	6.0	268	10.6	.21	10
32039	6.5	.255	1/4	150	6.0	268	10.6	.21	10
32042	8.0	.315	5/16	175	7.0	299	11.8	.34	10
32045	10.0	.393	3/8	200	8.0	318	12.5	.39	10




1000Volt

SHOP

321 Phillips Screwdriver, With Wiha-SoftFinish® Handle
Insulation According to ASTM F-1505-01, New VDE Specification 0682/part 201 and EN/IEC 60900, NFPA70E & CSA, **1000 Volt. Individually Tested.**

Item No.	Size	mm	Inch	mm	Inch	lbs.	pkg.
32100	0	60	2.4	164	6.5	.06	10
32101	1	80	3.0	191	7.5	.12	10
32102	2	100	4.0	218	8.6	.20	10
32103	3	150	6.0	268	10.6	.34	10
32104	4	200	8.0	318	12.5	.39	10



32092 6 Piece Slotted & Phillips Set

Item No.	Slotted	Phillips	lbs.
32092	3.5, 4.5, 6.5	1, 2, 3	1.38

SHOP

32091 5 Piece Slotted & Phillips Set

Item No.	Slotted	Phillips	lbs.
32091	3.0, 4.5, 6.5	1, 2	1.31

SHOP



1000Volt

32090 4 Piece Slotted & Phillips Set

Item No.	mm	mm	mm	Size	mm	lbs.
32090	Slotted	3.5	100	0.6	Phillips 1	80
	Slotted	4.5	125	1.0	Phillips 2	100




1000Volt

32188 7 Piece Slotted & Phillips Set

Item No.	Slotted	Phillips	lbs.
32188	2.0, 2.5, 3.0, 3.5, 4.0	0, 1	.92


Wiha Insulated Screwdriver Sets


 1000Volt



32094 13 Piece Slotted & Phillips Set

Item No.		
32094	Slotted: 2.0, 2.5, 3.0, 3.5, 4.5, 5.5, 6.5, 8.0, 10.0mm Phillips: 0, 1, 2, 3	lbs. 2.3


 1000Volt



32093 10 Piece Slotted & Phillips Set

Item No.		
32093	Slotted: 2.0, 2.5, 3.0, 3.5, 4.5, 6.5 Phillips: 0, 1, 2, 3	lbs. 1.63


 1000Volt



32190 15 Piece Slotted, Phillips & Inch Nut Drivers Set

Item No.			lbs.
32190	Slotted: 2.0, 2.5, 3.0, 3.5, 4.5, 6.5, 8.0mm Phillips: 1, 2, 3 Nut Drivers Inch: 1/4, 5/16, 3/8, 7/16, 1/2"		5.9


 1000Volt

 Tool box set
in blow molded tray

32095 19 Piece Slotted, Phillips, Square, Xeno Screwdriver Set

Item No.		
32095	Slotted: 2.5, 3.0, 3.5, 4.0, 4.5, 5.5, 6.0, 6.5, 8.0, 10.0mm Phillips: #0, #1, #2, #3 Square: #1, #2 Xeno Terminal: #1, #2	lbs. 4.92
	Single Pole Voltage Detector 110V to 250V	



Wiha Insulated Hex Metric Screwdrivers

 1000Volt


323 Hex Metric Screwdriver, With Wiha-SoftFinish® Handle
 Insulation According to ASTM F-1505-01, New VDE Specification 0682/part 201 and EN/IEC 60900, NFPA70E & CSA,  up to 1000 Volt. Individually Tested. Blade high alloy CVM steel, hardened, black finish. Insulation molded directly onto blade. Wiha-SoftFinish® handle, multi-component, cushion grip.



Item No.	Size	mm	Inch	mm	Inch	lbs.	pkg.
32302	2.5	75	3.0	179	7.0	.06	10
32303	3.0	75	3.0	179	7.0	.08	10
32304	4.0	75	3.0	186	7.3	.12	10
32305	5.0	75	3.0	186	7.3	.15	10
32306	6.0	100	3.9	218	8.6	.24	10
32308	8.0	100	3.9	218	8.6	.34	10

 1000Volt



32366 6 Piece Insulated Hex Metric Screwdriver Set

Item No.			lbs.
32366	Hex Metric: 2.5, 3.0, 4.0, 5.0, 6.0, 8.0mm		1.06



Wiha Insulated Square Tip Screwdrivers


 1000Volt



358 Square Tip Screwdriver, With Wiha-SoftFinish® Handle
 Insulation According to ASTM F-1505-01, New VDE Specification 0682/part 201 and EN/IEC 60900, NFPA70E and CSA,  up to 1000 Volt. Individually Tested. Blade high alloy CVM steel, hardened, black finish. Insulation molded directly onto blade.

Item No.	Size	mm	Inch	mm	Inch	lbs.	pkg.
35811	1	100	4.0	210	8.2	.12	10
35812	2	150	6.0	268	10.5	.19	10



 1000Volt

35890 6 Pc. Insulated Slotted, Phillips & Square Screwdrivers

Item No.		
35890	Slotted: 4.5, 6.5mm Phillips: 1, 2 Square: 1, 2	lbs. .83

35891 6 Pc. Insulated Slotted, Phillips & Square Screwdrivers

Item No.		
35891	Slotted: 3.0, 5.5mm Phillips: 1, 2 Square: 1, 2	lbs. .83

Wiha Insulated Nut Drivers



1000Volt

SHOP

322 Metric Nut Drivers, With Wiha-SoftFinish® Handle Insulation

According to ASTM F-1505-01, New VDE Specification 0682/part 201 and EN/IEC 60900, NFPA70E & CSA, up to 1000 Volt. Individually Tested. Blade CVM steel, hardened. Insulation molded directly onto blade. Deep drawn 1" socket. Wiha-SoftFinish® handle, multi-component.

Item	⊙	—	—	—	—	—
No.	mm	mm	mm	Inch	lbs.	pkg.
32206	4.0	125	236	9.3	.15	10
32209	5.0	125	236	9.3	.16	10
32212	5.5	125	236	9.3	.16	10
32215	6.0	125	236	9.3	.16	10
32218	7.0	125	243	9.6	.25	10
32221	8.0	125	243	9.6	.25	10
32224	9.0	125	243	9.6	.25	10
32227	10.0	125	243	9.6	.27	10
32230	11.0	125	243	9.6	.37	10
32233	12.0	125	243	9.6	.38	10
32236	13.0	125	243	9.6	.39	10
32238	14.0	125	243	9.6	.39	10
32239	15.0	125	243	9.6	.40	10
32240	16.0	125	243	9.6	.42	10
32241	17.0	125	243	9.6	.44	10

322 Inch Nut Drivers, With Wiha-SoftFinish® Handle

Item	⊙	—	—	—	—	—
No.	Inch	Inch	mm	Inch	lbs.	pkg.
32255	5/32	5.0	236	9.3	.15	10
32258	3/16	5.0	236	9.3	.15	10
32261	7/32	5.0	236	9.3	.16	10
32264	1/4	5.0	243	9.5	.24	10
32267	5/16	5.0	243	9.5	.25	10
32268	11/32	5.0	242	9.5	.26	10
32270	3/8	5.0	243	9.5	.26	10
32273	7/16	5.0	243	9.5	.36	10
32276	1/2	5.0	243	9.5	.39	10
32278	9/16	5.0	243	9.5	.39	10
32280	5/8	5.0	243	9.5	.41	10




1000Volt

SHOP

32296 11 Piece Nut Driver Set - Inch Sizes

Item	⊙	—	⊙	—	—
No.	Inch	Inch	Inch	Inch	lbs.
32296	5/32	5.0	3/8	5.0	3.00
	3/16	5.0	7/16	5.0	
	7/32	5.0	1/2	5.0	
	1/4	5.0	9/16	5.0	
	5/16	5.0	5/8	5.0	
	11/32	5.0			



1000Volt

SHOP

32291 5 Piece Nut Driver Set - Metric Sizes

Item	⊙	—	⊙	—	—
No.	mm	mm	mm	mm	lbs.
32291	6.0	125	9.0	125	1.36
	7.0	125	10.0	125	
	8.0	125			




1000Volt

SHOP

32293 7 Piece Nut Driver Set - Metric Sizes

Item	⊙	—	⊙	—	—
No.	mm	mm	mm	mm	lbs.
32293	5.0	125	8.0	125	2.05
	5.5	125	10.0	125	
	6.0	125	13.0	125	
	7.0	125			



1000Volt

SHOP

32292 5 Piece Nut Driver Set - Inch Sizes

Item	⊙	—	⊙	—	—
No.	Inch	Inch	Inch	Inch	lbs.
32292	7/32	5.0	3/8	5.0	1.52
	1/4	5.0	1/2	5.0	
	5/16	5.0			



1000Volt

SHOP

32294 7 Piece Nut Driver Set - Inch Sizes

Item	⊙	—	⊙	—	—
No.	Inch	Inch	Inch	Inch	lbs.
32294	3/16	5.0	3/8	5.0	2.24
	7/32	5.0	7/16	5.0	
	1/4	5.0	1/2	5.0	
	5/16	5.0			

Wiha Insulated Inch Nut Driver Set




SHOP

32288 9 Piece Nut Driver Set - Inch Sizes. In roll-up pouch

Item					
No.	Inch	Inch	Inch	Inch	lbs.
32288	3/16	5.0	7/16	5.0	3.16
	1/4	5.0	1/2	5.0	
	5/16	5.0	9/16	5.0	
	11/32	5.0	5/8	5.0	
	3/8	5.0			

Insulated Terminal Block Xeno Screwdrivers



Slotted & Phillips



SHOP

307 Combination Terminal Block Xeno Screwdriver, With Wiha SoftFinish® Handle. Insulation According to ASTM F-1505-01, VDE, 0682/part 201, EN/IEC 60900, NFPA70E & CSA specification. Individually Tested. Blade CVM steel, hardened, black finish. Insulation molded directly onto blade. Wiha-SoftFinish® handle, multi-component, cushion grip. For combination Slotted/Phillips head terminal screws.

Item					
No.	Size	mm	mm	Inch	lbs. pkg.
30700	1	80	191	7.5	1.23 10
30701	2	100	218	8.6	1.23 10

WARNING!

Insulated Tools are intended to provide protection against accidental contact with charged energized circuits. For maximum safety we recommend de-energizing all circuits whenever possible before starting work on electrical apparatus or conductors. Always visually inspect insulation on tools before use, do not use tools if insulation shows signs of wear or damage to the insulated areas of the tool. Wear appropriate eye protection when using hand tools. Use NFPA70E certified insulated protective outer wear when appropriate.

Wiha Insulated TORX® Screwdrivers



SHOP

325 TORX® Screwdriver, With Wiha-SoftFinish® Handle

Insulation According to ASTM F-1505-01, New VDE Specification 0682/part 201 and EN/IEC 60900, NFPA70E and CSA, up to 1000 Volt. Individually Tested. Blade high alloy cvm steel, hardened, black finish. Insulation molded directly onto blade.


Item						
No.	Size	mm	Inch	mm	Inch	lbs. pkg.
32505	T5	60	2.4	164	6.5	.06 10
32511	T6	60	2.4	164	6.5	.06 10
32516	T7	60	2.4	164	6.5	.06 10
32521	T8	60	2.4	164	6.5	.06 10
32526	T9	60	2.4	164	6.5	.06 10
32531	T10	60	2.4	164	6.5	.06 10
32536	T15	80	3.0	191	7.5	.12 10
32541	T20	80	3.0	191	7.5	.12 10
32546	T25	80	3.0	198	7.8	.17 10
32551	T27	100	4.0	218	8.6	.20 10
32556	T30	100	4.0	218	8.6	.20 10
32561	T40	150	6.0	274	10.8	.30 10



SHOP

32590 6 Piece TORX® Set

Item					
No.	Size	mm	Size	mm	lbs.
32590	T8	60	T15	80	.83
	T9	60	T20	80	
	T10	60	T25	80	



SHOP


32592 10 Piece TORX® Set

Item					
No.	Size	mm	Size	mm	lbs.
32592	T6	60	T15	80	1.2
	T7	60	T20	80	
	T8	60	T25	80	
	T9	60	T27	100	
	T10	60	T30	100	

Wiha Insulated "BitFlip" Sets

"8-In-1 Bit Sets"

BitFlip standard SoftFinish® handle, multi-component, cushion grip, easy access & 8 bit storage



Each insulated tool individually tested to 10,000 volts

Blade CVM tool steel, hardened



8-in-1 Bit Sets

Tested to 10,000Volts

Insulated



[SHOP](#)

38017 Insulated BitFlip With Slotted/Phillips/TORX® Bits

Wiha cushion grip handle and insulated shaft. Tested to 10,000 volts.

Set includes the following 1/4" bits:

⌚	Slotted:	4.5, 6.5mm	↔
⊕	Phillips:	1, 2	lbs.
⊗	TORX®:	T10, T15, T20, T25	.45



8-in-1 Bit Sets

Tested to 10,000 Volts



Insulated

[SHOP](#)

38016 Insulated BitFlip With Slotted/Phillips/Square Bits

Wiha cushion grip handle and insulated shaft. Tested to 10,000 volts.

Set includes the following 1/4" bits:

⌚	Slotted:	4.5, 6.5mm	↔
⊕	Phillips:	0, 1, 2, 3	lbs.
◻	Square:	1, 2	.45



8-in-1 Bit Sets

Tested to 10,000 Volts



Insulated

[SHOP](#)

38018 Insulated BitFlip With Slotted/Phillips Bits

Wiha cushion grip handle and insulated shaft. Tested to 10,000 volts.

Set includes the following 1/4" bits:

⌚	Slotted:	4.5, 5.5, 6.5, 8.0mm	↔
⊕	Phillips:	0, 1, 2, 3	.45

Insulated Single-Pole Voltage Detector

⚡ 1000Volt



[SHOP](#)

25511 Insulated Single-Pole Voltage Detector. 110-250 Volts.

Insulation According To DIN 57860/6 And DIN VDE 0680-6, GS Tested. Blade CVM steel, hardened, nickel-plated. Insulation molded directly onto blade. Amber LED light. 10,000Volt tested.

Item No.	⌚	mm	mm	mm	Inch	lbs.	pkg.
25511		3.0	65	145	5.7	.04	1

Insulated Voltage Detector



⚡ 1000Volt



[SHOP](#)

25500 Insulated Voltage Detector. Tests 90-1000 Volts.

Category III, CE IEC 61010-1

With audible sound and light warnings. Requires 2 AAA batteries.

Item No.	mm	Inch	lbs.	pkg.
25500	150	6.0	.13	1

Wiha Insulated Belt Pack Pouch Sets

Insulation Test Standards:

Insulation according to EN/IEC 60900,
 ASTM F-1505-01, New VDE 0682/part 201,
 DIN 7437, NFPA70E & CSA


[SHOP](#)

△ 1000Volt

32871 3 Piece Insulated Pliers/Cutters & Multi-Bit Set In Belt Pack Pouch Tools meet EN/IEC, ASTM, VDE, NFPA70E & CSA standards. Pliers chrome finish for long lasting corrosion protection. Soft grip ergo designed handle body, safety slip guard. Insulated multi-bit screwdriver includes Slotted, Phillips & Square bits.

Item No. Pliers/Cutters & Multi-Bit Set

32871 6.3" / 160mm Diagonal Cutters
 8.0" / 200mm Long Nose Pliers

Set includes Bit Holder and the following bits:

Slotted: 4.5, 6.5mm • **Phillips:** 1, 2 • **Square:** 1, 2

🔌 lbs. 1.67


[SHOP](#)

△ 1000Volt

32872 5 Piece Insulated Pliers/Cutters & Screwdrivers In Belt Pack Pouch Tools meet EN/IEC, ASTM, VDE, NFPA70E & CSA standards. Pliers chrome finish for long lasting corrosion protection. Soft grip ergo designed handle body, safety slip guard. Insulated cushion grip drivers, multi-component. Blade CVM tool steel, hardened.

Item No. Insulated Pliers/Cutters & Screwdrivers

32872 6.3" / 160mm Diagonal Cutters
 8.0" / 200mm Long Nose Pliers

Insulated Screwdrivers:

Slotted: 3.0, 4.5mm • **Phillips:** 2

🔌 lbs. 1.77


[SHOP](#)

△ 1000Volt

32873 3 Piece Insulated Pliers/Cutters In Belt Pack Pouch Tools meet EN/IEC, ASTM, VDE, NFPA70E & CSA standards. Pliers chrome finish for long lasting corrosion protection. Soft grip ergo designed handle body, safety slip guard.

Item No. Insulated Pliers & Cutters

32873 6.3" / 160mm Diagonal Cutters
 8.0" / 200mm Long Nose Pliers
 8.0" / 200mm Combination Pliers

🔌 lbs. 2.07


[SHOP](#)

△ 1000Volt

32875 5 Pc. Insulated Pliers/Cutters & SlimLine Screwdrivers In Belt Pack Pouch Tools meet EN/IEC, ASTM, VDE, NFPA70E & CSA standards. Pliers chrome finish for long lasting corrosion protection. Soft grip ergo designed handle body, safety slip guard. Insulated cushion grip drivers, multi-component. Blade CVM tool steel, hardened.

Item No. Insulated Pliers/Cutters & Screwdrivers

32875 9.0" / 225mm Lineman's Pliers
 8.0" / 200mm Long Nose Pliers



Insulated SlimLine Screwdrivers:

Slotted: 4.5, 6.5mm • **Phillips:** 2

🔌 lbs. 2.26

Wiha Insulated Tools-Comfort Grip Handles

All Tools In
Dedicated
Positions For
Quick Storage
& Easy Location
Tracking



32800 80 Piece Insulated Master Electrician's Tool Set In Rolling Water Tight Traveling Tool Box - 10,000Volt Tested, 1000Volt Rated

Item# 32800	Set Includes:	⚡ lbs. 33.9
6.3" Long Nose Pliers	6.3" Diagonal Cutters	
8.0" Long Nose Pliers	8.0" High Leverage Cutters	
6.3" Bent Nose Pliers	6.3" Cable Cutters	
6.3" Long Flat Nose Pliers	6.3" Stripping Pliers	
9.0" Combo Pliers/Crimpers	8.0" Adjustable Wrench	
Insulated Socket 1/2"	Insulated Nut Driver 7/32"	
Insulated Socket 9/16"	Insulated Nut Driver 1/4"	
Insulated Socket 5/8"	Insulated Nut Driver 5/16"	
Insulated Socket 11/16"	Insulated Nut Driver 3/8"	
Insulated Socket 3/4"	Insulated Nut Driver 7/16"	
Insulated Socket 13/16"	Insulated Nut Driver 5.0mm	
Insulated Socket 7/8"	Insulated Nut Driver 5.5mm	
Insulated Socket 13mm	Insulated Nut Driver 6.0mm	
Insulated Socket 14mm	Insulated Nut Driver 7.0mm	
Insulated Socket 15mm	Insulated Nut Driver 8.0mm	
Insulated Socket 17mm	Insulated Nut Driver 10.0mm	
Insulated Socket 19mm	Insulated Nut Driver 13.0mm	
Insulated Socket 20mm	Insulated Cable Knife 50mm	
Insulated Socket 22mm	2 Meter Ruler In/MM	
Insulated Ratchet 3/8" Drive	Single Pole Voltage Detector-	
Insulated 4.9" Extension 3/8" Dr.	110V to 250V	

Insulated Slotted 2.5mm	Insulated Phillips #0
Insulated Slotted 3.0mm	Insulated Phillips #1
Insulated Slotted 3.5mm	Insulated Phillips #2
Insulated Slotted 4.0mm	Insulated Phillips #3
Insulated Slotted 4.5mm	Insulated Slit/Ph Terminal #1
Insulated Slotted 5.5mm	Insulated Slit/Ph Terminal #2
Insulated Slotted 6.0mm	Insulated Square #1
Insulated Slotted 6.5mm	Insulated Square #2
Insulated Slotted 8.0mm	Insulated Torx T6
Insulated Slotted 10.0mm	Insulated Torx T7
Insulated T-handle Hex 5/32"	Insulated Torx T8
Insulated T-handle Hex 3/16"	Insulated Torx T9
Insulated T-handle Hex 7/32"	Insulated Torx T10
Insulated T-handle Hex 1/4"	Insulated Torx T15
Insulated T-handle Hex 5/16"	Insulated Torx T20
Insulated T-handle Hex 3/8"	Insulated Torx T25
Insulated T-handle Hex 4.0mm	Insulated Torx T30
Insulated T-handle Hex 5.0mm	Insulated L-key 10mm
Insulated T-handle Hex 6.0mm	Insulated L-key 1/2"
Insulated T-handle Hex 8.0mm	

Use & Care Guide For Insulated Tools:

Store tools to minimize risk of damage to insulation, always wear approved eye protection, Inspect insulation prior to each use of any insulated tool. Use insulated tools where the ambient temperature is between -20 to +70° C. Have a qualified safety technician visually inspect insulation on tools annually for safe use.

WARNING!

Insulated Tools are intended to provide protection against accidental contact with charged energized circuits. For maximum safety we recommend de-energizing all circuits whenever possible before starting work on electrical apparatus or conductors. Always visually inspect insulation on tools before use, do not use tools if insulation shows signs of wear or damage to the insulated areas of the tool. Wear appropriate eye protection when using hand tools. Use NFPA70E certified insulated protective outer wear when appropriate.

Wiha 1000Volt Insulated Tool Sets - Comfort Grip Handles



△1000Volt

32877 80 Piece Insulated Master Electrician's Set

SHOP

Item# 32877	Set Includes:	lbs. 27.0
6.3" Long Nose Pliers	6.3" Diagonal Cutters	
6.3" Bent Nose Pliers	8.0" High Leverage Cutters	
8.0" Long Nose Pliers	8.0" Cable Cutters	
6.3" Long Flat Nose Pliers	6.3" Stripping Pliers	
9.0" Combo Pliers/Crimpers	8.0" Adjustable Wrench	
Insulated Slotted 2.0mm	Insulated Nut Driver 7/32"	
Insulated Slotted 2.5mm	Insulated Nut Driver 1/4"	
Insulated Slotted 3.0mm	Insulated Nut Driver 5/16"	
Insulated Slotted 3.5mm	Insulated Nut Driver 3/8"	
Insulated Slotted 4.0mm	Insulated Nut Driver 7/16"	
Insulated Slotted 4.5mm	Insulated Nut Driver 5.0mm	
Insulated Slotted 5.5mm	Insulated Nut Driver 5.5mm	
Insulated Slotted 6.0mm	Insulated Nut Driver 6.0mm	
Insulated Slotted 6.5mm	Insulated Nut Driver 7.0mm	
Insulated Slotted 8.0mm	Insulated Nut Driver 8.0mm	
Insulated Slotted 10.0mm	Insulated Nut Driver 10.0mm	
Insulated Phillips #0	Insulated Nut Driver 13.0mm	
Insulated Phillips #1	Insulated T-handle Hex 5/32"	
Insulated Phillips #2	Insulated T-handle Hex 3/16"	
Insulated Phillips #3	Insulated T-handle Hex 7/32"	
Insulated Slit/Ph Terminal #1	Insulated T-handle Hex 1/4"	
Insulated Slit/Ph Terminal #2	Insulated T-handle Hex 5/16"	
Insulated Torx T6	Insulated T-handle Hex 3/8"	
Insulated Torx T7	Insulated T-handle Hex 4.0mm	
Insulated Torx T8	Insulated T-handle Hex 5.0mm	
Insulated Torx T9	Insulated T-handle Hex 6.0mm	
Insulated Torx T10	Insulated T-handle Hex 8.0mm	
Insulated Torx T15	Insulated L-key 10mm	
Insulated Torx T20	Insulated L-key 1/2"	
Insulated Torx T25	Insulated Cable Knife 50mm	
Insulated Torx T30	2 Meter Ruler In/MM	
Insulated Square #1	Insulated Ratchet 3/8" Dr.	
Insulated Square #2	Insulated 4.9" Extension	
Insulated Socket 1/2"	Insulated Socket 13mm	
Insulated Socket 9/16"	Insulated Socket 14mm	
Insulated Socket 5/8"	Insulated Socket 15mm	
Insulated Socket 11/16"	Insulated Socket 17mm	
Insulated Socket 3/4"	Insulated Socket 19mm	
Insulated Socket 13/16"	Insulated Socket 20mm	
Insulated Socket 7/8"	Insulated Socket 22mm	



Master Electrician's Set



**66 Pc.
BIGGER
SET**

△1000Volt

32876 66 Pc. Master Electrician's Set. Insulation According to VDE 0682/part 201, EN/IEC 60900, ASTM F-1505-01, NFPA70E & CSA,

△up to 1000 volt. Individually Tested. Pliers drop-forged from special tool steel, individually high frequency induction hardened, chrome/nickel plated, mirror-polished.

SHOP

Item# 32876	Set Includes:	lbs. 21.5
8.0" Long Nose	6.3" Side Cutters	
6.3" Long Flat Nose	8.0" High Leverage Cutters	
9.0" Combo Pliers/Crimpers	6.3" Stripping Pliers	
8.0" Cable Cutters	8.0" Adjustable Wrench	
Insulated Nut Driver 1/4"	Insulated Slotted 2.0mm	
Insulated Nut Driver 5/16"	Insulated Slotted 2.5mm	
Insulated Nut Driver 11/32"	Insulated Slotted 3.0mm	
Insulated Nut Driver 3/8"	Insulated Slotted 4.0mm	
Insulated Nut Driver 7/16"	Insulated Slotted 4.5mm	
Insulated T-handle Hex 4.0mm	Insulated Slotted 5.5mm	
Insulated T-handle Hex 5.0mm	Insulated Slotted 6.0mm	
Insulated T-handle Hex 6.0mm	Insulated Slotted 8.0mm	
Insulated T-handle Hex 8.0mm	Insulated Slotted 10.0mm	
Insulated T-handle Hex 5/32"	Insulated Phillips #0	
Insulated T-handle Hex 3/16"	Insulated Phillips #1	
Insulated T-handle Hex 7/32"	Insulated Phillips #2	
Insulated T-handle Hex 1/4"	Insulated Phillips #3	
Insulated T-handle Hex 5/16"	Insulated Torx T8	
Insulated T-handle Hex 3/8"	Insulated Torx T10	
Insulated Hex L-key 10.0mm	Insulated Torx T15	
Insulated Hex L-key 1/2"	Insulated Torx T20	
Insulated Socket 1/2"	Insulated Torx T25	
Insulated Socket 9/16"	Insulated Torx T30	
Insulated Socket 5/8"	Insulated Square #1	
Insulated Socket 11/16"	Insulated Square #2	
Insulated Socket 3/4"	Insulated Slit/Ph Terminal #1x80	
Insulated Socket 13/16"	Insulated Slit/Ph Terminal #2x100	
Insulated Socket 7/8"	Insulated Cable Knife 50mm	
Insulated Socket 8.0mm	Insulated Extension 4.9"	
Insulated Socket 10.0mm	Insulated Ratchet 3/8" Driver	
Insulated Socket 13.0mm	Insulated Socket 17.0mm	
Insulated Socket 14.0mm	Insulated Socket 19.0mm	
Insulated Socket 15.0mm	Insulated Socket 22.0mm	

Wiha 1000Volt Insulated Tool Sets - Comfort Grip Handles

 **1000Volt** **48 Pc. BIG SET**
[SHOP](#)

32874 48 Piece Insulated Tool Set. Insulation According to VDE 0682/part 201, EN/IEC 60900, ASTM F-1505-01, NFPA70E & CSA,  up to 1000 volt. Individually Tested. Pliers drop-forged from special tool steel, individually high frequency induction hardened, chrome/nickel plated, mirror-polished. Cushion Grip Insulated handles. Canvas tool bag.

Item# 32874	Set Includes:	 lbs. 19.4
6.3" Long Nose Pliers	6.3" Side Cutters	
8.0" Long Nose Pliers	8.0" High Leverage Cutters	
6.3" Combination Pliers	6.3" Stripping Pliers	
9.0" Combo Pliers/Crimpers	8.0" Adjustable Wrench	

Slotted: 2.0, 2.5, 3.0, 3.5, 4.0, 4.5, 5.5, 6.0, 6.5, 8.0mm

Phillips: #0, 1, 2, 3 **Square:** #1, 2 **Slt/Ph Terminal:** #1, 2

TORX: T8, T9, T10, T15, T20, T25, T27, T30

Hex Inch: 5/32, 3/16, 7/32, 1/4, 5/16, 3/8"

Nut Driver Inch: 7/32, 1/4, 5/16, 3/8, 7/16, 1/2"

Insulated Cable Knife & 2 Meter In/MM


25 Pc. Set
 **1000Volt**
[SHOP](#)

32879 25 Pc. Pliers & Screwdriver Set. Insulation According to VDE 0682/part 201, EN/IEC 60900, ASTM F-1505-01, NFPA70E & CSA,  up to 1000 volt. Individually Tested.

Pliers drop-forged from special tool steel, individually high frequency induction hardened, chrome/nickel plated, mirror-polished. In tool box.

Item# 32879	Set Includes:	 lbs. 11.92
8.0" Long Nose	6.3" Stripping Pliers	
9.0" Combination Pliers	Inch & Metric Folding Ruler	
8.0" High Leverage Cutters	8.5" Insulated Knife	

Slotted: 3.0, 4.5, 6.0mm **Phillips:** #1, #2

Square: #1, #2

Terminal Block Driver: #1, #2


Inch Nut Driver: 1/4, 5/16, 11/32, 3/8, 7/16, 1/2"

Metric Nut Driver: 7.0, 8.0, 10.0, 13.0mm


13 Pc. Set
 **1000Volt**
[SHOP](#)

32878 13 Piece Pliers & Screwdriver Set. In canvas tool bag

Item# 32878	Set Includes:	 lbs. 6.60
8.0" Long Nose	9.0" Combo Pliers/Crimpers	
8.0" High Leverage Cutters	50mm Cable Stripping Knife	
Insulated Slotted: 3.0mm	Insulated Phillips: #1	
Insulated Slotted: 4.5mm	Insulated Phillips: #2	
Insulated Slotted: 6.0mm	Insulated Square: #1	
Insulated Slt/Ph Terminal: #1	Insulated Square: #2	
Insulated Slt/Ph Terminal: #2		


31 Pc. Set
 **1000Volt**
[SHOP](#)

32896 31 Pc. Pliers & Screwdriver Set. Insulation According to VDE 0682/part 201, EN/IEC 60900, ASTM F-1505-01, NFPA70E & CSA,  up to 1000 volt. Individually Tested. Pliers drop-forged from special tool steel, individually high frequency induction hardened, chrome/nickel plated, mirror-polished. Set includes 6ft. Fiber glass folding ruler.

Item# 32896	Set Includes:	 lbs. 12.85
6.3" Long Nose Pliers	6.3" Side Cutters	
8.0" Long Nose Pliers	8.0" High Leverage Cutters	
7.0" Linemans Pliers	6.3" Stripping Pliers	
9.0" Combination Pliers	6.3" Round Nose Pliers	

Slotted: 2.0, 2.5, 3.0, 3.5, 4.5, 5.5, 6.5, 8.0, 10.0mm

Phillips: #0, #1, #2, #3

Inch Nut Driver: 5/32, 3/16, 7/32, 1/4, 5/16, 3/8, 7/16, 1/2, 9/16"

Wiha Insulated Pliers with High Visibility Comfort Grip Handle

⚡ 1000Volt



- Pliers drop-forged from special tool steel, individually high frequency induction hardened, chrome and nickel plated, mirror-polished.
- In zipper carry case

SHOP

32891 10 Piece Pliers & Screwdriver Set

Insulation According to VDE 0682/part 201, EN/IEC 60900, ASTM F-1505-01, NFPA70E & CSA, ⚡ up to 1000 volt. Individually Tested.

Item# 32891 Set Includes: ⚡ lbs. 5.54	
8.0" Combination Pliers	8.0" Long Nose
8.0" Side Cutters	8.0" Cable Cutters
6.3" Universal Wire Stripper	
Insulated Phillips #1	Insulated Slotted 4.5mm
Insulated Phillips #2	Insulated Slotted 6.5mm
Insulated Phillips #3	



- Pliers drop-forged from special tool steel, individually high frequency induction hardened, chrome and nickel plated, mirror-polished.
- In zipper carry case

⚡ 1000Volt

SHOP

32895 14 Piece Pliers & Screwdriver Set

Insulation According to VDE 0682/part 201, EN/IEC 60900, ASTM F-1505-01, NFPA70E & CSA, ⚡ up to 1000 volt. Individually Tested.

Item# 32895 Set Includes: ⚡ lbs. 6.60	
8.0" Long Nose	6.3" Side Cutters
9.0" Combination Pliers	8.0" High Leverage Cutters
6.3" Stripping Pliers	Insulated Slotted 2.5mm
Insulated Phillips #1	Insulated Slotted 3.0mm
Insulated Phillips #2	Insulated Slotted 3.5mm
Insulated Phillips #3	Insulated Slotted 4.5mm
Insulated Slotted 2.0mm	Insulated Slotted 6.5mm



⚡ 1000Volt

SHOP

32888

11 Piece Pliers & Screwdriver Set In Canvas Pouch

Item# 32888 Set Includes: ⚡ lbs. 3.58	
6.3" Long Nose	6.3" Side Cutters
8.0" Combination Pliers	6.3" Stripping Pliers
Insulated Slotted 2.5mm	Insulated Phillips #0
Insulated Slotted 3.5mm	Insulated Phillips #1
Insulated Slotted 4.5mm	Insulated Phillips #2
Insulated Slotted 6.0mm	



⚡ 1000Volt

SHOP

32892

10 Piece Pliers & Screwdriver Set. Insulation According to VDE 0682/part 201, EN/IEC 60900, ASTM F-1505-01, NFPA70E & CSA, ⚡ up to 1000 volt. Individually Tested.

Pliers drop-forged from special tool steel, individually high frequency induction hardened, chrome and nickel plated, mirror-polished. In canvas tool bag

Item# 32892 Set Includes: ⚡ lbs. 6.64	
8.0" Bent Nose	8.0" Combination Pliers
6.3" Long Nose	6.3" Side Cutters
Insulated Phillips #0	Insulated Slotted 3.0mm
Insulated Phillips #1	Insulated Slotted 4.5mm
Insulated Phillips #2	Insulated Slotted 6.5mm



⚡ 1000Volt

SHOP

32894

12 Piece Pliers & Screwdriver Set In canvas tool bag

Item# 32894 Set Includes: ⚡ lbs. 8.60	
8.0" Bent Nose	8.0" Combination Pliers
6.3" Long Nose	6.3" Side Cutters
Insulated Slotted 4.5mm	Insulated Nut Driver 1/4"
Insulated Slotted 6.5mm	Insulated Nut Driver 5/16"
Insulated Phillips #1	Insulated Nut Driver 3/8"
Insulated Phillips #2	Insulated Nut Driver 1/2"



Wiha Insulated Pliers with High Visibility Comfort Grip Handle

- Pliers drop-forged from special tool steel, individually high frequency induction hardened, chrome and nickel plated, mirror-polished.



⚡ 1000Volt

SHOP

32889 8 Piece Pliers & Cutters Set

Insulation According to VDE 0682/part 201, EN/IEC 60900, ASTM F-1505-01, NFPA70E & CSA, ⚡ up to 1000 volt. Individually Tested.

Item# 32889	Set Includes:	⚡ lbs. 4.63
6.3" Long Nose Pliers	8.0" Long Nose Pliers	
6.3" Lineman's Pliers	6.3" Diagonal Cutters	
9.0" Lineman's Pliers	8.0" High Lev. Cutters	
6.3" Wire Stripping Pliers	Electrician's Knife	



⚡ 1000Volt

SHOP

32869 14 Piece Pliers/Cutters & Screwdrivers Set

Insulation According to VDE 0682/part 201, EN/IEC 60900, ASTM F-1505-01, NFPA70E & CSA, ⚡ up to 1000 volt. Individually Tested.

Item# 32869	Set Includes:	⚡ lbs. 6.52
9.0" Lineman's Pliers	8.0" High Leverage Cutters	
8.0" Cable Cutters	8.0" Long Nose Pliers	
6.0" Stripping Pliers 10-20 AWG		
SlimLine Slotted 3.0mm	SlimLine Phillips #1	
SlimLine Slotted 4.5mm	SlimLine Phillips #2	
SlimLine Slotted 6.5mm	SlimLine Terminal #2	
SlimLine Square #1	Single Pole Tester	
SlimLine Square #2		



⚡ 1000Volt

SHOP

32867 10 Piece Pliers & Screwdriver Set In Canvas Pouch

Item# 32867	Set Includes:	⚡ lbs. 4.06
6.3" Diagonal Cutters	9.0" Combo Pliers	
6.3" Long Nose Pliers	6.3" Wire Strippers	
7.0" Crimping Pliers		
Insulated Slotted 4.5mm	Insulated Phillips #1	
Insulated Slotted 6.0mm	Insulated Phillips #2	
Insulated Square: #2		



⚡ 1000Volt

SHOP

32868 10 Piece Pliers & Screwdriver Set In Canvas Pouch

Item# 32868	Set Includes:	⚡ lbs. 4.24
7.0" Diagonal Cutters	9.0" Combo Pliers	
8.0" Long Nose Pliers	6.3" Wire Strippers	
7.0" Crimping Pliers		
Insulated Slotted 3.0mm	Insulated Phillips #1	
Insulated Slotted 4.5mm	Insulated Phillips #2	
Insulated Slotted 6.0mm		

WARNING!

Insulated Tools are intended to provide protection against accidental contact with charged energized circuits. For maximum safety we recommend de-energizing all circuits whenever possible before starting work on electrical apparatus or conductors. Always visually inspect insulation on tools before use, do not use tools if insulation shows signs of wear or damage to the insulated areas of the tool. Wear appropriate eye protection when using hand tools. Use NFPA70E certified insulated protective outer wear when appropriate.

Use & Care Guide For Insulated Tools:


Store tools to minimize risk of damage to insulation, always wear approved eye protection, Inspect insulation prior to each use of any insulated tool. Use insulated tools where the ambient temperature is between -20 to +70° C. Have a qualified safety technician visually inspect insulation on tools annually for safe use.

Wiha Insulated Pliers & Cutters

Insulation Standards:

EN/IEC 60900, ASTM F-1505-01,
and or According to VDE 0682/part 201,
NFPA70E and CSA

Hard chrome finish for
long lasting corrosion
protection



 **1000V**

Cutters additionally
induction hardened

Soft grip ergonomically
designed handle body

Safety slip
guard

**Tools Meet 10,000 Volt Test Standards
Rated to 1000 Volt ac or 1500 Volt dc**

Insulated Linemans Pliers With Crimpers

5-In-1 Lineman's Pliers

64HRC
cutting edges

 **1000volt**



With Lower Crimping Jaw

SHOP

32821 Insulated Lineman's Pliers "5-In-1" Professional Design
Insulation According to EN/IEC, ASTM, NFPA70E & CSA,
 **up to 1000 volt. Individually Tested.**

Deep cut radius conduit jaws for non-slip handling. Sure grip knurled & cross hatched flat jaw for non-slip gripping. Extra long induction hardened precision matched cutting edges. Lower crimping jaw accepts most standard non-insulated electrical connectors. Large head with square anvil surface on each side. Made from premium CV tool steel forgings. Two component cushion grips for best user comfort.

Item	↔	↔	Cutting Capacity		
No.	mm	Inch	Copper AWG	Pkg.	wt.
32821	225	9.0	#4	1	.88

Insulated High Leverage Combination Pliers

Lineman's

 **1000volt**



SHOP

32820 High Leverage Combination Pliers. Insulation According to EN/IEC 60900, ASTM F-1505-01, NFPA70E & CSA,  up to 1000 volt. Individually Tested. DIN ISO 5746

Extra long cutting edge for flat and round cables. Serrated jaws. Cutting edges additionally induction hardened to approx. 64HRC. C60 Special tool steel. Use for gripping, pulling & holding as well as cutting wires and cables ranging in hardness from soft to extremely hard. Two component soft grip ergonomic handles.

Item	↔	↔	Cutting Capacity		
No.	mm	Inch	Copper AWG	Pkg.	wt.
32820	225	9.0	#4	1	.86

Insulated Combination Lineman's Pliers

 **1000volt**



SHOP

328 Combination Pliers. Insulation According to VDE 0682/part 201, EN/IEC 60900, ASTM F-1505-01, NFPA70E & CSA,  up to 1000 volt. Individually Tested. DIN ISO 5746 Extra long cutting edge for flat & round cables. Serrated jaws. Cutting edges additionally induction hardened to approx. 64HRC. Special CV tool steel forgings, Chrome finish. Use for gripping and holding as well as cutting soft and hard wires and cables. Two component soft grip ergonomic handles.

Item	↔	↔	Cutting Capacity		
No.	mm	Inch	Copper AWG	Pkg.	wt.
32814	160	6.3	#10	1	.53
32816	180	7.0	#9	1	.58
32818	200	8.0	#8	1	.72

Insulated Diagonal Cutters



64HRC
cutting edges

1000volt

SHOP

Insulated High Leverage Diagonal Cutters



New dynamic joint provides
40% easier cuts and
significantly longer tool life

1000volt

SHOP

Insulated Electrician's Diagonal Cutters

Strips AWG
#10 & #14



1000volt

SHOP

Insulated Serrated Edge Cable Cutters



1000volt

SHOP

Insulated Crimping Pliers



SHOP

328 Diagonal Cutters. Insulation According to VDE 0682/part 201, EN/IEC 60900, ASTM F-1505-01, NFPA70E & CSA, Δ up to 1000 volt. Individually Tested. DIN ISO 5749 Low wear lap joint, riveted and able to withstand high levels of load. Lightweight action, clean cutting. Long term cutting is achieved through additional inductive hardening to approx. 60 HRC. Special tool steel hardened and tempered. For soft & medium hard wire. 32832 & 32834 for soft, hard & piano wire.

Item No.	mm	Inch	Cutting Capacity Copper AWG	Pkg.	wt.
32830	140	5.5	#6	1	.47
32832	160	6.3	#6	1	.49
32834	180	7.0	#6	1	.62

328 High Leverage Diagonal Cutters. Insulation According to VDE 0682/part 201, EN/IEC 60900, ASTM F-1505-01, NFPA70E & CSA, Δ up to 1000 volt. Individually Tested. DIN ISO 5749 Semi-circular. Low wear lap joint, riveted and able to withstand high levels of load. Lightweight action, clean cutting. Long term cutting is achieved through additional inductive hardening to approx. 64HRC. C 60 special tool steel hardened and tempered to high quality. For soft, hard and piano wire, lay-on joint, optimized power transmission.

Item No.	mm	Inch	Cutting Capacity Copper AWG	Pkg.	wt.
32835	160	6.3	#6	1	.64
32836	180	7.0	#5	1	.67
32838	200	8.0	#4	1	.80

32861 Diagonal Cutters W/Stripping Holes. Insulation According to VDE 0682/part 201, EN/IEC 60900, ASTM F-1505-01, NFPA70E & CSA, Δ up to 1000 volt. Individually Tested. Drop-forged from special tool steel, cutters additionally induction hardened to approx. 64HRC, chrome-nickel plated, mirror-polished. Ergo comfort grip with slip guard. Holes in the cutting edge for stripping copper wire of $\varnothing$ 1.5 and 2.5.

Item No.	mm	Inch	Cutting Capacity Copper AWG	Pkg.	wt.
32861	160	6.3	#6	1	.55


328 Serrated Edge Cable Cutters. Insulation According to VDE 0682/part 201, EN/IEC 60900, ASTM F-1505-01, NFPA70E and CSA, Δ up to 1000 Volt. Individually Tested. Light, clean cutting ground precision cutting edges. Durable cutting is achieved through additional inductive hardening to approx. 64HRC. Special tool steel, hardened & tempered. For cutting of copper & aluminum cables without crushing.

Item No.	mm	Inch	$\varnothing$	mm ²	Pkg.	lbs.
32826	160	6.3	16	50	1	.42
32828	200	8.0	20	60	1	.67

32841 Insulated Crimping Pliers. Insulation According to VDE 0682/part 201, EN/IEC 60900, ASTM F-1505-01, NFPA70E and CSA, Δ up to 1000 Volt. Individually Tested. Semi-circular profiles for secure connection between end sleeve and conductor. Long life is achieved through additional induction hardening to 64HRC. CV 60 special tool steel hardened & tempered.

Item No.	mm	Inch	mm ²	AWG	Pkg.	wt.
32841	180	7.0	0.25-2.5	6-30	1	.57

Insulated Long Nose Pliers


[SHOP](#)

328 Long Nose Pliers With Cutters. Insulation According to VDE 0682/part 201, EN/IEC 60900, ASTM F-1505-01, NFPA70E & CSA, Δ up to 1000 volt. Individually Tested. Drop-forged from special tool steel, cutters additionally induction hardened to approx. 64HRC, chrome-nickel plated, mirror-polished, ergonomic comfort grip with slip guard, half-round jaws, serrated gripping surface.

Item	mm	Inch	Cutting Capacity	Pkg.	wt.
No.			Copper AWG		
32806	160	6.3	#10	1	.32
32808	200	8.0	#8	1	.42

Insulated Bent Nose Pliers

Angled 40°


[SHOP](#)

328 Bent Nose Pliers With Cutters. Insulation According to VDE 0682/part 201, EN/IEC 60900, ASTM F-1505-01, NFPA70E & CSA, Δ up to 1000 volt. Individually Tested.

Drop-forged from special tool steel, cutters additionally induction hardened to approx. 64HRC, chrome-nickel plated, mirror-polished. Ergonomic comfort grip with slip guard. Half-round jaws, serrated gripping surface, nose bent 40°.

Item	mm	Inch	Cutting Capacity	Pkg.	wt.
No.			Copper AWG		
32804	200	8.0	#8	1	.43
32807	160	6.3	#10	1	.32

Round Nose Pliers




[SHOP](#)

32870 Round Nose Pliers. Insulation According to VDE 0682/part 01, EN/IEC 60900, ASTM F-1505-01, NFPA70E & CSA, Δ up to 1000 volt. Individually Tested. Drop-forged from special tool steel, individually induction hardened, chrome and nickel plated, mirror-polished. Ergonomic comfort grip with slip guard. Serrated jaws.

Item	mm	Inch	Pkg.	wt.
No.				
32870	160	6.3	1	.34

Insulated Long Flat Nose Pliers



[SHOP](#)

32810 Long Flat Nose Pliers. Insulation According to VDE 0682/part 201, EN/IEC 60900, ASTM F-1505-01, NFPA70E & CSA, Δ up to 1000 volt. Individually Tested. DIN ISO 5745 Extra long head. Serrated Jaws are induction hardened. Special CV tool steel forgings, Chrome finish. Two component Soft Grip handles. Use for Gripping and right-angle bending of wires and sheet metal parts.

Item	mm	Inch	Pkg.	wt.
No.				
32810	160	6.3	1	.39

Insulated Stripping Pliers

64HRC cutting edges




32860 Stripping Pliers. Insulation According to VDE 0682/part 201, EN/IEC 60900, ASTM F-1505-01, NFPA70E and CSA, Δ up to 1000 volt. Individually Tested. Heavy duty forged, induction hardened cutting edges for even stripping of insulation. Drop-forged from special tool steel, chrome and nickel plated, mirror-polished. Spring and adjusting screw, for stripping up to Ø 5mm/#4 Awg.

Item	mm	Inch	Stripping Capacity	Pkg.	wt.
No.			Copper AWG		
32860	160	6.3	#8 - #28	1	.50

Wiha Canvas Pliers Holster

- Canvas holster with belt clip and belt loop
- Security pliers strap
- Screwdriver holder in the front

[SHOP](#)

91256 Pliers Canvas Holster

Item	Width	Height	lbs.	pkg.
No.	Size	Size		
91256	3.5 x	6.75	.15	1



Insulated Stripping Pliers




SHOP

1000Volt

10250	Insulated Stripping Pliers. Insulation According to EN/IEC 60900, DIN ISO 8976, ASTM F-1505 & CSA Specification. Individually Tested. Wide long head with ridged gripping surface, shears blade and firm wire stripping stations. Wire stripping stations 0.81 / 1.0 / 1.3 / 1.6 / 2.0 / 2.59mm, AWG 20 / 18 / 16 / 14 / 12 / 10.					
Item No.	mm	Inch	Ø	AWG	Pkg.	lbs.
10250	160	6.3"	0.81-2.59	20-10	5	.26

Switch Cabinet Key



SHOP

21103 Switch Cabinet Keys

For applications with all common switch cabinets and locking systems. Diecast Zinc

Item No.	mm	Inch	Pkg.	lbs.
21103	76	3.0"	5	.22

Protturn Insulated Electrician's Shears



SHOP

32951 Protturn Insulated Electrician's Shears

Insulation meets VDE, ASTM F1505, EN/IEC 60900, CSA, NFPA 70E, OSHA Specifications. Made from stainless 420 grade steel

Item No.	mm	Inch	Pkg.	lbs.
32951	160	6.3	1	.22

Tools Meet
10,000 Volt Test Standards
Rated to 1000Volt ac or 1500 Volt dc

91230 Inomic Canvas Holster

Item No.	Width	Height	Weight	Pkg.
91230	4.0 x	4.5	.05	1

Holds any Inomic Pliers



Wiha Inomic 1000Volt Insulated Pliers



Award winning ergonomic design with head mounted at 23° angle to grip for reduced user fatigue

Each tool includes a convenient jaw lock & handle return spring

Heads drop forged CV premium tool steel



32850

32852

32854

Tools Meet 10,000 Volt Test Standards Rated to 1000 Volt ac or 1500 Volt dc

1000volt

SHOP

32850

Inomic Combo Pliers. Insulation According to EN/IEC 60900, ASTM F-1505-01, NFPA70E & CSA,  up to 1000 volt. Individually Tested. DIN ISO 5749 Precision machined forged head. Induction hardened for longest tool life. Cross hatched flat jaw & deep cut radius jaws for secure gripping of the work piece. Cutting edges are matched for precise cutting action. Award winning ergonomic design with head mounted at 23° angle to grip for reduced user fatigue. Palm side of grip has molded soft panel for added comfort in prolonged use.

32852 Inomic Long Nose Pliers

Item No.	mm	Inch	Cutting Capacity Copper AWG	Pkg.	lbs.
32852	160	6.3	#6	1	.43

32854 Inomic Diagonal Cutters

Item No.	mm	Inch	Cutting Capacity Copper AWG	Pkg.	lbs.
32854	160	6.3	#6	1	.41

Insulation Standards:
EN/IEC 60900,
ASTM F-1505-01,
NFPA70E & CSA



SHOP

1000Volt

32859 3 Pc. Insulated Inomic Pliers/Cutters Set

Award winning ergonomic design with head mounted at 23° angle to grip for reduced user fatigue.

Item# 32859 Set Includes: lbs. 1.45

32850 - Combo Pliers	32854 - Diagonal Cutters
32852 - Long Nose Pliers	91230 - Inomic Holster (Includes 3)

Three Holsters Included




Insulated Industrial Pliers & Cutters

Tools meet ASTM, IEC, VDE, EN, NFPA & CSA standards

10,000 Volt tested
1000 Volt Rated

Industrial
brushed finish



Induction hardened
jaws and cutters
to 60 HRC

Two component ergo
cushion grip handles

 **1000V**



New dynamic joint provides
**40% easier cuts & significantly
longer tool life**

Insulated Lineman's Pliers With Crimpers

64HRC
cutting edges



Long life high
performance
dynamic 60/40 joint

 **1000volt**

SHOP

32917 Insulated Industrial Lineman's Pliers "5-In-1" Professional Design Insulation According to EN/IEC, ASTM, NFPA70E & CSA,  **up to 1000 volt. Individually Tested.** Deep cut radius conduit jaws for non-slip handling. Sure grip knurled & cross hatched flat jaw for non-slip gripping. Extra long induction hardened precision matched cutting edges. Lower crimping jaw accepts most standard non-insulated electrical connectors. Large head with square anvil surface on each side. Premium CV tool steel forgings.

Item No.	mm	Inch	Cutting Capacity Copper AWG	Pkg.	wt.
32917	225	9.0	#4	1	.98

Insulated Long Nose Pliers With Cutters



 **1000volt**

SHOP

329 Insulated Industrial Long Nose Pliers With Cutters. Insulation According to VDE 0682/part 201, EN/IEC 60900, ASTM F-1505-01, NFPA70E & CSA,  **up to 1000 volt. Individually Tested.** Drop-forged from special tool steel, cutters additionally induction hardened to approx. 64HRC, half-round jaws, serrated gripping surface. Industrial brushed finish. Ergonomic comfort grip with slip guard.

Item No.	mm	Inch	Cutting Capacity Copper AWG	Pkg.	wt.
32926	160	6.3	#10	1	.36
32923	200	8.0	#8	1	.46

Insulated Diagonal Cutters



Long life high performance
dynamic 60/40 joint

 **1000volt**

SHOP

329 Insulated Industrial Diagonal Cutters. Insulation According to VDE 0682/part 201, EN/IEC 60900, ASTM F-1505-01, NFPA70E & CSA,  **up to 1000 volt. Individually Tested.** DIN ISO 5749 Low wear lap joint, riveted and able to withstand high levels of load. Lightweight action, clean cutting. Long term cutting is achieved through additional inductive hardening to approx. 64HRC. Special tool steel hardened & tempered. Industrial brushed finish. For soft, medium hard wire & piano wire.

Item No.	mm	Inch	Cutting Capacity Copper AWG	Pkg.	wt.
32933	160	6.3	#6	1	.64
32929	200	8.0	#6	1	.80

Insulated Stripping Pliers



 **1000volt**

SHOP

32947 Insulated Industrial Stripping Pliers. Insulation According to VDE 0682/part 201, DIN 7437, EN/IEC 60900, ASTM F-1505-01, NFPA70E & CSA, **1000 volt rated. Individually Tested.** DIN ISO 5745 Made from Premium CV tool steel forgings. Induction hardened jaws and cutters to 64HRC. Industrial brushed finish. Two component ergo cushion grips for best user comfort. Spring & adjusting screw, for stripping up to Ø 5mm/#4 Awg.

Item No.	mm	Inch	Stripping Capacity Copper AWG	Pkg.	wt.
32947	160	6.3	#8 - #28	1	.46

Insulated Combo Pliers With Dynamic Joint

 1000volt


Long life high performance dynamic 60/40 joint

[SHOP](#)

Insulated Heavy Duty Cable Cutters

 1000volt

[SHOP](#)

Insulated Crimpers

 1000volt

[SHOP](#)

Insulated Water Pump Pliers

 1000volt

[SHOP](#)

Insulated Push Button Water Pump Pliers

 1000volt

[SHOP](#)

32930 Insulated Industrial High Leverage Combination Pliers. Insulation According to EN/IEC 60900, ASTM F-1505-01, NFPA70E & CSA,  up to 1000 volt. Individually Tested. DIN ISO 5746 Extra long cutting edge for flat and round cables. Serrated jaws. Cutting edges additionally induction hardened to approx. 64HRC. Use for gripping, pulling & holding as well as cutting wires and cables ranging in hardness from soft to extremely hard. Industrial brushed finish. Two component soft grip ergonomic handles.

Item	↔	↔	Cutting Capacity		
No.	mm	Inch	Copper AWG	Pkg.	wt.
32930	200	8.0	#4	1	.92

32927 Insulated Industrial Serrated Edge Cable Cutters. Insulation According to VDE 0682/part 201, EN/IEC 60900, ASTM F-1505-01, NFPA70E and CSA,  up to 1000 Volt. Individually Tested. Light, clean cutting ground precision cutting edges. Durable cutting is achieved through additional inductive hardening to approx. 64HRC. Premium CV tool steel forgings. For cutting of copper & aluminum cables without crushing. Two component ergo cushion grips for best user comfort.

Item	↔	↔				
No.	mm	Inch	Ø	mm2	Pkg.	lbs.
32927	200	8.0	20	60	1	.78

32945 Insulated Industrial Crimping Pliers. Insulation According to VDE 0682/part 201, EN/IEC 60900, ASTM F-1505-01, NFPA70E and CSA,  up to 1000 Volt. Individually Tested. Semi-circular profiles for secure connection between end sleeve and conductor. Long life is achieved through additional induction hardening to 64HRC. Industrial brushed finish. Two component ergo cushion grips for best user comfort. Crimps 6 - 30 AWG Connectors.

Item	↔	↔				
No.	mm	Inch	mm2	AWG	Pkg.	wt.
32945	180	7.0	0.25-2.5	6-30	1	.64

32954 Insulated Industrial Water Pump Pliers. Insulation According to VDE 0682/part 201, EN/IEC 60900, ASTM F-1505-01, NFPA70E and CSA,  up to 1000 Volt. Individually Tested. 10 opening settings provides optimal adjustment to objects being gripped. Long life achieved through additional induction hardening of jaws to approx. 62HRC. Chrome-vanadium tool steel forgings, hardened and tempered. Black finish.

Item	↔	↔	Capacities		
No.	mm	Inch	Round Hex	Pkg.	wt.
32954	250	10.0	1 3/4 2	1	.90

32956 Insulated Industrial Push Button Water Pump Pliers. Insulation According to VDE 0682/part 201, EN/IEC 60900, ASTM F-1505-01, NFPA70E and CSA,  up to 1000 Volt. Individually Tested. Extra narrow head for working in small spaces. Rapid and simple push button setting & locking. Long life achieved through additional induction hardening of jaws to approx. 62HRC. Finger jam protection for safe operation at all settings. CVM tool steel forgings, hardened & tempered.

Item	↔	↔	Capacities		
No.	mm	Inch	Round Hex	Pkg.	wt.
32956	250	10.0	1 3/4 2"	1	.90

Wiha Insulated Industrial Tool Sets



32982 3 Pc. Insulated Industrial Pliers/Cutters & Voltage Detector

Item No. Insulated Pliers/Cutters & Voltage Detector

32982 6.3" Long Pliers, 6.3" Diagonal Cutters

Voltage Detector with both light and sound alerts

lbs. .98



Tools meet ASTM,
IEC, VDE, EN,
NFPA & CSA
standards

1000Volt

Tool box set
in blow molded tray

32999 9 Piece Insulated Industrial Pliers & Cutters Set

Insulated pliers & cutters set in a light weight tool box tray.

Item No. 9.0" Lineman's Pliers 8.0" High Lev. Combo Pliers

32999 6.3" Long Nose Pliers 8.0" Cable Cutters

8.0" Long Nose Pliers 6.3" Stripping Pliers

lbs. 6.3" Diagonal Cutters 7.0" Crimping Pliers

6.34 8.0" Diagonal Cutters



Tools meet ASTM,
IEC, VDE, EN,
NFPA & CSA
standards

1000Volt

32985 7 Pc. Insulated Industrial Pliers/Cutters & Screwdrivers


Item No. Insulated Pliers/Cutters & Screwdrivers

32985 8.0" Combo Pliers, 6.3" Long Nose, 6.3" Diagonal Cutters

Insulated Drivers: Slotted: 3.0, 4.5mm • Phillips: #1, #2

lbs. 2.30

Wiha Insulated Tool Tray Sets



Tools meet ASTM,
IEC, VDE, EN,
NFPA & CSA
standards

1000Volt

Tool box set
in blow molded trays



Tools meet ASTM,
IEC, VDE, EN,
NFPA & CSA
standards

Individually Tested



1000Volt

32981 3 Pc. Insulated Industrial Pliers & Cutters

Item No. Insulated Pliers & Cutters

32981 8.0" Combo Pliers, 8.0" Long Pliers, 8.0" Diagonal Cutters

lbs. 2.18



Tools meet ASTM,
IEC, VDE, EN,
NFPA & CSA
standards

Individually Tested



1000Volt

32983 5 Pc. Insulated Industrial Diagonal Cutters & Screwdrivers

Item No. Insulated Diagonal Cutters & Screwdrivers

32983 6.3"/160mm Diagonal Cutter

Insulated Drivers: Slotted: 3.0, 4.5mm • Phillips: #1, #2

lbs. 1.17



Tools meet ASTM,
IEC, VDE, EN,
NFPA & CSA
standards

Individually Tested



1000Volt

32984 6 Pc. Insulated Industrial Combo Pliers & Screwdrivers

Item No. Insulated Combination Pliers & Screwdrivers

32984 8.0" Combination Pliers & 8" Long Nose Pliers

Drivers: Slotted: 3.0, 4.5mm • Phillips: #2 • Square: #2

lbs. 2.06

32989 28 Piece Insulated Industrial Pliers & Cutters Set

Insulated pliers & cutters set in a light weight tool box tray.

Item No. Set Includes:

32989 9.0" Lineman's Pliers

8.0" High Leverage Combo Pliers

6.3" & 8.0" Long Nose Pliers

8.0" Cable Cutters

6.3" & 8.0" Diagonal Cutters

6.3" Stripping Pliers

7.0" Crimping Pliers

lbs.

6.34

Slotted: 2.5, 3.0, 3.5, 4.0, 4.5, 5.5, 6.0, 6.5, 8.0, 10.0mm

Phillips: #0, #1, #2, #3

Xeno Slotted/Phillips: #1, #2 & Square: #1, #2

Voltage Detector 3.0mm 110-225Volts

Wiha Insulated Industrial Tool Sets

In Roll
Out
Pouch



⚡ 1000Volt



[SHOP](#)

32986 11 Pc. Pliers & Screwdriver Set. Insulation According to VDE 0682/part 201, DIN EN 60900, EN/IEC 60900, ASTM F-1505-01, NFPA70E, ⚡ up to 1000 volt. Individually Tested. In Roll Out Pouch
Item# 32986 Set Includes: ⚡ lbs. 3.62
6.3" Long Nose Pliers 6.3" Diagonal Cutters
8.0" Combination Pliers 6.3" Stripping Pliers
Insulated Slotted: 3.0, 4.5, 5.5mm
Insulated Phillips: #1, #2 Insulated Square: #1, #2

In Roll
Out
Pouch



⚡ 1000Volt



[SHOP](#)

32987 8 Pc. Pliers & Cutters Set. Insulation According to VDE 0682/part 201, DIN EN 60900, EN/IEC 60900, ASTM F-1505-01, NFPA70E, ⚡ up to 1000 volt. Individually Tested. In Roll Out Pouch
Item# 32987 Set Includes: ⚡ lbs. 5.52
6.3" Long Nose Pliers 6.3" Diagonal Cutters
8.0" Long Nose Pliers 8.0" H.D. Diagonal Cutters
9.0" Lineman's w/Cutters 6.3" Stripping Pliers
8.0" Cable Cutters 7.0" Crimpers

⚡ 1000Volt




In Roll
Out
Pouches



[SHOP](#)

32988 22 Pc. Pliers & Cutters Set. Insulation According to VDE 0682/part 201, DIN EN 60900, EN/IEC 60900, ASTM F-1505-01, NFPA70E, ⚡ up to 1000 volt. Individually Tested. In Roll Out Pouches
Item# 32988 Set Includes: ⚡ lbs. 5.74
8.0" Long Nose Pliers 6.3" Diagonal Cutters
9.0" Lineman's w/Cutters 8.0" H.D. Diagonal Cutters
8.0" Cable Cutters 6.3" Stripping Pliers
7.0" Crimping Pliers
15 Pc. *SlimLine* Blade Set includes: Insulated *SlimLine* Blade Holder
Slotted: 3.0, 4.0, 5.5, 6.5 Phillips: #1, #2 Xeno: #1, #2
TORX: T8, T10, T15, T20 Square: #1, #2



⚡ 1000Volt



[SHOP](#)

32973 22 Pc. Pliers & Driver Set. Insulation According to VDE 0682/part 201, EN/IEC 60900, ASTM F-1505-01, NFPA70E & CSA, ⚡ up to 1000 volt. Individually Tested. In molded tool box
Item# 32973 Set Includes: ⚡ lbs. 8.70
9.0" Linemans Pliers W/Cutters 8.0" Long Nose Pliers W/Cutter
8.0" Diagonal Cutters 50mm Cable Stripping Knife
Insulated Slim Phillips #1, 2 Insulated Slim Slotted 3.5, 4.5mm
Insulated Slim Xeno #1, 2 Insulated Slim Square #1, 2
Insulated T-handle Hex Inch: 5/32, 3/16, 7/32, 1/4, 5/16, 3/8"
Insulated Inch Nut Drivers: 3/8, 7/16, 1/4, 5/16"



Now in
canvas
tool bag

⚡ 1000Volt



[SHOP](#)

32390 11 Pc. Pliers & Driver Set. Insulation According to VDE 0682/part 201, EN/IEC 60900, ASTM F-1505-01, NFPA70E & CSA, ⚡ up to 1000 volt. Individually Tested. In canvas tool bag
Item# 32390 Set Includes: ⚡ lbs. 6.30
8.0" Linemans Pliers 6.3" Long Nose Pliers W/Cutter
8.0" Long Nose Pliers W/Cutter 6.3" Diagonal Cutter
8.0" High Leverage Cutter
Insulated Phillips #0, 1, 2 Insulated Slotted 3.0, 4.5, 6.5mm



⚡ 1000Volt

[SHOP](#)

32399 10 Pc. Pliers & Driver Set. Insulation According to VDE 0682/part 201, EN/IEC 60900, ASTM F-1505-01, NFPA70E & CSA, ⚡ up to 1000 volt. Individually Tested. In canvas zipper pouch
Item# 32399 Set Includes: ⚡ lbs. 5.74
8.0" Linemans Pliers 8.0" Long Nose Pliers W/Cutter
8.0" Diagonal Cutter 6.3" Wire Stripper
10.0" Adjustable Pliers
Insulated Phillips #1, 2 Insulated Slotted 3.0, 4.5, 6.5mm



Numerical Index by Item Number

Item No. Page	Item No. Page	Item No. Page	Item No. Page	Item No. Page
10250 37	20011 5	21032 7	28347 20	31435 12
11625 15	20012 5	21040 7	28350 18	31436 12
11630 15	20013 5	21042 7	28390 20	31437 12
11950 15	20014 5	21044 7	28391 20	31438 12
11960 16	20015 5	21046 7	28724 18	31439 12
11975 16	20016 5	21048 7	28726 18	31491 12
11980 16	20017 5	21050 7	28727 18	31493 12
12326 14	20018 5	21052 7	28734 18	31495 13
12327 13	20019 5	21054 7	28736 18	31496 13
12851 10	20020 5	21056 7	28737 18	31506 12
12852 13	20022 5	21057 7	28791 18	31507 12
12853 15	20024 5	21058 7	28792 18	31508 12
12854 11	20027 5	21060 7	29006 11	31509 12
12855 11	20030 5	21062 7	29009 13	31510 12
12856 13	20032 5	21064 7	29012 15	31511 12
12857 13	20091 4	21066 7	29240 15	31512 12
12858 15	20093 4	21068 7	29250 15	31513 12
12859 15	20131 5	21093 7	30700 26	31514 12
13650 9	20133 5	21094 7	30701 26	31515 12
13651 9	20135 5	21095 7	30746 21	31516 12
13652 9	20136 5	21096 7	30747 21	31517 12
13653 9	20137 5	21103 37	31326 10	31518 12
13654 9	20138 5	21208 6	31327 10	31519 12
13655 9	20140 5	21210 6	31328 10	31520 12
13656 9	20141 5	21212 6	31329 10	31521 12
13657 9	20142 5	21213 6	31330 10	31522 12
13658 9	20144 5	21214 6	31331 10	31524 12
13659 9	20145 5	21217 6	31332 10	31590 12
13662 9	20146 5	21219 6	31333 10	31592 13
13663 9	20147 5	21290 6	31334 10	31595 13
13664 9	20148 5	21325 6	31335 10	31608 14
13665 9	20149 5	21327 6	31336 10	31609 14
13666 9	20151 5	21329 6	31337 10	31610 14
13667 9	20154 5	21331 6	31338 10	31611 14
13668 9	20190 4	21333 6	31339 10	31612 14
13669 9	20192 4	21335 6	31340 10	31613 14
13670 9	20194 5	21391 6	31341 10	31614 14
13671 9	20196 5	25500 27	31342 10	31615 14
13672 9	21008 7	25511 27	31343 10	31616 14
13673 9	21009 7	28301 19	31344 10	31617 14
13690 9	21010 7	28308 19	31345 10	31618 14
13691 9	21011 7	28309 19	31390 11	31619 14
13693 9	21012 7	28312 19	31391 11	31620 14
13694 9	21013 7	28315 19	31394 11	31621 14
15000 8	21014 7	28317 19	31395 11	31622 14
15003 8	21015 7	28319 19	31425 12	31623 14
15050 8	21017 7	28327 20	31428 12	31624 14
19767 15	21019 7	28329 20	31429 12	31626 14
20006 5	21020 7	28339 20	31430 12	31627 14
20007 5	21022 7	28340 20	31431 12	31628 14
20008 5	21024 7	28341 20	31432 12	31630 14
20009 5	21027 7	28342 20	31433 12	31632 14
20010 5	21030 7	28346 20	31434 12	31691 14

Item No.	Page	Item No.	Page	Item No.	Page	Item No.	Page	Item No.	Page
31703	14	32102	23	32511	26	32889	33	38007	18
31704	14	32103	23	32516	26	32891	32	38016	27
31705	14	32104	23	32521	26	32892	32	38017	27
31707	14	32145	21	32526	26	32894	32	38018	27
31708	14	32146	21	32531	26	32895	32	38025	18
31709	14	32188	23	32536	26	32896	31	40800	15
31710	14	32189	22	32541	26	32917	38	75205	16
31712	14	32190	24	32546	26	32923	38	75210	16
31713	14	32196	22	32551	26	32926	38	75215	16
31714	14	32197	22	32556	26	32927	39	75220	16
31715	14	32198	22	32561	26	32929	38	75302	16
31716	14	32206	25	32590	26	32930	39	75304	16
31718	14	32209	25	32592	26	32933	38	76208	8
31720	14	32212	25	32800	29	32945	39	76210	8
31722	14	32215	25	32804	36	32947	38	76212	8
31790	14	32218	25	32806	36	32951	37	76215	8
31805	10	32221	25	32807	36	32954	39	76290	8
31807	10	32224	25	32808	36	32956	39	91230	37
31809	10	32227	25	32810	36	32973	41	91256	36
31811	10	32230	25	32814	34	32981	40		
31813	10	32233	25	32816	34	32982	40		
31815	10	32236	25	32818	34	32983	40		
31817	10	32238	25	32820	34	32984	40		
31890	10	32239	25	32821	34	32985	40		
32005	23	32240	25	32826	35	32986	41		
32010	23	32241	25	32828	35	32987	41		
32012	23	32255	25	32830	35	32988	41		
32015	23	32258	25	32832	35	32989	40		
32017	23	32261	25	32834	35	32999	40		
32023	23	32264	25	32835	35	33441	17		
32024	23	32267	25	32836	35	33443	17		
32025	23	32268	25	32838	35	33445	17		
32026	23	32270	25	32841	35	33447	17		
32027	23	32273	25	32850	37	33449	17		
32028	23	32276	25	32852	37	33478	17		
32031	23	32278	25	32854	37	33481	17		
32034	23	32280	25	32859	37	33482	17		
32039	23	32288	26	32860	36	33483	17		
32042	23	32291	25	32861	35	33485	17		
32045	23	32292	25	32867	33	33486	17		
32046	21	32293	25	32868	33	33487	17		
32049	21	32294	25	32869	33	33490	17		
32052	21	32296	25	32870	36	33632	17		
32055	21	32302	24	32871	28	33634	17		
32058	21	32303	24	32872	28	33637	17		
32090	23	32304	24	32873	28	33641	17		
32091	23	32305	24	32874	31	35811	24		
32092	23	32306	24	32875	28	35812	24		
32093	24	32308	24	32876	30	35844	21		
32094	24	32366	24	32877	30	35845	21		
32095	24	32390	41	32878	31	35890	24		
32100	23	32399	41	32879	31	35891	24		
32101	23	32505	26	32888	32	38006	18		

(800) 494-6104
 fax: (800) 494-7456
 email: cservice@wiha.com
 www.wiha.com

**SEE OUR GREAT
 WEB SPECIALS!**



Insulation Test



Cold Impact Test



Material Integrity Test



Puncture Test



Flame Resistance Test



Adhesion Test

Subject to change without notice

©2014 Willi Hahn Corporation

®Torx is a registered trademark of
 Acument Intellectual Properties LLC.

Catalog Item No. 99919.wo
 version - 5/15/14



Wiha Quality Tools

1348 Dundas Circle
 Monticello, MN 55362
 tel: 763.295.6591
 fax: 763.295.6598

Wiha Tools Canada Ltd.

www.wiha.com
 Brampton, ONT L6T 4X4
 tel: 866.494.0096 or 763.295.6591
 fax: 763.295.6598

To:




99951.wo - Bits Catalog



99004.wo - Shop Tools Catalog



99914.wo - TORX Catalog



99002.wo - Screwdrivers Catalog



91330.wo - Tooling Catalog



99001.wo - TorqueControl Catalog



99934.wo - Hex Tools Catalog



99006.wo - Tech Tools Catalog



99945.wo - ESD Catalog



99977.wo - Pliers/Crimpers Catalog