

## MKDS 5 HV/ 8-9,52

Order No.: 1933516

<http://eshop.phoenixcontact.de/phoenix/treeViewClick.do?UID=1933516>

PC terminal block, Nominal current: 32 A, Nom. voltage: 800 V, Pitch: 9.52 mm, Number of positions: 8, Type of connection: Screw connection, Assembly: Soldering, Conductor/PCB connection direction: 0 °, Color: green, The article can be aligned to create different nos. of positions!

### Commercial data

|                |               |
|----------------|---------------|
| EAN            | 4017918887049 |
| Pack           | 50 pcs.       |
| Customs tariff | 85369010      |
| Weight/Piece   | 0.02617 KG    |

### Product notes

WEEE/RoHS-compliant since:  
01/01/2003



<http://www.download.phoenixcontact.com>  
Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation. The General Terms and Conditions of Use apply to Internet downloads.

### Certificates / Approvals



Certification

CB, CCA, CUL, SEV, UL

### CUL

|                       |       |
|-----------------------|-------|
| Nominal voltage $U_N$ | 600 V |
| Nominal current $I_N$ | 30 A  |

|                       |       |
|-----------------------|-------|
| AWG/kcmil             | 30-10 |
| <b>UL</b>             |       |
| Nominal voltage $U_N$ | 600 V |
| Nominal current $I_N$ | 30 A  |
| AWG/kcmil             | 30-10 |

#### Accessories

| Item           | Designation            | Description                                                                                                                                                                               |
|----------------|------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>Marking</b> |                        |                                                                                                                                                                                           |
| 1051993        | B-STIFT                | Marker pen, for manual labeling of unprinted Zack strips, smear-proof and waterproof, line thickness 0.5 mm                                                                               |
| 0803906        | SK U/3,8 WH:UNBEDRUCKT | Unprinted marker cards, DIN A4 format, pitch as desired, self-adhesive, with 40 stamped marker strips, 185 mm strip length, can be labeled with the CMS system or manually with the M-PEN |
| <b>Tools</b>   |                        |                                                                                                                                                                                           |
| 1205053        | SZS 0,6X3,5            | Screwdriver, bladed, matches all screw terminal blocks up to 4.0 mm <sup>2</sup> connection cross section, blade: 0.6 x 3.5 mm, without VDE approval                                      |

**Address**

PHOENIX CONTACT Inc., USA  
586 Fulling Mill Road  
Middletown, PA 17057, USA  
Phone (800) 888-7388  
Fax (717) 944-1625  
<http://www.phoenixcon.com>



© 2010 Phoenix Contact  
Technical modifications reserved;