

[Home](#) - [Distributor Area](#) - [Distributors](#) - [Support](#) - [Jobs](#) - [Contact](#)

Choose your language: English (US)

Search Product:

[[Advanced](#)]



- [Adapters & power supplies](#)
- [Batteries & chargers](#)
- [Cables & accessories](#)
- [Connectors](#)
- [Consumer products & pc acc.](#)
- [Electronic components](#)
- [High-q tools & dmm's](#)
- [Lamps & led's](#)
- [Led products & lamps](#)
- [Light products](#)
- [Loudspeakers & pa systems](#)
- [Perel tools](#)
- [Security products](#)
- [Velleman kits & oscilloscopes](#)



[ROHS Info](#)

[HIGH-Q TOOLS & DMM'S](#) > [TOOL SETS](#) >



BIT SET (40pcs)

Order Code: VTBT12



Features

- in metal box

Specifications

- hexagonal chrome-vanadium shank 0.39": all bits in length 1.2" and 2.95"
- 7 x hexagonal: from 0.16" to 0.47"
- 7 x 'star': from T20 to T55
- m5-6-8-10-12
- drive ratchet adapters: 1/2" and 3/8"

Stock Info

- Inner carton:
- Outer Carton: 10
- EAN Barcode: 5410329340179
- UPC Barcode: 836479007642
- Packaging: Box (Carton)

(C) 2005 Velleman Components N.V.

[[Disclaimer](#)]