




14. BNC-Einbaubuchse isoliert BNC-Bulkhead Receptacle Insulated



A



B


Bestell-Nr.	Z	Montage	Anmerkungen
Order Nr.	Z	Assembly	Remarks

			mit Isolierflansch/with insulating flange
J01001A0043	50	Z01	A weiß/white
J01001B0043	50	Z01	A blau/blue
J01001C0043	50	Z01	A rot/red
J01001D0043	50	Z01	A schwarz/black
J01001E0043	50	Z01	A gelb/yellow
J01001F0043	50	Z01	A grün/green


			mit Isolierscheiben/with insulating washers
J01001A1222	50	Z03	B schwarz/black
J01001B1222	50	Z03	B weiß/white
J01001C1222	50	Z03	B rot/red
J01001D1222	50	Z03	B blau/blue
J01003A1286	75	Z03	B schwarz/black
J01003B1286	75	Z03	B weiß/white
J01003C1286	75	Z03	B rot/red
J01003D1286	75	Z03	B blau/blue
J01003E1286	75	Z03	B grün/green

BNC-Steckverbindungen nach IEC Publ. 169-8



BNC-Connectors according to IEC Publ. 169-8





B



C




D




E

Bestell-Nr. Order Nr.	MIL-Std. MIL-Std.	Z Z	Montage Assembly	Anmerkungen Remarks
J01001A0615	UG 1094B/U	50	Z01	A a = 31 b = 12.5
J01001B0615	UG 1094/U	50	Z01	A a = 27 b = 6.5
J01001A1219	UG 625 B/U	50	Z03	B
J01001A0614	UG 657/U	50	Z02	C mit Dichtring/with panel seal
J01001A1225		50	Z04	D
J01001A0031		50	Z40	E
J01003A0619		75	Z01	A a = 27 b = 6.5
J01003A1218		75	Z01	A a = 31 b = 12.5
J01003A1220		75	Z03	B
J01003A1221		75	Z02	C mit Dichtring/with panel seal
J01003A0027		75	Z04	D


Z01





Z02



Z03




Z04



Einbau von hinten

Z05



Einbau von vorne