

DIGITUS®



Enjoy connections. Live

- Multimedia
- Accesories
- Datacom
- Network

Order online @



or call 1.800.344.4539

DIGITUS® External premium HDD enclosure 2.5" USB 2.0 & Firewire A


- External aluminium case for 2.5" hard drives
- Conforms to USB 2.0 or USB2.0 and IEEE1394a specification (DA-70502-1)
- Data transfer rate up to 480 Mbps (USB) and 400 bps (Firewire A)
- Two Firewire ports, 1x 6-pin and 1x 4-pin (DA-70502-1)
- Conforms to ATA/ATAPI-6 specification (Rev.1.0 for USB)
- Conforms to USB storage class specification Ver.1.0
- Compatible with Win98/SE, 2000, ME and XP
- Supports Mac OS 9.0, supports LINUX 2.4.x and better
- LED power (green)/ status (red)
- Power supply via USB port, external power supply (optional)

Accessories

191896 / DA-70550
2.5" HDD enclosure USB 2.0

[DA-70550-ND](#)

[Click part number to purchase online @](#)



DIGITUS® External S-ATA HDD enclosure 3.5" ALU

- Serial ATA 1.0 compliant
- Automation 3.0/1.5 Gbps transmission rate negotiation
- Support S-ATA Hot Plug
- Support S-ATA connector
- Thinner and longer cable
- Serialize/ Deserialize a 40 Bit (double word aligned) or 10 Bit with 4X speed signal from/to the link layer
- Provide specified OOB signal detection and transmission
- 32 Bits CRC error checking on all data and control information
- Supports 32 Bits and 48 Bits LBA hard disk
- Compatible with WIN98, WIN98 se, WIN 2000, WIN ME and WIN XP
- Support MAC OS which support S-ATA HDD

Accessories

192121 / DA-70585

[DA-70585-ND](#)

DIGITUS External HDD enclosure 3.5" ALU S-ATA → S-ATA

[Click part number to purchase online @](#)



DIGITUS® USB to serial adapter, USB 2.0



DIGITUS® USB to serial adapter, USB 1.1

DIGITUS® USB 1.1 to PS/2 adapter



Accessories

117933 / DA-70118
USB 1.1 → PS/2 adapter

[AE10287-ND](#)

[Click part number to purchase online](#)

USB to Serial Converter, DSUB 9 pin Male



Accessories

170426 / DA-70119
USB to serial converter, 9pin, 25pin

[AE1488-ND](#)

[Click part number to purchase online](#)

Accessories

170426 / DA-70146
USB to serial adapter, USB 2.0

[AE10289-ND](#)

[Click part number to purchase online](#)



Accessories

170426 / DA-70145
USB to serial adapter, USB 1.1

[AE10288-ND](#)

USB Repeater Cable USB 2.0



Accessories

170426 / DA-70130
USB repeater cable 2.0

[AE10290-ND](#)

[Click part number to purchase online](#)

DIGITUS® Pocket KVM switch PS/2, 2-port



- Controls two PCs with one PS/2 keyboard, one PS/2 mouse and one monitor
- Simple installation - no additional software required
- PC selection via hotkey
- Excellent video quality - up to 1920 x 1440 pixels 200 MHz bandwidth
- Supports DDC, DDC2, DDC2B, DDC2AB
- Hot Plug & Play
- Keyboard and mouse emulation for faultless booting of the computer
- Autoscan (5,10,15,20,25,30 sec. options) / autoskip function
- No external power supply required
- Integrated KVM cable for connection of two PCs 1.2 m
- Supports standard PS/2 mouse, Microsoft IntelliMouse and full support for Microsoft IntelliPoint 5.0 mouse driver and Logitech Mouse Ware driver
- Supports Windows 95/98/98SE/ME/NT4.0/2000/XP/VISTA, DOS, Linux, Novell Netware, FreeBSD

DIGITUS® Pocket KVM switch PS/2, 2-port for USB PC



- Control two PCs with one PS/2 keyboard, one PS/2 mouse and one monitor
- Simple installation - no additional software required
- PC selection via hotkey
- Excellent video quality - up to 1920 x 1440 pixels, 200 MHz bandwidth
- Supports DDC, DDC2, DDC2B, DDC2AB
- Hot Plug & Play
- Keyboard and mouse emulation for faultless booting of the computer
- Autoscan (5,10,15,20,25,30 sec. options) / autoskip function
- No external power supply required
- Integrated KVM cable for connection of two PCs 1.5 m
- Supports standard PS/2 mouse, Microsoft IntelliMouse and full support for Microsoft IntelliPoint 5.0 mouse driver and Logitech Mouse Ware driver
- Supports Windows 95/98/98SE/ME/NT4.0/2000/XP, DOS, Linux, Novell Netware, FreeBSD
- Mouse and keyboard connection to USB-port of the PC

DIGITUS® USB pocket KVM switch, 2-port



- Control two PCs with one USB keyboard, one USB mouse and one monitor
- Simple installation: No additional software required
- PC selection via hotkey
- Excellent video quality-up to 2048 x 1536 pixels at 85 HZ
- Support DDC, DDC2, DDC2B, DDC2AB
- Audio IN/OUT - support
- Hot Plug & Play
- Keyboard and mouse emulation for faultless booting of the computer
- Autoscan- (5 to 60 sec.)
- No external power supply required
- Integrated KVM cable for connection of two PCs 1.2 m
- Supports Windows 95/98/98SE/ME/NT4.0/2000/2003 Server/XP/VISTA, Linux, Mac and Sun Micro Systems

Datacom

[DC-OC12-ND](#)

159056 / DC-OC12
Pocket KVM switch PS/2, 2-port

[Click part number to purchase online](#)

Datacom

[DC-OC12U-ND](#)

159056 / DC-OC12U
Pocket KVM switch PS/2, 2-port

[Click part number to purchase online](#)

Datacom

[DC-11402-ND](#)

206064 / DC-11402
USB pocket KVM switch, 2-port

[Click part number to purchase online](#)

DIGITUS® USB-KVM switch, 2-port



- Controls two PCs with one PS/2 or USB-keyboard, one PS/2 or USB-mouse and one monitor
- Simple installation - no additional software needed
- PC-choice over push-buttons, Hot-Key or OSD-Utility
- Excellent video quality - up to 1920 x 1440 pixels
- Supports DDC, DDC2
- Hot Plug & Play
- Emulates a keyboard on each PC to allow your computers to boot normally without a keyboard error
- Autoscan- (5 bis 250 sec.)
- USB Bus Powered and downstream-port activated by external Power DC 5V 2A
- incl. 3-Port USB - Hub
- Supports Windows 95/98/98SE/ME/NT4.0/2000/2003 Server/XP/VISTA, Linux, Mac and Sun Micro Systems

DIGITUS® USB-PS/2-KVM switch



- Controls up to two PCs with one PS/2- or USB-keyboard, one PS/2- or USB-mouse and one monitor
- Simple installation - no additional software needed
- PC-choice over push-buttons or Hot-Key
- Excellent video quality - up to 2048 x 1536 pixels at 85 Hz
- Supports DDC, DDC2
- Hot Plug & Play
- Emulates a keyboard on each PC to allow your computers to boot normally without a keyboard error
- Autoscan (5 to 250 sec.)
- No external power supply needed, self powered through PS/2 and/or USB connection (optional Power supply 5V; 2,0A - Art.-Nr. DN-R-PS)
- Fully compliant with the USB 1.1/ 2.0 specification
- Supports Windows 95/98/98SE/ME/NT4.0/2000/2003 Server/XP/VISTA, Linux, Mac and Sun Micro Systems

DIGITUS® USB-PS/2-KVM switch



- Controls up to four PCs with one PS/2- or USB-keyboard, one PS/2- or USB-mouse and one monitor
- Simple installation - no additional software needed
- PC-choice over push-buttons or Hot-Key
- Excellent video quality - up to 2048 x 1536 pixels at 85 Hz
- Supports DDC, DDC2
- Hot Plug & Play
- Emulates a keyboard on each PC to allow your computers to boot normally without a keyboard error
- Autoscan (5 to 250 sec.)
- No external power supply needed, self powered through PS/2 and/or USB connection (optional Power supply 5V; 2,0A - Art.-Nr. DN-R-PS)
- Fully compliant with the USB 1.1/ 2.0 specification
- Supports Windows 95/98/98SE/ME/NT4.0/2000/2003 Server/XP/VISTA, Linux, Mac and Sun Micro Systems

Datacom

[DC-11201-1-ND](#)

201076 / DC-11201-1
USB-KVM switch, 2-port

[Click part number to purchase online](#)

Datacom

[DC-11202-1-ND](#)

200994 / DC-11202-1
USB-PS/2-KVM switch, 2-port

[Click part number to purchase online](#)

Datacom

[DC-12202-1-ND](#)

201007 / DC-12202-1
USB-PS/2-KVM switch, 4-port

[Click part number to purchase online](#)

DIGITUS® Wireless LAN USB 2.0 adapter, 802.11g

- IEEE 802.11b and IEEE 802.11g compatible
- Compliant to USB 2.0 standard
- Supported data transfer rates 54,11,5.5,2.0,1.0 Mbps
- 128-bit WEP (Wired equivalent privacy) encryption
- WPA and WPA2 encryption (Wireless fidelity protected access)
- Realtek-Chipset
- Suitable for all current network environments
- Support for Windows 98SE/ME/2000/XP

Easy Installation and great networking!



DIGITUS® Wireless LAN PCI adapter, 802.11g



- IEEE 802.11b and IEEE 802.11g compatible
- 32 bit PC card compatible
- Supported data transfer rates 54,11,5.5,2.0,1.0 Mbps
- 128-bit WEP (Wired equivalent privacy) encryption
- Support for WPA and WPA2
- Realtek-Chipset
- Suitable for all current network environments
- Support for Windows 98SE/ME/2000/XP/Vista

200406 / DN-7003GT

Wireless LAN USB 2.0 adapter, 802.11g

Network

[DN-7003GT-ND](#)

Click part number to purchase online @



211655 / DN-7006GS

Wireless LAN PCI adapter, 802.11g

Network

[DN-7006GS-ND](#)

Click part number to purchase online @



DIGITUS® Wi-Fi finder with integrated USB 2.0 wireless LAN adapter, 802.11g

- LC Display shows: Number of Access Points, Wi-Fi standard, Channel, SSID, encryption and Signal strength
- Shows several Access Points in the Wireless LAN environment
- Blue lightend, easy to read LC Display
- Integrated rechargeable long life battery, charged over the USB Port
- Easy to use, Simple function keys on the device
- Integrated USB Wireless LAN Adapter based on Zydas chipset
- IEEE 802.11b and IEEE 802.11g compatible
- Supported data transfer rate 54,11,5.5,2.0,1.0 Mbps
- Security: 64/128/256-bit WEP Data Encryption, WPA/WPA2 (TKIP with IEEE 802.1x) and AES
- Suitable for all current network environments
- Support for Windows XP/2000

**Detect WiFi signals with out
a computer!**



Enjoy connections.
Live.

195535 / DN-7020

Wi-Fi Finder with integrated USB 2.0 wireless LAN adapter

Network

[DN-7020-ND](#)

Click part number to purchase online @



DIGITUS® Fast Ethernet N-Way 8 Port Desktop Switch



- IEEE 802.3 and IEEE 802.3u compatible
- 20/200 MBIT full duplex
- Automatic speed and half/full duplex detection / configuration
- Store and forward architecture
- Auto MDI / MDI-X function
- CE compliant
- External power supply

136750 / DN-5002C

N-Way Desktop Switch, 8-port

Network

[DN-5002C-ND](#)

Click part number to purchase online



is a Trademark of ASSMANN Electronics

DIGITUS®

DIGITUS® Microscope camera with built-in light

The universal digital microscope camera shows objects in „live view“ with up to 200x magnification on the computer screen. The built-in bright LED lighting guarantees for sharp and brilliant pictures.

- Universal microscope camera for the computer with built-in white and bright lighting
- Magnification continuous 10 - 200x
- Screen capture resolution 640 x 480 pixel
- "Live view" with up to 30 fps
- USB 1.1 / 2.0 interface
- 1,8m USB Cable length
- Ideal for business and hobby e.g. for industrial inspection like textile and printing, for skin and scalp examination, for stamp, coin and gem collectors, for science and learning.
- As reading aid.
- Incl. desktop stand, manual and capture software on CD-ROM
- For Windows-PC operating WIN98SE, ME, 2000, XP, Vista and Mac

Amazing 200x magnification and Live View at 30fps!



Multimedia

200154 / DA-70350
Digital USB Microscope

[DA-70350-ND](#)

Click part number to purchase online @



Perfect gift for everyone, even yourself!
Bright image and outstanding quality,
built in 4 in 1 Card Reader!



DIGITUS® Digital photo frame

- 7" Screen size
- Memory card slot for SD and MMC memory cards
- Slideshow for JPEG files
- Slideshow interval adjustable
- Autoplay when inserting memory card
- Keys for the simple controlling of important functions (Play/Pause, Prev, Next, Interval, Modus)
- Vertically, horizontal arrangeable and additionally with hanging for wall fastening

Technical features

- Size: 7 inch
- Resolution: 480 x 234
- Brightness: 350 cd/m2
- Contrast: 300
- View angle: 60/60/5 (CR>10)
- Response time: 30 ms
- Format: JPEG

Multimedia

211358 / DA-70871
Digital photo frame

[DA-70871-ND](#)

Click part number to purchase online @



Top of the line USB HUBS & Card Readers!

DIGITUS® „Twister“ notebook USB 2.0 Hub

- 4 x USB A female, each twistable about 180 degree
- 1 x USB A male, integrated and twistable about 180 degree
- Space-saving design, direct Pluggable to the notebook without additional cable
- High-quality „softtouch“ material
- With status LED and connector for an additional power supply
- USB 2.0 and USB 1.1 compatible
- Supports Hot Plug and Plug & Play



Accessories

205890 / DA-70213-1
„Twister“ notebook USB 2.0 Hub

[DA-70213-1-ND](#)

Click part number to purchase online @





DIGITUS® USB 2.0 Hub, 4-and 7-Port

- USB 2.0 and USB 1.1 compatible
- 4 und 7 x USB A, female (USB 1.1 and 2.0 devices)
- Maximum data transfer rate 480 Mbps (USB 2.0)
- Over current protection on all outputs
- Hot Plug and Plug & Play compatible
- Additional USB cable and power supply included
- Plastic housing with aluminium design
- Operating system support for Windows XP / Vista and MAC OS 10.x and higher



Accessories

211884 / DA-70224
USB 2.0 Hub, 4-port

[DA-70224-ND](#)

211891 / DA-70227
USB 2.0 Hub, 7-port

[DA-70227-ND](#)



[Click part number to purchase online @](#)

DIGITUS® USB 2.0 mini Hub

- USB 2.0 and USB 1.1 compatible
- 4 x USB A, female (USB 1.1 and 2.0 devices)
- Maximum data transfer rate 480 Mbps (USB 2.0)
- Over current protection on all outputs
- Hot Plug and Plug & Play compatible
- Power supply via USB
- Additional USB cable included
- Operating system support for Windows XP / Vista and MAC OS 10.x and higher



Accessories

157229 / DA-70132-1
USB 2.0 mini Hub, 4-port

[DA-70132-1-ND](#)

[Click part number to purchase online @](#)



DIGITUS® USB 2.0 card reader 56in1

- Compliant to USB 2.0 specification
- Supports USB High Speed 480 Mbps and Full Speed 12 Mbps
- Supports Media Copy and Hot-Swap
- Supports Hot Plug, Plug & Play
- Supports following memory cards: Compact Flash (CF) series, Memory Stick (MS) series, Smart Media (SM) + XD series, Secure Digital (SD), T-Flash series
- Bus powered
- USB connection cable incl.
- Supported OS: WIN 98SE/ ME/ 2000/ XP / Vista, Mac OS 10.x



Accessories

211907 / DA-70316-1
Card reader USB 2.0 56in1

[DA-70316-1-ND](#)

[Click part number to purchase online @](#)



USB HUB + Card Reader all in one unit!



DIGITUS® USB 2.0 card reader 56in1 + Hub

- Compliant to USB 2.0 specification
- Supports USB High Speed 480 Mbps and Full Speed 12 Mbps
- Supports Media Copy und Hot-Swap
- Supports Hot Plug, Plug & Play
- Supports following memory cards: Compact Flash (CF) series, Memory Stick (MS) series, Smart Media (SM) + XD series, Secure Digital (SD) series
- Integrated 3-port Hub
- USB connection cable and power supply incl.
- Supported OS: WIN 98SE/ ME/ 2000/ XP / Vista, Mac OS 10.x



Accessories

184669 / DA-70312
Card reader USB 2.0 56in1 + Hub

[DA-70312-ND](#)

[Click part number to purchase online @](#)



DIGITUS® USB 2.0 multi card reader



- Supports MS, MS Pro, MS Duo, MS Pro Duo, HS MS, SD, mini SD, MMC, RS-MMC, Trans-Flash
- Compliant with USB 2.0
- Complies with USB Storage Class specification Rev. 1.0
- Operating System Supported: Windows 98SE/ME/2000/XP/Vista, Mac 9.x/X, Linux



Accessories

205746 / DA-70310
USB 2.0 multi card reader

[DA-70310-ND](#)

[Click part number to purchase online @](#)





DIGITUS® USB webcam

- Manual adjustable fokus, automatic whitebalance, automatic exposure
- Resolution: 480k Pixel, 800x600, 640x480, 352x288, 320x240, 176x144, 160x120
- Framerrates: up to 30 fps
- Color: 24 Bit TrueColor
- Color depth: 32 Byte
- JPEG-compression integrated
- Operatin System: Win 2000/ XP / Vista

Excellent laptop Add-on!



Multimedia

211631 / DA-70812
USB webcam

[DA-70812-ND](#)

Click part number to purchase online @



DIGITUS® USB webcam

- Built-in microphone
- Manual adjustable fokus, automatic whitebalance, automatic exposure
- Resolution: 480k Pixel, 800x600, 640x480, 352x288, 320x240, 176x144, 160x120
- Framerrates: up to 30 fps
- Color: 24 Bit TrueColor
- Color depth: 32 Byte
- JPEG-compression integrated
- incl. driver and VP EYE software
- Operatin System: Win 2000/ XP / Vista

Built-in Microphone,

Start your webconference right away!

Multimedia

211648 / DA-70814
USB webcam

[DA-70814-ND](#)

Click part number to purchase online @



DIGITUS® USB Bluetooth 2.0 EDR adapter

- Bluetooth 1.1 / 1.2 / 2.0 and USB 1.1 compatible
- Supported data rates: up to 3 Mbps(Max)
- Range: up to 80 m DN-3017, up to 150m DN-3018
- CSR Bluetooth Chipset
- Toshiba Bluetooth Software
- Suitable for Windows 98 SE / ME / 2000 / XP
- Dimension: (LxWxH) 59 x 7 x 19 mm
- Weight: 8 g

Bluetooth 2.0
high speed



**Turn your PC into a Bluetooth device
the next edge on communications!**

Multimedia

193708 / DN-3018
USB Bluetooth 2.0 EDR adapter, class 1

[DN-3018-ND](#)

Click part number to purchase online @



DIGITUS® Bluetooth audio transmitter

- Bluetooth Audio Transmitter: Plug into your Stereo audio source via audio jack in your MP3 .PSP, PC, TV, DVD player, ipod, home audio system ... etc.
- Compatible with Bluetooth 1.1 / 1.2 standard
- Data transfer rate up to 732 kbps
- Range up to approx. 15m
- Ultra-compact design
- Rechargeable polymer battery
- Working time up to 6,5 hours
- Automatically pair with Stereo Bluetooth headphone by pressing a button
- Support A2DP profile
- Size: 52 x 14 x 22 mm



Multimedia

195702 / DN-3014
Bluetooth audio transmitter

[DN-3014-ND](#)



DIGITUS® USB 2.0 IDE & SATA cable

- Support 1,8"/2,5"/3,5" IDE and Serial ATA HardDisk
- Support SATA, SATA II
- Compliance with USB 2.0 (Hi-Speed)
- Compliance with USB Mass Storage Class
- Support 480 Mbps High Speed (HS) and 12 Mbps Full Speed USB operation
- Support ATA/ATAPI Ultra DMA Mode
- Support ATA/ATAPI PACKET command feature set
- Support ATA/ATAPI LBA48 Bit addressing mode
- Support dual LUN (Logic Unit Number) with automatic master/slave enumeration
- High-Speed Data Transfer, Low Power Consumption
- Red / green LED's indicating operation
- Operating System Support: Windows 98SE/ME/2000/XP/2003/Vista



Accessories

195580 / DA-70148-1

USB 2.0 IDE & SATA cable

[DA-70148-1-ND](#)

[Click part number to purchase online @](#)



DIGITUS® 2.5" Hard drive installation kit including 2.5" to 3.5"



To install 2.5" hard drives in 3.5" drive slots

Supplied:

- Two metal installation brackets including screws
- Adapter for 40 pin IDE cable and power supply adapter

Accessories

170372/DA-70430

2.3" HDD Installation Kit

[DA-70430-ND](#)

[Click part number to purchase online @](#)



DIGITUS® USB 2.0 to IDE adapter cable



- USB 2.0 compliant
- Support for ATA / ATAPI devices
- Cable length 1,2 m
- inclusive 2,5" Adapter
- Support for: Windows XP, Windows 2000



Accessories

171003 / DA-70147

USB 2.0 to IDE adapter cable

[DA-70147-ND](#)

[Click part number to purchase online @](#)



DIGITUS® Notebook cooler pad with Hub and CardReader



- Metallcase
- 2 powerfull, silent Fan
- 3 Port USB 2.0 Hub integrated (DA-70341)
- 4 Slot Multicardreader with USB 2.0 Interface is integrated (DA-70341)
- Support for: CompactFlash, Micro Drive, Memory Stick, Memory Stick pro, Secure Digital, MultiMedia Card
- Support für Windows 98/2000/XP



DIGITUS® USB Fingerprint sensor USB stick version

- Fingerprint-Sensor for efficient, high security and convenience access to the notebook computer
- Never need anymore passwords, only the users thumb
- User-friendly integration of fingerprint authentication for login, internet access and applications
- The delivered software manage logins, users passwords and data encryption for files, folders and virtual drives and inserts the user data automatically in required data fields after successful fingerprint scan
- Semiconductor sensor, swipe type
- 192 x 16 pixel, 8 bit / pixel, 508 dpi resolution
- ESD +/- 15 kV
- False rejection rate < 1:1.000
- False acceptance rate < 1:1.000.000
- Matching time < 1 second
- USB 1.1 interface / bus powered
- Power LED
- Supports Windows 98 / ME / 2000 / XP / Vista



**Protect your information,
use your fingerprint
instead of password!**

Accessories

206019 / DA-70700

USB fingerprint-sensor - USB stick version

[DA-70700-ND](#)

[Click part number to purchase online @](#)



Accessories

205753 / DA-70341

Notebook cooler pad, with Hub and CardReader

[DA-70341-ND](#)

[Click part number to purchase online @](#)



is a Trademark of ASSMANN Electronics