



LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
G	14		U1	REVISED PER ECO-11-004917	11MAR11	RK	HMR

AMP WIRE RANGE	 Listed	 LR7189 Certified
22-16 AWG SOLID OR STRANDED	22-16 AWG SOLID OR STRANDED	22-16 AWG SOLID OR STRANDED



- 1 STAMP AMP 22-18* APPROX AS SHOWN
22-16 TERMINALS ARE STAMPED 22-18 IN
ACCORDANCE WITH MILITARY SPEC MIL-T-7928
COMMERCIAL WIRE RANGE IS 22-16
- 2 WIRE INSULATION DIA: .080 - .125
- 3 TONGUE MATERIAL THK: 0.79 ±0.05 [.031 ±.002]
- 4 TIN PL 0.00254[.000100] MIN EXT
THK PER MIL-T-10727
- 5 GOLD PL 0.00127[.000050] MIN EXT
THK PER MIL-G-45204 TYPE II OVER
NICKEL PL 0.00762[.000030] MIN EXT
THK PER QQ-N-290

-	-	LOOSE PIECE	5 2-31888-1
-	-	LOOSE PIECE	4 31888
MILITARY P/N AND CLASS	QUANTITY	PACKAGE TYPE	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 02/11/93 DK SCHRUM	 TE Connectivity			
		CHK 4/28/93 RE HERSEY				
DIMENSIONS: MM[INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD 4/28/93 ML ELLIS	NAME TERMINAL, RING TONGUE, PIDG™, WIRE SIZE, 22-16 AWG			
	0 PLC ± - 1 PLC ± - 2 PLC ± 0.20[.008] 3 PLC ± - 4 PLC ± - ANGLES ± -	PRODUCT SPEC UL 486A				
MATERIAL COPPER PER ASTM B-152 SLEEVE, RED VINYL	FINISH SEE	APPLICATION SPEC NOT AVAILABLE	SIZE A3	CAGE CODE 00779	DRAWING NO C-31888	RESTRICTED TO -
CUSTOMER DRAWING				SCALE 4:1	SHEET 1 of 1	REV U1