



English



[Suppliers](#)

[Investor Relations](#)

[Contact Us](#)



[Home](#) [Products](#) [Division | Brand](#) [Literature](#) [Where To Buy](#) [Careers](#) [About Us](#)

Enter keyword

Enter part number

Search

[Home](#) > [0107-4-4](#) > [0168 21 13](#) > [0169 13 21](#) > [0220 13 00](#) > [0901 00 13](#) > 1025T12 00

1025T12 00



[Where to Buy](#)

[Contact Us](#)

[View All Parts](#)

[Download 3D Model](#)

No CAD available

DESCRIPTION	ATTRIBUTE VALUE
PRODUCT TYPE	TUBING FLUOROPOLYMER
TYPE	CLOSE TOLERANCE FLUOROPOLYMER TUBE; CLOSE TOLERANCE FLUOROPOLYMER TUBE
SIZE	-
INSIDE DIAMETER	INSIDE DIAM: 10; INSIDE DIAM: 10 MM
OUTSIDE DIAMETER	OUTSIDE DIAM: 12; OUTSIDE DIAM: 12 MM
WALL	-
MATERIAL	FEP140; FEP140
COLOR	White; White
LENGTH	25 m; 25 m
MAX TEMPERATURE RATING	MAXIMUM WORKING TEMPERATURE: 150; MAXIMUM WORKING TEMPERATURE: 150 CE
ADDITIONAL DETAIL	-
TRADE/BRAND NAME	LEGRIS
UNSPSC	40180000; 40180000