



Termékek

Rólunk	
Termékek	
Újdonságok	
Cable Ties and Fixings	(1636)
Insulation Products	(2249)
Cable Protection Systems	(1667)
HelaGuard Non-Metallic Conduits and Fittings	(522)
HelaGuard Steel Conduits and Fittings	(95)
HelaGuard Steel Conduits with Plastic Coating and Fittings	(134)
HelaGuard Steel Conduits with Liquid-Tight Cover and Fittings	(82)
HelaGuard Steel Conduits with Plastic Coating and Steel Overbraid	(62)
HelaGuard Steel Conduits with Steel Overbraid and Fittings	(41)
HelaGuard PSR and PSRSC Spiral-Reinforced PVC Conduits and Fittings	(63)
HelaGuard Accessories	(210)
FlexiGuard Flexible Conduits and Fittings	(32)
Conduits for extreme conditions	(10)
Cable Management Systems	(46)
Spiral Binding	(94)
Wiring Ducts and Accessories	(8)
Wiring Ducts and Accessories 2	(8)
Braided Sleeving and Fabric Tubing	(165)
Edge Protection	(28)
Grommets	(67)
Installation Devices	(168)
Identification Systems	(2191)
Application Tooling	(129)
Connectivity	(0)
Connectivity	(0)
Kompetenciák	
Hírek & Események	
Letöltések	

Non-Metallic Conduits HG-SW21



HelaGuard PA6 Standard for industrial applications.

HG-SW PA6 Standard Weight, Cikkszám: 166-11104

- Very flexible and high fatigue life
- Very abrasion resistant
- High impact strength, recovers if crushed
- Highly resistant to solvents and oils
- Free of halogen, sulphur and phosphorus
- Low smoke and low toxicity
- Self-extinguishing according to UL94 V2
- Colour: black (UV resistant); grey on request

Machine building, plant construction, control panels, public buildings.



Catalogue page (Date of issue: April 2011)



All catalogue pages



Nyomtatás

▼ Base Data

Colour	Black (BK)
Conduit Model	Plastic corrugated
Features and Benefits 2	Standard weight corrugated flexible conduit for industrial applications.
Product Family	HG-SW PA6 Standard Weight
Product Group	Non-Metallic Conduits
Type	HG-SW21-PA6-BK-50M

▼ Product Dimensions

Bending Radius	45 mm
Inside Ø	16.7 mm
Length (L)	50 m
Min.Tensile Strength (N)	400 N
NW Ø	17 mm
Nominal Ø	21 mm
Outside Ø (OD)	21.2 mm
Weight (g/m)	60
Ø D	16.7 mm

▼ Logistic and Packaging

Carton Quantity	50 Meter
EAN code	4031026302270
Pack Cont.	50 m
Quantity of Europallet	800 pcs.
Quantity per	Reel
Reel Length	50 m
Weight (Kg)	6 kg

▼ Material and Specifications

Compression Strength (kg/100mm)	75
EN61386 Classification	24244066-210
Flammability	UL94 V2
IP-Rating	IP66 (in conjunction with HG fittings)
Impact Strength (Joule)	6
Material	Polyamide 6 (PA6)
Material Shortcut	PA6
Operating Temperature	-40 °C to +120 °C
Operating Temperature Moving	-20 °C to +100 °C
Oxygen Index	26,4 %
Specification	IEC 61386, Lloyd's Register, UL-Recognised
UL OCD link	Link
UL-File Number	E325250