

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

39537-8524

Status:


Active

Overview:

Eurostyle™ Terminal Blocks

Description:

5.08mm Pitch Eurostyle™ Vertical Plug, with Retention Screws, Front Wire Entry, Green Housing, Gold (Au) Plated, 24 Circuits



Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

General	
Product Family	Terminal Blocks
Series	39537
Application	N/A
Comments	Front Wire Entry
Component Type	Plug
Overview	Eurostyle™ Terminal Blocks
Product Name	ESE, Eurostyle™Pluggable
Type	Euro Block
UPC	822350677660
Physical	
Circuits (Loaded)	24
Entry Angle	Horizontal
Lock to Mating Part	Yes
Number of Rows	1
Orientation	Vertical
Panel Mount	No
Pitch - Mating Interface	5.08mm
Pitch - Termination Interface	5.08mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40°C to +105°C
Wire Size AWG	12, 14, 16, 18, 20, 22, 24, 26
Wire Size mm²	0.13 - 3.31
Electrical	
Current - Maximum per Contact	18A
Voltage - Maximum	300V
Material Info	
Reference - Drawing Numbers	
Sales Drawing	SD-39537-001

EU RoHS

ELV and RoHS

Compliant

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Reviewed

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

39537Series

Mates With

Most 5.08mm (.200") Pitch Industry Standard PCB Headers, 39535 Vertical PCB Header with Threaded Retention Inserts, 39536 Horizontal PCB Header with Threaded Retention Inserts

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

39537-8524